

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001113

Luminaire Tested: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001113
REPORT IS A COMBINATION OF REPORTS P995729 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5626.0 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30
2	85	78	72	67	75	70	65	60	54	51	48	41	38	37	28	26	25
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	14
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	16	14	13
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	12
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10
10	44	32	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4536	4536	4536	4536
5°	4525	5204	4551	3911
10°	4491	6071	4525	3430
15°	4437	6999	4468	3069
20°	4380	7590	4412	2752
25°	4296	7503	4337	2518
30°	4214	6201	4265	2397
35°	4098	4621	4143	2324
40°	3964	3481	4003	2288
45°	3759	2794	3806	2239
50°	3515	2354	3565	2216
55°	3226	2049	3277	2191
60°	2947	1804	3033	2154
65°	2685	1552	2709	2064
70°	2376	1278	2427	1901
75°	2072	982	2058	1615
80°	1629	644	1612	1226
85°	1070	289	1004	715

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5865 cd/sqm

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	1.0
10°-20°	167.1	3.0
20°-30°	265.5	4.7
30°-40°	295.0	5.2
40°-50°	268.3	4.8
50°-60°	219.2	3.9
60°-70°	156.5	2.8
70°-80°	86.1	1.5
80°-90°	26.0	0.5
90°-100°	43.9	0.8
100°-110°	288.8	5.1
110°-120°	551.5	9.8
120°-130°	700.1	12.4
130°-140°	749.0	13.3
140°-150°	700.4	12.4
150°-160°	564.8	10.0
160°-170°	364.2	6.5
170°-180°	125.5	2.2
0°-30°	486.7	8.7
0°-40°	781.7	13.9
0°-60°	1269.2	22.6
0°-90°	1537.7	27.3
90°-120°	884.2	15.7
90°-150°	3033.7	53.9
90°-180°	4088.0	72.7
0°-180°	5626.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	556	556	556	556	556	
5°	554	653	557	490	554	53
15°	529	896	533	393	529	149
25°	483	952	488	319	483	223
35°	419	563	424	283	419	262
45°	334	316	338	253	334	258
55°	235	206	239	221	235	211
65°	147	133	148	176	147	145
75°	72	66	71	109	72	76
85°	15	14	14	34	15	17
90°	3	30	3	30	3	4
95°	54	29	54	29	54	67
105°	297	282	297	282	297	311
115°	555	559	555	559	555	547
125°	781	787	781	787	781	697
135°	968	975	968	975	968	746
145°	1117	1123	1117	1123	1117	698
155°	1224	1223	1224	1223	1224	565
165°	1292	1286	1292	1286	1292	365
175°	1321	1313	1321	1313	1321	126
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	556.3	561.8	564.1	566.0	571.9	573.8	574.2	577.0	579.3	579.8	579.8
5°	554.0	562.7	569.6	576.1	585.8	589.9	595.0	600.5	607.9	612.5	614.8
7.5°	550.3	563.2	573.8	584.8	598.2	606.5	611.1	625.9	636.0	644.3	654.4
10°	544.8	561.3	576.6	592.7	611.6	621.7	631.9	649.8	664.1	680.2	693.2
12.5°	536.5	558.1	576.6	599.1	622.6	634.6	646.6	677.9	694.5	708.8	731.9
15°	529.1	550.7	577.0	600.1	629.1	647.1	664.6	684.9	711.1	742.0	764.1
17.5°	520.8	548.0	572.4	604.7	636.9	654.0	668.3	699.6	736.5	766.9	787.2
20°	509.3	536.9	569.2	603.3	641.5	654.9	673.8	715.7	748.9	778.9	812.1
22.5°	495.9	528.2	562.3	595.0	634.6	662.7	683.5	720.3	760.4	795.0	832.3
25°	483.0	518.0	548.0	592.7	634.6	653.5	677.0	720.8	764.6	806.5	844.8
27.5°	469.2	501.9	542.4	577.9	625.4	646.1	671.5	719.4	766.0	807.9	848.9
30°	454.0	489.0	522.6	564.6	610.7	637.4	660.9	713.0	760.4	804.2	842.5
32.5°	436.9	470.1	506.0	545.7	594.1	621.3	650.8	704.2	754.9	792.7	822.2
35°	418.9	452.6	483.9	524.5	574.2	601.4	630.0	689.0	739.2	770.1	787.2
37.5°	399.1	430.9	461.8	501.9	551.7	580.7	609.7	666.9	714.4	740.2	735.6
40°	380.2	408.8	437.4	475.2	527.2	558.1	583.5	641.1	682.6	693.6	678.4
42.5°	358.6	383.0	410.6	449.4	500.0	529.1	560.9	613.4	644.3	639.7	613.9
45°	334.1	355.8	383.4	419.9	471.5	501.4	528.2	577.9	600.5	589.0	542.0
47.5°	310.6	331.8	354.4	390.8	441.1	466.4	493.6	538.3	551.2	526.8	479.8
50°	285.3	302.8	326.3	360.9	407.9	434.6	457.2	493.1	497.7	467.8	418.9
52.5°	260.9	275.6	298.2	332.3	376.1	397.3	419.4	451.2	447.5	416.6	369.6
55°	235.0	248.9	269.6	301.0	339.7	359.9	378.8	407.0	399.1	367.3	326.3
57.5°	213.4	223.1	243.3	272.4	304.2	326.3	342.4	364.6	352.6	320.8	282.5
60°	188.5	200.5	217.5	241.0	272.4	287.1	301.4	316.2	307.9	277.4	243.3
62.5°	165.9	175.1	189.9	212.5	236.9	250.3	265.5	274.7	266.4	238.3	209.7
65°	146.6	153.9	165.5	183.9	207.4	218.5	227.2	236.0	229.1	202.8	182.0
67.5°	125.4	131.8	141.5	156.2	176.1	183.9	192.2	198.2	190.3	172.8	152.5
70°	106.5	111.1	120.3	131.3	145.2	152.5	159.5	165.5	158.5	143.8	128.6
72.5°	87.1	90.8	99.1	106.9	119.4	124.4	129.5	134.1	131.8	118.0	105.5
75°	71.9	73.3	78.8	85.3	93.1	98.6	102.3	105.1	103.2	92.2	84.3
77.5°	54.4	56.2	60.4	65.4	72.4	75.6	77.9	80.7	78.3	69.6	64.1
80°	39.6	40.1	42.4	47.0	51.6	52.1	54.4	58.1	56.7	50.7	46.5
82.5°	25.3	26.7	27.7	30.4	33.6	34.6	35.9	36.9	36.4	32.7	31.3
85°	14.7	14.7	15.7	17.5	18.4	19.8	20.3	20.7	21.7	19.4	18.0
87.5°	6.5	6.9	6.9	7.4	8.3	8.3	8.8	9.2	9.7	9.2	7.8
90°	3.0	5.4	7.8	10.2	12.6	13.8	14.7	16.4	18.2	19.9	21.7
92.5°	14.8	14.4	13.9	13.5	13.0	12.8	13.7	15.5	17.2	19.0	20.8
95°	54.4	46.9	39.5	32.0	24.5	20.8	20.9	21.1	21.3	21.5	21.7
97.5°	103.8	108.6	113.4	118.3	123.1	125.5	114.0	90.9	67.8	44.8	21.7
100°	162.1	166.0	170.0	173.9	177.8	179.8	164.7	134.4	104.1	73.8	43.5
102.5°	227.3	229.9	232.5	235.2	237.8	239.1	240.4	243.1	245.7	248.4	251.0
105°	297.4	298.7	300.1	301.4	302.7	303.4	303.9	305.0	306.1	307.2	308.3
107.5°	361.7	362.3	363.0	363.6	364.3	364.6	365.4	366.9	368.5	370.0	371.6
110°	426.9	427.6	428.2	428.9	429.6	429.9	430.6	431.9	433.2	434.5	435.8

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	490.1	491.4	492.8	494.1	495.4	496.1	496.3	496.7	497.2	497.6	498.0
115°	555.4	556.0	556.7	557.3	558.0	558.3	558.2	558.0	557.7	557.5	557.3
117.5°	613.7	614.6	615.4	616.3	617.2	617.6	617.9	618.6	619.3	619.9	620.6
120°	673.0	673.9	674.7	675.6	676.5	676.9	676.8	676.6	676.3	676.1	675.9
122.5°	728.3	728.7	729.2	729.6	730.1	730.3	730.5	730.9	731.4	731.8	732.2
125°	780.7	781.6	782.4	783.3	784.2	784.6	784.4	783.9	783.5	783.0	782.6
127.5°	831.1	831.3	831.5	831.8	832.0	832.1	832.6	833.7	834.8	835.9	837.0
130°	879.5	879.7	879.9	880.2	880.4	880.5	880.8	881.5	882.1	882.8	883.4
132.5°	924.0	924.4	924.8	925.3	925.7	925.9	926.3	927.2	928.1	929.0	929.9
135°	968.4	968.2	968.0	967.7	967.5	967.4	967.8	968.7	969.6	970.5	971.4
137.5°	1007.9	1007.9	1007.9	1007.9	1007.9	1007.9	1008.5	1009.6	1010.7	1011.8	1012.9
140°	1046.5	1046.9	1047.4	1047.8	1048.3	1048.5	1048.7	1049.1	1049.6	1050.0	1050.4
142.5°	1081.1	1082.0	1082.8	1083.7	1084.6	1085.0	1085.1	1085.3	1085.6	1085.8	1086.0
145°	1116.6	1117.3	1117.9	1118.6	1119.3	1119.6	1119.6	1119.6	1119.6	1119.6	1119.6
147.5°	1144.3	1145.6	1146.9	1148.2	1149.5	1150.2	1150.1	1149.9	1149.7	1149.5	1149.3
150°	1175.0	1175.9	1176.7	1177.6	1178.5	1178.9	1178.8	1178.6	1178.3	1178.1	1177.9
152.5°	1200.6	1201.3	1201.9	1202.6	1203.3	1203.6	1203.4	1202.9	1202.5	1202.0	1201.6
155°	1224.4	1224.6	1224.8	1225.1	1225.3	1225.4	1225.1	1224.4	1223.7	1223.1	1222.4
157.5°	1245.1	1245.1	1245.1	1245.1	1245.1	1245.1	1244.7	1243.8	1242.9	1242.1	1241.2
160°	1262.9	1262.2	1261.6	1260.9	1260.2	1259.9	1259.8	1259.6	1259.3	1259.1	1258.9
162.5°	1278.7	1277.8	1277.0	1276.1	1275.2	1274.8	1274.7	1274.5	1274.2	1274.0	1273.8
165°	1291.6	1290.5	1289.4	1288.3	1287.2	1286.6	1286.6	1286.6	1286.6	1286.6	1286.6
167.5°	1302.4	1301.3	1300.2	1299.1	1298.0	1297.5	1297.4	1297.2	1296.9	1296.7	1296.5
170°	1311.3	1310.0	1308.7	1307.4	1306.1	1305.4	1305.5	1305.7	1306.0	1306.2	1306.4
172.5°	1317.3	1316.0	1314.6	1313.3	1312.0	1311.3	1311.4	1311.6	1311.9	1312.1	1312.3
175°	1321.2	1319.9	1318.6	1317.3	1316.0	1315.3	1315.4	1315.6	1315.9	1316.1	1316.3
177.5°	1324.2	1322.7	1321.1	1319.6	1318.1	1317.3	1317.5	1317.9	1318.4	1318.8	1319.2
180°	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	581.2	589.5	593.1	594.1	599.1	595.9	597.3	596.8	600.5	601.0	601.0
5°	623.6	633.2	636.5	641.1	648.0	649.8	648.4	651.2	656.3	652.6	658.1
7.5°	668.3	678.9	686.2	696.4	698.7	704.7	708.4	711.6	712.5	713.0	713.9
10°	709.7	723.1	733.3	750.3	754.0	757.2	773.3	766.9	775.2	772.4	773.3
12.5°	743.4	769.7	778.0	806.5	809.3	820.4	819.4	829.6	831.4	835.1	831.4
15°	787.6	818.1	831.4	847.5	856.8	869.7	872.0	885.8	891.3	896.4	891.3
17.5°	828.2	844.3	878.4	891.3	897.3	904.2	921.7	926.8	935.1	931.9	941.1
20°	848.5	871.5	907.5	929.6	938.8	945.3	960.0	967.8	971.1	971.1	972.0
22.5°	866.4	899.6	926.4	951.7	960.0	964.6	973.4	979.4	980.7	981.7	982.6
25°	882.6	912.5	934.2	948.5	951.7	951.7	956.8	953.1	947.1	951.7	954.5
27.5°	882.6	903.8	913.5	918.5	918.5	906.1	898.7	883.5	870.6	866.9	875.2
30°	867.8	877.5	864.1	851.7	842.0	833.7	804.7	781.6	777.0	773.8	786.3
32.5°	833.7	821.3	795.0	759.1	744.8	725.9	703.3	685.8	675.2	671.5	668.7
35°	773.3	741.1	707.0	658.6	648.4	624.5	593.6	580.7	563.2	562.7	568.7
37.5°	707.4	657.7	620.8	574.7	560.4	535.1	506.0	492.7	480.7	471.5	482.5
40°	630.5	587.2	530.9	493.1	472.9	459.5	435.1	420.3	414.8	410.2	417.1
42.5°	558.6	511.1	467.3	428.6	412.0	396.8	380.7	366.4	362.2	361.8	366.9
45°	487.1	440.6	400.0	366.9	356.3	347.0	331.4	327.2	320.3	315.7	318.0
47.5°	430.0	382.1	348.4	323.1	313.9	306.0	295.9	289.0	283.0	281.1	283.9
50°	373.8	341.5	306.9	285.7	278.8	271.5	263.6	257.2	254.4	252.6	254.4
52.5°	328.6	294.0	270.5	253.5	246.6	241.0	235.5	232.7	229.1	230.0	231.8
55°	288.0	257.6	237.8	225.4	221.2	218.9	212.0	208.8	207.4	206.5	207.4
57.5°	249.8	227.7	212.9	202.3	196.8	195.4	189.9	189.9	188.5	187.1	187.6
60°	219.4	200.5	186.2	177.9	177.0	174.7	171.0	170.5	167.3	168.7	169.1
62.5°	188.5	173.3	163.6	158.5	155.3	154.4	152.1	151.6	150.2	150.7	149.8
65°	164.1	151.6	141.9	137.8	136.4	136.0	134.1	132.7	131.8	132.7	131.8
67.5°	139.6	131.3	124.0	119.8	118.0	117.5	116.1	115.2	115.7	114.3	115.2
70°	116.6	108.3	103.7	101.4	100.5	99.1	99.1	99.1	99.1	98.2	97.7
72.5°	98.2	89.9	86.6	85.3	84.3	83.9	82.5	83.0	82.5	82.0	83.9
75°	77.9	72.8	69.6	68.2	69.1	67.7	66.4	67.3	65.9	66.4	68.2
77.5°	59.0	56.7	54.8	53.9	53.0	52.1	52.1	51.2	51.2	51.2	51.2
80°	42.9	42.4	39.2	38.7	38.7	37.8	37.8	37.8	37.8	37.3	37.8
82.5°	28.6	28.1	27.2	26.7	25.8	26.3	26.3	25.3	25.3	24.9	25.3
85°	16.6	16.6	15.7	15.2	14.7	15.2	14.3	13.8	14.3	13.8	14.3
87.5°	7.8	6.9	7.4	6.9	6.0	6.5	5.5	6.0	5.5	5.1	6.0
90°	23.0	24.4	25.7	27.0	27.7	27.9	28.3	28.8	29.2	29.6	29.2
92.5°	22.1	23.4	24.7	26.0	26.7	26.7	26.7	26.7	26.7	26.7	26.7
95°	23.0	24.4	25.7	27.0	27.7	27.8	28.0	28.3	28.5	28.7	28.5
97.5°	22.8	23.9	25.0	26.1	26.7	26.8	27.0	27.3	27.5	27.7	27.5
100°	39.8	36.0	32.3	28.6	26.7	26.8	27.0	27.3	27.5	27.7	27.5
102.5°	201.6	152.2	102.8	53.4	28.7	28.7	28.7	28.7	28.7	28.7	28.7
105°	310.3	312.3	314.2	316.2	317.2	313.2	305.3	297.4	289.5	281.6	289.5
107.5°	372.7	373.8	374.9	376.0	376.5	376.9	377.8	378.7	379.6	380.5	379.6
110°	436.2	436.7	437.1	437.6	437.8	438.1	438.8	439.4	440.1	440.7	440.1

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	497.8	497.6	497.4	497.2	497.1	497.5	498.4	499.3	500.1	501.0	500.1
115°	557.7	558.2	558.6	559.1	559.3	559.3	559.3	559.3	559.3	559.3	559.3
117.5°	620.4	620.2	619.9	619.7	619.6	619.6	619.6	619.6	619.6	619.6	619.6
120°	676.3	676.8	677.2	677.7	677.9	677.7	677.2	676.8	676.3	675.9	676.3
122.5°	732.4	732.6	732.9	733.1	733.2	733.0	732.6	732.1	731.7	731.3	731.7
125°	783.3	783.9	784.6	785.3	785.6	785.7	785.9	786.2	786.4	786.6	786.4
127.5°	836.8	836.6	836.3	836.1	836.0	835.9	835.7	835.4	835.2	835.0	835.2
130°	883.6	883.8	884.1	884.3	884.4	884.4	884.4	884.4	884.4	884.4	884.4
132.5°	930.1	930.3	930.6	930.8	930.9	930.8	930.6	930.3	930.1	929.9	930.1
135°	971.8	972.3	972.7	973.2	973.4	973.6	974.0	974.5	974.9	975.3	974.9
137.5°	1013.3	1013.8	1014.2	1014.7	1014.9	1014.8	1014.6	1014.3	1014.1	1013.9	1014.1
140°	1051.1	1051.7	1052.4	1053.1	1053.4	1053.5	1053.7	1054.0	1054.2	1054.4	1054.2
142.5°	1086.4	1086.9	1087.3	1087.8	1088.0	1088.0	1088.0	1088.0	1088.0	1088.0	1088.0
145°	1119.8	1120.0	1120.3	1120.5	1120.6	1120.8	1121.3	1121.7	1122.2	1122.6	1122.2
147.5°	1149.5	1149.7	1149.9	1150.1	1150.2	1150.3	1150.5	1150.8	1151.0	1151.2	1151.0
150°	1177.9	1177.9	1177.9	1177.9	1177.9	1178.0	1178.2	1178.5	1178.7	1178.9	1178.7
152.5°	1202.0	1202.5	1202.9	1203.4	1203.6	1203.5	1203.3	1203.0	1202.8	1202.6	1202.8
155°	1223.3	1224.1	1225.0	1225.9	1226.3	1226.0	1225.3	1224.7	1224.0	1223.4	1224.0
157.5°	1242.3	1243.4	1244.5	1245.6	1246.1	1245.6	1244.5	1243.4	1242.3	1241.2	1242.3
160°	1260.2	1261.6	1262.9	1264.2	1264.9	1264.2	1262.9	1261.6	1260.2	1258.9	1260.2
162.5°	1275.1	1276.4	1277.7	1279.0	1279.7	1278.9	1277.4	1275.9	1274.3	1272.8	1274.3
165°	1288.4	1290.1	1291.9	1293.6	1294.5	1293.5	1291.5	1289.6	1287.6	1285.6	1287.6
167.5°	1298.5	1300.5	1302.4	1304.4	1305.4	1304.3	1302.1	1299.9	1297.7	1295.5	1297.7
170°	1308.2	1309.9	1311.7	1313.4	1314.3	1313.2	1311.0	1308.8	1306.6	1304.4	1306.6
172.5°	1314.1	1315.8	1317.6	1319.3	1320.2	1319.0	1316.6	1314.1	1311.7	1309.3	1311.7
175°	1318.3	1320.3	1322.2	1324.2	1325.2	1323.9	1321.2	1318.6	1315.9	1313.3	1315.9
177.5°	1321.0	1322.7	1324.5	1326.2	1327.1	1325.8	1323.2	1320.5	1317.9	1315.3	1317.9
180°	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	600.1	598.7	596.8	596.8	594.5	594.5	590.8	584.4	578.9	577.0	577.9
5°	651.2	651.7	648.9	646.6	642.5	639.2	633.2	621.7	618.0	610.7	605.6
7.5°	709.7	707.9	702.8	699.1	698.2	690.8	677.9	664.1	653.1	645.7	635.1
10°	775.7	768.3	760.9	758.6	753.1	740.6	725.9	710.7	695.5	679.3	661.4
12.5°	831.0	816.7	816.2	810.7	800.1	793.2	775.7	754.0	727.7	709.7	689.5
15°	890.4	877.0	866.0	855.8	850.8	830.5	815.7	788.6	757.2	737.9	724.0
17.5°	932.8	926.8	907.9	903.3	896.4	872.9	849.4	822.7	795.5	768.3	730.9
20°	966.9	963.2	950.8	944.3	933.3	914.8	886.3	855.4	824.0	785.3	750.3
22.5°	981.7	977.1	966.9	961.4	954.5	938.8	914.4	879.3	838.3	803.8	766.4
25°	952.6	960.9	958.2	955.9	953.1	943.9	925.4	894.6	854.5	815.3	768.7
27.5°	887.2	901.5	915.3	917.1	921.7	925.4	918.1	895.9	862.3	820.8	769.7
30°	799.2	805.6	833.7	842.0	848.5	872.0	885.8	880.3	854.5	817.1	770.1
32.5°	686.2	703.3	731.9	751.7	769.2	795.5	831.4	845.7	836.5	806.1	759.5
35°	579.3	599.6	632.8	658.1	675.6	713.0	755.4	786.3	797.8	782.6	741.1
37.5°	491.8	516.2	545.7	555.4	575.6	621.7	680.2	723.1	751.2	752.6	720.3
40°	425.8	438.3	461.8	476.5	496.4	535.1	592.2	648.9	691.3	705.6	688.5
42.5°	370.1	379.8	397.3	415.2	433.2	462.7	515.3	568.3	625.4	654.0	653.5
45°	325.8	336.0	348.0	362.7	375.2	407.0	448.4	502.8	552.1	596.4	607.4
47.5°	287.1	295.9	310.6	317.1	325.4	355.3	391.3	442.0	493.1	543.8	556.7
50°	258.6	265.9	276.1	280.2	289.4	311.6	341.0	382.1	438.8	485.3	509.3
52.5°	232.7	238.3	246.1	249.3	255.8	272.4	299.1	331.4	378.4	426.3	460.0
55°	210.6	214.3	219.8	223.5	228.1	242.9	262.7	291.7	332.3	373.8	406.5
57.5°	189.9	192.6	198.2	200.0	203.7	215.2	229.1	253.5	290.8	327.7	359.5
60°	170.5	172.4	175.6	179.7	182.5	190.3	203.2	223.5	253.5	287.1	312.9
62.5°	152.1	154.9	155.8	157.6	159.9	167.3	177.4	192.2	218.5	246.1	273.3
65°	133.2	135.5	137.3	137.8	140.1	145.6	154.9	167.8	184.8	208.8	234.1
67.5°	115.7	117.1	118.0	119.8	122.1	124.9	132.3	141.9	157.6	177.0	197.3
70°	99.5	99.5	100.9	101.4	104.2	107.4	110.6	119.8	133.7	149.3	163.1
72.5°	82.0	84.3	83.9	86.2	85.7	88.0	92.2	98.2	108.3	120.7	134.1
75°	66.8	68.2	68.2	68.2	69.1	71.0	73.3	78.8	86.6	96.8	104.6
77.5°	52.1	53.0	53.0	53.0	53.5	55.3	57.6	61.3	66.8	72.8	77.4
80°	37.3	38.3	38.3	39.2	39.2	39.6	41.9	43.8	46.5	51.2	55.8
82.5°	25.3	25.8	26.7	26.7	26.3	27.2	27.7	29.5	32.3	33.2	36.4
85°	13.8	14.3	14.7	14.7	15.2	16.1	15.7	17.5	17.5	19.4	20.3
87.5°	5.5	6.5	6.5	6.0	6.5	6.5	6.5	7.4	7.8	8.3	7.8
90°	28.8	28.3	27.9	27.7	27.0	25.7	24.4	23.0	21.7	19.9	18.2
92.5°	26.7	26.7	26.7	26.7	26.0	24.7	23.4	22.1	20.8	19.0	17.2
95°	28.3	28.0	27.8	27.7	27.0	25.7	24.4	23.0	21.7	21.5	21.3
97.5°	27.3	27.0	26.8	26.7	26.1	25.0	23.9	22.8	21.7	44.8	67.8
100°	27.3	27.0	26.8	26.7	28.6	32.3	36.0	39.8	43.5	73.8	104.1
102.5°	28.7	28.7	28.7	28.7	53.4	102.8	152.2	201.6	251.0	248.4	245.7
105°	297.4	305.3	313.2	317.2	316.2	314.2	312.3	310.3	308.3	307.2	306.1
107.5°	378.7	377.8	376.9	376.5	376.0	374.9	373.8	372.7	371.6	370.0	368.5
110°	439.4	438.8	438.1	437.8	437.6	437.1	436.7	436.2	435.8	434.5	433.2

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	499.3	498.4	497.5	497.1	497.2	497.4	497.6	497.8	498.0	497.6	497.2
115°	559.3	559.3	559.3	559.3	559.1	558.6	558.2	557.7	557.3	557.5	557.7
117.5°	619.6	619.6	619.6	619.6	619.7	619.9	620.2	620.4	620.6	619.9	619.3
120°	676.8	677.2	677.7	677.9	677.7	677.2	676.8	676.3	675.9	676.1	676.3
122.5°	732.1	732.6	733.0	733.2	733.1	732.9	732.6	732.4	732.2	731.8	731.4
125°	786.2	785.9	785.7	785.6	785.3	784.6	783.9	783.3	782.6	783.0	783.5
127.5°	835.4	835.7	835.9	836.0	836.1	836.3	836.6	836.8	837.0	835.9	834.8
130°	884.4	884.4	884.4	884.4	884.3	884.1	883.8	883.6	883.4	882.8	882.1
132.5°	930.3	930.6	930.8	930.9	930.8	930.6	930.3	930.1	929.9	929.0	928.1
135°	974.5	974.0	973.6	973.4	973.2	972.7	972.3	971.8	971.4	970.5	969.6
137.5°	1014.3	1014.6	1014.8	1014.9	1014.7	1014.2	1013.8	1013.3	1012.9	1011.8	1010.7
140°	1054.0	1053.7	1053.5	1053.4	1053.1	1052.4	1051.7	1051.1	1050.4	1050.0	1049.6
142.5°	1088.0	1088.0	1088.0	1088.0	1087.8	1087.3	1086.9	1086.4	1086.0	1085.8	1085.6
145°	1121.7	1121.3	1120.8	1120.6	1120.5	1120.3	1120.0	1119.8	1119.6	1119.6	1119.6
147.5°	1150.8	1150.5	1150.3	1150.2	1150.1	1149.9	1149.7	1149.5	1149.3	1149.5	1149.7
150°	1178.5	1178.2	1178.0	1177.9	1177.9	1177.9	1177.9	1177.9	1177.9	1178.1	1178.3
152.5°	1203.0	1203.3	1203.5	1203.6	1203.4	1202.9	1202.5	1202.0	1201.6	1202.0	1202.5
155°	1224.7	1225.3	1226.0	1226.3	1225.9	1225.0	1224.1	1223.3	1222.4	1223.1	1223.7
157.5°	1243.4	1244.5	1245.6	1246.1	1245.6	1244.5	1243.4	1242.3	1241.2	1242.1	1242.9
160°	1261.6	1262.9	1264.2	1264.9	1264.2	1262.9	1261.6	1260.2	1258.9	1259.1	1259.3
162.5°	1275.9	1277.4	1278.9	1279.7	1279.0	1277.7	1276.4	1275.1	1273.8	1274.0	1274.2
165°	1289.6	1291.5	1293.5	1294.5	1293.6	1291.9	1290.1	1288.4	1286.6	1286.6	1286.6
167.5°	1299.9	1302.1	1304.3	1305.4	1304.4	1302.4	1300.5	1298.5	1296.5	1296.7	1296.9
170°	1308.8	1311.0	1313.2	1314.3	1313.4	1311.7	1309.9	1308.2	1306.4	1306.2	1306.0
172.5°	1314.1	1316.6	1319.0	1320.2	1319.3	1317.6	1315.8	1314.1	1312.3	1312.1	1311.9
175°	1318.6	1321.2	1323.9	1325.2	1324.2	1322.2	1320.3	1318.3	1316.3	1316.1	1315.9
177.5°	1320.5	1323.2	1325.8	1327.1	1326.2	1324.5	1322.7	1321.0	1319.2	1318.8	1318.4
180°	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	573.8	571.9	570.6	570.6	566.4	562.3	560.0	559.0	558.1	554.4	549.4
5°	597.3	591.3	587.2	583.0	576.1	568.7	561.3	557.2	551.2	542.9	536.9
7.5°	623.6	609.3	604.7	599.6	585.8	573.3	563.2	554.4	544.8	534.2	523.6
10°	645.7	630.5	620.3	611.6	593.6	577.0	561.8	548.9	536.5	522.6	509.7
12.5°	666.9	645.2	634.6	621.7	602.8	578.9	559.0	542.9	524.5	510.2	494.5
15°	696.4	660.0	642.5	634.2	608.8	580.7	556.7	532.8	517.6	495.9	482.1
17.5°	701.0	671.5	660.0	638.8	608.4	576.6	548.9	524.9	501.9	482.5	464.6
20°	717.1	678.4	660.0	646.6	606.5	574.2	543.8	513.0	490.8	470.1	449.8
22.5°	727.3	683.5	664.1	642.9	604.7	566.0	530.0	503.3	476.1	454.9	438.8
25°	724.5	680.7	659.0	639.2	592.7	554.0	521.7	487.6	462.3	439.2	418.0
27.5°	723.1	673.8	650.8	628.6	584.8	544.3	503.7	476.1	448.0	421.2	405.6
30°	719.4	665.0	638.3	614.3	568.7	526.3	491.8	459.5	431.4	407.0	386.2
32.5°	707.0	650.3	624.5	598.7	551.2	508.8	473.8	443.8	415.7	390.4	370.5
35°	690.4	632.8	604.7	577.5	530.0	487.1	454.9	423.5	397.3	372.8	354.0
37.5°	673.8	612.5	586.2	554.9	511.1	466.4	433.2	405.1	380.7	355.3	334.6
40°	649.8	588.5	559.5	532.8	481.6	439.7	409.3	383.9	359.9	336.0	318.5
42.5°	617.1	562.3	532.3	502.8	454.9	413.4	383.9	361.3	338.7	318.9	299.6
45°	583.9	530.5	503.7	477.5	425.4	386.2	359.0	338.3	319.4	297.7	282.1
47.5°	543.8	498.7	471.9	446.1	396.8	357.6	332.8	313.4	295.9	277.9	263.2
50°	502.8	463.6	439.2	412.5	365.5	330.0	305.6	289.4	275.1	258.1	246.1
52.5°	458.6	424.5	403.7	377.9	336.4	303.7	278.8	262.7	250.7	238.3	227.7
55°	411.6	386.7	364.6	343.8	304.6	275.1	253.0	238.7	230.4	218.9	209.7
57.5°	369.2	345.2	331.8	308.3	274.2	245.2	227.7	215.7	206.0	199.1	191.7
60°	324.9	305.6	290.8	273.8	243.8	219.4	200.9	194.0	183.9	178.8	175.6
62.5°	282.5	268.7	254.9	242.0	215.2	192.2	178.4	169.6	163.6	158.5	155.8
65°	242.4	229.5	219.8	208.3	186.2	167.8	154.9	147.9	141.9	140.6	137.3
67.5°	203.2	197.7	187.1	177.9	159.0	144.7	135.0	126.3	123.1	121.7	118.9
70°	170.1	163.6	155.3	147.5	133.2	120.7	112.0	108.8	104.2	103.7	100.5
72.5°	140.1	132.3	126.3	120.3	109.7	98.6	94.0	89.4	87.1	85.3	83.9
75°	111.1	105.5	101.4	96.3	87.1	79.7	73.3	71.4	70.1	69.6	68.7
77.5°	83.0	79.3	77.4	72.4	65.9	59.5	56.7	53.9	53.9	53.0	53.5
80°	59.0	56.7	54.4	51.6	46.1	43.3	41.0	39.2	38.3	37.8	38.3
82.5°	37.3	35.9	35.5	33.6	30.0	28.6	26.7	25.3	25.3	25.3	25.3
85°	20.7	20.7	20.7	18.0	16.6	15.2	14.3	13.8	13.8	13.8	14.3
87.5°	8.8	8.8	7.4	7.4	6.9	6.0	5.5	5.5	6.0	6.0	6.5
90°	16.4	14.7	13.8	12.6	10.2	7.8	5.4	3.0	5.4	7.8	10.2
92.5°	15.5	13.7	12.8	13.0	13.5	13.9	14.4	14.8	14.4	13.9	13.5
95°	21.1	20.9	20.8	24.5	32.0	39.5	46.9	54.4	46.9	39.5	32.0
97.5°	90.9	114.0	125.5	123.1	118.3	113.4	108.6	103.8	108.6	113.4	118.3
100°	134.4	164.7	179.8	177.8	173.9	170.0	166.0	162.1	166.0	170.0	173.9
102.5°	243.1	240.4	239.1	237.8	235.2	232.5	229.9	227.3	229.9	232.5	235.2
105°	305.0	303.9	303.4	302.7	301.4	300.1	298.7	297.4	298.7	300.1	301.4
107.5°	366.9	365.4	364.6	364.3	363.6	363.0	362.3	361.7	362.3	363.0	363.6
110°	431.9	430.6	429.9	429.6	428.9	428.2	427.6	426.9	427.6	428.2	428.9

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	496.7	496.3	496.1	495.4	494.1	492.8	491.4	490.1	491.4	492.8	494.1
115°	558.0	558.2	558.3	558.0	557.3	556.7	556.0	555.4	556.0	556.7	557.3
117.5°	618.6	617.9	617.6	617.2	616.3	615.4	614.6	613.7	614.6	615.4	616.3
120°	676.6	676.8	676.9	676.5	675.6	674.7	673.9	673.0	673.9	674.7	675.6
122.5°	730.9	730.5	730.3	730.1	729.6	729.2	728.7	728.3	728.7	729.2	729.6
125°	783.9	784.4	784.6	784.2	783.3	782.4	781.6	780.7	781.6	782.4	783.3
127.5°	833.7	832.6	832.1	832.0	831.8	831.5	831.3	831.1	831.3	831.5	831.8
130°	881.5	880.8	880.5	880.4	880.2	879.9	879.7	879.5	879.7	879.9	880.2
132.5°	927.2	926.3	925.9	925.7	925.3	924.8	924.4	924.0	924.4	924.8	925.3
135°	968.7	967.8	967.4	967.5	967.7	968.0	968.2	968.4	968.2	968.0	967.7
137.5°	1009.6	1008.5	1007.9	1007.9	1007.9	1007.9	1007.9	1007.9	1007.9	1007.9	1007.9
140°	1049.1	1048.7	1048.5	1048.3	1047.8	1047.4	1046.9	1046.5	1046.9	1047.4	1047.8
142.5°	1085.3	1085.1	1085.0	1084.6	1083.7	1082.8	1082.0	1081.1	1082.0	1082.8	1083.7
145°	1119.6	1119.6	1119.6	1119.3	1118.6	1117.9	1117.3	1116.6	1117.3	1117.9	1118.6
147.5°	1149.9	1150.1	1150.2	1149.5	1148.2	1146.9	1145.6	1144.3	1145.6	1146.9	1148.2
150°	1178.6	1178.8	1178.9	1178.5	1177.6	1176.7	1175.9	1175.0	1175.9	1176.7	1177.6
152.5°	1202.9	1203.4	1203.6	1203.3	1202.6	1201.9	1201.3	1200.6	1201.3	1201.9	1202.6
155°	1224.4	1225.1	1225.4	1225.3	1225.1	1224.8	1224.6	1224.4	1224.6	1224.8	1225.1
157.5°	1243.8	1244.7	1245.1	1245.1	1245.1	1245.1	1245.1	1245.1	1245.1	1245.1	1245.1
160°	1259.6	1259.8	1259.9	1260.2	1260.9	1261.6	1262.2	1262.9	1262.2	1261.6	1260.9
162.5°	1274.5	1274.7	1274.8	1275.2	1276.1	1277.0	1277.8	1278.7	1277.8	1277.0	1276.1
165°	1286.6	1286.6	1286.6	1287.2	1288.3	1289.4	1290.5	1291.6	1290.5	1289.4	1288.3
167.5°	1297.2	1297.4	1297.5	1298.0	1299.1	1300.2	1301.3	1302.4	1301.3	1300.2	1299.1
170°	1305.7	1305.5	1305.4	1306.1	1307.4	1308.7	1310.0	1311.3	1310.0	1308.7	1307.4
172.5°	1311.6	1311.4	1311.3	1312.0	1313.3	1314.6	1316.0	1317.3	1316.0	1314.6	1313.3
175°	1315.6	1315.4	1315.3	1316.0	1317.3	1318.6	1319.9	1321.2	1319.9	1318.6	1317.3
177.5°	1317.9	1317.5	1317.3	1318.1	1319.6	1321.1	1322.7	1324.2	1322.7	1321.1	1319.6
180°	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	548.0	546.1	547.1	542.4	538.3	532.3	527.2	526.3	525.4	528.2	526.3
5°	532.3	530.0	527.7	522.2	513.9	508.8	501.4	501.0	498.2	494.1	495.0
7.5°	515.3	513.9	510.6	501.9	494.5	485.8	479.8	474.7	472.4	468.7	467.3
10°	501.4	496.4	493.6	483.9	475.2	465.9	458.1	454.4	450.3	447.0	444.7
12.5°	482.5	481.2	473.3	465.5	458.1	447.5	441.5	430.9	425.4	428.2	427.2
15°	470.1	463.6	461.8	450.7	438.3	431.4	420.3	413.4	411.1	407.0	401.9
17.5°	453.5	449.4	442.9	432.8	418.5	408.8	401.0	394.5	391.7	386.2	382.1
20°	437.8	430.9	425.8	416.6	402.8	390.4	380.7	376.5	369.6	365.0	362.7
22.5°	423.5	418.5	411.1	397.3	385.3	373.3	361.8	355.8	349.3	346.6	342.9
25°	406.0	397.7	392.7	377.5	364.6	354.9	344.3	336.4	332.8	328.1	327.2
27.5°	389.0	381.1	375.2	361.8	346.1	333.7	327.2	321.7	315.2	315.2	312.9
30°	371.9	366.4	357.2	344.3	329.5	317.5	310.2	305.1	302.8	301.0	300.5
32.5°	354.9	347.5	342.0	324.5	313.4	302.3	296.8	292.7	289.9	289.4	289.9
35°	337.4	329.1	323.5	307.9	296.8	286.7	284.4	280.7	279.3	278.8	281.1
37.5°	318.9	312.5	305.6	292.7	280.2	274.2	269.6	268.2	267.8	270.5	271.5
40°	301.9	296.3	289.9	276.1	266.8	260.4	258.1	256.7	258.6	261.3	262.7
42.5°	285.7	277.9	272.8	260.4	252.1	248.4	245.6	245.6	247.5	250.7	253.0
45°	268.7	262.7	257.6	246.6	239.2	235.0	234.6	235.0	237.4	239.7	242.4
47.5°	252.1	246.1	240.6	231.4	224.9	222.6	222.1	222.6	226.3	229.5	232.7
50°	236.9	230.4	225.4	216.6	211.5	208.8	209.2	211.5	214.3	218.9	223.1
52.5°	218.9	214.3	209.7	201.9	197.3	195.4	196.8	198.6	203.7	206.9	212.0
55°	201.4	197.3	193.6	187.6	183.9	182.5	183.4	186.2	190.3	195.9	201.9
57.5°	185.3	180.7	177.0	172.8	168.7	169.1	169.6	173.3	178.4	183.4	190.3
60°	167.3	164.5	161.3	156.2	154.4	154.4	155.8	159.9	164.5	172.8	178.8
62.5°	151.2	147.5	145.2	141.9	139.2	139.6	142.9	146.6	152.1	159.0	166.8
65°	134.6	130.4	128.6	125.8	124.9	125.4	127.7	133.2	139.2	145.2	152.5
67.5°	116.1	114.8	112.9	110.1	111.1	111.5	113.8	118.4	124.9	130.9	139.2
70°	100.5	97.7	97.2	94.9	94.9	96.3	100.9	104.2	110.1	116.6	125.4
72.5°	83.9	81.6	81.6	79.7	81.1	82.5	84.8	89.4	94.9	101.4	108.8
75°	66.8	65.9	66.8	65.9	65.9	68.2	71.0	74.7	80.7	87.6	93.6
77.5°	51.6	51.6	51.2	52.5	52.5	53.9	57.6	61.3	65.9	71.4	77.9
80°	37.8	37.8	37.8	39.2	40.6	40.6	42.9	47.5	51.6	55.3	61.3
82.5°	25.8	25.8	25.8	26.7	28.6	28.6	31.3	34.1	38.7	41.9	44.7
85°	15.7	15.7	15.2	16.1	16.6	18.0	20.3	22.1	24.4	27.2	30.0
87.5°	6.9	6.9	7.4	7.8	8.3	9.2	10.1	11.1	13.4	14.3	15.7
90°	12.6	13.8	14.7	16.4	18.2	19.9	21.7	23.0	24.4	25.7	27.0
92.5°	13.0	12.8	13.7	15.5	17.2	19.0	20.8	22.1	23.4	24.7	26.0
95°	24.5	20.8	20.9	21.1	21.3	21.5	21.7	23.0	24.4	25.7	27.0
97.5°	123.1	125.5	114.0	90.9	67.8	44.8	21.7	22.8	23.9	25.0	26.1
100°	177.8	179.8	164.7	134.4	104.1	73.8	43.5	39.8	36.0	32.3	28.6
102.5°	237.8	239.1	240.4	243.1	245.7	248.4	251.0	201.6	152.2	102.8	53.4
105°	302.7	303.4	303.9	305.0	306.1	307.2	308.3	310.3	312.3	314.2	316.2
107.5°	364.3	364.6	365.4	366.9	368.5	370.0	371.6	372.7	373.8	374.9	376.0
110°	429.6	429.9	430.6	431.9	433.2	434.5	435.8	436.2	436.7	437.1	437.6

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	495.4	496.1	496.3	496.7	497.2	497.6	498.0	497.8	497.6	497.4	497.2
115°	558.0	558.3	558.2	558.0	557.7	557.5	557.3	557.7	558.2	558.6	559.1
117.5°	617.2	617.6	617.9	618.6	619.3	619.9	620.6	620.4	620.2	619.9	619.7
120°	676.5	676.9	676.8	676.6	676.3	676.1	675.9	676.3	676.8	677.2	677.7
122.5°	730.1	730.3	730.5	730.9	731.4	731.8	732.2	732.4	732.6	732.9	733.1
125°	784.2	784.6	784.4	783.9	783.5	783.0	782.6	783.3	783.9	784.6	785.3
127.5°	832.0	832.1	832.6	833.7	834.8	835.9	837.0	836.8	836.6	836.3	836.1
130°	880.4	880.5	880.8	881.5	882.1	882.8	883.4	883.6	883.8	884.1	884.3
132.5°	925.7	925.9	926.3	927.2	928.1	929.0	929.9	930.1	930.3	930.6	930.8
135°	967.5	967.4	967.8	968.7	969.6	970.5	971.4	971.8	972.3	972.7	973.2
137.5°	1007.9	1007.9	1008.5	1009.6	1010.7	1011.8	1012.9	1013.3	1013.8	1014.2	1014.7
140°	1048.3	1048.5	1048.7	1049.1	1049.6	1050.0	1050.4	1051.1	1051.7	1052.4	1053.1
142.5°	1084.6	1085.0	1085.1	1085.3	1085.6	1085.8	1086.0	1086.4	1086.9	1087.3	1087.8
145°	1119.3	1119.6	1119.6	1119.6	1119.6	1119.6	1119.6	1119.8	1120.0	1120.3	1120.5
147.5°	1149.5	1150.2	1150.1	1149.9	1149.7	1149.5	1149.3	1149.5	1149.7	1149.9	1150.1
150°	1178.5	1178.9	1178.8	1178.6	1178.3	1178.1	1177.9	1177.9	1177.9	1177.9	1177.9
152.5°	1203.3	1203.6	1203.4	1202.9	1202.5	1202.0	1201.6	1202.0	1202.5	1202.9	1203.4
155°	1225.3	1225.4	1225.1	1224.4	1223.7	1223.1	1222.4	1223.3	1224.1	1225.0	1225.9
157.5°	1245.1	1245.1	1244.7	1243.8	1242.9	1242.1	1241.2	1242.3	1243.4	1244.5	1245.6
160°	1260.2	1259.9	1259.8	1259.6	1259.3	1259.1	1258.9	1260.2	1261.6	1262.9	1264.2
162.5°	1275.2	1274.8	1274.7	1274.5	1274.2	1274.0	1273.8	1275.1	1276.4	1277.7	1279.0
165°	1287.2	1286.6	1286.6	1286.6	1286.6	1286.6	1286.6	1288.4	1290.1	1291.9	1293.6
167.5°	1298.0	1297.5	1297.4	1297.2	1296.9	1296.7	1296.5	1298.5	1300.5	1302.4	1304.4
170°	1306.1	1305.4	1305.5	1305.7	1306.0	1306.2	1306.4	1308.2	1309.9	1311.7	1313.4
172.5°	1312.0	1311.3	1311.4	1311.6	1311.9	1312.1	1312.3	1314.1	1315.8	1317.6	1319.3
175°	1316.0	1315.3	1315.4	1315.6	1315.9	1316.1	1316.3	1318.3	1320.3	1322.2	1324.2
177.5°	1318.1	1317.3	1317.5	1317.9	1318.4	1318.8	1319.2	1321.0	1322.7	1324.5	1326.2
180°	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	524.9	524.5	522.2	523.1	520.3	521.2	522.6	523.1	524.9	523.6	523.1
5°	492.7	491.8	490.4	489.0	488.5	490.4	487.1	488.1	489.0	490.4	492.2
7.5°	466.4	465.9	464.6	462.3	461.3	460.4	460.9	464.1	463.6	463.2	466.4
10°	442.4	442.9	440.1	439.7	436.9	436.4	436.9	437.8	439.2	441.1	441.5
12.5°	417.6	423.5	418.5	416.6	412.5	414.8	415.7	411.6	413.9	415.2	422.2
15°	401.9	399.1	395.9	395.9	394.0	393.1	390.8	394.0	395.9	398.7	397.7
17.5°	380.2	375.6	373.8	371.9	372.4	374.2	369.2	376.5	376.5	377.9	375.6
20°	361.3	357.6	355.3	354.4	353.0	352.1	351.6	353.5	356.3	357.2	359.5
22.5°	341.5	341.5	337.8	336.4	335.5	334.1	336.4	335.1	336.9	338.7	342.4
25°	324.9	324.9	323.5	321.7	320.3	319.4	320.8	320.3	321.7	324.0	324.9
27.5°	311.6	310.2	309.7	309.2	308.8	309.2	308.8	310.2	311.6	312.0	311.1
30°	300.0	298.6	299.1	299.1	299.6	299.1	298.6	300.0	300.5	299.6	300.0
32.5°	289.4	289.4	290.4	290.8	290.8	291.3	291.7	290.8	291.3	289.9	290.4
35°	280.7	281.6	282.5	283.0	283.4	283.0	283.9	283.4	282.5	281.6	281.1
37.5°	271.9	272.8	274.7	275.1	276.5	277.0	276.1	276.1	275.6	273.8	272.8
40°	262.7	263.6	265.9	267.3	268.2	269.6	268.7	268.7	266.8	265.0	263.6
42.5°	253.9	255.8	258.1	259.5	261.3	261.3	261.3	260.4	258.1	256.2	254.9
45°	245.2	245.6	248.9	251.2	253.0	253.0	253.0	251.6	250.3	246.6	244.7
47.5°	235.5	236.9	240.6	242.9	244.7	245.2	245.2	243.8	241.0	237.8	235.5
50°	224.9	227.2	231.4	234.6	236.9	237.8	236.4	235.5	232.3	228.6	225.8
52.5°	214.8	217.5	222.6	225.4	228.6	229.1	228.6	227.2	223.5	218.5	216.1
55°	204.6	206.9	212.5	217.1	219.8	220.8	219.8	217.5	212.9	207.9	205.5
57.5°	193.6	196.8	202.8	207.4	210.6	211.1	210.2	207.9	204.2	197.7	194.5
60°	182.0	186.2	192.2	196.8	200.9	201.4	200.5	197.3	192.6	186.2	183.4
62.5°	170.5	173.7	180.7	185.7	189.0	191.3	189.4	186.2	181.6	175.1	171.0
65°	157.2	161.8	167.8	172.4	176.1	176.5	175.6	172.8	167.8	160.8	157.6
67.5°	144.3	147.5	153.5	159.5	160.8	162.2	160.8	158.1	153.9	147.9	143.3
70°	128.6	131.3	138.7	142.9	144.7	146.1	145.2	142.4	138.7	133.2	129.5
72.5°	112.9	115.2	122.1	125.4	129.0	128.6	128.1	126.3	121.2	117.5	115.2
75°	96.3	99.1	103.7	107.8	109.2	109.2	109.2	107.8	104.6	98.6	96.3
77.5°	81.1	82.5	86.2	88.5	89.9	90.3	89.9	87.6	85.7	81.6	80.2
80°	62.2	65.9	68.7	69.1	71.0	71.0	71.0	70.1	68.2	64.1	63.6
82.5°	47.0	47.9	50.7	52.1	53.0	52.5	52.5	50.7	50.2	47.9	47.0
85°	31.8	33.2	32.7	34.6	35.0	34.1	34.1	35.0	32.7	33.2	31.8
87.5°	17.5	17.5	18.4	18.0	19.8	19.8	18.9	19.4	18.4	18.0	17.5
90°	27.7	27.9	28.3	28.8	29.2	29.6	29.2	28.8	28.3	27.9	27.7
92.5°	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.7
95°	27.7	27.8	28.0	28.3	28.5	28.7	28.5	28.3	28.0	27.8	27.7
97.5°	26.7	26.8	27.0	27.3	27.5	27.7	27.5	27.3	27.0	26.8	26.7
100°	26.7	26.8	27.0	27.3	27.5	27.7	27.5	27.3	27.0	26.8	26.7
102.5°	28.7	28.7	28.7	28.7	28.7	28.7	28.7	28.7	28.7	28.7	28.7
105°	317.2	313.2	305.3	297.4	289.5	281.6	289.5	297.4	305.3	313.2	317.2
107.5°	376.5	376.9	377.8	378.7	379.6	380.5	379.6	378.7	377.8	376.9	376.5
110°	437.8	438.1	438.8	439.4	440.1	440.7	440.1	439.4	438.8	438.1	437.8

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	497.1	497.5	498.4	499.3	500.1	501.0	500.1	499.3	498.4	497.5	497.1
115°	559.3	559.3	559.3	559.3	559.3	559.3	559.3	559.3	559.3	559.3	559.3
117.5°	619.6	619.6	619.6	619.6	619.6	619.6	619.6	619.6	619.6	619.6	619.6
120°	677.9	677.7	677.2	676.8	676.3	675.9	676.3	676.8	677.2	677.7	677.9
122.5°	733.2	733.0	732.6	732.1	731.7	731.3	731.7	732.1	732.6	733.0	733.2
125°	785.6	785.7	785.9	786.2	786.4	786.6	786.4	786.2	785.9	785.7	785.6
127.5°	836.0	835.9	835.7	835.4	835.2	835.0	835.2	835.4	835.7	835.9	836.0
130°	884.4	884.4	884.4	884.4	884.4	884.4	884.4	884.4	884.4	884.4	884.4
132.5°	930.9	930.8	930.6	930.3	930.1	929.9	930.1	930.3	930.6	930.8	930.9
135°	973.4	973.6	974.0	974.5	974.9	975.3	974.9	974.5	974.0	973.6	973.4
137.5°	1014.9	1014.8	1014.6	1014.3	1014.1	1013.9	1014.1	1014.3	1014.6	1014.8	1014.9
140°	1053.4	1053.5	1053.7	1054.0	1054.2	1054.4	1054.2	1054.0	1053.7	1053.5	1053.4
142.5°	1088.0	1088.0	1088.0	1088.0	1088.0	1088.0	1088.0	1088.0	1088.0	1088.0	1088.0
145°	1120.6	1120.8	1121.3	1121.7	1122.2	1122.6	1122.2	1121.7	1121.3	1120.8	1120.6
147.5°	1150.2	1150.3	1150.5	1150.8	1151.0	1151.2	1151.0	1150.8	1150.5	1150.3	1150.2
150°	1177.9	1178.0	1178.2	1178.5	1178.7	1178.9	1178.7	1178.5	1178.2	1178.0	1177.9
152.5°	1203.6	1203.5	1203.3	1203.0	1202.8	1202.6	1202.8	1203.0	1203.3	1203.5	1203.6
155°	1226.3	1226.0	1225.3	1224.7	1224.0	1223.4	1224.0	1224.7	1225.3	1226.0	1226.3
157.5°	1246.1	1245.6	1244.5	1243.4	1242.3	1241.2	1242.3	1243.4	1244.5	1245.6	1246.1
160°	1264.9	1264.2	1262.9	1261.6	1260.2	1258.9	1260.2	1261.6	1262.9	1264.2	1264.9
162.5°	1279.7	1278.9	1277.4	1275.9	1274.3	1272.8	1274.3	1275.9	1277.4	1278.9	1279.7
165°	1294.5	1293.5	1291.5	1289.6	1287.6	1285.6	1287.6	1289.6	1291.5	1293.5	1294.5
167.5°	1305.4	1304.3	1302.1	1299.9	1297.7	1295.5	1297.7	1299.9	1302.1	1304.3	1305.4
170°	1314.3	1313.2	1311.0	1308.8	1306.6	1304.4	1306.6	1308.8	1311.0	1313.2	1314.3
172.5°	1320.2	1319.0	1316.6	1314.1	1311.7	1309.3	1311.7	1314.1	1316.6	1319.0	1320.2
175°	1325.2	1323.9	1321.2	1318.6	1315.9	1313.3	1315.9	1318.6	1321.2	1323.9	1325.2
177.5°	1327.1	1325.8	1323.2	1320.5	1317.9	1315.3	1317.9	1320.5	1323.2	1325.8	1327.1
180°	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3	556.3
2.5°	523.1	525.9	523.1	524.9	525.9	528.2	529.1	533.2	534.6	537.8	537.8
5°	491.8	493.1	493.6	495.4	497.3	501.9	505.1	511.1	518.0	518.9	523.1
7.5°	466.4	468.7	472.4	471.0	474.2	481.2	485.3	492.7	499.6	503.3	508.3
10°	443.8	446.6	448.0	449.4	455.3	461.3	467.8	472.9	482.1	487.6	491.8
12.5°	425.4	423.1	425.8	430.9	437.8	441.5	450.3	458.1	465.0	471.0	474.7
15°	401.4	403.3	406.0	414.8	416.6	425.8	429.1	437.8	450.7	456.3	460.9
17.5°	378.4	384.4	389.9	393.1	398.7	406.0	415.2	424.9	433.2	439.7	445.2
20°	359.9	365.9	369.2	371.5	377.0	387.1	395.9	407.9	418.5	423.5	430.9
22.5°	345.2	345.2	349.8	356.7	359.9	369.6	377.0	389.9	401.4	407.9	414.8
25°	326.8	329.5	333.2	339.2	343.8	351.6	362.2	373.3	385.8	391.3	400.0
27.5°	311.6	314.8	319.8	321.2	325.8	332.8	343.8	355.8	368.7	374.7	382.1
30°	300.0	301.9	303.7	306.5	310.6	316.6	325.8	336.4	352.1	356.7	365.9
32.5°	289.9	290.8	291.7	294.0	296.3	302.3	309.7	321.2	334.1	341.0	349.3
35°	280.7	279.8	280.2	281.6	283.9	286.2	294.0	303.7	315.7	324.0	330.4
37.5°	271.9	270.1	269.6	269.6	270.5	273.3	279.3	287.6	300.5	307.4	313.9
40°	262.2	260.4	259.5	259.0	258.6	260.4	265.0	273.3	283.4	289.9	297.3
42.5°	253.0	251.2	248.9	248.4	247.5	248.4	251.6	259.5	268.2	274.7	280.7
45°	243.8	240.6	237.8	236.0	236.4	235.0	237.4	243.3	253.5	257.6	263.6
47.5°	233.7	230.0	226.3	224.4	222.6	223.5	224.4	229.5	238.3	242.4	248.4
50°	224.0	218.9	214.8	212.5	211.1	210.2	211.1	216.1	222.6	226.3	231.4
52.5°	212.9	207.9	203.7	200.0	198.2	196.8	197.3	201.9	207.9	211.5	216.6
55°	202.8	196.3	190.8	186.2	184.8	184.3	183.9	187.1	192.2	195.9	200.0
57.5°	191.3	184.8	178.8	173.3	170.5	170.1	170.1	171.0	177.4	180.2	182.5
60°	179.7	172.8	166.4	161.3	157.2	155.8	155.3	157.2	160.4	163.1	166.4
62.5°	166.8	159.9	152.1	147.5	143.3	139.6	141.0	141.5	146.1	147.5	150.2
65°	154.4	146.6	140.1	132.7	128.1	125.8	124.9	125.8	129.5	130.0	131.8
67.5°	140.1	132.7	124.9	119.8	115.7	111.5	110.6	110.6	112.5	113.8	116.1
70°	126.3	118.9	110.1	104.6	100.5	96.8	95.4	94.9	96.3	97.2	99.5
72.5°	110.1	102.8	96.3	90.3	85.3	82.5	81.1	80.2	81.6	82.5	83.0
75°	93.1	87.1	80.7	74.7	71.4	68.7	66.8	65.4	66.4	66.4	66.4
77.5°	77.0	71.0	65.9	61.8	57.6	54.4	53.0	51.6	52.1	52.1	53.0
80°	59.9	55.8	51.6	47.9	44.2	41.5	40.6	39.2	38.3	37.8	37.8
82.5°	44.2	41.0	37.3	34.1	32.3	29.5	28.6	26.7	26.7	26.3	26.3
85°	29.5	27.7	24.0	21.7	20.3	18.9	18.0	17.1	15.7	15.7	15.2
87.5°	15.7	14.7	13.8	11.1	11.1	9.7	9.2	8.8	7.4	7.8	7.8
90°	27.0	25.7	24.4	23.0	21.7	19.9	18.2	16.4	14.7	13.8	12.6
92.5°	26.0	24.7	23.4	22.1	20.8	19.0	17.2	15.5	13.7	12.8	13.0
95°	27.0	25.7	24.4	23.0	21.7	21.5	21.3	21.1	20.9	20.8	24.5
97.5°	26.1	25.0	23.9	22.8	21.7	44.8	67.8	90.9	114.0	125.5	123.1
100°	28.6	32.3	36.0	39.8	43.5	73.8	104.1	134.4	164.7	179.8	177.8
102.5°	53.4	102.8	152.2	201.6	251.0	248.4	245.7	243.1	240.4	239.1	237.8
105°	316.2	314.2	312.3	310.3	308.3	307.2	306.1	305.0	303.9	303.4	302.7
107.5°	376.0	374.9	373.8	372.7	371.6	370.0	368.5	366.9	365.4	364.6	364.3
110°	437.6	437.1	436.7	436.2	435.8	434.5	433.2	431.9	430.6	429.9	429.6

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	497.2	497.4	497.6	497.8	498.0	497.6	497.2	496.7	496.3	496.1	495.4
115°	559.1	558.6	558.2	557.7	557.3	557.5	557.7	558.0	558.2	558.3	558.0
117.5°	619.7	619.9	620.2	620.4	620.6	619.9	619.3	618.6	617.9	617.6	617.2
120°	677.7	677.2	676.8	676.3	675.9	676.1	676.3	676.6	676.8	676.9	676.5
122.5°	733.1	732.9	732.6	732.4	732.2	731.8	731.4	730.9	730.5	730.3	730.1
125°	785.3	784.6	783.9	783.3	782.6	783.0	783.5	783.9	784.4	784.6	784.2
127.5°	836.1	836.3	836.6	836.8	837.0	835.9	834.8	833.7	832.6	832.1	832.0
130°	884.3	884.1	883.8	883.6	883.4	882.8	882.1	881.5	880.8	880.5	880.4
132.5°	930.8	930.6	930.3	930.1	929.9	929.0	928.1	927.2	926.3	925.9	925.7
135°	973.2	972.7	972.3	971.8	971.4	970.5	969.6	968.7	967.8	967.4	967.5
137.5°	1014.7	1014.2	1013.8	1013.3	1012.9	1011.8	1010.7	1009.6	1008.5	1007.9	1007.9
140°	1053.1	1052.4	1051.7	1051.1	1050.4	1050.0	1049.6	1049.1	1048.7	1048.5	1048.3
142.5°	1087.8	1087.3	1086.9	1086.4	1086.0	1085.8	1085.6	1085.3	1085.1	1085.0	1084.6
145°	1120.5	1120.3	1120.0	1119.8	1119.6	1119.6	1119.6	1119.6	1119.6	1119.6	1119.3
147.5°	1150.1	1149.9	1149.7	1149.5	1149.3	1149.5	1149.7	1149.9	1150.1	1150.2	1149.5
150°	1177.9	1177.9	1177.9	1177.9	1177.9	1178.1	1178.3	1178.6	1178.8	1178.9	1178.5
152.5°	1203.4	1202.9	1202.5	1202.0	1201.6	1202.0	1202.5	1202.9	1203.4	1203.6	1203.3
155°	1225.9	1225.0	1224.1	1223.3	1222.4	1223.1	1223.7	1224.4	1225.1	1225.4	1225.3
157.5°	1245.6	1244.5	1243.4	1242.3	1241.2	1242.1	1242.9	1243.8	1244.7	1245.1	1245.1
160°	1264.2	1262.9	1261.6	1260.2	1258.9	1259.1	1259.3	1259.6	1259.8	1259.9	1260.2
162.5°	1279.0	1277.7	1276.4	1275.1	1273.8	1274.0	1274.2	1274.5	1274.7	1274.8	1275.2
165°	1293.6	1291.9	1290.1	1288.4	1286.6	1286.6	1286.6	1286.6	1286.6	1286.6	1287.2
167.5°	1304.4	1302.4	1300.5	1298.5	1296.5	1296.7	1296.9	1297.2	1297.4	1297.5	1298.0
170°	1313.4	1311.7	1309.9	1308.2	1306.4	1306.2	1306.0	1305.7	1305.5	1305.4	1306.1
172.5°	1319.3	1317.6	1315.8	1314.1	1312.3	1312.1	1311.9	1311.6	1311.4	1311.3	1312.0
175°	1324.2	1322.2	1320.3	1318.3	1316.3	1316.1	1315.9	1315.6	1315.4	1315.3	1316.0
177.5°	1326.2	1324.5	1322.7	1321.0	1319.2	1318.8	1318.4	1317.9	1317.5	1317.3	1318.1
180°	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2	1321.2

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	556.3	556.3	556.3	556.3
2.5°	541.1	545.7	549.8	556.3
5°	529.1	535.5	544.3	554.0
7.5°	515.3	525.4	536.9	550.3
10°	502.4	513.9	528.6	544.8
12.5°	489.0	502.8	518.9	536.5
15°	473.8	487.6	505.6	529.1
17.5°	460.0	476.5	495.9	520.8
20°	443.8	459.5	480.7	509.3
22.5°	429.5	447.5	471.0	495.9
25°	413.9	429.5	453.0	483.0
27.5°	398.2	417.6	440.1	469.2
30°	383.0	399.1	423.5	454.0
32.5°	366.4	385.8	408.3	436.9
35°	348.4	366.9	388.1	418.9
37.5°	332.3	350.3	371.9	399.1
40°	314.3	333.2	353.0	380.2
42.5°	296.8	313.9	333.7	358.6
45°	279.8	294.5	312.5	334.1
47.5°	262.2	274.7	291.3	310.6
50°	243.3	256.7	269.2	285.3
52.5°	225.8	237.4	247.5	260.9
55°	208.8	216.6	224.9	235.0
57.5°	190.8	196.8	202.8	213.4
60°	172.8	178.4	181.6	188.5
62.5°	155.3	157.6	161.8	165.9
65°	136.0	139.2	141.5	146.6
67.5°	118.4	119.8	122.1	125.4
70°	100.0	103.2	104.2	106.5
72.5°	84.3	85.7	86.6	87.1
75°	66.8	68.2	69.1	71.9
77.5°	52.5	52.1	53.9	54.4
80°	38.7	37.3	37.8	39.6
82.5°	25.3	25.8	25.3	25.3
85°	15.7	15.2	14.3	14.7
87.5°	6.9	6.9	6.5	6.5
90°	10.2	7.8	5.4	3.0
92.5°	13.5	13.9	14.4	14.8
95°	32.0	39.5	46.9	54.4
97.5°	118.3	113.4	108.6	103.8
100°	173.9	170.0	166.0	162.1
102.5°	235.2	232.5	229.9	227.3
105°	301.4	300.1	298.7	297.4
107.5°	363.6	363.0	362.3	361.7
110°	428.9	428.2	427.6	426.9

TEST NUMBER: P1001113

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	494.1	492.8	491.4	490.1
115°	557.3	556.7	556.0	555.4
117.5°	616.3	615.4	614.6	613.7
120°	675.6	674.7	673.9	673.0
122.5°	729.6	729.2	728.7	728.3
125°	783.3	782.4	781.6	780.7
127.5°	831.8	831.5	831.3	831.1
130°	880.2	879.9	879.7	879.5
132.5°	925.3	924.8	924.4	924.0
135°	967.7	968.0	968.2	968.4
137.5°	1007.9	1007.9	1007.9	1007.9
140°	1047.8	1047.4	1046.9	1046.5
142.5°	1083.7	1082.8	1082.0	1081.1
145°	1118.6	1117.9	1117.3	1116.6
147.5°	1148.2	1146.9	1145.6	1144.3
150°	1177.6	1176.7	1175.9	1175.0
152.5°	1202.6	1201.9	1201.3	1200.6
155°	1225.1	1224.8	1224.6	1224.4
157.5°	1245.1	1245.1	1245.1	1245.1
160°	1260.9	1261.6	1262.2	1262.9
162.5°	1276.1	1277.0	1277.8	1278.7
165°	1288.3	1289.4	1290.5	1291.6
167.5°	1299.1	1300.2	1301.3	1302.4
170°	1307.4	1308.7	1310.0	1311.3
172.5°	1313.3	1314.6	1316.0	1317.3
175°	1317.3	1318.6	1319.9	1321.2
177.5°	1319.6	1321.1	1322.7	1324.2
180°	1321.2	1321.2	1321.2	1321.2

(END OF REPORT)