

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001150

Luminaire Tested: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001150
REPORT IS A COMBINATION OF REPORTS P995766 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5047.3 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001150

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001150

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	87	83	80	82	78	75	72	60	58	56	44	43	41	29	28	27
2	83	76	70	65	74	68	63	58	52	49	46	38	36	34	25	24	23
3	76	67	59	54	67	59	53	48	46	42	38	34	31	28	22	20	19
4	69	59	51	45	61	52	46	41	41	36	32	30	27	24	20	18	16
5	63	52	44	38	56	46	40	35	36	31	28	27	23	21	18	16	14
6	58	46	38	33	52	42	35	30	32	27	24	24	20	18	16	14	12
7	54	42	34	29	48	37	31	26	29	24	21	22	18	16	14	12	11
8	50	38	30	25	44	34	27	23	26	22	18	20	16	14	13	11	10
9	46	34	27	22	41	31	24	20	24	19	16	18	15	12	12	10	9
10	43	31	24	20	38	28	22	18	22	18	14	17	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3337	3337	3337
5°	3346	3249	3255
10°	3324	3186	3176
15°	3293	3114	3087
20°	3246	3036	3001
25°	3195	2950	2907
30°	3138	2865	2813
35°	3075	2778	2728
40°	3024	2695	2640
45°	2949	2616	2563
50°	2884	2527	2481
55°	2818	2441	2386
60°	2715	2335	2298
65°	2600	2220	2192
70°	2463	2088	2069
75°	2271	1942	1952
80°	2052	1793	1828
85°	1768	1643	1729

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2949 cd/sqm

TEST NUMBER: P1001150

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.8	0.8
10°-20°	111.1	2.2
20°-30°	168.0	3.3
30°-40°	203.2	4.0
40°-50°	214.8	4.3
50°-60°	202.2	4.0
60°-70°	167.7	3.3
70°-80°	117.7	2.3
80°-90°	68.3	1.4
90°-100°	411.1	8.1
100°-110°	784.9	15.6
110°-120°	693.2	13.7
120°-130°	576.8	11.4
130°-140°	476.9	9.4
140°-150°	361.5	7.2
150°-160°	253.5	5.0
160°-170°	149.1	3.0
170°-180°	48.5	1.0
0°-30°	317.8	6.3
0°-40°	521.0	10.3
0°-60°	938.0	18.6
0°-90°	1291.7	25.6
90°-120°	1889.2	37.4
90°-150°	3304.5	65.5
90°-180°	3756.0	74.4
0°-180°	5047.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	410	408	405	409	408	39
15°	393	393	392	396	395	111
25°	359	362	363	368	369	165
35°	314	320	324	331	332	197
45°	262	271	280	287	290	203
55°	205	215	229	238	240	183
65°	142	157	172	184	187	141
75°	79	96	115	128	132	84
85°	24	44	64	78	82	25
90°	8	34	63	78	83	7
95°	38	123	841	449	296	40
105°	119	180	675	1430	1428	127
115°	205	261	596	1136	1362	204
125°	284	336	585	961	1084	253
135°	336	400	571	846	962	260
145°	387	442	564	706	778	243
155°	439	474	548	621	648	203
165°	479	493	526	557	565	135
175°	499	500	504	511	509	47
180°	500	500	500	500	500	

TEST NUMBER: P1001150

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	409.2	409.2	409.2	409.2	409.2
2.5°	411.0	409.6	406.0	409.2	408.7
5°	409.6	408.2	405.0	408.7	408.2
7.5°	406.9	406.0	403.2	407.3	406.9
10°	403.2	402.7	400.5	404.6	404.1
12.5°	398.2	398.2	396.8	400.5	400.5
15°	392.7	393.1	391.8	395.9	395.4
17.5°	385.3	386.7	386.3	390.4	389.9
20°	377.5	378.9	379.4	384.0	384.0
22.5°	368.8	370.7	371.6	376.2	377.1
25°	359.2	362.0	363.3	368.4	368.8
27.5°	348.7	352.8	354.6	359.2	359.7
30°	338.1	341.8	345.0	350.1	351.0
32.5°	326.7	331.3	334.9	340.9	341.8
35°	314.3	319.8	324.4	330.8	332.2
37.5°	301.9	308.4	313.9	320.3	321.6
40°	290.0	296.0	302.4	309.3	311.1
42.5°	276.3	283.2	290.9	298.7	300.1
45°	262.1	270.8	279.5	287.3	289.6
47.5°	248.8	257.5	267.6	275.4	278.1
50°	234.1	244.2	254.3	263.5	266.2
52.5°	219.5	229.6	241.5	250.6	253.4
55°	205.3	214.9	228.6	237.8	240.5
57.5°	189.2	201.1	214.4	225.4	227.7
60°	173.7	185.6	200.7	211.2	214.9
62.5°	158.5	171.8	186.9	197.5	201.1
65°	142.0	156.7	172.3	183.7	187.4
67.5°	126.5	142.0	158.5	170.0	173.7
70°	110.4	126.0	143.4	155.8	159.0
72.5°	94.8	110.9	129.7	141.6	145.2
75°	78.8	95.8	115.0	127.8	132.0
77.5°	63.7	81.6	101.7	114.5	119.1
80°	49.9	68.3	88.4	102.2	105.8
82.5°	36.2	55.4	75.6	89.8	93.9
85°	24.3	43.5	64.1	77.9	82.5
87.5°	15.1	33.9	54.1	67.4	71.5
90°	8.3	33.6	63.1	78.3	82.9
92.5°	20.7	98.6	427.8	182.6	148.5
95°	38.4	123.3	840.8	448.7	296.2
97.5°	59.5	131.8	894.5	859.2	629.5
100°	79.7	144.8	824.9	1167.4	951.5
102.5°	99.3	160.5	739.1	1359.2	1232.3
105°	119.1	179.9	674.8	1429.8	1428.1
107.5°	141.7	200.0	632.3	1405.4	1519.6
110°	163.9	219.9	611.8	1324.0	1519.3

TEST NUMBER: P1001150

CATALOG NUMBER: SA4XXDIP-B350D1035UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	185.0	240.2	600.6	1225.0	1458.6
115°	205.1	261.0	596.4	1136.2	1362.4
117.5°	226.8	280.6	593.1	1065.6	1268.7
120°	248.0	299.4	590.9	1017.2	1191.3
122.5°	267.6	318.2	587.6	984.9	1129.6
125°	283.8	336.5	584.7	961.4	1083.6
127.5°	299.6	354.2	580.5	938.6	1053.8
130°	311.9	370.8	577.2	912.2	1027.4
132.5°	324.7	385.6	574.4	881.4	998.7
135°	336.0	399.9	571.1	845.8	961.5
137.5°	347.8	411.8	569.3	808.1	918.5
140°	360.6	423.1	566.9	771.4	872.0
142.5°	373.9	433.4	566.0	737.6	822.5
145°	386.7	442.2	564.1	706.4	778.0
147.5°	401.4	451.0	561.1	680.0	736.4
150°	415.2	459.4	558.2	657.4	701.6
152.5°	427.5	467.2	553.3	638.8	672.2
155°	439.3	474.2	548.3	621.1	647.6
157.5°	451.1	480.5	543.4	604.3	625.0
160°	461.9	485.9	537.5	587.7	604.4
162.5°	471.7	490.4	531.6	571.4	584.7
165°	478.6	493.4	525.7	556.7	565.1
167.5°	486.4	495.8	519.8	543.9	549.3
170°	491.3	497.8	514.0	531.2	534.6
172.5°	496.3	499.2	508.1	519.8	519.8
175°	499.2	500.2	504.1	511.0	509.0
177.5°	501.2	500.2	501.2	504.6	501.2
180°	500.2	500.2	500.2	500.2	500.2

(END OF REPORT)