

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001117

Luminaire Tested: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001117
REPORT IS A COMBINATION OF REPORTS P995733 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5447.0 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001117

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001117

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	91	87	83	80	81	77	74	71	59	57	55	43	41	40	27	27	26
2	83	76	70	65	73	67	62	58	52	48	45	37	35	33	24	23	21
3	76	66	59	53	67	59	53	48	45	41	38	33	30	28	21	19	18
4	69	58	51	45	61	52	45	40	40	35	32	29	26	23	19	17	15
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13
6	58	46	38	33	51	41	34	30	32	27	23	23	20	17	15	13	12
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10
8	49	37	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9
9	46	34	27	22	41	30	24	20	24	19	16	17	14	12	11	10	8
10	43	31	24	19	38	28	22	18	22	17	14	16	13	11	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3327	3327	3327
5°	3336	3240	3246
10°	3314	3176	3168
15°	3283	3105	3079
20°	3238	3027	2993
25°	3186	2942	2900
30°	3130	2857	2805
35°	3066	2770	2720
40°	3015	2687	2633
45°	2940	2609	2555
50°	2877	2520	2474
55°	2810	2435	2380
60°	2707	2328	2292
65°	2593	2214	2186
70°	2456	2082	2062
75°	2265	1937	1946
80°	2048	1789	1822
85°	1761	1640	1723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 3327 cd/sqm

TEST NUMBER: P1001117

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	0.7
10°-20°	110.8	2.0
20°-30°	167.5	3.1
30°-40°	202.6	3.7
40°-50°	214.2	3.9
50°-60°	201.6	3.7
60°-70°	167.3	3.1
70°-80°	117.4	2.2
80°-90°	68.9	1.3
90°-100°	82.9	1.5
100°-110°	315.5	5.8
110°-120°	566.4	10.4
120°-130°	705.2	12.9
130°-140°	747.4	13.7
140°-150°	695.3	12.8
150°-160°	560.0	10.3
160°-170°	361.1	6.6
170°-180°	124.5	2.3
0°-30°	316.9	5.8
0°-40°	519.5	9.5
0°-60°	935.3	17.2
0°-90°	1288.8	23.7
90°-120°	964.8	17.7
90°-150°	3112.7	57.1
90°-180°	4158.0	76.3
0°-180°	5447.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	408	408	408	408	408	
5°	408	407	404	408	407	39
15°	392	392	391	395	394	110
25°	358	361	362	367	368	165
35°	313	319	324	330	331	196
45°	261	270	279	286	289	202
55°	205	214	228	237	240	182
65°	142	156	172	183	187	140
75°	79	96	115	128	132	84
85°	24	43	64	78	82	25
90°	10	39	67	86	92	8
95°	60	42	61	80	85	71
105°	299	314	336	356	324	313
115°	553	560	574	586	589	545
125°	776	779	789	800	804	693
135°	961	960	967	976	981	741
145°	1108	1110	1110	1114	1118	692
155°	1214	1215	1212	1216	1213	560
165°	1280	1276	1276	1283	1275	362
175°	1310	1304	1305	1314	1302	125
180°	1310	1310	1310	1310	1310	

TEST NUMBER: P1001117

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	408.0	408.0	408.0	408.0	408.0
2.5°	409.8	408.4	404.8	408.0	407.5
5°	408.4	407.1	403.9	407.5	407.1
7.5°	405.7	404.8	402.0	406.2	405.7
10°	402.0	401.6	399.3	403.4	403.0
12.5°	397.0	397.0	395.7	399.3	399.3
15°	391.5	392.0	390.6	394.7	394.3
17.5°	384.2	385.6	385.1	389.3	388.8
20°	376.5	377.8	378.3	382.9	382.9
22.5°	367.8	369.6	370.5	375.1	376.0
25°	358.2	360.9	362.3	367.3	367.8
27.5°	347.7	351.8	353.6	358.2	358.6
30°	337.2	340.8	344.0	349.1	350.0
32.5°	325.8	330.3	334.0	339.9	340.8
35°	313.4	318.9	323.5	329.9	331.2
37.5°	301.1	307.5	313.0	319.4	320.7
40°	289.2	295.1	301.5	308.4	310.2
42.5°	275.5	282.3	290.1	297.9	299.3
45°	261.3	270.0	278.7	286.5	288.7
47.5°	248.1	256.8	266.8	274.6	277.3
50°	233.5	243.5	253.6	262.7	265.4
52.5°	218.8	228.9	240.8	249.9	252.7
55°	204.7	214.3	228.0	237.1	239.9
57.5°	188.7	200.6	213.8	224.8	227.1
60°	173.2	185.0	200.1	210.6	214.3
62.5°	158.1	171.3	186.4	196.9	200.6
65°	141.6	156.3	171.8	183.2	186.9
67.5°	126.1	141.6	158.1	169.5	173.2
70°	110.1	125.6	143.0	155.3	158.5
72.5°	94.6	110.6	129.3	141.2	144.8
75°	78.6	95.5	114.7	127.5	131.6
77.5°	63.5	81.3	101.4	114.2	118.8
80°	49.8	68.1	88.2	101.9	105.5
82.5°	36.1	55.3	75.4	89.5	93.7
85°	24.2	43.4	64.0	77.7	82.2
87.5°	15.1	33.8	53.9	67.2	71.3
90°	10.2	39.3	66.8	85.9	91.5
92.5°	21.6	35.5	63.1	81.8	85.4
95°	59.8	41.6	61.3	79.5	84.6
97.5°	108.4	143.1	59.1	75.8	80.9
100°	165.7	195.2	77.8	73.6	77.7
102.5°	230.3	252.2	281.3	72.7	76.4
105°	299.0	314.0	335.9	356.1	324.4
107.5°	362.7	373.4	396.3	412.6	419.7
110°	426.9	436.3	458.1	470.5	477.2

TEST NUMBER: P1001117

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	489.1	500.5	517.6	526.6	534.2
115°	553.3	560.4	574.1	586.0	589.2
117.5°	611.1	617.8	634.5	643.1	646.7
120°	669.5	674.8	687.0	698.1	699.8
122.5°	724.4	726.3	740.6	750.8	752.0
125°	775.8	779.3	788.7	800.4	804.1
127.5°	825.8	826.3	840.3	847.6	849.8
130°	873.4	873.8	884.1	893.3	896.1
132.5°	917.4	918.9	928.3	937.1	938.8
135°	961.0	960.1	967.2	976.4	981.2
137.5°	1000.2	999.8	1006.5	1015.3	1016.6
140°	1038.4	1040.0	1042.4	1051.3	1054.5
142.5°	1072.3	1076.2	1076.7	1083.7	1085.6
145°	1107.6	1110.0	1110.0	1113.7	1117.6
147.5°	1135.0	1140.4	1139.4	1140.9	1143.7
150°	1165.4	1168.8	1167.8	1167.8	1168.8
152.5°	1190.4	1193.3	1191.4	1193.3	1192.3
155°	1213.9	1214.9	1211.9	1215.8	1212.9
157.5°	1234.5	1234.5	1230.5	1235.4	1230.5
160°	1252.1	1249.2	1248.2	1254.1	1248.2
162.5°	1267.8	1263.9	1262.9	1268.8	1261.9
165°	1280.5	1275.6	1275.6	1283.4	1274.6
167.5°	1291.3	1286.4	1285.4	1294.2	1284.4
170°	1300.1	1294.2	1295.2	1303.0	1293.2
172.5°	1306.0	1300.1	1301.1	1308.9	1298.1
175°	1309.9	1304.0	1305.0	1313.8	1302.1
177.5°	1312.8	1306.0	1307.9	1315.8	1304.0
180°	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)