

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001118

Luminaire Tested: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001118
REPORT IS A COMBINATION OF REPORTS P995734 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5494.0 lumens
Efficiency: N/A
Efficacy: 132.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001118

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001118

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	91	87	83	80	81	77	74	71	59	57	55	43	41	40	27	27	26
2	83	76	70	65	73	67	62	58	52	48	45	37	35	33	24	23	21
3	76	66	59	53	67	59	53	48	45	41	38	33	30	28	21	19	18
4	69	58	51	45	61	52	45	40	40	35	32	29	26	23	19	17	15
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13
6	58	46	38	33	51	41	34	30	32	27	23	23	20	17	15	13	12
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10
8	49	37	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9
9	46	34	27	22	41	30	24	20	24	19	16	17	14	12	11	10	8
10	43	31	24	19	38	28	22	18	22	17	14	16	13	11	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3356	3356	3356
5°	3365	3268	3274
10°	3343	3204	3194
15°	3312	3132	3105
20°	3265	3054	3018
25°	3213	2967	2925
30°	3157	2881	2829
35°	3093	2794	2744
40°	3041	2710	2656
45°	2966	2631	2577
50°	2901	2542	2495
55°	2833	2455	2400
60°	2729	2348	2311
65°	2617	2233	2205
70°	2479	2100	2080
75°	2285	1954	1962
80°	2065	1803	1838
85°	1776	1653	1738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 3392 cd/sqm

TEST NUMBER: P1001118

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.0	0.7
10°-20°	111.7	2.0
20°-30°	168.9	3.1
30°-40°	204.4	3.7
40°-50°	216.0	3.9
50°-60°	203.3	3.7
60°-70°	168.7	3.1
70°-80°	118.4	2.2
80°-90°	69.5	1.3
90°-100°	83.6	1.5
100°-110°	318.3	5.8
110°-120°	571.3	10.4
120°-130°	711.3	12.9
130°-140°	753.8	13.7
140°-150°	701.3	12.8
150°-160°	564.8	10.3
160°-170°	364.2	6.6
170°-180°	125.5	2.3
0°-30°	319.6	5.8
0°-40°	524.0	9.5
0°-60°	943.3	17.2
0°-90°	1299.9	23.7
90°-120°	973.1	17.7
90°-150°	3139.5	57.1
90°-180°	4194.0	76.3
0°-180°	5494.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	412	412	412	412	412	
5°	412	411	407	411	411	39
15°	395	395	394	398	398	111
25°	361	364	365	370	371	166
35°	316	322	326	333	334	198
45°	264	272	281	289	291	204
55°	206	216	230	239	242	184
65°	143	158	173	185	188	142
75°	79	96	116	129	133	84
85°	24	44	64	78	83	25
90°	10	40	67	87	92	8
95°	60	42	62	80	85	72
105°	302	317	339	359	327	316
115°	558	565	579	591	594	550
125°	782	786	796	807	811	699
135°	969	968	976	985	990	747
145°	1117	1120	1120	1123	1127	698
155°	1224	1225	1222	1226	1223	565
165°	1292	1287	1287	1294	1286	365
175°	1321	1315	1316	1325	1313	126
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1001118

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	411.5	411.5	411.5	411.5	411.5
2.5°	413.4	412.0	408.3	411.5	411.0
5°	412.0	410.6	407.4	411.0	410.6
7.5°	409.2	408.3	405.5	409.7	409.2
10°	405.5	405.1	402.8	406.9	406.4
12.5°	400.4	400.4	399.1	402.8	402.8
15°	394.9	395.4	394.0	398.1	397.7
17.5°	387.5	388.9	388.5	392.6	392.2
20°	379.7	381.1	381.6	386.2	386.2
22.5°	371.0	372.8	373.7	378.3	379.3
25°	361.3	364.0	365.4	370.5	371.0
27.5°	350.7	354.8	356.7	361.3	361.7
30°	340.1	343.8	347.0	352.1	353.0
32.5°	328.6	333.2	336.9	342.8	343.8
35°	316.1	321.6	326.3	332.7	334.1
37.5°	303.7	310.1	315.7	322.1	323.5
40°	291.7	297.7	304.1	311.1	312.9
42.5°	277.9	284.8	292.6	300.5	301.8
45°	263.6	272.3	281.1	288.9	291.2
47.5°	250.2	259.0	269.1	277.0	279.7
50°	235.5	245.6	255.8	265.0	267.7
52.5°	220.7	230.9	242.8	252.1	254.8
55°	206.4	216.1	229.9	239.2	241.9
57.5°	190.3	202.3	215.7	226.7	229.0
60°	174.6	186.6	201.8	212.4	216.1
62.5°	159.4	172.8	188.0	198.6	202.3
65°	142.9	157.6	173.3	184.8	188.5
67.5°	127.2	142.9	159.4	171.0	174.6
70°	111.1	126.7	144.2	156.7	159.9
72.5°	95.4	111.5	130.4	142.4	146.1
75°	79.3	96.3	115.7	128.6	132.7
77.5°	64.1	82.0	102.3	115.2	119.8
80°	50.2	68.7	88.9	102.8	106.4
82.5°	36.4	55.8	76.0	90.3	94.5
85°	24.4	43.8	64.5	78.3	82.9
87.5°	15.2	34.1	54.4	67.7	71.9
90°	10.4	39.6	67.3	86.7	92.3
92.5°	21.7	35.8	63.7	82.5	86.1
95°	60.4	42.0	61.8	80.2	85.4
97.5°	109.3	144.4	59.5	76.5	81.6
100°	167.2	196.9	78.5	74.2	78.4
102.5°	232.4	254.3	283.7	73.4	77.1
105°	301.5	316.8	338.7	359.1	327.2
107.5°	365.8	376.6	399.7	416.1	423.4
110°	430.6	440.0	462.1	474.7	481.3

TEST NUMBER: P1001118

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	493.3	504.9	522.0	531.2	538.8
115°	558.2	565.2	579.0	591.1	594.3
117.5°	616.5	623.1	640.0	648.6	652.3
120°	675.3	680.6	693.0	704.2	705.9
122.5°	730.6	732.6	746.9	757.2	758.5
125°	782.5	786.0	795.5	807.3	811.0
127.5°	832.9	833.5	847.6	854.9	857.1
130°	880.9	881.4	891.7	901.0	903.8
132.5°	925.4	926.8	936.4	945.2	947.0
135°	969.3	968.3	975.5	984.9	989.6
137.5°	1008.8	1008.4	1015.2	1024.1	1025.4
140°	1047.4	1049.0	1051.3	1060.3	1063.6
142.5°	1081.6	1085.5	1086.0	1093.1	1094.9
145°	1117.1	1119.6	1119.6	1123.4	1127.2
147.5°	1144.8	1150.2	1149.3	1150.7	1153.5
150°	1175.5	1178.9	1177.9	1177.9	1178.9
152.5°	1200.6	1203.6	1201.6	1203.6	1202.6
155°	1224.4	1225.4	1222.4	1226.3	1223.4
157.5°	1245.1	1245.1	1241.2	1246.1	1241.2
160°	1262.9	1259.9	1258.9	1264.9	1258.9
162.5°	1278.7	1274.8	1273.8	1279.7	1272.8
165°	1291.6	1286.6	1286.6	1294.5	1285.6
167.5°	1302.4	1297.5	1296.5	1305.4	1295.5
170°	1311.3	1305.4	1306.4	1314.3	1304.4
172.5°	1317.3	1311.3	1312.3	1320.2	1309.3
175°	1321.2	1315.3	1316.3	1325.2	1313.3
177.5°	1324.2	1317.3	1319.2	1327.1	1315.3
180°	1321.2	1321.2	1321.2	1321.2	1321.2

(END OF REPORT)