

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001168

Luminaire Tested: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001168
REPORT IS A COMBINATION OF REPORTS P995784 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5669.5 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001168

CATALOG NUMBER: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001168

CATALOG NUMBER: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	31	31	23
1	91	87	83	79	81	77	74	71	59	57	55	42	41	40	27	26	25	25	25	18
2	83	76	69	64	73	67	62	58	51	48	45	37	34	33	23	22	21	21	21	15
3	75	66	59	53	66	59	53	48	45	41	37	32	30	27	20	19	18	18	18	12
4	69	58	51	45	61	52	45	40	40	35	32	29	26	23	18	16	15	15	15	10
5	63	52	44	38	55	46	39	34	35	31	27	25	22	20	16	14	13	13	13	9
6	58	46	38	33	51	41	34	29	32	27	23	23	20	17	15	13	11	11	11	8
7	53	41	34	28	47	37	30	26	29	24	20	21	17	15	13	11	10	10	10	7
8	49	37	30	25	44	33	27	22	26	21	18	19	16	13	12	10	9	9	9	6
9	46	34	27	22	40	30	24	20	24	19	16	17	14	12	11	9	8	8	8	5
10	43	31	24	19	38	28	22	18	22	17	14	16	13	11	10	8	7	7	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3327	3327	3327
5°	3336	3240	3246
10°	3314	3176	3168
15°	3283	3105	3079
20°	3238	3027	2993
25°	3186	2942	2900
30°	3130	2857	2805
35°	3066	2770	2720
40°	3015	2687	2633
45°	2940	2609	2555
50°	2877	2520	2474
55°	2810	2435	2380
60°	2707	2328	2292
65°	2593	2214	2186
70°	2456	2082	2062
75°	2265	1937	1946
80°	2048	1789	1822
85°	1761	1640	1723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2940 cd/sqm

TEST NUMBER: P1001168

CATALOG NUMBER: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	0.7
10°-20°	110.8	2.0
20°-30°	167.5	3.0
30°-40°	202.6	3.6
40°-50°	214.2	3.8
50°-60°	201.6	3.6
60°-70°	167.3	3.0
70°-80°	117.4	2.1
80°-90°	68.4	1.2
90°-100°	474.6	8.4
100°-110°	914.4	16.1
110°-120°	808.7	14.3
120°-130°	673.8	11.9
130°-140°	557.9	9.8
140°-150°	423.4	7.5
150°-160°	296.9	5.2
160°-170°	174.6	3.1
170°-180°	56.8	1.0
0°-30°	316.9	5.6
0°-40°	519.5	9.2
0°-60°	935.3	16.5
0°-90°	1288.4	22.7
90°-120°	2197.7	38.8
90°-150°	3852.8	68.0
90°-180°	4381.0	77.3
0°-180°	5669.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	408	408	408	408	408	
5°	408	407	404	408	407	39
15°	392	392	391	395	394	110
25°	358	361	362	367	368	165
35°	313	319	324	330	331	196
45°	261	270	279	286	289	202
55°	205	214	228	237	240	182
65°	142	156	172	183	187	140
75°	79	96	115	128	132	84
85°	24	43	64	78	82	25
90°	8	35	66	82	86	8
95°	44	141	978	517	337	46
105°	139	208	785	1668	1665	148
115°	240	304	695	1325	1590	238
125°	332	394	683	1123	1265	296
135°	394	468	668	989	1124	304
145°	453	518	661	827	911	284
155°	515	555	642	728	759	237
165°	561	578	616	652	662	158
175°	585	586	591	599	596	56
180°	586	586	586	586	586	

TEST NUMBER: P1001168

CATALOG NUMBER: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	408.0	408.0	408.0	408.0	408.0
2.5°	409.8	408.4	404.8	408.0	407.5
5°	408.4	407.1	403.9	407.5	407.1
7.5°	405.7	404.8	402.0	406.2	405.7
10°	402.0	401.6	399.3	403.4	403.0
12.5°	397.0	397.0	395.7	399.3	399.3
15°	391.5	392.0	390.6	394.7	394.3
17.5°	384.2	385.6	385.1	389.3	388.8
20°	376.5	377.8	378.3	382.9	382.9
22.5°	367.8	369.6	370.5	375.1	376.0
25°	358.2	360.9	362.3	367.3	367.8
27.5°	347.7	351.8	353.6	358.2	358.6
30°	337.2	340.8	344.0	349.1	350.0
32.5°	325.8	330.3	334.0	339.9	340.8
35°	313.4	318.9	323.5	329.9	331.2
37.5°	301.1	307.5	313.0	319.4	320.7
40°	289.2	295.1	301.5	308.4	310.2
42.5°	275.5	282.3	290.1	297.9	299.3
45°	261.3	270.0	278.7	286.5	288.7
47.5°	248.1	256.8	266.8	274.6	277.3
50°	233.5	243.5	253.6	262.7	265.4
52.5°	218.8	228.9	240.8	249.9	252.7
55°	204.7	214.3	228.0	237.1	239.9
57.5°	188.7	200.6	213.8	224.8	227.1
60°	173.2	185.0	200.1	210.6	214.3
62.5°	158.1	171.3	186.4	196.9	200.6
65°	141.6	156.3	171.8	183.2	186.9
67.5°	126.1	141.6	158.1	169.5	173.2
70°	110.1	125.6	143.0	155.3	158.5
72.5°	94.6	110.6	129.3	141.2	144.8
75°	78.6	95.5	114.7	127.5	131.6
77.5°	63.5	81.3	101.4	114.2	118.8
80°	49.8	68.1	88.2	101.9	105.5
82.5°	36.1	55.3	75.4	89.5	93.7
85°	24.2	43.4	64.0	77.7	82.2
87.5°	15.1	33.8	53.9	67.2	71.3
90°	8.5	34.8	65.9	81.5	86.3
92.5°	23.0	111.4	493.8	204.4	163.7
95°	43.9	140.7	977.9	516.6	337.1
97.5°	68.8	151.1	1041.3	997.9	728.1
100°	92.5	166.5	960.3	1359.5	1105.9
102.5°	115.5	185.4	860.1	1584.6	1435.2
105°	138.8	208.3	785.4	1667.7	1664.9
107.5°	165.3	232.4	735.9	1639.4	1772.8
110°	191.3	255.8	712.1	1544.6	1772.8

TEST NUMBER: P1001168

CATALOG NUMBER: SA4XXDIP-B350D1205UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	216.2	279.8	699.6	1429.0	1702.1
115°	239.8	304.4	695.0	1325.4	1590.0
117.5°	265.2	327.8	691.5	1243.4	1480.6
120°	290.1	350.2	689.2	1187.0	1390.4
122.5°	313.1	372.4	685.7	1149.6	1318.6
125°	332.2	393.9	682.8	1122.6	1265.2
127.5°	350.6	414.7	678.2	1096.2	1230.7
130°	365.2	434.3	674.7	1065.7	1200.3
132.5°	380.1	451.6	671.8	1030.1	1166.9
135°	393.5	468.3	668.3	988.8	1124.0
137.5°	407.3	482.3	666.5	945.0	1074.0
140°	422.2	495.5	664.0	902.6	1019.9
142.5°	438.0	507.6	663.1	863.2	962.4
145°	452.9	518.0	660.8	827.0	910.6
147.5°	470.2	528.4	657.3	796.6	862.2
150°	486.3	538.2	653.9	770.2	822.0
152.5°	500.8	547.4	648.1	748.2	787.4
155°	514.6	555.4	642.4	727.6	758.6
157.5°	528.4	562.9	636.6	708.0	732.2
160°	541.1	569.2	629.7	688.4	708.0
162.5°	552.6	574.4	622.8	669.4	685.0
165°	560.6	577.9	615.9	652.2	661.9
167.5°	569.8	580.8	609.0	637.2	643.5
170°	575.6	583.1	602.1	622.2	626.3
172.5°	581.4	584.8	595.2	609.0	609.0
175°	584.8	586.0	590.6	598.6	596.3
177.5°	587.1	586.0	587.1	591.2	587.1
180°	586.0	586.0	586.0	586.0	586.0

(END OF REPORT)