

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001121

Luminaire Tested: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001121
REPORT IS A COMBINATION OF REPORTS P995737 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_5000K
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5283.0 lumens
Efficiency: N/A
Efficacy: 127.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001121

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001121

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	91	87	83	80	81	77	74	71	59	57	55	43	41	40	27	27	26
2	83	76	70	65	73	67	62	58	52	48	45	37	35	33	24	23	21
3	76	66	59	53	67	59	53	48	45	41	38	33	30	28	21	19	18
4	69	58	51	45	61	52	45	40	40	35	32	29	26	23	19	17	15
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13
6	58	46	38	33	51	41	34	30	32	27	23	23	20	17	15	13	12
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10
8	49	37	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9
9	46	34	27	22	41	30	24	20	24	19	16	17	14	12	11	10	8
10	43	31	24	19	38	28	22	18	22	17	14	16	13	11	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3227	3227	3227
5°	3235	3143	3148
10°	3214	3081	3072
15°	3184	3011	2986
20°	3140	2936	2902
25°	3090	2853	2812
30°	3035	2770	2720
35°	2974	2686	2638
40°	2925	2605	2554
45°	2851	2530	2478
50°	2789	2444	2399
55°	2725	2361	2308
60°	2625	2258	2222
65°	2516	2147	2119
70°	2383	2020	2000
75°	2196	1878	1887
80°	1987	1734	1769
85°	1710	1589	1673

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 3262 cd/sqm

TEST NUMBER: P1001121

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.5	0.7
10°-20°	107.4	2.0
20°-30°	162.4	3.1
30°-40°	196.5	3.7
40°-50°	207.7	3.9
50°-60°	195.5	3.7
60°-70°	162.2	3.1
70°-80°	113.8	2.2
80°-90°	66.8	1.3
90°-100°	80.4	1.5
100°-110°	306.0	5.8
110°-120°	549.3	10.4
120°-130°	684.0	12.9
130°-140°	724.9	13.7
140°-150°	674.4	12.8
150°-160°	543.1	10.3
160°-170°	350.3	6.6
170°-180°	120.7	2.3
0°-30°	307.3	5.8
0°-40°	503.8	9.5
0°-60°	907.0	17.2
0°-90°	1249.9	23.7
90°-120°	935.8	17.7
90°-150°	3019.0	57.1
90°-180°	4033.0	76.3
0°-180°	5283.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	396	396	396	396	396	
5°	396	395	392	395	395	38
15°	380	380	379	383	382	107
25°	347	350	351	356	357	160
35°	304	309	314	320	321	190
45°	253	262	270	278	280	196
55°	198	208	221	230	233	177
65°	137	152	167	178	181	136
75°	76	93	111	124	128	81
85°	24	42	62	75	80	24
90°	10	38	65	83	89	8
95°	58	40	59	77	82	69
105°	290	304	326	345	315	304
115°	537	544	557	568	572	528
125°	752	756	765	776	780	672
135°	932	931	938	947	952	718
145°	1074	1077	1077	1080	1084	671
155°	1177	1178	1176	1179	1176	543
165°	1242	1237	1237	1245	1236	351
175°	1270	1265	1266	1274	1263	121
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1001121

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	395.7	395.7	395.7	395.7	395.7
2.5°	397.4	396.1	392.6	395.7	395.2
5°	396.1	394.8	391.7	395.2	394.8
7.5°	393.5	392.6	389.9	393.9	393.5
10°	389.9	389.5	387.3	391.2	390.8
12.5°	385.0	385.0	383.7	387.3	387.3
15°	379.7	380.2	378.8	382.8	382.4
17.5°	372.6	374.0	373.5	377.5	377.1
20°	365.1	366.4	366.9	371.3	371.3
22.5°	356.7	358.5	359.3	363.8	364.7
25°	347.4	350.0	351.4	356.2	356.7
27.5°	337.2	341.2	342.9	347.4	347.8
30°	327.0	330.5	333.6	338.5	339.4
32.5°	315.9	320.3	323.9	329.7	330.5
35°	304.0	309.3	313.7	319.9	321.2
37.5°	292.0	298.2	303.5	309.7	311.0
40°	280.5	286.2	292.4	299.1	300.9
42.5°	267.2	273.8	281.4	288.9	290.2
45°	253.4	261.9	270.3	277.8	280.0
47.5°	240.6	249.0	258.8	266.3	268.9
50°	226.4	236.2	245.9	254.8	257.4
52.5°	212.2	222.0	233.5	242.4	245.0
55°	198.5	207.8	221.1	230.0	232.6
57.5°	183.0	194.5	207.4	218.0	220.2
60°	167.9	179.4	194.1	204.3	207.8
62.5°	153.3	166.2	180.8	191.0	194.5
65°	137.4	151.5	166.6	177.7	181.2
67.5°	122.3	137.4	153.3	164.4	167.9
70°	106.8	121.8	138.7	150.6	153.7
72.5°	91.7	107.2	125.4	136.9	140.5
75°	76.2	92.6	111.2	123.6	127.6
77.5°	61.6	78.9	98.4	110.8	115.2
80°	48.3	66.0	85.5	98.8	102.4
82.5°	35.0	53.6	73.1	86.8	90.8
85°	23.5	42.1	62.0	75.3	79.8
87.5°	14.6	32.8	52.3	65.1	69.1
90°	10.0	38.1	64.8	83.3	88.8
92.5°	20.9	34.6	61.2	79.3	82.9
95°	58.1	40.4	59.4	77.1	82.1
97.5°	105.1	138.9	57.2	73.6	78.4
100°	160.7	189.3	75.5	71.3	75.3
102.5°	223.5	244.6	272.9	70.6	74.1
105°	290.0	304.5	325.7	345.3	314.7
107.5°	351.8	362.1	384.3	400.1	407.1
110°	414.0	423.1	444.4	456.4	462.8

TEST NUMBER: P1001121

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	474.4	485.4	501.9	510.8	518.1
115°	536.7	543.5	556.7	568.4	571.5
117.5°	592.8	599.2	615.4	623.7	627.3
120°	649.3	654.4	666.4	677.2	678.8
122.5°	702.5	704.4	718.3	728.1	729.3
125°	752.5	755.8	765.0	776.3	779.9
127.5°	801.0	801.4	815.1	822.1	824.3
130°	847.0	847.6	857.5	866.5	869.1
132.5°	889.8	891.3	900.4	908.8	910.6
135°	932.2	931.2	938.1	947.1	951.6
137.5°	970.2	969.7	976.2	984.8	986.1
140°	1007.2	1008.6	1011.0	1019.6	1022.8
142.5°	1040.0	1043.8	1044.3	1051.1	1052.8
145°	1074.2	1076.6	1076.6	1080.3	1083.9
147.5°	1100.8	1106.1	1105.2	1106.5	1109.3
150°	1130.3	1133.7	1132.7	1132.7	1133.7
152.5°	1154.6	1157.4	1155.5	1157.4	1156.5
155°	1177.4	1178.3	1175.5	1179.3	1176.4
157.5°	1197.3	1197.3	1193.5	1198.3	1193.5
160°	1214.4	1211.6	1210.6	1216.3	1210.6
162.5°	1229.6	1225.8	1224.9	1230.6	1223.9
165°	1242.0	1237.2	1237.2	1244.8	1236.3
167.5°	1252.4	1247.7	1246.7	1255.3	1245.8
170°	1261.0	1255.3	1256.2	1263.8	1254.3
172.5°	1266.7	1261.0	1261.9	1269.6	1259.1
175°	1270.5	1264.8	1265.7	1274.3	1262.9
177.5°	1273.4	1266.7	1268.6	1276.2	1264.8
180°	1270.5	1270.5	1270.5	1270.5	1270.5

(END OF REPORT)