

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001195

Luminaire Tested: SA4XXDIP-B350D1205UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001195
REPORT IS A COMBINATION OF REPORTS P995811 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1205UB30-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5791.6 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001195

CATALOG NUMBER: SA4XXDIP-B350D1205UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001195

CATALOG NUMBER: SA4XXDIP-B350D1205UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	84	81	82	79	76	73	61	59	57	45	43	42	30	29	28
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	67	60	55	68	60	54	50	47	43	40	35	32	30	23	22	20
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	21	19	17
5	64	53	45	39	57	47	41	36	37	32	29	28	24	22	19	17	15
6	59	47	40	34	52	42	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	9
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4690	4690	4690
5°	4693	4555	4560
10°	4654	4428	4397
15°	4587	4278	4213
20°	4502	4115	4023
25°	4405	3944	3818
30°	4290	3758	3593
35°	4170	3567	3375
40°	4045	3363	3144
45°	3914	3157	2928
50°	3770	2959	2689
55°	3612	2726	2451
60°	3450	2471	2203
65°	3265	2209	1924
70°	3054	1892	1625
75°	2735	1525	1301
80°	2332	1103	916
85°	1812	615	493

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3914 cd/sqm

TEST NUMBER: P1001195

CATALOG NUMBER: SA4XXDIP-B350D1205UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	0.9
10°-20°	152.7	2.6
20°-30°	224.7	3.9
30°-40°	261.2	4.5
40°-50°	261.2	4.5
50°-60°	228.5	3.9
60°-70°	169.6	2.9
70°-80°	96.2	1.7
80°-90°	29.8	0.5
90°-100°	439.0	7.6
100°-110°	893.0	15.4
110°-120°	795.9	13.7
120°-130°	668.6	11.5
130°-140°	557.9	9.6
140°-150°	426.1	7.4
150°-160°	299.5	5.2
160°-170°	176.2	3.0
170°-180°	57.3	1.0
0°-30°	431.6	7.5
0°-40°	692.9	12.0
0°-60°	1182.6	20.4
0°-90°	1478.3	25.5
90°-120°	2127.9	36.7
90°-150°	3780.4	65.3
90°-180°	4313.0	74.5
0°-180°	5791.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	575	575	575	575	575	
5°	575	573	568	573	572	55
15°	547	545	538	541	540	154
25°	495	492	486	486	484	228
35°	426	423	416	413	411	267
45°	348	345	337	332	331	268
55°	263	262	255	250	247	236
65°	178	176	171	167	164	176
75°	95	93	90	88	88	101
85°	25	25	24	24	24	27
90°	1	9	21	23	24	4
95°	38	121	946	469	283	42
105°	136	197	762	1640	1634	145
115°	239	300	679	1305	1569	237
125°	333	396	676	1111	1252	297
135°	396	471	670	986	1119	306
145°	456	523	666	831	914	286
155°	519	560	648	734	765	239
165°	566	583	621	658	668	160
175°	590	591	596	604	602	56
180°	591	591	591	591	591	

TEST NUMBER: P1001195

CATALOG NUMBER: SA4XXDIP-B350D1205UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	575.1	575.1	575.1	575.1	575.1
2.5°	576.9	575.5	570.5	575.1	574.6
5°	574.6	572.8	567.7	572.8	571.8
7.5°	570.5	568.6	563.1	567.2	566.8
10°	564.5	562.6	556.6	560.3	559.4
12.5°	556.6	554.8	548.3	552.5	551.1
15°	547.0	545.1	538.2	541.0	539.6
17.5°	535.9	533.6	527.1	529.0	528.1
20°	523.5	521.1	514.2	515.6	514.7
22.5°	510.1	506.9	500.0	502.7	500.9
25°	495.3	492.1	485.7	486.1	484.3
27.5°	478.8	475.5	469.5	468.6	466.3
30°	462.2	458.5	452.5	450.6	448.3
32.5°	444.7	441.4	435.0	432.7	430.4
35°	426.2	423.0	416.5	413.3	411.0
37.5°	406.9	404.1	397.2	394.0	390.7
40°	388.0	384.3	377.4	372.8	370.5
42.5°	367.7	365.9	358.0	352.5	351.1
45°	347.9	344.7	337.3	332.2	330.8
47.5°	327.2	324.9	317.9	312.4	308.7
50°	306.0	304.1	297.7	291.2	288.5
52.5°	285.2	282.9	276.0	270.5	266.8
55°	263.1	261.7	255.3	249.7	247.0
57.5°	242.4	241.0	234.5	229.0	226.2
60°	220.7	218.4	212.4	208.3	206.0
62.5°	199.5	197.7	191.2	187.5	185.2
65°	178.3	176.0	171.4	166.8	164.5
67.5°	156.7	154.8	150.2	145.6	145.1
70°	136.9	133.6	129.9	126.3	124.9
72.5°	115.7	112.4	109.7	106.9	105.5
75°	94.9	92.6	90.3	88.5	88.0
77.5°	74.6	73.7	71.4	71.0	69.6
80°	56.7	55.3	54.4	53.5	53.0
82.5°	39.2	38.7	38.7	38.2	37.8
85°	24.9	24.9	24.0	24.0	23.5
87.5°	12.0	11.5	11.1	11.1	11.1
90°	1.2	9.3	20.9	23.2	24.4
92.5°	16.3	89.4	455.2	150.4	105.7
95°	38.3	120.8	946.4	468.6	283.3
97.5°	63.9	133.5	1012.5	956.8	680.4
100°	88.2	151.0	933.6	1323.8	1064.8
102.5°	111.5	171.9	834.9	1553.6	1399.2
105°	135.9	196.8	761.7	1640.2	1633.8
107.5°	162.6	222.4	714.1	1614.0	1745.2
110°	189.3	247.9	692.1	1521.2	1747.6

TEST NUMBER: P1001195

CATALOG NUMBER: SA4XXDIP-B350D1205UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.8	273.5	681.6	1407.4	1679.1
115°	239.2	300.2	679.3	1305.2	1568.7
117.5°	264.7	325.2	678.1	1225.0	1460.8
120°	290.3	349.6	678.1	1171.0	1372.5
122.5°	313.5	373.3	677.0	1135.6	1302.8
125°	333.3	396.0	675.8	1110.6	1251.7
127.5°	351.8	416.8	673.5	1086.8	1219.2
130°	366.9	437.2	672.3	1058.4	1191.4
132.5°	382.0	454.6	671.2	1024.8	1160.0
135°	396.0	471.4	670.0	985.8	1119.4
137.5°	409.9	486.0	670.0	944.0	1071.8
140°	425.0	499.3	668.8	903.4	1019.5
142.5°	441.2	511.5	668.8	865.6	963.8
145°	456.3	522.6	666.5	831.4	913.8
147.5°	473.8	533.0	663.0	803.0	867.4
150°	490.0	542.8	659.5	776.8	829.1
152.5°	505.1	552.2	653.7	754.8	794.2
155°	519.0	560.3	647.9	733.8	765.2
157.5°	533.0	567.8	642.1	714.1	738.5
160°	545.8	574.2	635.2	694.4	714.1
162.5°	557.4	579.4	628.2	675.2	690.9
165°	565.5	582.9	621.2	657.8	667.7
167.5°	574.8	585.8	614.3	642.8	649.1
170°	580.6	588.2	607.3	627.6	631.7
172.5°	586.4	589.8	600.3	614.2	614.3
175°	589.9	591.0	595.7	603.8	601.5
177.5°	592.2	591.0	592.2	596.2	592.2
180°	591.0	591.0	591.0	591.0	591.0

(END OF REPORT)