

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001180

Luminaire Tested: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001180
REPORT IS A COMBINATION OF REPORTS P995796 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-D_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6175.0 lumens
Efficiency: N/A
Efficacy: 128.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001180

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001180

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	29	29	29	21		
1	91	87	83	79	80	77	73	70	58	56	54	41	40	38	25	25	24	17		
2	82	75	69	64	73	67	62	57	51	47	44	36	34	32	22	21	20	14		
3	75	66	59	53	66	58	52	48	44	40	37	31	29	27	19	18	17	11		
4	68	58	50	45	60	52	45	40	39	35	31	28	25	23	17	15	14	10		
5	63	51	44	38	55	46	39	34	35	30	27	25	22	19	15	14	12	8		
6	58	46	38	33	51	41	34	29	31	26	23	22	19	17	14	12	11	7		
7	53	41	34	28	47	37	30	25	28	23	20	20	17	15	13	11	9	6		
8	49	37	30	25	43	33	27	22	25	21	18	18	15	13	11	10	8	6		
9	45	34	27	22	40	30	24	20	23	19	16	17	14	11	11	9	7	5		
10	42	31	24	19	37	28	21	17	21	17	14	15	12	10	10	8	7	5		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3337	3337	3337
5°	3346	3249	3255
10°	3324	3186	3176
15°	3293	3114	3087
20°	3246	3036	3001
25°	3195	2950	2907
30°	3138	2865	2813
35°	3075	2778	2728
40°	3024	2695	2640
45°	2949	2616	2563
50°	2884	2527	2481
55°	2818	2441	2386
60°	2715	2335	2298
65°	2600	2220	2192
70°	2463	2088	2069
75°	2271	1942	1952
80°	2052	1793	1828
85°	1768	1643	1729

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 3523 cd/sqm

TEST NUMBER: P1001180

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.8	0.6
10°-20°	111.1	1.8
20°-30°	168.0	2.7
30°-40°	203.2	3.3
40°-50°	214.8	3.5
50°-60°	202.2	3.3
60°-70°	167.7	2.7
70°-80°	117.7	1.9
80°-90°	69.6	1.1
90°-100°	90.7	1.5
100°-110°	366.7	5.9
110°-120°	664.0	10.8
120°-130°	829.1	13.4
130°-140°	879.9	14.2
140°-150°	819.3	13.3
150°-160°	659.9	10.7
160°-170°	425.6	6.9
170°-180°	146.7	2.4
0°-30°	317.8	5.1
0°-40°	521.0	8.4
0°-60°	938.0	15.2
0°-90°	1293.0	20.9
90°-120°	1121.5	18.2
90°-150°	3649.8	59.1
90°-180°	4882.0	79.1
0°-180°	6175.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	410	408	405	409	408	39
15°	393	393	392	396	395	111
25°	359	362	363	368	369	165
35°	314	320	324	331	332	197
45°	262	271	280	287	290	203
55°	205	215	229	238	240	183
65°	142	157	172	184	187	141
75°	79	96	115	128	132	84
85°	24	44	64	78	82	25
90°	11	42	71	91	97	8
95°	70	45	65	84	90	83
105°	352	368	390	412	374	368
115°	652	659	673	685	688	642
125°	914	918	927	939	943	816
135°	1132	1131	1139	1149	1154	873
145°	1305	1308	1308	1312	1316	816
155°	1431	1432	1428	1433	1429	660
165°	1509	1503	1503	1512	1502	426
175°	1544	1537	1538	1548	1534	147
180°	1544	1544	1544	1544	1544	

TEST NUMBER: P1001180

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	409.2	409.2	409.2	409.2	409.2
2.5°	411.0	409.6	406.0	409.2	408.7
5°	409.6	408.2	405.0	408.7	408.2
7.5°	406.9	406.0	403.2	407.3	406.9
10°	403.2	402.7	400.5	404.6	404.1
12.5°	398.2	398.2	396.8	400.5	400.5
15°	392.7	393.1	391.8	395.9	395.4
17.5°	385.3	386.7	386.3	390.4	389.9
20°	377.5	378.9	379.4	384.0	384.0
22.5°	368.8	370.7	371.6	376.2	377.1
25°	359.2	362.0	363.3	368.4	368.8
27.5°	348.7	352.8	354.6	359.2	359.7
30°	338.1	341.8	345.0	350.1	351.0
32.5°	326.7	331.3	334.9	340.9	341.8
35°	314.3	319.8	324.4	330.8	332.2
37.5°	301.9	308.4	313.9	320.3	321.6
40°	290.0	296.0	302.4	309.3	311.1
42.5°	276.3	283.2	290.9	298.7	300.1
45°	262.1	270.8	279.5	287.3	289.6
47.5°	248.8	257.5	267.6	275.4	278.1
50°	234.1	244.2	254.3	263.5	266.2
52.5°	219.5	229.6	241.5	250.6	253.4
55°	205.3	214.9	228.6	237.8	240.5
57.5°	189.2	201.1	214.4	225.4	227.7
60°	173.7	185.6	200.7	211.2	214.9
62.5°	158.5	171.8	186.9	197.5	201.1
65°	142.0	156.7	172.3	183.7	187.4
67.5°	126.5	142.0	158.5	170.0	173.7
70°	110.4	126.0	143.4	155.8	159.0
72.5°	94.8	110.9	129.7	141.6	145.2
75°	78.8	95.8	115.0	127.8	132.0
77.5°	63.7	81.6	101.7	114.5	119.1
80°	49.9	68.3	88.4	102.2	105.8
82.5°	36.2	55.4	75.6	89.8	93.9
85°	24.3	43.5	64.1	77.9	82.5
87.5°	15.1	33.9	54.1	67.4	71.5
90°	10.8	41.9	70.8	90.9	96.9
92.5°	24.2	37.9	66.8	86.6	90.3
95°	69.5	45.3	65.3	84.5	89.9
97.5°	126.7	165.4	63.0	80.7	85.9
100°	194.4	227.1	85.6	78.4	82.7
102.5°	270.6	294.5	325.8	77.9	81.6
105°	351.6	367.8	390.4	412.3	374.5
107.5°	426.7	438.0	462.0	479.3	487.1
110°	502.5	512.4	535.3	548.2	555.3

TEST NUMBER: P1001180

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	575.9	588.3	605.7	614.7	623.0
115°	651.6	659.3	672.7	685.1	688.3
117.5°	719.7	727.1	744.3	752.8	756.4
120°	788.6	794.6	806.8	818.2	819.6
122.5°	853.3	855.6	870.3	880.5	881.4
125°	913.9	918.2	927.3	939.4	943.4
127.5°	972.8	973.6	988.5	995.6	997.6
130°	1029.0	1029.7	1040.4	1049.9	1052.6
132.5°	1081.0	1082.8	1092.9	1101.8	1103.5
135°	1132.4	1131.3	1139.1	1148.8	1153.8
137.5°	1178.6	1178.2	1185.8	1195.0	1196.1
140°	1223.6	1225.5	1228.3	1237.7	1241.2
142.5°	1263.6	1268.3	1268.9	1276.2	1278.1
145°	1305.2	1308.2	1308.2	1312.0	1316.2
147.5°	1337.5	1344.0	1342.8	1344.5	1347.4
150°	1373.3	1377.5	1376.3	1376.3	1377.5
152.5°	1402.9	1406.3	1404.0	1406.3	1405.2
155°	1430.6	1431.7	1428.3	1432.9	1429.4
157.5°	1454.8	1454.8	1450.2	1456.0	1450.2
160°	1475.6	1472.1	1471.0	1477.9	1471.0
162.5°	1494.1	1489.5	1488.3	1495.2	1487.1
165°	1509.1	1503.3	1503.3	1512.5	1502.2
167.5°	1521.8	1516.0	1514.9	1525.2	1513.7
170°	1532.2	1525.2	1526.4	1535.6	1524.1
172.5°	1539.1	1532.2	1533.3	1542.6	1529.9
175°	1543.7	1536.8	1537.9	1548.3	1534.5
177.5°	1547.2	1539.1	1541.4	1550.6	1536.8
180°	1543.7	1543.7	1543.7	1543.7	1543.7

(END OF REPORT)