

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001182

Luminaire Tested: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001182
REPORT IS A COMBINATION OF REPORTS P995798 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6229.0 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001182

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001182

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32			24
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27			20
2	84	76	71	66	74	68	63	59	52	49	46	38	36	34	25	24	22			17
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	20	19			14
4	70	59	52	46	62	53	47	42	41	36	33	30	27	25	19	18	16			12
5	64	53	45	39	56	47	40	35	37	32	28	27	24	21	18	16	14			10
6	59	47	39	34	52	42	35	31	33	28	24	24	21	18	16	14	13			9
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	13	11			8
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10			7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9			7
10	43	32	25	20	38	29	22	18	22	18	15	17	14	11	11	9	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4648	4648	4648
5°	4652	4514	4520
10°	4612	4389	4359
15°	4546	4240	4176
20°	4461	4079	3988
25°	4367	3909	3784
30°	4252	3724	3561
35°	4134	3536	3346
40°	4010	3333	3116
45°	3879	3129	2902
50°	3736	2932	2665
55°	3580	2702	2429
60°	3420	2450	2184
65°	3238	2189	1907
70°	3025	1876	1611
75°	2712	1511	1289
80°	2311	1093	907
85°	1797	607	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3879 cd/sqm

TEST NUMBER: P1001182

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	0.9
10°-20°	151.4	2.4
20°-30°	222.8	3.6
30°-40°	258.9	4.2
40°-50°	258.9	4.2
50°-60°	226.5	3.6
60°-70°	168.1	2.7
70°-80°	95.4	1.5
80°-90°	30.5	0.5
90°-100°	51.1	0.8
100°-110°	336.5	5.4
110°-120°	642.5	10.3
120°-130°	815.7	13.1
130°-140°	872.6	14.0
140°-150°	815.9	13.1
150°-160°	658.0	10.6
160°-170°	424.3	6.8
170°-180°	146.2	2.3
0°-30°	427.8	6.9
0°-40°	686.8	11.0
0°-60°	1172.2	18.8
0°-90°	1466.2	23.5
90°-120°	1030.1	16.5
90°-150°	3534.3	56.7
90°-180°	4763.0	76.5
0°-180°	6229.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	570	570	570	570	570	
5°	570	568	563	568	567	54
15°	542	540	534	536	535	153
25°	491	488	481	482	480	226
35°	422	419	413	410	407	264
45°	345	342	334	329	328	266
55°	261	259	253	248	245	234
65°	177	174	170	165	163	175
75°	94	92	90	88	87	100
85°	25	25	24	24	23	27
90°	4	16	25	32	34	5
95°	63	24	25	32	33	78
105°	346	353	359	370	328	363
115°	647	650	649	652	652	637
125°	910	914	912	915	916	812
135°	1128	1127	1132	1134	1136	869
145°	1301	1304	1304	1306	1308	813
155°	1426	1428	1424	1429	1425	658
165°	1505	1499	1499	1508	1498	425
175°	1539	1532	1533	1544	1530	147
180°	1539	1539	1539	1539	1539	

TEST NUMBER: P1001182

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.0	570.0	570.0	570.0	570.0
2.5°	571.8	570.5	565.4	570.0	569.5
5°	569.5	567.7	562.7	567.7	566.8
7.5°	565.4	563.6	558.1	562.2	561.8
10°	559.5	557.7	551.7	555.4	554.5
12.5°	551.7	549.9	543.5	547.6	546.2
15°	542.1	540.3	533.5	536.2	534.8
17.5°	531.2	528.9	522.5	524.3	523.4
20°	518.8	516.6	509.7	511.1	510.2
22.5°	505.6	502.4	495.5	498.3	496.5
25°	491.0	487.8	481.4	481.8	480.0
27.5°	474.5	471.3	465.4	464.5	462.2
30°	458.1	454.4	448.5	446.7	444.4
32.5°	440.7	437.5	431.1	428.9	426.6
35°	422.5	419.3	412.9	409.7	407.4
37.5°	403.3	400.5	393.7	390.5	387.3
40°	384.6	380.9	374.1	369.5	367.2
42.5°	364.5	362.6	354.9	349.4	348.0
45°	344.8	341.6	334.3	329.3	327.9
47.5°	324.3	322.0	315.1	309.7	306.0
50°	303.3	301.4	295.0	288.7	285.9
52.5°	282.7	280.4	273.6	268.1	264.4
55°	260.8	259.4	253.0	247.5	244.8
57.5°	240.2	238.9	232.5	227.0	224.3
60°	218.8	216.5	210.6	206.4	204.2
62.5°	197.8	195.9	189.5	185.9	183.6
65°	176.8	174.5	169.9	165.3	163.1
67.5°	155.3	153.5	148.9	144.3	143.9
70°	135.6	132.5	128.8	125.1	123.8
72.5°	114.6	111.4	108.7	106.0	104.6
75°	94.1	91.8	89.5	87.7	87.2
77.5°	74.0	73.1	70.8	70.3	69.0
80°	56.2	54.8	53.9	53.0	52.5
82.5°	38.8	38.4	38.4	37.9	37.5
85°	24.7	24.7	23.7	23.7	23.3
87.5°	11.9	11.4	11.0	11.0	11.0
90°	3.5	16.1	25.3	32.2	34.5
92.5°	17.3	15.0	24.2	31.1	31.1
95°	63.3	24.2	25.3	32.2	33.4
97.5°	120.9	146.2	25.3	31.1	32.2
100°	188.8	209.5	50.7	31.1	32.2
102.5°	264.8	278.6	292.4	33.4	33.4
105°	346.5	353.4	359.2	369.5	328.1
107.5°	421.4	424.8	432.9	438.6	443.2
110°	497.3	500.8	507.7	510.0	513.4

TEST NUMBER: P1001182

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	571.0	577.9	580.2	579.1	583.7
115°	647.0	650.4	649.3	651.6	651.6
117.5°	714.9	719.5	723.0	721.8	721.8
120°	784.0	788.6	787.4	789.7	787.4
122.5°	848.5	850.8	853.1	854.2	851.9
125°	909.5	914.1	911.8	915.2	916.4
127.5°	968.2	969.3	975.1	973.9	972.8
130°	1024.6	1025.7	1029.2	1030.4	1030.4
132.5°	1076.4	1078.7	1083.3	1084.5	1083.3
135°	1128.2	1127.1	1131.7	1134.0	1136.3
137.5°	1174.3	1174.3	1180.0	1182.3	1181.2
140°	1219.2	1221.5	1223.8	1227.2	1228.4
142.5°	1259.4	1264.1	1265.2	1267.5	1267.5
145°	1300.9	1304.3	1304.3	1305.5	1307.8
147.5°	1333.1	1340.0	1338.9	1340.0	1341.2
150°	1368.8	1373.4	1372.3	1372.3	1373.4
152.5°	1398.7	1402.2	1399.9	1402.2	1401.1
155°	1426.4	1427.5	1424.1	1428.7	1425.2
157.5°	1450.6	1450.6	1445.9	1451.7	1445.9
160°	1471.3	1467.8	1466.7	1473.6	1466.7
162.5°	1489.7	1485.1	1483.9	1490.8	1482.8
165°	1504.7	1498.9	1498.9	1508.1	1497.8
167.5°	1517.3	1511.6	1510.4	1520.8	1509.3
170°	1527.7	1520.8	1521.9	1531.1	1519.6
172.5°	1534.6	1527.7	1528.8	1538.0	1525.4
175°	1539.2	1532.3	1533.4	1543.8	1530.0
177.5°	1542.7	1534.6	1536.9	1546.1	1532.3
180°	1539.2	1539.2	1539.2	1539.2	1539.2

(END OF REPORT)