

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001241

Luminaire Tested: SA4XXDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001241
REPORT IS A COMBINATION OF REPORTS P995859 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2948.0 lumens
Efficiency: N/A
Efficacy: 132.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001241

CATALOG NUMBER: SA4XXDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001241

CATALOG NUMBER: SA4XXDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	52	45	40	45	39	35	38	34	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4690	4690	4690
5°	4693	4555	4560
10°	4654	4428	4397
15°	4587	4278	4213
20°	4502	4115	4023
25°	4405	3944	3818
30°	4290	3758	3593
35°	4170	3567	3375
40°	4045	3363	3144
45°	3914	3157	2928
50°	3770	2959	2689
55°	3612	2726	2451
60°	3450	2471	2203
65°	3265	2209	1924
70°	3054	1892	1625
75°	2735	1525	1301
80°	2332	1103	916
85°	1812	615	493

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3914 cd/sqm

TEST NUMBER: P1001241

CATALOG NUMBER: SA4XXDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	1.8
10°-20°	152.7	5.2
20°-30°	224.7	7.6
30°-40°	261.2	8.9
40°-50°	261.2	8.9
50°-60°	228.5	7.7
60°-70°	169.6	5.8
70°-80°	96.2	3.3
80°-90°	28.6	1.0
90°-100°	15.8	0.5
100°-110°	103.9	3.5
110°-120°	198.4	6.7
120°-130°	251.9	8.5
130°-140°	269.5	9.1
140°-150°	252.0	8.5
150°-160°	203.2	6.9
160°-170°	131.1	4.4
170°-180°	45.2	1.5
0°-30°	431.6	14.6
0°-40°	692.9	23.5
0°-60°	1182.6	40.1
0°-90°	1477.0	50.1
90°-120°	318.1	10.8
90°-150°	1091.6	37.0
90°-180°	1471.0	49.9
0°-180°	2948.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	575	575	575	575	575	
5°	575	573	568	573	572	55
15°	547	545	538	541	540	154
25°	495	492	486	486	484	228
35°	426	423	416	413	411	267
45°	348	345	337	332	331	268
55°	263	262	255	250	247	236
65°	178	176	171	167	164	176
75°	95	93	90	88	88	101
85°	25	25	24	24	24	27
90°	1	5	8	10	11	3
95°	20	8	8	10	10	24
105°	107	109	111	114	101	112
115°	200	201	200	201	201	197
125°	281	282	282	283	283	251
135°	348	348	350	350	351	269
145°	402	403	403	403	404	251
155°	440	441	440	441	440	203
165°	465	463	463	466	463	131
175°	475	473	474	477	472	45
180°	475	475	475	475	475	

TEST NUMBER: P1001241

CATALOG NUMBER: SA4XXDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	575.1	575.1	575.1	575.1	575.1
2.5°	576.9	575.5	570.5	575.1	574.6
5°	574.6	572.8	567.7	572.8	571.8
7.5°	570.5	568.6	563.1	567.2	566.8
10°	564.5	562.6	556.6	560.3	559.4
12.5°	556.6	554.8	548.3	552.5	551.1
15°	547.0	545.1	538.2	541.0	539.6
17.5°	535.9	533.6	527.1	529.0	528.1
20°	523.5	521.1	514.2	515.6	514.7
22.5°	510.1	506.9	500.0	502.7	500.9
25°	495.3	492.1	485.7	486.1	484.3
27.5°	478.8	475.5	469.5	468.6	466.3
30°	462.2	458.5	452.5	450.6	448.3
32.5°	444.7	441.4	435.0	432.7	430.4
35°	426.2	423.0	416.5	413.3	411.0
37.5°	406.9	404.1	397.2	394.0	390.7
40°	388.0	384.3	377.4	372.8	370.5
42.5°	367.7	365.9	358.0	352.5	351.1
45°	347.9	344.7	337.3	332.2	330.8
47.5°	327.2	324.9	317.9	312.4	308.7
50°	306.0	304.1	297.7	291.2	288.5
52.5°	285.2	282.9	276.0	270.5	266.8
55°	263.1	261.7	255.3	249.7	247.0
57.5°	242.4	241.0	234.5	229.0	226.2
60°	220.7	218.4	212.4	208.3	206.0
62.5°	199.5	197.7	191.2	187.5	185.2
65°	178.3	176.0	171.4	166.8	164.5
67.5°	156.7	154.8	150.2	145.6	145.1
70°	136.9	133.6	129.9	126.3	124.9
72.5°	115.7	112.4	109.7	106.9	105.5
75°	94.9	92.6	90.3	88.5	88.0
77.5°	74.6	73.7	71.4	71.0	69.6
80°	56.7	55.3	54.4	53.5	53.0
82.5°	39.2	38.7	38.7	38.2	37.8
85°	24.9	24.9	24.0	24.0	23.5
87.5°	12.0	11.5	11.1	11.1	11.1
90°	1.1	5.0	7.8	10.0	10.7
92.5°	5.3	4.6	7.5	9.6	9.6
95°	19.6	7.5	7.8	10.0	10.3
97.5°	37.3	45.2	7.8	9.6	10.0
100°	58.3	64.7	15.6	9.6	10.0
102.5°	81.8	86.0	90.3	10.3	10.3
105°	107.0	109.2	110.9	114.1	101.3
107.5°	130.1	131.2	133.7	135.5	136.9
110°	153.6	154.7	156.8	157.5	158.6

TEST NUMBER: P1001241

CATALOG NUMBER: SA4XXDIP-B350D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	178.5	179.2	178.8	180.3
115°	199.8	200.9	200.5	201.2	201.2
117.5°	220.8	222.2	223.3	222.9	222.9
120°	242.1	243.6	243.2	243.9	243.2
122.5°	262.1	262.8	263.5	263.8	263.1
125°	280.9	282.3	281.6	282.7	283.0
127.5°	299.0	299.4	301.2	300.8	300.5
130°	316.5	316.8	317.9	318.2	318.2
132.5°	332.5	333.2	334.6	334.9	334.6
135°	348.5	348.1	349.5	350.2	350.9
137.5°	362.7	362.7	364.5	365.2	364.8
140°	376.5	377.3	378.0	379.0	379.4
142.5°	389.0	390.4	390.8	391.5	391.5
145°	401.8	402.9	402.9	403.2	403.9
147.5°	411.7	413.9	413.5	413.9	414.2
150°	422.8	424.2	423.8	423.8	424.2
152.5°	432.0	433.1	432.4	433.1	432.7
155°	440.5	440.9	439.8	441.3	440.2
157.5°	448.0	448.0	446.6	448.4	446.6
160°	454.4	453.3	453.0	455.1	453.0
162.5°	460.1	458.7	458.3	460.5	458.0
165°	464.7	462.9	462.9	465.8	462.6
167.5°	468.6	466.9	466.5	469.7	466.1
170°	471.8	469.7	470.1	472.9	469.3
172.5°	474.0	471.8	472.2	475.0	471.1
175°	475.4	473.3	473.6	476.8	472.5
177.5°	476.5	474.0	474.7	477.5	473.3
180°	475.4	475.4	475.4	475.4	475.4

(END OF REPORT)