

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001297

Luminaire Tested: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001297
REPORT IS A COMBINATION OF REPORTS P995916 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-D_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3748.0 lumens
Efficiency: N/A
Efficacy: 132.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001297

CATALOG NUMBER: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001297

CATALOG NUMBER: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42
1	94	89	85	81	84	80	77	74	64	62	60	50	48	46	36	35	34
2	85	77	71	66	76	70	65	60	56	52	49	43	40	38	31	29	28
3	77	68	60	54	69	61	55	50	49	44	41	38	35	32	27	25	23
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	22	20
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15
7	55	43	35	29	49	39	32	27	31	26	22	24	21	18	18	15	13
8	51	38	31	26	46	35	28	24	28	23	20	22	18	16	16	14	12
9	47	35	28	23	42	32	25	21	26	21	17	20	17	14	15	12	11
10	44	32	25	20	40	29	23	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3337	3337	3337
5°	3346	3249	3255
10°	3324	3186	3176
15°	3293	3114	3087
20°	3246	3036	3001
25°	3195	2950	2907
30°	3138	2865	2813
35°	3075	2778	2728
40°	3024	2695	2640
45°	2949	2616	2563
50°	2884	2527	2481
55°	2818	2441	2386
60°	2715	2335	2298
65°	2600	2220	2192
70°	2463	2088	2069
75°	2271	1942	1952
80°	2052	1793	1828
85°	1768	1643	1729

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2949 cd/sqm

TEST NUMBER: P1001297

CATALOG NUMBER: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.8	1.0
10°-20°	111.1	3.0
20°-30°	168.0	4.5
30°-40°	203.2	5.4
40°-50°	214.8	5.7
50°-60°	202.2	5.4
60°-70°	167.7	4.5
70°-80°	117.7	3.1
80°-90°	67.9	1.8
90°-100°	64.7	1.7
100°-110°	195.4	5.2
110°-120°	336.9	9.0
120°-130°	413.8	11.0
130°-140°	435.6	11.6
140°-150°	403.8	10.8
150°-160°	324.9	8.7
160°-170°	209.5	5.6
170°-180°	72.2	1.9
0°-30°	317.8	8.5
0°-40°	521.0	13.9
0°-60°	938.0	25.0
0°-90°	1291.4	34.5
90°-120°	596.9	15.9
90°-150°	1850.0	49.4
90°-180°	2457.0	65.6
0°-180°	3748.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	410	408	405	409	408	39
15°	393	393	392	396	395	111
25°	359	362	363	368	369	165
35°	314	320	324	331	332	197
45°	262	271	280	287	290	203
55°	205	215	229	238	240	183
65°	142	157	172	184	187	141
75°	79	96	115	128	132	84
85°	24	44	64	78	82	25
90°	9	34	58	74	79	7
95°	37	33	52	68	73	43
105°	175	188	208	224	207	184
115°	322	328	342	353	356	317
125°	451	453	463	473	477	403
135°	558	557	563	571	575	430
145°	643	644	644	647	650	402
155°	704	705	703	705	704	325
165°	743	740	740	745	739	210
175°	760	756	757	762	755	72
180°	760	760	760	760	760	

TEST NUMBER: P1001297

CATALOG NUMBER: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	409.2	409.2	409.2	409.2	409.2
2.5°	411.0	409.6	406.0	409.2	408.7
5°	409.6	408.2	405.0	408.7	408.2
7.5°	406.9	406.0	403.2	407.3	406.9
10°	403.2	402.7	400.5	404.6	404.1
12.5°	398.2	398.2	396.8	400.5	400.5
15°	392.7	393.1	391.8	395.9	395.4
17.5°	385.3	386.7	386.3	390.4	389.9
20°	377.5	378.9	379.4	384.0	384.0
22.5°	368.8	370.7	371.6	376.2	377.1
25°	359.2	362.0	363.3	368.4	368.8
27.5°	348.7	352.8	354.6	359.2	359.7
30°	338.1	341.8	345.0	350.1	351.0
32.5°	326.7	331.3	334.9	340.9	341.8
35°	314.3	319.8	324.4	330.8	332.2
37.5°	301.9	308.4	313.9	320.3	321.6
40°	290.0	296.0	302.4	309.3	311.1
42.5°	276.3	283.2	290.9	298.7	300.1
45°	262.1	270.8	279.5	287.3	289.6
47.5°	248.8	257.5	267.6	275.4	278.1
50°	234.1	244.2	254.3	263.5	266.2
52.5°	219.5	229.6	241.5	250.6	253.4
55°	205.3	214.9	228.6	237.8	240.5
57.5°	189.2	201.1	214.4	225.4	227.7
60°	173.7	185.6	200.7	211.2	214.9
62.5°	158.5	171.8	186.9	197.5	201.1
65°	142.0	156.7	172.3	183.7	187.4
67.5°	126.5	142.0	158.5	170.0	173.7
70°	110.4	126.0	143.4	155.8	159.0
72.5°	94.8	110.9	129.7	141.6	145.2
75°	78.8	95.8	115.0	127.8	132.0
77.5°	63.7	81.6	101.7	114.5	119.1
80°	49.9	68.3	88.4	102.2	105.8
82.5°	36.2	55.4	75.6	89.8	93.9
85°	24.3	43.5	64.1	77.9	82.5
87.5°	15.1	33.9	54.1	67.4	71.5
90°	9.0	33.7	57.9	74.5	79.4
92.5°	15.4	30.3	54.5	70.7	74.4
95°	37.3	33.0	52.4	68.1	72.9
97.5°	65.2	91.0	50.1	64.8	69.5
100°	98.2	120.4	59.8	62.5	66.3
102.5°	135.7	152.6	176.9	60.9	64.6
105°	175.2	187.8	207.5	224.1	207.4
107.5°	212.1	221.6	241.6	255.9	261.4
110°	249.2	257.3	276.8	288.5	293.8

TEST NUMBER: P1001297

CATALOG NUMBER: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.1	294.0	310.3	319.8	325.8
115°	322.1	328.0	342.1	353.3	356.5
117.5°	355.7	360.7	376.1	385.3	388.9
120°	389.4	393.0	405.8	416.0	418.6
122.5°	421.2	422.3	435.9	445.5	447.6
125°	450.8	452.7	462.9	473.4	476.7
127.5°	479.8	480.0	491.9	499.6	502.3
130°	507.2	507.3	516.3	525.2	527.9
132.5°	532.8	533.5	541.2	549.6	551.8
135°	557.9	557.3	562.8	571.3	575.2
137.5°	580.6	580.2	584.9	592.9	594.6
140°	602.8	603.5	605.1	612.8	615.7
142.5°	622.3	624.6	624.6	630.8	632.7
145°	642.8	644.0	644.0	647.2	650.3
147.5°	658.7	661.6	661.0	662.1	664.5
150°	676.3	678.1	677.5	677.5	678.1
152.5°	690.6	692.3	691.1	692.3	691.7
155°	704.2	704.8	703.1	705.3	703.6
157.5°	716.1	716.1	713.9	716.7	713.9
160°	726.4	724.7	724.1	727.5	724.1
162.5°	735.5	733.2	732.6	736.0	732.1
165°	742.9	740.0	740.0	744.6	739.4
167.5°	749.1	746.3	745.7	750.8	745.1
170°	754.2	750.8	751.4	755.9	750.2
172.5°	757.6	754.2	754.8	759.3	753.1
175°	759.9	756.5	757.1	762.2	755.4
177.5°	761.6	757.6	758.8	763.3	756.5
180°	759.9	759.9	759.9	759.9	759.9

(END OF REPORT)