

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001360

Luminaire Tested: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001360
REPORT IS A COMBINATION OF REPORTS P995979 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4637.0 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001360

CATALOG NUMBER: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001360

CATALOG NUMBER: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33
2	85	78	72	67	76	70	65	61	56	53	50	43	41	39	31	29	28
3	78	69	61	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4690	4690	4690
5°	4693	4555	4560
10°	4654	4428	4397
15°	4587	4278	4213
20°	4502	4115	4023
25°	4405	3944	3818
30°	4290	3758	3593
35°	4170	3567	3375
40°	4045	3363	3144
45°	3914	3157	2928
50°	3770	2959	2689
55°	3612	2726	2451
60°	3450	2471	2203
65°	3265	2209	1924
70°	3054	1892	1625
75°	2735	1525	1301
80°	2332	1103	916
85°	1812	615	493

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3914 cd/sqm

TEST NUMBER: P1001360

CATALOG NUMBER: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	1.2
10°-20°	152.7	3.3
20°-30°	224.7	4.8
30°-40°	261.2	5.6
40°-50°	261.2	5.6
50°-60°	228.5	4.9
60°-70°	169.6	3.7
70°-80°	96.2	2.1
80°-90°	29.7	0.6
90°-100°	33.9	0.7
100°-110°	223.2	4.8
110°-120°	426.1	9.2
120°-130°	541.0	11.7
130°-140°	578.7	12.5
140°-150°	541.2	11.7
150°-160°	436.4	9.4
160°-170°	281.4	6.1
170°-180°	97.0	2.1
0°-30°	431.6	9.3
0°-40°	692.9	14.9
0°-60°	1182.6	25.5
0°-90°	1478.1	31.9
90°-120°	683.2	14.7
90°-150°	2344.0	50.6
90°-180°	3159.0	68.1
0°-180°	4637.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	575	575	575	575	575	
5°	575	573	568	573	572	55
15°	547	545	538	541	540	154
25°	495	492	486	486	484	228
35°	426	423	416	413	411	267
45°	348	345	337	332	331	268
55°	263	262	255	250	247	236
65°	178	176	171	167	164	176
75°	95	93	90	88	88	101
85°	25	25	24	24	24	27
90°	2	11	17	21	23	4
95°	42	16	17	21	22	52
105°	230	234	238	245	218	241
115°	429	431	431	432	432	422
125°	603	606	605	607	608	539
135°	748	748	751	752	754	577
145°	863	865	865	866	867	539
155°	946	947	944	948	945	436
165°	998	994	994	1000	993	282
175°	1021	1016	1017	1024	1015	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1001360

CATALOG NUMBER: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	575.1	575.1	575.1	575.1	575.1
2.5°	576.9	575.5	570.5	575.1	574.6
5°	574.6	572.8	567.7	572.8	571.8
7.5°	570.5	568.6	563.1	567.2	566.8
10°	564.5	562.6	556.6	560.3	559.4
12.5°	556.6	554.8	548.3	552.5	551.1
15°	547.0	545.1	538.2	541.0	539.6
17.5°	535.9	533.6	527.1	529.0	528.1
20°	523.5	521.1	514.2	515.6	514.7
22.5°	510.1	506.9	500.0	502.7	500.9
25°	495.3	492.1	485.7	486.1	484.3
27.5°	478.8	475.5	469.5	468.6	466.3
30°	462.2	458.5	452.5	450.6	448.3
32.5°	444.7	441.4	435.0	432.7	430.4
35°	426.2	423.0	416.5	413.3	411.0
37.5°	406.9	404.1	397.2	394.0	390.7
40°	388.0	384.3	377.4	372.8	370.5
42.5°	367.7	365.9	358.0	352.5	351.1
45°	347.9	344.7	337.3	332.2	330.8
47.5°	327.2	324.9	317.9	312.4	308.7
50°	306.0	304.1	297.7	291.2	288.5
52.5°	285.2	282.9	276.0	270.5	266.8
55°	263.1	261.7	255.3	249.7	247.0
57.5°	242.4	241.0	234.5	229.0	226.2
60°	220.7	218.4	212.4	208.3	206.0
62.5°	199.5	197.7	191.2	187.5	185.2
65°	178.3	176.0	171.4	166.8	164.5
67.5°	156.7	154.8	150.2	145.6	145.1
70°	136.9	133.6	129.9	126.3	124.9
72.5°	115.7	112.4	109.7	106.9	105.5
75°	94.9	92.6	90.3	88.5	88.0
77.5°	74.6	73.7	71.4	71.0	69.6
80°	56.7	55.3	54.4	53.5	53.0
82.5°	39.2	38.7	38.7	38.2	37.8
85°	24.9	24.9	24.0	24.0	23.5
87.5°	12.0	11.5	11.1	11.1	11.1
90°	2.3	10.7	16.8	21.4	22.9
92.5°	11.5	9.9	16.0	20.6	20.6
95°	42.0	16.0	16.8	21.4	22.1
97.5°	80.2	97.0	16.8	20.6	21.4
100°	125.2	139.0	33.6	20.6	21.4
102.5°	175.6	184.8	193.9	22.1	22.1
105°	229.8	234.4	238.2	245.1	217.6
107.5°	279.5	281.7	287.1	290.9	294.0
110°	329.9	332.1	336.7	338.2	340.5

TEST NUMBER: P1001360

CATALOG NUMBER: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	378.7	383.3	384.8	384.1	387.1
115°	429.1	431.4	430.6	432.2	432.2
117.5°	474.2	477.2	479.5	478.7	478.7
120°	520.0	523.0	522.3	523.8	522.3
122.5°	562.7	564.3	565.8	566.5	565.0
125°	603.2	606.3	604.7	607.0	607.8
127.5°	642.1	642.9	646.7	646.0	645.2
130°	679.6	680.3	682.6	683.4	683.4
132.5°	713.9	715.4	718.5	719.3	718.5
135°	748.3	747.5	750.6	752.1	753.6
137.5°	778.8	778.8	782.6	784.2	783.4
140°	808.6	810.1	811.6	813.9	814.7
142.5°	835.3	838.4	839.1	840.7	840.7
145°	862.8	865.1	865.1	865.9	867.4
147.5°	884.2	888.8	888.0	888.8	889.5
150°	907.9	910.9	910.1	910.1	910.9
152.5°	927.7	930.0	928.5	930.0	929.2
155°	946.0	946.8	944.5	947.6	945.3
157.5°	962.1	962.1	959.0	962.8	959.0
160°	975.8	973.5	972.8	977.3	972.8
162.5°	988.0	985.0	984.2	988.8	983.4
165°	998.0	994.1	994.1	1000.2	993.4
167.5°	1006.3	1002.5	1001.8	1008.6	1001.0
170°	1013.2	1008.6	1009.4	1015.5	1007.9
172.5°	1017.8	1013.2	1014.0	1020.1	1011.7
175°	1020.9	1016.3	1017.0	1023.9	1014.7
177.5°	1023.1	1017.8	1019.3	1025.4	1016.3
180°	1020.9	1020.9	1020.9	1020.9	1020.9

(END OF REPORT)