

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001261

Luminaire Tested: SA4XXDIP-B350D365UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001261
REPORT IS A COMBINATION OF REPORTS P995880 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB35-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2809.7 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001261

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001261

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	49
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	46	44	42
3	82	72	65	59	75	67	61	55	57	53	48	49	45	42	40	38	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	23
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4708	4708	4708
5°	4712	4573	4579
10°	4673	4446	4415
15°	4606	4295	4230
20°	4520	4132	4039
25°	4424	3959	3834
30°	4307	3772	3608
35°	4187	3581	3389
40°	4062	3376	3157
45°	3930	3171	2940
50°	3784	2971	2699
55°	3627	2737	2461
60°	3464	2482	2212
65°	3278	2218	1932
70°	3065	1900	1631
75°	2746	1532	1307
80°	2340	1107	919
85°	1819	618	495

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3930 cd/sqm

TEST NUMBER: P1001261

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	1.9
10°-20°	153.3	5.5
20°-30°	225.7	8.0
30°-40°	262.3	9.3
40°-50°	262.3	9.3
50°-60°	229.4	8.2
60°-70°	170.3	6.1
70°-80°	96.6	3.4
80°-90°	28.4	1.0
90°-100°	135.1	4.8
100°-110°	274.7	9.8
110°-120°	244.9	8.7
120°-130°	205.7	7.3
130°-140°	171.6	6.1
140°-150°	131.1	4.7
150°-160°	92.1	3.3
160°-170°	54.2	1.9
170°-180°	17.6	0.6
0°-30°	433.4	15.4
0°-40°	695.7	24.8
0°-60°	1187.4	42.3
0°-90°	1482.7	52.8
90°-120°	654.6	23.3
90°-150°	1163.0	41.4
90°-180°	1327.0	47.2
0°-180°	2809.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	577	575	570	575	574	55
15°	549	547	540	543	542	155
25°	497	494	488	488	486	229
35°	428	425	418	415	413	268
45°	349	346	339	334	332	269
55°	264	263	256	251	248	237
65°	179	177	172	168	165	177
75°	95	93	91	89	88	101
85°	25	25	24	24	24	27
90°	0	3	6	7	8	2
95°	12	37	291	144	87	13
105°	42	61	234	505	503	45
115°	74	92	209	402	483	73
125°	102	122	208	342	385	91
135°	122	145	206	303	344	94
145°	140	161	205	256	281	88
155°	160	172	199	226	235	74
165°	174	179	191	202	205	49
175°	182	182	183	186	185	17
180°	182	182	182	182	182	

TEST NUMBER: P1001261

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	577.4	577.4	577.4	577.4	577.4
2.5°	579.2	577.9	572.8	577.4	576.9
5°	576.9	575.1	570.0	575.1	574.2
7.5°	572.8	570.9	565.4	569.5	569.1
10°	566.8	564.9	558.9	562.6	561.7
12.5°	558.9	557.0	550.6	554.7	553.3
15°	549.2	547.3	540.4	543.2	541.8
17.5°	538.1	535.8	529.3	531.1	530.2
20°	525.6	523.3	516.3	517.7	516.8
22.5°	512.2	508.9	502.0	504.8	502.9
25°	497.4	494.1	487.6	488.1	486.3
27.5°	480.7	477.5	471.4	470.5	468.2
30°	464.0	460.3	454.3	452.5	450.2
32.5°	446.5	443.2	436.7	434.4	432.1
35°	428.0	424.7	418.2	415.0	412.7
37.5°	408.5	405.8	398.8	395.6	392.3
40°	389.6	385.9	378.9	374.3	372.0
42.5°	369.2	367.3	359.5	353.9	352.5
45°	349.3	346.1	338.7	333.6	332.2
47.5°	328.5	326.2	319.2	313.7	310.0
50°	307.2	305.4	298.9	292.4	289.6
52.5°	286.4	284.1	277.1	271.6	267.9
55°	264.2	262.8	256.3	250.8	248.0
57.5°	243.4	242.0	235.5	229.9	227.2
60°	221.6	219.3	213.3	209.1	206.8
62.5°	200.3	198.5	192.0	188.3	186.0
65°	179.0	176.7	172.1	167.5	165.2
67.5°	157.3	155.5	150.8	146.2	145.7
70°	137.4	134.2	130.5	126.8	125.4
72.5°	116.1	112.9	110.1	107.3	105.9
75°	95.3	93.0	90.7	88.8	88.4
77.5°	75.0	74.0	71.7	71.2	69.9
80°	56.9	55.5	54.6	53.7	53.2
82.5°	39.3	38.9	38.9	38.4	37.9
85°	25.0	25.0	24.1	24.1	23.6
87.5°	12.0	11.6	11.1	11.1	11.1
90°	0.4	2.9	6.4	7.1	7.5
92.5°	5.0	27.5	140.0	46.2	32.5
95°	11.8	37.2	291.1	144.2	87.2
97.5°	19.6	41.1	311.5	294.4	209.3
100°	27.1	46.4	287.2	407.2	327.6
102.5°	34.3	52.8	256.8	478.0	430.5
105°	41.8	60.6	234.3	504.6	502.6
107.5°	50.0	68.4	219.7	496.5	536.9
110°	58.2	76.2	212.9	468.0	537.6

TEST NUMBER: P1001261

CATALOG NUMBER: SA4XXDIP-B350D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	66.1	84.1	209.7	433.0	516.5
115°	73.6	92.4	209.0	401.5	482.6
117.5°	81.4	100.0	208.6	376.9	449.4
120°	89.3	107.5	208.6	360.2	422.2
122.5°	96.4	114.8	208.3	349.4	400.8
125°	102.5	121.8	207.9	341.7	385.1
127.5°	108.2	128.2	207.2	334.4	375.1
130°	112.9	134.5	206.8	325.6	366.5
132.5°	117.5	139.8	206.5	315.2	356.9
135°	121.8	145.0	206.1	303.3	344.4
137.5°	126.1	149.5	206.1	290.4	329.7
140°	130.7	153.6	205.8	277.9	313.6
142.5°	135.7	157.4	205.8	266.4	296.5
145°	140.4	160.8	205.0	255.8	281.1
147.5°	145.7	164.0	204.0	247.0	266.8
150°	150.7	167.0	202.9	239.0	255.1
152.5°	155.4	169.9	201.1	232.2	244.3
155°	159.7	172.4	199.3	225.8	235.4
157.5°	164.0	174.6	197.5	219.7	227.2
160°	167.9	176.6	195.4	213.6	219.7
162.5°	171.5	178.2	193.3	207.8	212.5
165°	174.0	179.4	191.1	202.4	205.4
167.5°	176.8	180.2	189.0	197.8	199.7
170°	178.6	181.0	186.8	193.0	194.3
172.5°	180.4	181.4	184.7	189.0	189.0
175°	181.5	181.8	183.3	185.8	185.0
177.5°	182.2	181.8	182.2	183.4	182.2
180°	181.8	181.8	181.8	181.8	181.8

(END OF REPORT)