

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001361

Luminaire Tested: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001361
REPORT IS A COMBINATION OF REPORTS P995980 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4657.0 lumens
Efficiency: N/A
Efficacy: 136.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001361

CATALOG NUMBER: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1001361

CATALOG NUMBER: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33
2	85	78	72	67	76	70	65	61	56	53	50	43	41	38	31	29	28
3	78	69	61	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4708	4708	4708
5°	4712	4573	4579
10°	4673	4446	4415
15°	4606	4295	4230
20°	4520	4132	4039
25°	4424	3959	3834
30°	4307	3772	3608
35°	4187	3581	3389
40°	4062	3376	3157
45°	3930	3171	2940
50°	3784	2971	2699
55°	3627	2737	2461
60°	3464	2482	2212
65°	3278	2218	1932
70°	3065	1900	1631
75°	2746	1532	1307
80°	2340	1107	919
85°	1819	618	495

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3930 cd/sqm

TEST NUMBER: P1001361

CATALOG NUMBER: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	1.2
10°-20°	153.3	3.3
20°-30°	225.7	4.8
30°-40°	262.3	5.6
40°-50°	262.3	5.6
50°-60°	229.4	4.9
60°-70°	170.3	3.7
70°-80°	96.6	2.1
80°-90°	29.8	0.6
90°-100°	34.0	0.7
100°-110°	224.1	4.8
110°-120°	428.0	9.2
120°-130°	543.4	11.7
130°-140°	581.3	12.5
140°-150°	543.6	11.7
150°-160°	438.3	9.4
160°-170°	282.7	6.1
170°-180°	97.4	2.1
0°-30°	433.4	9.3
0°-40°	695.7	14.9
0°-60°	1187.4	25.5
0°-90°	1484.1	31.9
90°-120°	686.2	14.7
90°-150°	2354.4	50.6
90°-180°	3173.0	68.1
0°-180°	4657.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	577	575	570	575	574	55
15°	549	547	540	543	542	155
25°	497	494	488	488	486	229
35°	428	425	418	415	413	268
45°	349	346	339	334	332	269
55°	264	263	256	251	248	237
65°	179	177	172	168	165	177
75°	95	93	91	89	88	101
85°	25	25	24	24	24	27
90°	2	11	17	22	23	4
95°	42	16	17	22	22	52
105°	231	235	239	246	219	242
115°	431	433	432	434	434	424
125°	606	609	607	610	610	541
135°	752	751	754	755	757	579
145°	867	869	869	870	871	542
155°	950	951	949	952	950	438
165°	1002	998	998	1005	998	283
175°	1025	1021	1022	1028	1019	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1001361

CATALOG NUMBER: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	577.4	577.4	577.4	577.4	577.4
2.5°	579.2	577.9	572.8	577.4	576.9
5°	576.9	575.1	570.0	575.1	574.2
7.5°	572.8	570.9	565.4	569.5	569.1
10°	566.8	564.9	558.9	562.6	561.7
12.5°	558.9	557.0	550.6	554.7	553.3
15°	549.2	547.3	540.4	543.2	541.8
17.5°	538.1	535.8	529.3	531.1	530.2
20°	525.6	523.3	516.3	517.7	516.8
22.5°	512.2	508.9	502.0	504.8	502.9
25°	497.4	494.1	487.6	488.1	486.3
27.5°	480.7	477.5	471.4	470.5	468.2
30°	464.0	460.3	454.3	452.5	450.2
32.5°	446.5	443.2	436.7	434.4	432.1
35°	428.0	424.7	418.2	415.0	412.7
37.5°	408.5	405.8	398.8	395.6	392.3
40°	389.6	385.9	378.9	374.3	372.0
42.5°	369.2	367.3	359.5	353.9	352.5
45°	349.3	346.1	338.7	333.6	332.2
47.5°	328.5	326.2	319.2	313.7	310.0
50°	307.2	305.4	298.9	292.4	289.6
52.5°	286.4	284.1	277.1	271.6	267.9
55°	264.2	262.8	256.3	250.8	248.0
57.5°	243.4	242.0	235.5	229.9	227.2
60°	221.6	219.3	213.3	209.1	206.8
62.5°	200.3	198.5	192.0	188.3	186.0
65°	179.0	176.7	172.1	167.5	165.2
67.5°	157.3	155.5	150.8	146.2	145.7
70°	137.4	134.2	130.5	126.8	125.4
72.5°	116.1	112.9	110.1	107.3	105.9
75°	95.3	93.0	90.7	88.8	88.4
77.5°	75.0	74.0	71.7	71.2	69.9
80°	56.9	55.5	54.6	53.7	53.2
82.5°	39.3	38.9	38.9	38.4	37.9
85°	25.0	25.0	24.1	24.1	23.6
87.5°	12.0	11.6	11.1	11.1	11.1
90°	2.3	10.7	16.9	21.5	23.0
92.5°	11.5	10.0	16.1	20.7	20.7
95°	42.2	16.1	16.9	21.5	22.2
97.5°	80.5	97.4	16.9	20.7	21.5
100°	125.8	139.6	33.7	20.7	21.5
102.5°	176.4	185.6	194.8	22.2	22.2
105°	230.8	235.4	239.3	246.2	218.6
107.5°	280.7	283.0	288.4	292.2	295.3
110°	331.3	333.6	338.2	339.7	342.0

TEST NUMBER: P1001361

CATALOG NUMBER: SA4XXDIP-B350D810UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.4	385.0	386.5	385.8	388.8
115°	431.0	433.3	432.5	434.1	434.1
117.5°	476.3	479.3	481.6	480.9	480.9
120°	522.3	525.3	524.6	526.1	524.6
122.5°	565.2	566.8	568.3	569.1	567.5
125°	605.9	608.9	607.4	609.7	610.5
127.5°	645.0	645.8	649.6	648.8	648.1
130°	682.6	683.3	685.6	686.4	686.4
132.5°	717.1	718.6	721.7	722.4	721.7
135°	751.6	750.8	753.9	755.4	757.0
137.5°	782.3	782.3	786.1	787.6	786.9
140°	812.2	813.7	815.2	817.5	818.3
142.5°	839.0	842.1	842.9	844.4	844.4
145°	866.6	868.9	868.9	869.7	871.2
147.5°	888.1	892.7	891.9	892.7	893.5
150°	911.9	914.9	914.2	914.2	914.9
152.5°	931.8	934.1	932.6	934.1	933.3
155°	950.2	951.0	948.7	951.8	949.5
157.5°	966.3	966.3	963.3	967.1	963.3
160°	980.1	977.8	977.1	981.7	977.1
162.5°	992.4	989.3	988.6	993.2	987.8
165°	1002.4	998.5	998.5	1004.7	997.8
167.5°	1010.8	1007.0	1006.2	1013.1	1005.4
170°	1017.7	1013.1	1013.9	1020.0	1012.3
172.5°	1022.3	1017.7	1018.5	1024.6	1016.2
175°	1025.4	1020.8	1021.5	1028.4	1019.2
177.5°	1027.7	1022.3	1023.8	1030.0	1020.8
180°	1025.4	1025.4	1025.4	1025.4	1025.4

(END OF REPORT)