

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001267

Luminaire Tested: SA4XXDIP-B350D365UB40-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001267
REPORT IS A COMBINATION OF REPORTS P995886 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB40-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2708.6 lumens
Efficiency: N/A
Efficacy: 121.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001267

CATALOG NUMBER: SA4XXDIP-B350D365UB40-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001267

CATALOG NUMBER: SA4XXDIP-B350D365UB40-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	96	92	87	84	88	84	81	77	70	68	65	58	56	54	46	45	44
2	87	79	73	67	80	73	67	63	61	57	53	50	47	44	40	38	36
3	79	69	62	56	72	64	57	52	54	49	44	44	40	37	35	32	30
4	72	61	53	47	66	56	49	44	47	42	37	39	35	31	31	28	26
5	66	54	46	40	61	50	43	37	42	36	32	35	30	27	28	25	22
6	61	49	40	34	56	45	38	32	38	32	28	31	27	24	25	22	19
7	56	44	36	30	52	41	33	28	34	29	24	28	24	21	23	20	17
8	52	40	32	26	48	37	30	25	31	26	22	26	22	18	21	18	15
9	49	36	29	23	45	34	27	22	29	23	19	24	20	16	19	16	14
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	18	15	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3337	3337	3337
5°	3346	3249	3255
10°	3324	3186	3176
15°	3293	3114	3087
20°	3246	3036	3001
25°	3195	2950	2907
30°	3138	2865	2813
35°	3075	2778	2728
40°	3024	2695	2640
45°	2949	2616	2563
50°	2884	2527	2481
55°	2818	2441	2386
60°	2715	2335	2298
65°	2600	2220	2192
70°	2463	2088	2069
75°	2271	1942	1952
80°	2052	1793	1828
85°	1768	1643	1729

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2949 cd/sqm

TEST NUMBER: P1001267

CATALOG NUMBER: SA4XXDIP-B350D365UB40-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.8	1.4
10°-20°	111.1	4.1
20°-30°	168.0	6.2
30°-40°	203.2	7.5
40°-50°	214.8	7.9
50°-60°	202.2	7.5
60°-70°	167.7	6.2
70°-80°	117.7	4.3
80°-90°	67.1	2.5
90°-100°	173.2	6.4
100°-110°	301.1	11.1
110°-120°	261.9	9.7
120°-130°	214.6	7.9
130°-140°	174.6	6.4
140°-150°	130.6	4.8
150°-160°	91.2	3.4
160°-170°	53.6	2.0
170°-180°	17.4	0.6
0°-30°	317.8	11.7
0°-40°	521.0	19.2
0°-60°	938.0	34.6
0°-90°	1290.5	47.6
90°-120°	736.1	27.2
90°-150°	1255.9	46.4
90°-180°	1418.0	52.4
0°-180°	2708.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	410	408	405	409	408	39
15°	393	393	392	396	395	111
25°	359	362	363	368	369	165
35°	314	320	324	331	332	197
45°	262	271	280	287	290	203
55°	205	215	229	238	240	183
65°	142	157	172	184	187	141
75°	79	96	115	128	132	84
85°	24	44	64	78	82	25
90°	8	28	52	66	70	6
95°	18	58	328	195	143	18
105°	46	73	262	541	543	49
115°	76	98	228	429	512	75
125°	103	122	218	360	405	92
135°	121	144	208	312	355	94
145°	139	159	203	256	283	88
155°	158	171	197	223	233	73
165°	172	177	189	200	203	49
175°	180	180	181	184	183	17
180°	180	180	180	180	180	

TEST NUMBER: P1001267

CATALOG NUMBER: SA4XXDIP-B350D365UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	409.2	409.2	409.2	409.2	409.2
2.5°	411.0	409.6	406.0	409.2	408.7
5°	409.6	408.2	405.0	408.7	408.2
7.5°	406.9	406.0	403.2	407.3	406.9
10°	403.2	402.7	400.5	404.6	404.1
12.5°	398.2	398.2	396.8	400.5	400.5
15°	392.7	393.1	391.8	395.9	395.4
17.5°	385.3	386.7	386.3	390.4	389.9
20°	377.5	378.9	379.4	384.0	384.0
22.5°	368.8	370.7	371.6	376.2	377.1
25°	359.2	362.0	363.3	368.4	368.8
27.5°	348.7	352.8	354.6	359.2	359.7
30°	338.1	341.8	345.0	350.1	351.0
32.5°	326.7	331.3	334.9	340.9	341.8
35°	314.3	319.8	324.4	330.8	332.2
37.5°	301.9	308.4	313.9	320.3	321.6
40°	290.0	296.0	302.4	309.3	311.1
42.5°	276.3	283.2	290.9	298.7	300.1
45°	262.1	270.8	279.5	287.3	289.6
47.5°	248.8	257.5	267.6	275.4	278.1
50°	234.1	244.2	254.3	263.5	266.2
52.5°	219.5	229.6	241.5	250.6	253.4
55°	205.3	214.9	228.6	237.8	240.5
57.5°	189.2	201.1	214.4	225.4	227.7
60°	173.7	185.6	200.7	211.2	214.9
62.5°	158.5	171.8	186.9	197.5	201.1
65°	142.0	156.7	172.3	183.7	187.4
67.5°	126.5	142.0	158.5	170.0	173.7
70°	110.4	126.0	143.4	155.8	159.0
72.5°	94.8	110.9	129.7	141.6	145.2
75°	78.8	95.8	115.0	127.8	132.0
77.5°	63.7	81.6	101.7	114.5	119.1
80°	49.9	68.3	88.4	102.2	105.8
82.5°	36.2	55.4	75.6	89.8	93.9
85°	24.3	43.5	64.1	77.9	82.5
87.5°	15.1	33.9	54.1	67.4	71.5
90°	7.7	28.5	51.8	65.7	69.7
92.5°	11.8	50.1	181.2	101.2	91.3
95°	17.7	57.8	328.0	194.9	142.6
97.5°	24.9	59.4	345.8	340.7	260.7
100°	31.9	63.0	319.0	450.2	374.5
102.5°	38.9	67.4	286.6	517.3	474.0
105°	45.5	73.2	262.1	541.0	542.7
107.5°	53.6	79.6	245.3	530.6	573.8
110°	61.3	85.6	236.8	499.8	572.2

TEST NUMBER: P1001267

CATALOG NUMBER: SA4XXDIP-B350D365UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	68.6	92.0	231.3	462.2	548.7
115°	75.5	98.2	228.3	428.8	512.3
117.5°	83.3	104.4	225.6	401.8	477.1
120°	90.7	110.0	223.4	382.6	447.6
122.5°	97.7	116.0	220.8	369.5	423.6
125°	103.2	122.0	218.5	359.6	405.3
127.5°	108.9	128.2	215.5	349.6	393.1
130°	113.1	134.0	212.8	338.6	381.8
132.5°	117.7	139.2	210.7	326.2	370.1
135°	121.4	144.4	208.0	311.5	354.9
137.5°	125.7	148.4	206.2	296.6	337.7
140°	130.3	152.4	204.5	281.9	319.5
142.5°	134.8	156.2	203.6	268.5	300.3
145°	139.4	159.0	202.9	255.8	282.8
147.5°	144.7	162.2	201.8	244.9	266.3
150°	149.7	165.2	200.8	236.4	252.4
152.5°	153.7	168.1	199.0	229.8	241.8
155°	158.0	170.6	197.2	223.4	232.9
157.5°	162.2	172.8	195.5	217.4	224.8
160°	166.1	174.8	193.3	211.4	217.4
162.5°	169.7	176.4	191.2	205.6	210.3
165°	172.1	177.4	189.1	200.2	203.2
167.5°	175.0	178.3	187.0	195.6	197.6
170°	176.7	179.0	184.9	191.0	192.3
172.5°	178.5	179.6	182.7	187.0	187.0
175°	179.6	179.9	181.3	183.8	183.1
177.5°	180.3	179.9	180.3	181.5	180.3
180°	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)