

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001416

Luminaire Tested: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001416
REPORT IS A COMBINATION OF REPORTS P996035 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6479.0 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001416

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1001416

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34		
1	93	89	85	81	84	80	77	74	64	62	59	49	48	46	35	34	33	27		
2	85	77	71	66	76	70	64	60	56	52	49	43	40	38	31	29	28	22		
3	77	68	60	54	69	61	55	50	49	44	40	37	34	32	27	25	23	18		
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	22	20	16		
5	64	53	45	39	58	48	41	36	38	33	29	30	26	23	21	19	17	13		
6	59	47	39	33	53	43	36	31	34	29	25	27	23	20	19	17	15	12		
7	55	42	35	29	49	39	32	27	31	26	22	24	20	18	18	15	13	10		
8	51	38	31	25	45	35	28	23	28	23	19	22	18	16	16	14	12	9		
9	47	35	28	23	42	32	25	21	26	21	17	20	17	14	15	12	10	8		
10	44	32	25	20	39	29	23	18	24	19	15	19	15	12	14	11	9	7		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5668	5668	5668
5°	5684	5521	5531
10°	5647	5412	5397
15°	5594	5290	5246
20°	5516	5157	5098
25°	5428	5012	4940
30°	5333	4868	4779
35°	5224	4720	4635
40°	5137	4578	4486
45°	5010	4445	4354
50°	4901	4294	4216
55°	4787	4148	4055
60°	4611	3967	3905
65°	4419	3772	3724
70°	4185	3547	3514
75°	3859	3300	3315
80°	3488	3046	3106
85°	3005	2793	2937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 5056 cd/sqm

TEST NUMBER: P1001416

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	1.0
10°-20°	188.7	2.9
20°-30°	285.3	4.4
30°-40°	345.2	5.3
40°-50°	364.9	5.6
50°-60°	343.5	5.3
60°-70°	285.0	4.4
70°-80°	200.0	3.1
80°-90°	115.5	1.8
90°-100°	111.2	1.7
100°-110°	339.8	5.2
110°-120°	587.3	9.1
120°-130°	722.0	11.1
130°-140°	760.4	11.7
140°-150°	705.1	10.9
150°-160°	567.3	8.8
160°-170°	365.8	5.6
170°-180°	126.1	1.9
0°-30°	539.9	8.3
0°-40°	885.1	13.7
0°-60°	1593.5	24.6
0°-90°	2194.0	33.9
90°-120°	1038.3	16.0
90°-150°	3225.8	49.8
90°-180°	4285.0	66.1
0°-180°	6479.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	696	694	688	694	694	66
15°	667	668	666	673	672	188
25°	610	615	617	626	627	281
35°	534	543	551	562	564	334
45°	445	460	475	488	492	344
55°	349	365	388	404	409	311
65°	241	266	293	312	318	239
75°	134	163	195	217	224	142
85°	41	74	109	132	140	43
90°	16	58	99	127	136	11
95°	65	57	90	116	124	75
105°	306	327	361	389	360	321
115°	562	572	596	616	621	554
125°	787	790	808	826	831	703
135°	974	973	983	997	1004	751
145°	1122	1124	1124	1130	1135	701
155°	1230	1231	1228	1232	1229	567
165°	1297	1292	1292	1300	1291	367
175°	1327	1321	1322	1331	1319	126
180°	1327	1327	1327	1327	1327	

TEST NUMBER: P1001416

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.1	695.1	695.1	695.1	695.1
2.5°	698.2	695.9	689.7	695.1	694.4
5°	695.9	693.6	688.1	694.4	693.6
7.5°	691.2	689.7	685.0	692.0	691.2
10°	685.0	684.2	680.3	687.4	686.6
12.5°	676.5	676.5	674.1	680.3	680.3
15°	667.1	667.9	665.6	672.6	671.8
17.5°	654.7	657.0	656.2	663.2	662.4
20°	641.4	643.8	644.5	652.3	652.3
22.5°	626.6	629.7	631.3	639.1	640.6
25°	610.3	615.0	617.3	625.9	626.6
27.5°	592.4	599.4	602.5	610.3	611.1
30°	574.5	580.7	586.2	594.7	596.3
32.5°	555.0	562.8	569.0	579.1	580.7
35°	534.0	543.3	551.1	562.0	564.4
37.5°	513.0	523.9	533.2	544.1	546.5
40°	492.7	502.9	513.8	525.4	528.6
42.5°	469.4	481.1	494.3	507.5	509.9
45°	445.3	460.1	474.8	488.1	492.0
47.5°	422.7	437.5	454.6	467.8	472.5
50°	397.8	414.9	432.0	447.6	452.3
52.5°	372.9	390.0	410.2	425.8	430.5
55°	348.7	365.1	388.4	404.0	408.7
57.5°	321.5	341.7	364.3	383.0	386.9
60°	295.0	315.3	341.0	358.9	365.1
62.5°	269.3	291.9	317.6	335.5	341.7
65°	241.3	266.2	292.7	312.1	318.4
67.5°	214.8	241.3	269.3	288.8	295.0
70°	187.6	214.1	243.6	264.7	270.1
72.5°	161.1	188.4	220.3	240.5	246.8
75°	133.9	162.7	195.4	217.2	224.2
77.5°	108.2	138.6	172.8	194.6	202.4
80°	84.8	116.0	150.2	173.6	179.8
82.5°	61.5	94.2	128.4	152.6	159.6
85°	41.3	74.0	109.0	132.3	140.1
87.5°	25.7	57.6	91.9	114.4	121.4
90°	15.5	57.5	98.9	127.4	135.7
92.5°	26.6	51.8	93.2	121.0	127.2
95°	64.7	56.6	89.5	116.5	124.5
97.5°	113.5	158.0	85.6	110.9	118.9
100°	171.4	209.4	102.9	107.0	113.4
102.5°	236.9	265.9	307.4	104.3	110.5
105°	305.8	327.3	361.1	389.4	360.0
107.5°	370.3	386.4	420.7	445.1	454.5
110°	435.0	448.9	482.1	502.0	511.2

TEST NUMBER: P1001416

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	497.7	513.1	540.7	556.8	567.0
115°	562.5	572.5	596.4	615.5	621.0
117.5°	621.1	629.6	656.0	671.3	677.6
120°	679.8	686.1	707.7	725.3	729.5
122.5°	735.4	737.4	760.4	777.0	780.4
125°	787.2	790.4	807.9	825.7	831.4
127.5°	837.8	838.0	858.6	871.6	876.1
130°	885.7	885.9	901.3	916.3	921.0
132.5°	930.3	931.6	944.9	959.1	962.8
135°	974.3	973.3	982.7	997.1	1003.7
137.5°	1014.0	1013.2	1021.2	1034.9	1037.8
140°	1052.7	1053.9	1056.7	1069.7	1074.6
142.5°	1086.6	1090.6	1090.8	1101.4	1104.5
145°	1122.4	1124.5	1124.5	1130.2	1135.3
147.5°	1150.2	1155.3	1154.3	1156.1	1160.2
150°	1180.9	1184.1	1183.1	1183.1	1184.1
152.5°	1205.9	1208.9	1206.9	1208.9	1207.9
155°	1229.7	1230.7	1227.8	1231.7	1228.8
157.5°	1250.6	1250.6	1246.6	1251.6	1246.6
160°	1268.5	1265.5	1264.5	1270.4	1264.5
162.5°	1284.3	1280.4	1279.4	1285.3	1278.4
165°	1297.2	1292.3	1292.3	1300.2	1291.3
167.5°	1308.2	1303.2	1302.2	1311.1	1301.2
170°	1317.1	1311.1	1312.1	1320.1	1310.1
172.5°	1323.0	1317.1	1318.1	1326.0	1315.1
175°	1327.0	1321.1	1322.1	1331.0	1319.1
177.5°	1330.0	1323.0	1325.0	1333.0	1321.1
180°	1327.0	1327.0	1327.0	1327.0	1327.0

(END OF REPORT)