

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001274

Luminaire Tested: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001274
REPORT IS A COMBINATION OF REPORTS P995893 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2764.0 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001274

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D

Luminous Intensity Polar Plot



TEST NUMBER: P1001274

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	96	91	87	83	88	84	80	77	69	67	64	56	54	53	44	43	42
2	87	79	73	67	79	72	67	62	60	56	52	49	46	43	38	36	34
3	79	69	61	55	72	63	57	51	53	48	44	43	39	36	34	31	29
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25
5	66	54	46	40	60	50	42	37	42	36	32	34	30	26	27	24	21
6	61	48	40	34	55	45	37	32	37	32	27	31	26	23	24	21	19
7	56	44	35	30	51	40	33	28	34	28	24	28	23	20	22	19	16
8	52	39	32	26	47	36	29	25	31	25	21	25	21	18	20	17	15
9	48	36	28	23	44	33	26	22	28	23	19	23	19	16	19	15	13
10	45	33	26	21	41	30	24	19	26	21	17	21	17	14	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3227	3227	3227
5°	3235	3143	3148
10°	3214	3081	3072
15°	3184	3011	2986
20°	3140	2936	2902
25°	3090	2853	2812
30°	3035	2770	2720
35°	2974	2686	2638
40°	2925	2605	2554
45°	2851	2530	2478
50°	2789	2444	2399
55°	2725	2361	2308
60°	2625	2258	2222
65°	2516	2147	2119
70°	2383	2020	2000
75°	2196	1878	1887
80°	1987	1734	1769
85°	1710	1589	1673

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2851 cd/sqm

TEST NUMBER: P1001274

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.5	1.4
10°-20°	107.4	3.9
20°-30°	162.4	5.9
30°-40°	196.5	7.1
40°-50°	207.7	7.5
50°-60°	195.5	7.1
60°-70°	162.2	5.9
70°-80°	113.8	4.1
80°-90°	65.1	2.4
90°-100°	53.4	1.9
100°-110°	128.2	4.6
110°-120°	209.7	7.6
120°-130°	252.9	9.1
130°-140°	263.7	9.5
140°-150°	243.2	8.8
150°-160°	195.4	7.1
160°-170°	126.0	4.6
170°-180°	43.4	1.6
0°-30°	307.3	11.1
0°-40°	503.8	18.2
0°-60°	907.0	32.8
0°-90°	1248.2	45.2
90°-120°	391.3	14.2
90°-150°	1151.0	41.6
90°-180°	1516.0	54.8
0°-180°	2764.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	396	396	396	396	396	
5°	396	395	392	395	395	38
15°	380	380	379	383	382	107
25°	347	350	351	356	357	160
35°	304	309	314	320	321	190
45°	253	262	270	278	280	196
55°	198	208	221	230	233	177
65°	137	152	167	178	181	136
75°	76	93	111	124	128	81
85°	24	42	62	75	80	24
90°	8	30	51	66	71	6
95°	25	28	46	60	64	28
105°	107	118	136	150	141	112
115°	195	200	214	224	227	192
125°	272	273	283	292	296	243
135°	336	336	340	348	351	259
145°	387	387	387	390	393	242
155°	424	424	423	424	423	195
165°	447	445	445	448	445	126
175°	457	455	455	458	454	44
180°	457	457	457	457	457	

TEST NUMBER: P1001274

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	395.7	395.7	395.7	395.7	395.7
2.5°	397.4	396.1	392.6	395.7	395.2
5°	396.1	394.8	391.7	395.2	394.8
7.5°	393.5	392.6	389.9	393.9	393.5
10°	389.9	389.5	387.3	391.2	390.8
12.5°	385.0	385.0	383.7	387.3	387.3
15°	379.7	380.2	378.8	382.8	382.4
17.5°	372.6	374.0	373.5	377.5	377.1
20°	365.1	366.4	366.9	371.3	371.3
22.5°	356.7	358.5	359.3	363.8	364.7
25°	347.4	350.0	351.4	356.2	356.7
27.5°	337.2	341.2	342.9	347.4	347.8
30°	327.0	330.5	333.6	338.5	339.4
32.5°	315.9	320.3	323.9	329.7	330.5
35°	304.0	309.3	313.7	319.9	321.2
37.5°	292.0	298.2	303.5	309.7	311.0
40°	280.5	286.2	292.4	299.1	300.9
42.5°	267.2	273.8	281.4	288.9	290.2
45°	253.4	261.9	270.3	277.8	280.0
47.5°	240.6	249.0	258.8	266.3	268.9
50°	226.4	236.2	245.9	254.8	257.4
52.5°	212.2	222.0	233.5	242.4	245.0
55°	198.5	207.8	221.1	230.0	232.6
57.5°	183.0	194.5	207.4	218.0	220.2
60°	167.9	179.4	194.1	204.3	207.8
62.5°	153.3	166.2	180.8	191.0	194.5
65°	137.4	151.5	166.6	177.7	181.2
67.5°	122.3	137.4	153.3	164.4	167.9
70°	106.8	121.8	138.7	150.6	153.7
72.5°	91.7	107.2	125.4	136.9	140.5
75°	76.2	92.6	111.2	123.6	127.6
77.5°	61.6	78.9	98.4	110.8	115.2
80°	48.3	66.0	85.5	98.8	102.4
82.5°	35.0	53.6	73.1	86.8	90.8
85°	23.5	42.1	62.0	75.3	79.8
87.5°	14.6	32.8	52.3	65.1	69.1
90°	8.1	29.6	51.4	66.3	70.6
92.5°	11.7	26.6	48.4	62.8	66.4
95°	24.6	27.6	46.0	60.1	64.4
97.5°	41.2	61.6	43.8	57.1	61.4
100°	61.0	78.6	48.7	54.8	58.3
102.5°	83.5	97.3	118.3	52.9	56.4
105°	106.9	117.7	135.8	150.0	141.3
107.5°	129.1	137.6	155.5	168.3	172.8
110°	151.2	158.4	176.0	186.8	191.4

TEST NUMBER: P1001274

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	172.6	180.0	195.3	204.7	209.6
115°	194.8	199.7	213.6	224.1	227.2
117.5°	215.0	218.9	233.2	242.2	245.8
120°	235.0	237.6	250.2	259.8	262.6
122.5°	254.1	254.8	267.5	276.6	279.0
125°	271.8	272.7	283.1	292.5	295.6
127.5°	289.2	289.1	299.7	307.4	310.1
130°	305.5	305.4	313.6	321.9	324.5
132.5°	320.9	321.2	327.8	335.7	338.0
135°	335.9	335.5	340.0	347.8	351.1
137.5°	349.5	349.0	352.5	359.9	361.8
140°	362.9	363.0	364.2	371.0	373.6
142.5°	374.3	375.7	375.6	381.2	382.9
145°	386.6	387.3	387.3	390.3	392.7
147.5°	396.2	397.8	397.5	398.2	400.4
150°	406.8	407.8	407.4	407.4	407.8
152.5°	415.3	416.3	415.6	416.3	416.0
155°	423.5	423.8	422.8	424.2	423.1
157.5°	430.7	430.7	429.3	431.0	429.3
160°	436.8	435.8	435.4	437.5	435.4
162.5°	442.3	440.9	440.6	442.6	440.2
165°	446.7	445.0	445.0	447.8	444.7
167.5°	450.5	448.8	448.4	451.5	448.1
170°	453.6	451.5	451.9	454.6	451.2
172.5°	455.6	453.6	453.9	456.6	452.9
175°	457.0	454.9	455.3	458.3	454.2
177.5°	458.0	455.6	456.3	459.0	454.9
180°	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)