

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001418

Luminaire Tested: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001418
REPORT IS A COMBINATION OF REPORTS P996037 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_5000K
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6203.0 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001418

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001418

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	93	89	85	81	84	80	77	74	64	62	59	49	48	46	35	34	33
2	85	77	71	66	76	70	64	60	56	52	49	43	40	38	31	29	28
3	77	68	60	54	69	61	55	50	49	44	40	37	34	32	27	25	23
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	22	20
5	64	53	45	39	58	48	41	36	38	33	29	30	26	23	21	19	17
6	59	47	39	33	53	43	36	31	34	29	25	27	23	20	19	17	15
7	55	42	35	29	49	39	32	27	31	26	22	24	20	18	18	15	13
8	51	38	31	25	45	35	28	23	28	23	19	22	18	16	16	14	12
9	47	35	28	23	42	32	25	21	26	21	17	20	17	14	15	12	10
10	44	32	25	20	39	29	23	18	24	19	15	19	15	12	14	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5427	5427	5427
5°	5442	5285	5295
10°	5406	5182	5167
15°	5356	5065	5022
20°	5281	4938	4881
25°	5197	4798	4729
30°	5105	4660	4575
35°	5001	4518	4437
40°	4918	4383	4294
45°	4796	4255	4168
50°	4691	4111	4036
55°	4583	3972	3883
60°	4416	3798	3738
65°	4230	3611	3565
70°	4007	3397	3364
75°	3694	3160	3173
80°	3340	2916	2975
85°	2874	2673	2811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 4827 cd/sqm

TEST NUMBER: P1001418

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.0
10°-20°	180.7	2.9
20°-30°	273.2	4.4
30°-40°	330.5	5.3
40°-50°	349.4	5.6
50°-60°	328.8	5.3
60°-70°	272.9	4.4
70°-80°	191.5	3.1
80°-90°	110.6	1.8
90°-100°	106.5	1.7
100°-110°	325.3	5.2
110°-120°	562.3	9.1
120°-130°	691.3	11.1
130°-140°	728.0	11.7
140°-150°	675.0	10.9
150°-160°	543.1	8.8
160°-170°	350.3	5.6
170°-180°	120.7	1.9
0°-30°	516.9	8.3
0°-40°	847.4	13.7
0°-60°	1525.6	24.6
0°-90°	2100.5	33.9
90°-120°	994.1	16.0
90°-150°	3088.4	49.8
90°-180°	4102.0	66.1
0°-180°	6203.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	666	666	666	666	666	
5°	666	664	659	665	664	63
15°	639	639	637	644	643	180
25°	584	589	591	599	600	269
35°	511	520	528	538	540	320
45°	426	440	455	467	471	329
55°	334	350	372	387	391	298
65°	231	255	280	299	305	229
75°	128	156	187	208	215	136
85°	40	71	104	127	134	41
90°	15	55	95	122	130	11
95°	62	54	86	112	119	72
105°	293	313	346	373	345	307
115°	538	548	571	589	594	530
125°	754	757	774	790	796	673
135°	933	932	941	955	961	719
145°	1074	1077	1077	1082	1087	671
155°	1177	1178	1176	1179	1176	543
165°	1242	1237	1237	1245	1236	351
175°	1270	1265	1266	1274	1263	121
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1001418

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	665.5	665.5	665.5	665.5	665.5
2.5°	668.5	666.3	660.3	665.5	664.8
5°	666.3	664.0	658.8	664.8	664.0
7.5°	661.8	660.3	655.8	662.5	661.8
10°	655.8	655.1	651.4	658.1	657.3
12.5°	647.6	647.6	645.4	651.4	651.4
15°	638.7	639.4	637.2	643.9	643.2
17.5°	626.8	629.0	628.2	635.0	634.2
20°	614.1	616.3	617.1	624.5	624.5
22.5°	599.9	602.9	604.4	611.9	613.3
25°	584.3	588.7	591.0	599.2	599.9
27.5°	567.1	573.8	576.8	584.3	585.0
30°	550.0	556.0	561.2	569.4	570.9
32.5°	531.4	538.8	544.8	554.5	556.0
35°	511.2	520.2	527.6	538.1	540.3
37.5°	491.1	501.6	510.5	520.9	523.2
40°	471.7	481.4	491.9	503.0	506.0
42.5°	449.4	460.6	473.2	485.9	488.1
45°	426.3	440.4	454.6	467.3	471.0
47.5°	404.7	418.8	435.2	447.9	452.4
50°	380.8	397.2	413.6	428.5	433.0
52.5°	357.0	373.4	392.7	407.7	412.1
55°	333.9	349.5	371.9	386.8	391.3
57.5°	307.8	327.2	348.8	366.7	370.4
60°	282.5	301.8	326.4	343.6	349.5
62.5°	257.9	279.5	304.1	321.2	327.2
65°	231.0	254.9	280.2	298.8	304.8
67.5°	205.7	231.0	257.9	276.5	282.5
70°	179.6	204.9	233.3	253.4	258.6
72.5°	154.3	180.4	210.9	230.3	236.2
75°	128.2	155.8	187.1	207.9	214.6
77.5°	103.6	132.7	165.4	186.3	193.8
80°	81.2	111.0	143.8	166.2	172.2
82.5°	58.9	90.2	123.0	146.1	152.8
85°	39.5	70.8	104.3	126.7	134.1
87.5°	24.6	55.1	87.9	109.6	116.3
90°	14.8	55.0	94.7	122.0	129.9
92.5°	25.5	49.7	89.3	115.9	121.8
95°	62.0	54.3	85.7	111.6	119.3
97.5°	108.7	151.3	82.0	106.2	113.8
100°	164.0	200.5	98.4	102.5	108.6
102.5°	226.8	254.6	294.3	99.9	105.9
105°	292.7	313.3	345.7	372.8	344.6
107.5°	354.5	370.0	402.8	426.1	435.2
110°	416.5	429.8	461.6	480.6	489.4



TEST NUMBER: P1001418

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	476.5	491.2	517.7	533.1	542.9
115°	538.5	548.1	570.9	589.2	594.4
117.5°	594.6	602.8	628.1	642.8	648.7
120°	650.8	656.9	677.6	694.4	698.4
122.5°	704.0	705.9	727.9	743.9	747.2
125°	753.7	756.7	773.5	790.5	795.9
127.5°	802.2	802.3	822.0	834.5	838.8
130°	847.9	848.2	862.9	877.3	881.8
132.5°	890.7	891.9	904.6	918.2	921.8
135°	932.8	931.8	940.8	954.6	961.0
137.5°	970.8	970.0	977.7	990.8	993.6
140°	1007.8	1008.9	1011.6	1024.2	1028.8
142.5°	1040.3	1044.1	1044.3	1054.4	1057.4
145°	1074.5	1076.6	1076.6	1082.1	1087.0
147.5°	1101.1	1106.1	1105.2	1106.8	1110.8
150°	1130.6	1133.7	1132.7	1132.7	1133.7
152.5°	1154.6	1157.4	1155.5	1157.4	1156.5
155°	1177.4	1178.3	1175.5	1179.3	1176.4
157.5°	1197.3	1197.3	1193.5	1198.3	1193.5
160°	1214.4	1211.6	1210.6	1216.3	1210.6
162.5°	1229.6	1225.8	1224.9	1230.6	1223.9
165°	1242.0	1237.2	1237.2	1244.8	1236.3
167.5°	1252.4	1247.7	1246.7	1255.3	1245.8
170°	1261.0	1255.3	1256.2	1263.8	1254.3
172.5°	1266.7	1261.0	1261.9	1269.6	1259.1
175°	1270.5	1264.8	1265.7	1274.3	1262.9
177.5°	1273.4	1266.7	1268.6	1276.2	1264.8
180°	1270.5	1270.5	1270.5	1270.5	1270.5

(END OF REPORT)