

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001275

Luminaire Tested: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001275
REPORT IS A COMBINATION OF REPORTS P995894 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2576.0 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001275

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001275

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	96	92	87	84	89	84	81	77	71	68	66	58	56	55	47	45	44
2	87	80	73	67	80	73	68	63	61	57	54	51	48	45	41	38	36
3	79	70	62	56	73	64	57	52	54	49	45	44	41	37	36	33	31
4	73	61	53	47	66	57	49	44	48	42	38	39	35	32	32	29	26
5	66	54	46	40	61	50	43	37	42	37	32	35	31	27	28	25	22
6	61	49	40	34	56	45	38	32	38	32	28	32	27	24	26	22	20
7	56	44	36	30	52	41	33	28	34	29	24	29	24	21	23	20	17
8	52	40	32	26	48	37	30	25	31	26	22	26	22	19	21	18	15
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	16	14
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3227	3227	3227
5°	3235	3143	3148
10°	3214	3081	3072
15°	3184	3011	2986
20°	3140	2936	2902
25°	3090	2853	2812
30°	3035	2770	2720
35°	2974	2686	2638
40°	2925	2605	2554
45°	2851	2530	2478
50°	2789	2444	2399
55°	2725	2361	2308
60°	2625	2258	2222
65°	2516	2147	2119
70°	2383	2020	2000
75°	2196	1878	1887
80°	1987	1734	1769
85°	1710	1589	1673

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2851 cd/sqm

TEST NUMBER: P1001275

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.5	1.5
10°-20°	107.4	4.2
20°-30°	162.4	6.3
30°-40°	196.5	7.6
40°-50°	207.7	8.1
50°-60°	195.5	7.6
60°-70°	162.2	6.3
70°-80°	113.8	4.4
80°-90°	65.1	2.5
90°-100°	67.0	2.6
100°-110°	114.6	4.4
110°-120°	165.5	6.4
120°-130°	204.0	7.9
130°-140°	221.7	8.6
140°-150°	214.3	8.3
150°-160°	179.5	7.0
160°-170°	119.4	4.6
170°-180°	41.8	1.6
0°-30°	307.3	11.9
0°-40°	503.8	19.6
0°-60°	907.0	35.2
0°-90°	1248.2	48.5
90°-120°	347.1	13.5
90°-150°	987.1	38.3
90°-180°	1328.0	51.6
0°-180°	2576.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	396	396	396	396	396	
5°	396	395	392	395	395	38
15°	380	380	379	383	382	107
25°	347	350	351	356	357	160
35°	304	309	314	320	321	190
45°	253	262	270	278	280	196
55°	198	208	221	230	233	177
65°	137	152	167	178	181	136
75°	76	93	111	124	128	81
85°	24	42	62	75	80	24
90°	8	30	51	66	71	6
95°	26	44	64	78	82	27
105°	84	93	110	123	127	89
115°	152	156	169	179	181	150
125°	219	218	229	237	239	195
135°	281	283	286	292	294	217
145°	340	341	342	344	345	213
155°	390	390	389	391	389	179
165°	424	423	422	424	423	120
175°	441	440	439	442	439	42
180°	442	442	442	442	442	

TEST NUMBER: P1001275

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	395.7	395.7	395.7	395.7	395.7
2.5°	397.4	396.1	392.6	395.7	395.2
5°	396.1	394.8	391.7	395.2	394.8
7.5°	393.5	392.6	389.9	393.9	393.5
10°	389.9	389.5	387.3	391.2	390.8
12.5°	385.0	385.0	383.7	387.3	387.3
15°	379.7	380.2	378.8	382.8	382.4
17.5°	372.6	374.0	373.5	377.5	377.1
20°	365.1	366.4	366.9	371.3	371.3
22.5°	356.7	358.5	359.3	363.8	364.7
25°	347.4	350.0	351.4	356.2	356.7
27.5°	337.2	341.2	342.9	347.4	347.8
30°	327.0	330.5	333.6	338.5	339.4
32.5°	315.9	320.3	323.9	329.7	330.5
35°	304.0	309.3	313.7	319.9	321.2
37.5°	292.0	298.2	303.5	309.7	311.0
40°	280.5	286.2	292.4	299.1	300.9
42.5°	267.2	273.8	281.4	288.9	290.2
45°	253.4	261.9	270.3	277.8	280.0
47.5°	240.6	249.0	258.8	266.3	268.9
50°	226.4	236.2	245.9	254.8	257.4
52.5°	212.2	222.0	233.5	242.4	245.0
55°	198.5	207.8	221.1	230.0	232.6
57.5°	183.0	194.5	207.4	218.0	220.2
60°	167.9	179.4	194.1	204.3	207.8
62.5°	153.3	166.2	180.8	191.0	194.5
65°	137.4	151.5	166.6	177.7	181.2
67.5°	122.3	137.4	153.3	164.4	167.9
70°	106.8	121.8	138.7	150.6	153.7
72.5°	91.7	107.2	125.4	136.9	140.5
75°	76.2	92.6	111.2	123.6	127.6
77.5°	61.6	78.9	98.4	110.8	115.2
80°	48.3	66.0	85.5	98.8	102.4
82.5°	35.0	53.6	73.1	86.8	90.8
85°	23.5	42.1	62.0	75.3	79.8
87.5°	14.6	32.8	52.3	65.1	69.1
90°	8.1	29.6	51.4	66.3	70.6
92.5°	15.5	35.5	56.2	69.7	73.6
95°	26.3	44.0	64.5	77.5	81.5
97.5°	38.1	53.7	74.6	87.5	91.4
100°	52.7	65.6	86.0	98.6	101.7
102.5°	68.5	78.5	98.1	110.7	114.5
105°	83.6	92.8	110.5	122.7	127.3
107.5°	100.4	108.2	124.1	136.5	139.3
110°	117.0	123.8	139.1	148.5	153.1

TEST NUMBER: P1001275

CATALOG NUMBER: SA4XXDIP-B350D365UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	134.3	139.6	153.5	163.3	166.8
115°	151.7	155.6	169.1	178.6	181.3
117.5°	168.4	171.0	184.0	192.3	194.9
120°	184.7	187.4	199.2	206.4	210.6
122.5°	202.1	202.5	214.1	221.9	223.3
125°	218.8	218.3	229.1	236.8	238.8
127.5°	234.2	234.7	242.9	250.2	253.0
130°	250.1	250.7	257.8	265.1	266.4
132.5°	266.8	267.1	272.1	278.9	281.3
135°	280.8	282.8	285.9	292.4	293.9
137.5°	296.9	297.4	299.9	305.5	308.1
140°	312.9	313.1	313.6	319.0	320.9
142.5°	327.1	327.8	327.1	332.0	333.7
145°	340.4	341.4	341.7	344.1	344.8
147.5°	354.1	355.4	355.1	355.1	356.6
150°	366.4	367.4	367.4	367.4	367.0
152.5°	377.6	378.3	378.7	379.7	378.7
155°	389.6	389.6	389.3	390.6	389.3
157.5°	399.8	399.2	399.2	400.2	399.2
160°	408.7	408.4	408.0	409.1	407.4
162.5°	416.9	415.9	415.6	417.6	415.9
165°	424.1	423.1	422.4	424.5	423.1
167.5°	429.9	428.6	428.6	430.6	428.6
170°	434.7	433.0	433.3	435.4	433.0
172.5°	438.1	436.8	436.8	439.1	436.8
175°	441.2	439.5	439.1	441.5	439.1
177.5°	442.6	440.9	440.9	443.2	440.5
180°	441.9	441.9	441.9	441.9	441.9

(END OF REPORT)