

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001422

Luminaire Tested: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001422
REPORT IS A COMBINATION OF REPORTS P996041 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6536.0 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001422

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001422

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45			38
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	40	39	38			32
2	86	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32			27
3	79	70	62	57	71	63	57	52	52	47	44	41	38	35	31	29	27			23
4	72	62	54	48	65	56	49	44	46	41	37	36	33	30	28	25	23			19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20			17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	23	20	18			15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	21	18	16			13
8	52	40	32	27	47	37	30	25	30	25	22	24	21	18	19	16	14			12
9	48	36	29	24	44	33	27	23	28	23	19	22	19	16	17	15	13			11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7841	7841	7841
5°	7848	7615	7625
10°	7781	7404	7353
15°	7669	7153	7045
20°	7527	6880	6726
25°	7367	6594	6384
30°	7173	6283	6008
35°	6973	5965	5644
40°	6763	5623	5258
45°	6545	5280	4896
50°	6302	4947	4495
55°	6038	4558	4098
60°	5770	4133	3683
65°	5461	3693	3217
70°	5104	3164	2717
75°	4573	2550	2176
80°	3899	1844	1530
85°	3027	1028	824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6545 cd/sqm

TEST NUMBER: P1001422

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.4
10°-20°	255.3	3.9
20°-30°	375.8	5.7
30°-40°	436.8	6.7
40°-50°	436.8	6.7
50°-60°	382.0	5.8
60°-70°	283.6	4.3
70°-80°	160.9	2.5
80°-90°	48.8	0.7
90°-100°	43.6	0.7
100°-110°	287.2	4.4
110°-120°	548.4	8.4
120°-130°	696.2	10.7
130°-140°	744.8	11.4
140°-150°	696.4	10.7
150°-160°	561.6	8.6
160°-170°	362.2	5.5
170°-180°	124.8	1.9
0°-30°	721.7	11.0
0°-40°	1158.6	17.7
0°-60°	1977.4	30.3
0°-90°	2470.7	37.8
90°-120°	879.2	13.5
90°-150°	3016.6	46.2
90°-180°	4065.0	62.2
0°-180°	6536.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	962	962	962	962	962	
5°	961	958	949	958	956	91
15°	914	912	900	904	902	258
25°	828	823	812	813	810	381
35°	713	707	696	691	687	446
45°	582	576	564	556	553	448
55°	440	438	427	418	413	394
65°	298	294	287	279	275	295
75°	159	155	151	148	147	168
85°	42	42	40	40	39	45
90°	3	14	22	28	30	6
95°	54	21	22	28	28	67
105°	296	302	307	315	280	310
115°	552	555	554	556	556	544
125°	776	780	778	781	782	693
135°	963	962	966	968	970	742
145°	1110	1113	1113	1114	1116	694
155°	1218	1218	1216	1219	1216	561
165°	1284	1279	1279	1287	1278	363
175°	1314	1308	1309	1318	1306	125
180°	1314	1314	1314	1314	1314	

TEST NUMBER: P1001422

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	961.5	961.5	961.5	961.5	961.5
2.5°	964.6	962.3	953.8	961.5	960.8
5°	960.8	957.7	949.2	957.7	956.2
7.5°	953.8	950.8	941.5	948.4	947.7
10°	943.8	940.7	930.7	936.9	935.4
12.5°	930.7	927.6	916.9	923.8	921.5
15°	914.5	911.5	899.9	904.5	902.2
17.5°	896.1	892.2	881.4	884.5	883.0
20°	875.3	871.4	859.8	862.2	860.6
22.5°	852.9	847.5	836.0	840.6	837.5
25°	828.3	822.9	812.1	812.8	809.8
27.5°	800.5	795.1	785.1	783.6	779.7
30°	772.8	766.6	756.6	753.5	749.7
32.5°	743.5	738.1	727.3	723.5	719.6
35°	712.7	707.3	696.5	691.1	687.3
37.5°	680.3	675.7	664.1	658.8	653.4
40°	648.7	642.6	631.0	623.3	619.5
42.5°	614.8	611.8	598.7	589.4	587.1
45°	581.7	576.3	564.0	555.5	553.2
47.5°	547.0	543.2	531.6	522.4	516.2
50°	511.6	508.5	497.7	486.9	482.3
52.5°	476.9	473.1	461.5	452.3	446.1
55°	439.9	437.6	426.8	417.6	413.0
57.5°	405.3	403.0	392.2	382.9	378.3
60°	369.1	365.2	355.2	348.3	344.4
62.5°	333.6	330.5	319.7	313.6	309.7
65°	298.2	294.3	286.6	278.9	275.1
67.5°	262.0	258.9	251.2	243.5	242.7
70°	228.8	223.4	217.3	211.1	208.8
72.5°	193.4	188.0	183.4	178.7	176.4
75°	158.7	154.9	151.0	147.9	147.2
77.5°	124.8	123.3	119.4	118.7	116.3
80°	94.8	92.5	90.9	89.4	88.6
82.5°	65.5	64.7	64.7	63.9	63.2
85°	41.6	41.6	40.1	40.1	39.3
87.5°	20.0	19.3	18.5	18.5	18.5
90°	2.9	13.8	21.6	27.5	29.5
92.5°	14.7	12.8	20.6	26.5	26.5
95°	54.0	20.6	21.6	27.5	28.5
97.5°	103.2	124.8	21.6	26.5	27.5
100°	161.2	178.8	43.2	26.5	27.5
102.5°	226.0	237.8	249.6	28.5	28.5
105°	295.8	301.7	306.6	315.4	280.0
107.5°	359.6	362.6	369.5	374.4	378.3
110°	424.5	427.4	433.3	435.3	438.3

TEST NUMBER: P1001422

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	487.4	493.3	495.2	494.3	498.2
115°	552.2	555.2	554.2	556.2	556.2
117.5°	610.2	614.1	617.1	616.1	616.1
120°	669.2	673.1	672.1	674.1	672.1
122.5°	724.2	726.2	728.1	729.1	727.1
125°	776.3	780.2	778.2	781.2	782.2
127.5°	826.4	827.4	832.3	831.3	830.3
130°	874.5	875.5	878.5	879.5	879.5
132.5°	918.8	920.7	924.7	925.6	924.7
135°	963.0	962.0	965.9	967.9	969.9
137.5°	1002.3	1002.3	1007.2	1009.2	1008.2
140°	1040.6	1042.6	1044.5	1047.5	1048.5
142.5°	1075.0	1078.9	1079.9	1081.9	1081.9
145°	1110.4	1113.3	1113.3	1114.3	1116.3
147.5°	1137.9	1143.8	1142.8	1143.8	1144.8
150°	1168.3	1172.3	1171.3	1171.3	1172.3
152.5°	1193.9	1196.8	1194.9	1196.8	1195.9
155°	1217.5	1218.5	1215.5	1219.4	1216.5
157.5°	1238.1	1238.1	1234.2	1239.1	1234.2
160°	1255.8	1252.9	1251.9	1257.8	1251.9
162.5°	1271.5	1267.6	1266.6	1272.5	1265.6
165°	1284.3	1279.4	1279.4	1287.2	1278.4
167.5°	1295.1	1290.2	1289.2	1298.1	1288.2
170°	1303.9	1298.1	1299.0	1306.9	1297.1
172.5°	1309.8	1303.9	1304.9	1312.8	1302.0
175°	1313.8	1307.9	1308.9	1317.7	1305.9
177.5°	1316.7	1309.8	1311.8	1319.7	1307.9
180°	1313.8	1313.8	1313.8	1313.8	1313.8

(END OF REPORT)