

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001476

Luminaire Tested: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001476
REPORT IS A COMBINATION OF REPORTS P996095 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7198.0 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001476

CATALOG NUMBER: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1001476

CATALOG NUMBER: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38
1	93	88	84	81	83	79	76	73	62	60	58	47	45	44	33	32	31
2	84	77	71	65	75	69	64	59	54	51	47	41	38	36	28	27	26
3	77	67	60	54	68	60	54	49	48	43	40	36	33	30	25	23	21
4	70	59	51	45	62	53	47	41	42	37	33	32	28	26	22	20	18
5	64	52	44	39	57	47	40	35	37	32	29	28	25	22	20	18	16
6	59	47	39	33	52	42	35	30	34	29	25	26	22	19	18	16	14
7	54	42	34	29	48	38	31	26	30	25	22	23	19	17	16	14	12
8	50	38	30	25	45	34	28	23	28	23	19	21	17	15	15	13	11
9	47	35	27	22	42	31	25	20	25	20	17	19	16	13	14	11	10
10	43	32	25	20	39	29	22	18	23	18	15	18	14	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5668	5668	5668
5°	5684	5521	5531
10°	5647	5412	5397
15°	5594	5290	5246
20°	5516	5157	5098
25°	5428	5012	4940
30°	5333	4868	4779
35°	5224	4720	4635
40°	5137	4578	4486
45°	5010	4445	4354
50°	4901	4294	4216
55°	4787	4148	4055
60°	4611	3967	3905
65°	4419	3772	3724
70°	4185	3547	3514
75°	3859	3300	3315
80°	3488	3046	3106
85°	3005	2793	2937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 90°
Luminance: 5219 cd/sqm

TEST NUMBER: P1001476

CATALOG NUMBER: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	0.9
10°-20°	188.7	2.6
20°-30°	285.3	4.0
30°-40°	345.2	4.8
40°-50°	364.9	5.1
50°-60°	343.5	4.8
60°-70°	285.0	4.0
70°-80°	200.0	2.8
80°-90°	116.0	1.6
90°-100°	118.9	1.7
100°-110°	390.6	5.4
110°-120°	684.2	9.5
120°-130°	845.1	11.7
130°-140°	892.1	12.4
140°-150°	828.2	11.5
150°-160°	666.5	9.3
160°-170°	429.9	6.0
170°-180°	148.2	2.1
0°-30°	539.9	7.5
0°-40°	885.1	12.3
0°-60°	1593.5	22.1
0°-90°	2194.5	30.5
90°-120°	1193.7	16.6
90°-150°	3759.0	52.2
90°-180°	5004.0	69.5
0°-180°	7198.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	696	694	688	694	694	66
15°	667	668	666	673	672	188
25°	610	615	617	626	627	281
35°	534	543	551	562	564	334
45°	445	460	475	488	492	344
55°	349	365	388	404	409	311
65°	241	266	293	312	318	239
75°	134	163	195	217	224	142
85°	41	74	109	132	140	43
90°	16	60	103	132	141	12
95°	74	60	93	121	130	87
105°	358	381	415	445	410	375
115°	660	671	694	714	719	650
125°	924	928	945	964	970	826
135°	1144	1143	1153	1168	1175	882
145°	1319	1321	1321	1327	1333	824
155°	1445	1446	1443	1447	1444	666
165°	1524	1518	1518	1528	1517	431
175°	1559	1552	1553	1564	1550	148
180°	1559	1559	1559	1559	1559	

TEST NUMBER: P1001476

CATALOG NUMBER: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.1	695.1	695.1	695.1	695.1
2.5°	698.2	695.9	689.7	695.1	694.4
5°	695.9	693.6	688.1	694.4	693.6
7.5°	691.2	689.7	685.0	692.0	691.2
10°	685.0	684.2	680.3	687.4	686.6
12.5°	676.5	676.5	674.1	680.3	680.3
15°	667.1	667.9	665.6	672.6	671.8
17.5°	654.7	657.0	656.2	663.2	662.4
20°	641.4	643.8	644.5	652.3	652.3
22.5°	626.6	629.7	631.3	639.1	640.6
25°	610.3	615.0	617.3	625.9	626.6
27.5°	592.4	599.4	602.5	610.3	611.1
30°	574.5	580.7	586.2	594.7	596.3
32.5°	555.0	562.8	569.0	579.1	580.7
35°	534.0	543.3	551.1	562.0	564.4
37.5°	513.0	523.9	533.2	544.1	546.5
40°	492.7	502.9	513.8	525.4	528.6
42.5°	469.4	481.1	494.3	507.5	509.9
45°	445.3	460.1	474.8	488.1	492.0
47.5°	422.7	437.5	454.6	467.8	472.5
50°	397.8	414.9	432.0	447.6	452.3
52.5°	372.9	390.0	410.2	425.8	430.5
55°	348.7	365.1	388.4	404.0	408.7
57.5°	321.5	341.7	364.3	383.0	386.9
60°	295.0	315.3	341.0	358.9	365.1
62.5°	269.3	291.9	317.6	335.5	341.7
65°	241.3	266.2	292.7	312.1	318.4
67.5°	214.8	241.3	269.3	288.8	295.0
70°	187.6	214.1	243.6	264.7	270.1
72.5°	161.1	188.4	220.3	240.5	246.8
75°	133.9	162.7	195.4	217.2	224.2
77.5°	108.2	138.6	172.8	194.6	202.4
80°	84.8	116.0	150.2	173.6	179.8
82.5°	61.5	94.2	128.4	152.6	159.6
85°	41.3	74.0	109.0	132.3	140.1
87.5°	25.7	57.6	91.9	114.4	121.4
90°	16.0	59.9	102.8	132.3	140.9
92.5°	29.2	54.1	96.9	125.7	131.9
95°	74.2	60.3	93.4	121.4	129.5
97.5°	131.8	180.0	89.5	115.6	123.8
100°	199.9	241.0	110.5	111.7	118.3
102.5°	276.8	307.9	351.5	109.3	115.5
105°	358.0	380.6	415.3	445.2	409.5
107.5°	433.8	450.5	486.0	511.2	521.4
110°	510.0	524.4	558.7	578.9	588.6

TEST NUMBER: P1001476

CATALOG NUMBER: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	583.8	600.2	628.3	644.2	655.1
115°	660.1	670.6	694.3	713.8	719.3
117.5°	728.9	738.2	765.1	780.2	786.5
120°	798.1	805.1	826.5	844.4	848.3
122.5°	863.4	865.7	889.1	905.8	908.9
125°	924.4	928.3	945.4	963.7	969.6
127.5°	983.9	984.2	1005.7	1018.5	1022.8
130°	1040.2	1040.7	1056.6	1071.8	1076.5
132.5°	1092.7	1094.3	1108.3	1122.7	1126.2
135°	1144.5	1143.3	1153.4	1168.2	1175.1
137.5°	1191.1	1190.3	1199.3	1213.3	1216.0
140°	1236.6	1238.1	1241.3	1254.9	1259.9
142.5°	1276.6	1281.3	1281.7	1292.6	1295.7
145°	1318.6	1321.3	1321.3	1327.2	1332.6
147.5°	1351.3	1357.5	1356.3	1358.3	1362.5
150°	1387.4	1391.3	1390.1	1390.1	1391.3
152.5°	1416.9	1420.4	1418.1	1420.4	1419.3
155°	1444.9	1446.1	1442.6	1447.3	1443.8
157.5°	1469.4	1469.4	1464.8	1470.6	1464.8
160°	1490.4	1486.9	1485.7	1492.7	1485.7
162.5°	1509.1	1504.4	1503.2	1510.2	1502.1
165°	1524.2	1518.4	1518.4	1527.7	1517.2
167.5°	1537.1	1531.2	1530.1	1540.6	1528.9
170°	1547.6	1540.6	1541.7	1551.1	1539.4
172.5°	1554.6	1547.6	1548.7	1558.1	1545.2
175°	1559.2	1552.2	1553.4	1563.9	1549.9
177.5°	1562.7	1554.6	1556.9	1566.2	1552.2
180°	1559.2	1559.2	1559.2	1559.2	1559.2

(END OF REPORT)