

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001534

Luminaire Tested: SA4XXDIP-B575D365UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001534
REPORT IS A COMBINATION OF REPORTS P996154 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D365UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3831.0 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001534

CATALOG NUMBER: SA4XXDIP-B575D365UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001534

CATALOG NUMBER: SA4XXDIP-B575D365UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57		
1	98	93	89	85	91	87	83	80	75	72	69	64	62	60	53	52	51	46		
2	89	81	74	68	82	75	69	64	65	60	56	55	52	49	46	44	42	37		
3	81	71	63	56	75	66	59	53	57	51	47	48	44	41	41	38	35	31		
4	74	62	54	47	68	58	51	45	50	44	40	43	38	35	36	33	30	26		
5	68	55	47	40	63	52	44	38	45	39	34	38	34	30	32	29	26	23		
6	62	50	41	35	58	46	39	33	40	34	29	35	30	26	29	25	22	20		
7	58	45	36	31	53	42	34	29	36	30	26	31	27	23	27	23	20	17		
8	53	41	32	27	49	38	31	26	33	27	23	29	24	20	24	21	18	15		
9	50	37	29	24	46	35	28	23	30	25	20	26	22	18	23	19	16	14		
10	46	34	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5642	5642	5642
5°	5658	5495	5505
10°	5621	5387	5372
15°	5568	5266	5221
20°	5490	5133	5075
25°	5403	4988	4917
30°	5307	4845	4756
35°	5200	4698	4613
40°	5114	4557	4465
45°	4986	4424	4334
50°	4877	4274	4196
55°	4765	4129	4037
60°	4591	3949	3887
65°	4399	3754	3706
70°	4165	3531	3498
75°	3841	3285	3299
80°	3475	3032	3092
85°	2991	2780	2924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4986 cd/sqm

TEST NUMBER: P1001534

CATALOG NUMBER: SA4XXDIP-B575D365UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	1.7
10°-20°	187.8	4.9
20°-30°	284.0	7.4
30°-40°	343.6	9.0
40°-50°	363.2	9.5
50°-60°	341.9	8.9
60°-70°	283.7	7.4
70°-80°	199.1	5.2
80°-90°	113.2	3.0
90°-100°	82.6	2.2
100°-110°	153.4	4.0
110°-120°	231.6	6.0
120°-130°	270.6	7.1
130°-140°	277.6	7.2
140°-150°	253.6	6.6
150°-160°	203.2	5.3
160°-170°	131.1	3.4
170°-180°	45.2	1.2
0°-30°	537.4	14.0
0°-40°	881.0	23.0
0°-60°	1586.1	41.4
0°-90°	2182.1	57.0
90°-120°	467.6	12.2
90°-150°	1269.5	33.1
90°-180°	1649.0	43.0
0°-180°	3831.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	692	692	692	692	692	
5°	693	690	685	691	690	66
15°	664	665	662	669	669	187
25°	608	612	614	623	624	280
35°	532	541	549	559	562	333
45°	443	458	473	486	490	343
55°	347	363	387	402	407	309
65°	240	265	291	311	317	238
75°	133	162	194	216	223	142
85°	41	74	108	132	140	43
90°	14	48	84	109	116	10
95°	30	43	75	98	106	32
105°	114	132	162	185	178	120
115°	204	212	237	255	260	202
125°	284	285	303	319	324	254
135°	350	350	356	370	375	270
145°	403	403	403	408	412	252
155°	440	441	440	441	440	203
165°	465	463	463	466	463	131
175°	475	473	474	477	472	45
180°	475	475	475	475	475	

TEST NUMBER: P1001534

CATALOG NUMBER: SA4XXDIP-B575D365UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	691.9	691.9	691.9	691.9	691.9
2.5°	695.0	692.7	686.5	691.9	691.1
5°	692.7	690.4	684.9	691.1	690.4
7.5°	688.0	686.5	681.8	688.8	688.0
10°	681.8	681.1	677.2	684.2	683.4
12.5°	673.3	673.3	671.0	677.2	677.2
15°	664.0	664.8	662.5	669.4	668.7
17.5°	651.6	653.9	653.2	660.1	659.4
20°	638.4	640.8	641.5	649.3	649.3
22.5°	623.7	626.8	628.4	636.1	637.7
25°	607.5	612.1	614.4	623.0	623.7
27.5°	589.6	596.6	599.7	607.5	608.2
30°	571.8	578.0	583.4	592.0	593.5
32.5°	552.4	560.2	566.4	576.5	578.0
35°	531.5	540.8	548.6	559.4	561.7
37.5°	510.6	521.4	530.7	541.6	543.9
40°	490.5	500.5	511.4	523.0	526.1
42.5°	467.2	478.8	492.0	505.2	507.5
45°	443.2	457.9	472.6	485.8	489.7
47.5°	420.7	435.4	452.5	465.7	470.3
50°	395.9	413.0	430.0	445.5	450.2
52.5°	371.1	388.2	408.3	423.8	428.5
55°	347.1	363.4	386.6	402.1	406.8
57.5°	320.0	340.1	362.6	381.2	385.1
60°	293.7	313.8	339.4	357.2	363.4
62.5°	268.1	290.6	316.1	333.9	340.1
65°	240.2	265.0	291.3	310.7	316.9
67.5°	213.8	240.2	268.1	287.5	293.7
70°	186.7	213.1	242.5	263.4	268.9
72.5°	160.4	187.5	219.3	239.4	245.6
75°	133.3	161.9	194.5	216.2	223.1
77.5°	107.7	137.9	172.0	193.7	201.5
80°	84.5	115.4	149.5	172.8	179.0
82.5°	61.2	93.8	127.8	151.9	158.8
85°	41.1	73.6	108.5	131.7	139.5
87.5°	25.6	57.3	91.4	113.9	120.9
90°	13.5	48.4	84.5	109.2	116.1
92.5°	16.9	43.3	79.6	103.4	109.6
95°	29.7	43.1	75.2	98.3	105.6
97.5°	46.6	77.0	71.3	93.3	100.7
100°	66.8	93.4	74.5	89.4	95.2
102.5°	90.3	111.6	145.3	85.5	91.7
105°	114.0	131.7	162.0	184.6	178.0
107.5°	137.1	151.3	181.0	202.1	209.0
110°	159.8	171.7	201.0	219.5	226.8



TEST NUMBER: P1001534

CATALOG NUMBER: SA4XXDIP-B575D365UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.8	193.2	219.5	236.1	243.8
115°	204.4	212.5	236.9	254.7	260.1
117.5°	225.4	231.5	255.8	271.7	277.9
120°	246.0	249.8	271.9	288.1	293.6
122.5°	266.0	266.7	288.3	304.1	308.8
125°	284.0	284.6	303.3	319.1	324.1
127.5°	302.1	301.7	319.0	332.6	337.7
130°	318.8	318.3	331.8	346.1	350.7
132.5°	334.8	334.7	345.4	358.9	363.3
135°	350.0	349.6	356.5	369.6	374.9
137.5°	364.2	363.5	368.4	380.7	384.2
140°	378.0	378.1	379.5	390.6	394.9
142.5°	389.8	391.2	390.8	400.0	403.1
145°	402.6	402.9	402.9	407.8	411.6
147.5°	412.5	413.9	413.5	414.7	418.1
150°	423.6	424.2	423.8	423.8	424.2
152.5°	432.0	433.1	432.4	433.1	432.7
155°	440.5	440.9	439.8	441.3	440.2
157.5°	448.0	448.0	446.6	448.4	446.6
160°	454.4	453.3	453.0	455.1	453.0
162.5°	460.1	458.7	458.3	460.5	458.0
165°	464.7	462.9	462.9	465.8	462.6
167.5°	468.6	466.9	466.5	469.7	466.1
170°	471.8	469.7	470.1	472.9	469.3
172.5°	474.0	471.8	472.2	475.0	471.1
175°	475.4	473.3	473.6	476.8	472.5
177.5°	476.5	474.0	474.7	477.5	473.3
180°	475.4	475.4	475.4	475.4	475.4

(END OF REPORT)