

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001600

Luminaire Tested: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001600
REPORT IS A COMBINATION OF REPORTS P996222 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4662.0 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001600

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001600

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48
2	89	82	76	70	82	76	70	66	64	61	57	54	51	49	44	42	41
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30
5	68	57	49	43	63	53	45	40	45	40	35	38	34	31	32	29	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	25	46	36	29	24	31	25	22	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7584	7584	7584
5°	7589	7366	7375
10°	7526	7161	7111
15°	7417	6918	6813
20°	7280	6655	6506
25°	7125	6377	6174
30°	6937	6077	5811
35°	6744	5769	5459
40°	6541	5438	5085
45°	6330	5106	4735
50°	6095	4785	4348
55°	5841	4408	3963
60°	5579	3997	3563
65°	5282	3572	3111
70°	4937	3059	2627
75°	4424	2467	2104
80°	3771	1783	1480
85°	2925	992	797

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6330 cd/sqm

TEST NUMBER: P1001600

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.9
10°-20°	247.0	5.3
20°-30°	363.4	7.8
30°-40°	422.5	9.1
40°-50°	422.5	9.1
50°-60°	369.5	7.9
60°-70°	274.3	5.9
70°-80°	155.6	3.3
80°-90°	46.1	1.0
90°-100°	24.4	0.5
100°-110°	160.6	3.4
110°-120°	306.7	6.6
120°-130°	389.4	8.4
130°-140°	416.5	8.9
140°-150°	389.5	8.4
150°-160°	314.1	6.7
160°-170°	202.6	4.3
170°-180°	69.8	1.5
0°-30°	698.1	15.0
0°-40°	1120.5	24.0
0°-60°	1912.5	41.0
0°-90°	2388.5	51.2
90°-120°	491.7	10.5
90°-150°	1687.0	36.2
90°-180°	2273.0	48.8
0°-180°	4662.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	930	930	930	930	930	
5°	929	926	918	926	925	88
15°	884	882	870	875	873	249
25°	801	796	785	786	783	369
35°	689	684	674	668	665	431
45°	563	557	546	537	535	434
55°	426	423	413	404	399	381
65°	288	285	277	270	266	285
75°	154	150	146	143	142	163
85°	40	40	39	39	38	43
90°	2	8	12	15	16	4
95°	30	12	12	15	16	37
105°	165	169	172	176	157	173
115°	309	310	310	311	311	304
125°	434	436	435	437	437	388
135°	538	538	540	541	542	415
145°	621	623	623	623	624	388
155°	681	681	680	682	680	314
165°	718	716	716	720	715	203
175°	735	731	732	737	730	70
180°	735	735	735	735	735	

TEST NUMBER: P1001600

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	930.0	930.0	930.0	930.0	930.0
2.5°	933.0	930.7	922.5	930.0	929.2
5°	929.2	926.3	918.1	926.3	924.8
7.5°	922.5	919.6	910.6	917.3	916.6
10°	912.9	909.9	900.2	906.1	904.7
12.5°	900.2	897.2	886.8	893.5	891.2
15°	884.5	881.6	870.4	874.8	872.6
17.5°	866.6	862.9	852.5	855.5	854.0
20°	846.5	842.8	831.6	833.9	832.4
22.5°	824.9	819.7	808.5	813.0	810.0
25°	801.1	795.9	785.4	786.2	783.2
27.5°	774.2	769.0	759.3	757.9	754.1
30°	747.4	741.5	731.8	728.8	725.1
32.5°	719.1	713.9	703.5	699.7	696.0
35°	689.3	684.1	673.6	668.4	664.7
37.5°	658.0	653.5	642.3	637.1	631.9
40°	627.4	621.5	610.3	602.9	599.1
42.5°	594.7	591.7	579.0	570.1	567.8
45°	562.6	557.4	545.5	537.3	535.0
47.5°	529.1	525.4	514.2	505.2	499.3
50°	494.8	491.8	481.4	471.0	466.5
52.5°	461.3	457.5	446.4	437.4	431.5
55°	425.5	423.3	412.8	403.9	399.4
57.5°	392.0	389.7	379.3	370.4	365.9
60°	356.9	353.2	343.5	336.8	333.1
62.5°	322.7	319.7	309.3	303.3	299.6
65°	288.4	284.7	277.2	269.8	266.0
67.5°	253.4	250.4	242.9	235.5	234.7
70°	221.3	216.1	210.1	204.2	201.9
72.5°	187.0	181.8	177.4	172.9	170.6
75°	153.5	149.8	146.1	143.1	142.3
77.5°	120.7	119.2	115.5	114.8	112.5
80°	91.7	89.4	87.9	86.4	85.7
82.5°	63.3	62.6	62.6	61.9	61.1
85°	40.2	40.2	38.7	38.7	38.0
87.5°	19.4	18.6	17.9	17.9	17.9
90°	1.6	7.7	12.1	15.4	16.5
92.5°	8.2	7.1	11.5	14.8	14.8
95°	30.2	11.5	12.1	15.4	15.9
97.5°	57.7	69.8	12.1	14.8	15.4
100°	90.1	100.0	24.2	14.8	15.4
102.5°	126.4	133.0	139.6	15.9	15.9
105°	165.4	168.7	171.5	176.4	156.6
107.5°	201.1	202.8	206.6	209.4	211.6
110°	237.4	239.0	242.3	243.4	245.1

TEST NUMBER: P1001600

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	272.6	275.9	277.0	276.4	278.6
115°	308.8	310.5	309.9	311.0	311.0
117.5°	341.3	343.5	345.1	344.6	344.6
120°	374.2	376.4	375.9	377.0	375.9
122.5°	405.0	406.1	407.2	407.8	406.7
125°	434.1	436.3	435.2	436.9	437.4
127.5°	462.2	462.7	465.5	464.9	464.4
130°	489.1	489.6	491.3	491.8	491.8
132.5°	513.8	514.9	517.1	517.7	517.1
135°	538.5	538.0	540.2	541.3	542.4
137.5°	560.5	560.5	563.3	564.4	563.8
140°	582.0	583.1	584.1	585.8	586.3
142.5°	601.2	603.4	603.9	605.0	605.0
145°	621.0	622.6	622.6	623.2	624.3
147.5°	636.4	639.7	639.1	639.7	640.2
150°	653.4	655.6	655.0	655.0	655.6
152.5°	667.7	669.3	668.2	669.3	668.8
155°	680.9	681.4	679.8	682.0	680.3
157.5°	692.4	692.4	690.2	693.0	690.2
160°	702.3	700.6	700.1	703.4	700.1
162.5°	711.1	708.9	708.3	711.6	707.8
165°	718.2	715.5	715.5	719.9	714.9
167.5°	724.3	721.5	721.0	725.9	720.4
170°	729.2	725.9	726.5	730.9	725.4
172.5°	732.5	729.2	729.8	734.2	728.1
175°	734.7	731.4	732.0	736.9	730.3
177.5°	736.4	732.5	733.6	738.0	731.4
180°	734.7	734.7	734.7	734.7	734.7

(END OF REPORT)