

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001651

Luminaire Tested: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001651
REPORT IS A COMBINATION OF REPORTS P996273 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5473.0 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001651

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001651

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47			40
1	95	90	86	82	86	82	78	75	67	64	62	53	51	49	40	39	38			32
2	86	78	72	66	78	71	66	61	58	54	51	46	43	41	35	33	31			26
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26			22
4	71	60	52	46	64	55	48	43	45	40	36	36	32	29	27	24	22			18
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	21	19			16
6	60	48	40	34	54	44	36	31	36	30	26	29	25	21	22	19	17			14
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15			12
8	51	39	31	26	46	36	29	24	29	24	20	24	20	17	18	15	13			11
9	48	35	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12			10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5594	5594	5594
5°	5610	5448	5458
10°	5574	5341	5326
15°	5521	5220	5177
20°	5444	5090	5032
25°	5357	4946	4875
30°	5263	4804	4716
35°	5156	4658	4574
40°	5070	4518	4427
45°	4944	4387	4297
50°	4836	4238	4161
55°	4725	4094	4002
60°	4552	3915	3854
65°	4362	3723	3675
70°	4130	3502	3469
75°	3807	3256	3272
80°	3442	3008	3066
85°	2962	2757	2899

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4944 cd/sqm

TEST NUMBER: P1001651

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	1.2
10°-20°	186.2	3.4
20°-30°	281.6	5.1
30°-40°	340.7	6.2
40°-50°	360.2	6.6
50°-60°	339.0	6.2
60°-70°	281.3	5.1
70°-80°	197.4	3.6
80°-90°	113.4	2.1
90°-100°	99.8	1.8
100°-110°	270.3	4.9
110°-120°	455.4	8.3
120°-130°	554.9	10.1
130°-140°	581.8	10.6
140°-150°	538.1	9.8
150°-160°	432.7	7.9
160°-170°	279.0	5.1
170°-180°	96.2	1.8
0°-30°	532.8	9.7
0°-40°	873.5	16.0
0°-60°	1572.7	28.7
0°-90°	2164.7	39.6
90°-120°	825.6	15.1
90°-150°	2500.4	45.7
90°-180°	3308.0	60.4
0°-180°	5473.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	686	686	686	686	686	
5°	687	684	679	685	684	65
15°	658	659	657	664	663	186
25°	602	607	609	618	618	277
35°	527	536	544	555	557	330
45°	439	454	469	482	486	340
55°	344	360	383	399	403	307
65°	238	263	289	308	314	236
75°	132	161	193	214	221	140
85°	41	73	108	131	138	42
90°	15	54	93	120	127	11
95°	52	51	84	109	116	59
105°	235	255	287	313	292	246
115°	430	439	463	482	487	424
125°	601	603	621	638	643	537
135°	743	743	751	765	771	573
145°	856	858	858	863	868	535
155°	938	939	936	940	937	433
165°	989	986	986	992	985	280
175°	1012	1008	1008	1015	1006	96
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P1001651

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	686.0	686.0	686.0	686.0	686.0
2.5°	689.1	686.8	680.7	686.0	685.3
5°	686.8	684.5	679.1	685.3	684.5
7.5°	682.2	680.7	676.1	683.0	682.2
10°	676.1	675.3	671.4	678.4	677.6
12.5°	667.6	667.6	665.3	671.4	671.4
15°	658.4	659.2	656.8	663.8	663.0
17.5°	646.1	648.4	647.6	654.5	653.8
20°	633.0	635.3	636.1	643.8	643.8
22.5°	618.4	621.5	623.0	630.7	632.3
25°	602.3	606.9	609.2	617.7	618.4
27.5°	584.6	591.5	594.6	602.3	603.1
30°	567.0	573.1	578.5	586.9	588.5
32.5°	547.8	555.4	561.6	571.6	573.1
35°	527.0	536.2	543.9	554.7	557.0
37.5°	506.3	517.0	526.2	537.0	539.3
40°	486.3	496.3	507.0	518.6	521.6
42.5°	463.3	474.8	487.8	500.9	503.2
45°	439.4	454.0	468.6	481.7	485.5
47.5°	417.2	431.8	448.7	461.7	466.3
50°	392.6	409.5	426.4	441.7	446.4
52.5°	368.0	384.9	404.9	420.2	424.8
55°	344.2	360.3	383.4	398.7	403.3
57.5°	317.3	337.3	359.5	378.0	381.8
60°	291.2	311.1	336.5	354.2	360.3
62.5°	265.8	288.1	313.4	331.1	337.3
65°	238.2	262.7	288.9	308.1	314.2
67.5°	212.0	238.2	265.8	285.0	291.2
70°	185.1	211.3	240.5	261.2	266.6
72.5°	159.0	185.9	217.4	237.4	243.5
75°	132.1	160.6	192.8	214.3	221.3
77.5°	106.8	136.7	170.6	192.1	199.7
80°	83.7	114.5	148.3	171.3	177.5
82.5°	60.7	93.0	126.8	150.6	157.5
85°	40.7	73.0	107.6	130.6	138.3
87.5°	25.4	56.9	90.7	112.9	119.8
90°	14.6	53.6	92.8	119.5	127.2
92.5°	22.9	48.2	87.3	113.4	119.5
95°	51.6	51.2	83.5	108.8	116.5
97.5°	88.7	127.6	79.7	103.4	111.1
100°	132.7	166.2	91.7	99.5	105.7
102.5°	182.6	208.6	246.8	96.5	102.7
105°	234.8	254.7	286.9	312.9	291.9
107.5°	284.0	299.3	331.5	354.5	362.9
110°	333.1	346.2	377.6	396.9	405.2

TEST NUMBER: P1001651

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.9	394.6	421.4	437.7	446.8
115°	430.0	439.2	463.1	481.5	486.9
117.5°	474.7	482.3	507.7	523.1	529.2
120°	519.3	524.7	546.2	563.1	567.7
122.5°	561.7	563.2	585.6	601.6	605.5
125°	601.1	603.4	621.1	637.9	643.3
127.5°	639.8	639.7	658.9	671.9	676.6
130°	676.0	676.0	690.6	705.2	709.8
132.5°	710.1	710.8	723.2	736.9	740.8
135°	743.4	742.6	751.1	764.9	771.0
137.5°	773.7	773.0	779.7	792.9	795.9
140°	803.2	804.0	806.2	818.5	823.1
142.5°	829.0	832.0	832.0	842.0	845.0
145°	856.2	857.7	857.7	863.1	867.7
147.5°	877.4	881.2	880.4	882.0	885.7
150°	900.9	903.1	902.4	902.4	903.1
152.5°	919.8	922.1	920.5	922.1	921.3
155°	937.9	938.7	936.4	939.5	937.2
157.5°	953.8	953.8	950.8	954.6	950.8
160°	967.5	965.2	964.4	969.0	964.4
162.5°	979.6	976.6	975.8	980.3	975.0
165°	989.4	985.6	985.6	991.7	984.9
167.5°	997.8	994.0	993.2	1000.0	992.5
170°	1004.6	1000.0	1000.8	1006.8	999.3
172.5°	1009.1	1004.6	1005.3	1011.4	1003.1
175°	1012.1	1007.6	1008.4	1015.2	1006.1
177.5°	1014.4	1009.1	1010.6	1016.7	1007.6
180°	1012.1	1012.1	1012.1	1012.1	1012.1

(END OF REPORT)