

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001653

Luminaire Tested: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001653
REPORT IS A COMBINATION OF REPORTS P996275 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5545.0 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001653

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1001653

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47
1	95	90	86	82	86	82	78	75	67	64	62	53	51	49	40	39	38
2	86	78	72	66	78	71	66	61	58	54	51	46	43	41	35	33	31
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26
4	71	60	52	46	64	55	48	43	45	40	36	36	32	29	27	24	22
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	21	19
6	60	48	40	34	54	44	36	31	36	30	26	29	25	21	22	19	17
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15
8	51	39	31	26	46	36	29	24	29	24	20	24	20	17	18	15	13
9	48	35	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5668	5668	5668
5°	5684	5521	5531
10°	5647	5412	5397
15°	5594	5290	5246
20°	5516	5157	5098
25°	5428	5012	4940
30°	5333	4868	4779
35°	5224	4720	4635
40°	5137	4578	4486
45°	5010	4445	4354
50°	4901	4294	4216
55°	4787	4148	4055
60°	4611	3967	3905
65°	4419	3772	3724
70°	4185	3547	3514
75°	3859	3300	3315
80°	3488	3046	3106
85°	3005	2793	2937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5010 cd/sqm

TEST NUMBER: P1001653

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	1.2
10°-20°	188.7	3.4
20°-30°	285.3	5.1
30°-40°	345.2	6.2
40°-50°	364.9	6.6
50°-60°	343.5	6.2
60°-70°	285.0	5.1
70°-80°	200.0	3.6
80°-90°	114.9	2.1
90°-100°	101.2	1.8
100°-110°	273.9	4.9
110°-120°	461.4	8.3
120°-130°	562.2	10.1
130°-140°	589.4	10.6
140°-150°	545.2	9.8
150°-160°	438.3	7.9
160°-170°	282.7	5.1
170°-180°	97.4	1.8
0°-30°	539.9	9.7
0°-40°	885.1	16.0
0°-60°	1593.5	28.7
0°-90°	2193.4	39.6
90°-120°	836.4	15.1
90°-150°	2533.2	45.7
90°-180°	3352.0	60.5
0°-180°	5545.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	696	694	688	694	694	66
15°	667	668	666	673	672	188
25°	610	615	617	626	627	281
35°	534	543	551	562	564	334
45°	445	460	475	488	492	344
55°	349	365	388	404	409	311
65°	241	266	293	312	318	239
75°	134	163	195	217	224	142
85°	41	74	109	132	140	43
90°	15	54	94	121	129	11
95°	52	52	85	110	118	60
105°	238	258	291	317	296	250
115°	436	445	469	488	493	429
125°	609	611	629	646	652	544
135°	753	752	761	775	781	581
145°	867	869	869	874	879	542
155°	950	951	949	952	950	438
165°	1002	998	998	1005	998	283
175°	1025	1021	1022	1028	1019	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1001653

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.1	695.1	695.1	695.1	695.1
2.5°	698.2	695.9	689.7	695.1	694.4
5°	695.9	693.6	688.1	694.4	693.6
7.5°	691.2	689.7	685.0	692.0	691.2
10°	685.0	684.2	680.3	687.4	686.6
12.5°	676.5	676.5	674.1	680.3	680.3
15°	667.1	667.9	665.6	672.6	671.8
17.5°	654.7	657.0	656.2	663.2	662.4
20°	641.4	643.8	644.5	652.3	652.3
22.5°	626.6	629.7	631.3	639.1	640.6
25°	610.3	615.0	617.3	625.9	626.6
27.5°	592.4	599.4	602.5	610.3	611.1
30°	574.5	580.7	586.2	594.7	596.3
32.5°	555.0	562.8	569.0	579.1	580.7
35°	534.0	543.3	551.1	562.0	564.4
37.5°	513.0	523.9	533.2	544.1	546.5
40°	492.7	502.9	513.8	525.4	528.6
42.5°	469.4	481.1	494.3	507.5	509.9
45°	445.3	460.1	474.8	488.1	492.0
47.5°	422.7	437.5	454.6	467.8	472.5
50°	397.8	414.9	432.0	447.6	452.3
52.5°	372.9	390.0	410.2	425.8	430.5
55°	348.7	365.1	388.4	404.0	408.7
57.5°	321.5	341.7	364.3	383.0	386.9
60°	295.0	315.3	341.0	358.9	365.1
62.5°	269.3	291.9	317.6	335.5	341.7
65°	241.3	266.2	292.7	312.1	318.4
67.5°	214.8	241.3	269.3	288.8	295.0
70°	187.6	214.1	243.6	264.7	270.1
72.5°	161.1	188.4	220.3	240.5	246.8
75°	133.9	162.7	195.4	217.2	224.2
77.5°	108.2	138.6	172.8	194.6	202.4
80°	84.8	116.0	150.2	173.6	179.8
82.5°	61.5	94.2	128.4	152.6	159.6
85°	41.3	74.0	109.0	132.3	140.1
87.5°	25.7	57.6	91.9	114.4	121.4
90°	14.8	54.3	94.0	121.1	128.9
92.5°	23.2	48.9	88.5	114.9	121.1
95°	52.3	51.9	84.6	110.2	117.9
97.5°	89.8	129.3	80.7	104.8	112.6
100°	134.4	168.4	92.9	100.9	107.1
102.5°	185.0	211.3	250.1	97.7	103.9
105°	237.8	258.0	290.7	317.0	295.7
107.5°	287.7	303.2	335.9	359.1	367.7
110°	337.5	350.7	382.6	402.0	410.5

TEST NUMBER: P1001653

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	385.8	399.8	427.0	443.4	452.6
115°	435.7	445.0	469.1	487.8	493.3
117.5°	481.0	488.6	514.3	529.9	536.2
120°	526.2	531.5	553.4	570.5	575.2
122.5°	569.1	570.7	593.2	609.6	613.4
125°	609.0	611.2	629.2	646.3	651.8
127.5°	648.1	648.1	667.5	680.7	685.5
130°	684.9	684.9	699.6	714.4	719.1
132.5°	719.4	720.2	732.6	746.5	750.5
135°	753.2	752.4	760.9	774.9	781.1
137.5°	783.9	783.1	790.0	803.2	806.4
140°	813.8	814.5	816.8	829.2	833.9
142.5°	839.8	842.9	842.9	853.0	856.1
145°	867.4	868.9	868.9	874.4	879.0
147.5°	888.9	892.7	891.9	893.5	897.4
150°	912.7	914.9	914.2	914.2	914.9
152.5°	931.8	934.1	932.6	934.1	933.3
155°	950.2	951.0	948.7	951.8	949.5
157.5°	966.3	966.3	963.3	967.1	963.3
160°	980.1	977.8	977.1	981.7	977.1
162.5°	992.4	989.3	988.6	993.2	987.8
165°	1002.4	998.5	998.5	1004.7	997.8
167.5°	1010.8	1007.0	1006.2	1013.1	1005.4
170°	1017.7	1013.1	1013.9	1020.0	1012.3
172.5°	1022.3	1017.7	1018.5	1024.6	1016.2
175°	1025.4	1020.8	1021.5	1028.4	1019.2
177.5°	1027.7	1022.3	1023.8	1030.0	1020.8
180°	1025.4	1025.4	1025.4	1025.4	1025.4

(END OF REPORT)