

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001655

Luminaire Tested: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001655
REPORT IS A COMBINATION OF REPORTS P996277 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_5000K
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5309.0 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001655

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001655

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47			40
1	95	90	86	82	86	82	78	75	67	64	62	53	51	49	40	39	38			32
2	86	78	72	66	78	71	66	61	58	54	51	46	43	41	35	33	31			26
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26			22
4	71	60	52	46	64	55	48	43	45	40	36	36	32	29	27	24	22			18
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	21	19			16
6	60	48	40	34	54	44	36	31	36	30	26	29	25	21	22	19	17			14
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15			12
8	51	39	31	26	46	36	29	24	29	24	20	24	20	17	18	15	13			11
9	48	35	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12			10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5427	5427	5427
5°	5442	5285	5295
10°	5406	5182	5167
15°	5356	5065	5022
20°	5281	4938	4881
25°	5197	4798	4729
30°	5105	4660	4575
35°	5001	4518	4437
40°	4918	4383	4294
45°	4796	4255	4168
50°	4691	4111	4036
55°	4583	3972	3883
60°	4416	3798	3738
65°	4230	3611	3565
70°	4007	3397	3364
75°	3694	3160	3173
80°	3340	2916	2975
85°	2874	2673	2811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4796 cd/sqm

TEST NUMBER: P1001655

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.2
10°-20°	180.7	3.4
20°-30°	273.2	5.1
30°-40°	330.5	6.2
40°-50°	349.4	6.6
50°-60°	328.8	6.2
60°-70°	272.9	5.1
70°-80°	191.5	3.6
80°-90°	110.0	2.1
90°-100°	96.9	1.8
100°-110°	262.2	4.9
110°-120°	441.8	8.3
120°-130°	538.3	10.1
130°-140°	564.3	10.6
140°-150°	522.0	9.8
150°-160°	419.7	7.9
160°-170°	270.7	5.1
170°-180°	93.3	1.8
0°-30°	516.9	9.7
0°-40°	847.4	16.0
0°-60°	1525.6	28.7
0°-90°	2099.9	39.6
90°-120°	800.9	15.1
90°-150°	2425.4	45.7
90°-180°	3209.0	60.4
0°-180°	5309.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	666	666	666	666	666	
5°	666	664	659	665	664	63
15°	639	639	637	644	643	180
25°	584	589	591	599	600	269
35°	511	520	528	538	540	320
45°	426	440	455	467	471	329
55°	334	350	372	387	391	298
65°	231	255	280	299	305	229
75°	128	156	187	208	215	136
85°	40	71	104	127	134	41
90°	14	52	90	116	123	10
95°	50	50	81	106	113	58
105°	228	247	278	304	283	239
115°	417	426	449	467	472	411
125°	583	585	602	619	624	521
135°	721	720	728	742	748	556
145°	830	832	832	837	842	519
155°	910	911	908	911	909	420
165°	960	956	956	962	955	271
175°	982	977	978	985	976	93
180°	982	982	982	982	982	

TEST NUMBER: P1001655

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	665.5	665.5	665.5	665.5	665.5
2.5°	668.5	666.3	660.3	665.5	664.8
5°	666.3	664.0	658.8	664.8	664.0
7.5°	661.8	660.3	655.8	662.5	661.8
10°	655.8	655.1	651.4	658.1	657.3
12.5°	647.6	647.6	645.4	651.4	651.4
15°	638.7	639.4	637.2	643.9	643.2
17.5°	626.8	629.0	628.2	635.0	634.2
20°	614.1	616.3	617.1	624.5	624.5
22.5°	599.9	602.9	604.4	611.9	613.3
25°	584.3	588.7	591.0	599.2	599.9
27.5°	567.1	573.8	576.8	584.3	585.0
30°	550.0	556.0	561.2	569.4	570.9
32.5°	531.4	538.8	544.8	554.5	556.0
35°	511.2	520.2	527.6	538.1	540.3
37.5°	491.1	501.6	510.5	520.9	523.2
40°	471.7	481.4	491.9	503.0	506.0
42.5°	449.4	460.6	473.2	485.9	488.1
45°	426.3	440.4	454.6	467.3	471.0
47.5°	404.7	418.8	435.2	447.9	452.4
50°	380.8	397.2	413.6	428.5	433.0
52.5°	357.0	373.4	392.7	407.7	412.1
55°	333.9	349.5	371.9	386.8	391.3
57.5°	307.8	327.2	348.8	366.7	370.4
60°	282.5	301.8	326.4	343.6	349.5
62.5°	257.9	279.5	304.1	321.2	327.2
65°	231.0	254.9	280.2	298.8	304.8
67.5°	205.7	231.0	257.9	276.5	282.5
70°	179.6	204.9	233.3	253.4	258.6
72.5°	154.3	180.4	210.9	230.3	236.2
75°	128.2	155.8	187.1	207.9	214.6
77.5°	103.6	132.7	165.4	186.3	193.8
80°	81.2	111.0	143.8	166.2	172.2
82.5°	58.9	90.2	123.0	146.1	152.8
85°	39.5	70.8	104.3	126.7	134.1
87.5°	24.6	55.1	87.9	109.6	116.3
90°	14.1	52.0	90.0	116.0	123.4
92.5°	22.2	46.8	84.7	110.0	115.9
95°	50.1	49.7	81.0	105.6	113.0
97.5°	86.0	123.9	77.3	100.3	107.8
100°	128.6	161.2	88.9	96.6	102.6
102.5°	177.1	202.3	239.4	93.6	99.6
105°	227.7	247.0	278.3	303.5	283.1
107.5°	275.5	290.4	321.6	343.9	352.0
110°	323.2	335.8	366.3	384.9	393.1

TEST NUMBER: P1001655

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	369.4	382.8	408.9	424.5	433.4
115°	417.2	426.1	449.2	467.0	472.2
117.5°	460.5	467.8	492.5	507.4	513.3
120°	503.8	509.0	529.9	546.2	550.7
122.5°	544.9	546.4	567.9	583.7	587.4
125°	583.1	585.2	602.5	618.8	624.0
127.5°	620.6	620.5	639.1	651.8	656.3
130°	655.7	655.8	669.9	684.0	688.5
132.5°	688.8	689.6	701.4	714.8	718.6
135°	721.1	720.4	728.5	741.9	747.9
137.5°	750.5	749.7	756.4	769.0	772.0
140°	779.1	779.8	782.1	794.0	798.4
142.5°	804.0	807.0	807.0	816.7	819.7
145°	830.5	832.0	832.0	837.2	841.7
147.5°	851.0	854.7	854.0	855.4	859.2
150°	873.8	876.0	875.3	875.3	876.0
152.5°	892.2	894.4	892.9	894.4	893.7
155°	909.8	910.6	908.3	911.3	909.1
157.5°	925.2	925.2	922.3	926.0	922.3
160°	938.5	936.3	935.5	939.9	935.5
162.5°	950.2	947.3	946.5	950.9	945.8
165°	959.8	956.1	956.1	962.0	955.3
167.5°	967.8	964.2	963.4	970.0	962.7
170°	974.4	970.0	970.8	976.6	969.3
172.5°	978.8	974.4	975.2	981.0	973.0
175°	981.8	977.4	978.1	984.7	975.9
177.5°	984.0	978.8	980.3	986.2	977.4
180°	981.8	981.8	981.8	981.8	981.8

(END OF REPORT)