

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001713

Luminaire Tested: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001713
REPORT IS A COMBINATION OF REPORTS P996335 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7379.0 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001713

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1001713

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41	41	41	41
1	95	90	86	82	86	82	79	76	67	65	63	54	52	50	41	40	39	33	33	33	33
2	86	78	72	67	78	71	66	61	59	55	51	47	44	41	36	34	32	27	27	27	27
3	78	69	61	55	71	63	56	51	51	46	42	41	37	34	31	29	27	22	22	22	22
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	28	25	23	19	19	19	19
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	25	22	20	16	16	16	16
6	60	48	40	34	54	44	37	31	36	31	27	29	25	22	22	20	17	14	14	14	14
7	56	43	35	30	50	40	32	27	33	27	23	26	22	19	20	17	15	12	12	12	12
8	51	39	31	26	47	36	29	24	30	24	21	24	20	17	19	16	14	11	11	11	11
9	48	36	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12	10	10	10	10
10	45	33	25	20	41	30	23	19	25	20	16	20	16	14	16	13	11	9	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7821	7821	7821
5°	7843	7617	7631
10°	7791	7467	7446
15°	7718	7299	7237
20°	7611	7116	7034
25°	7489	6915	6816
30°	7357	6715	6593
35°	7208	6512	6395
40°	7089	6317	6190
45°	6911	6133	6008
50°	6761	5924	5816
55°	6605	5723	5595
60°	6364	5473	5387
65°	6097	5203	5138
70°	5774	4896	4849
75°	5323	4553	4573
80°	4816	4204	4286
85°	4141	3854	4052

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6911 cd/sqm

TEST NUMBER: P1001713

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	1.2
10°-20°	260.4	3.5
20°-30°	393.7	5.3
30°-40°	476.3	6.5
40°-50°	503.5	6.8
50°-60°	473.9	6.4
60°-70°	393.2	5.3
70°-80°	276.0	3.7
80°-90°	158.3	2.1
90°-100°	136.7	1.9
100°-110°	358.7	4.9
110°-120°	600.0	8.1
120°-130°	729.2	9.9
130°-140°	763.5	10.3
140°-150°	705.7	9.6
150°-160°	567.3	7.7
160°-170°	365.8	5.0
170°-180°	126.1	1.7
0°-30°	744.9	10.1
0°-40°	1221.2	16.6
0°-60°	2198.6	29.8
0°-90°	3026.1	41.0
90°-120°	1095.3	14.8
90°-150°	3293.6	44.6
90°-180°	4353.0	59.0
0°-180°	7379.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	960	957	949	958	957	91
15°	920	922	918	928	927	259
25°	842	848	852	864	865	388
35°	737	750	760	776	779	461
45°	614	635	655	673	679	475
55°	481	504	536	557	564	429
65°	333	367	404	431	439	330
75°	185	224	270	300	309	196
85°	57	102	150	183	193	59
90°	20	74	128	165	176	15
95°	69	70	115	150	161	78
105°	308	336	381	416	389	324
115°	564	577	610	636	643	556
125°	788	791	816	840	847	704
135°	975	974	985	1004	1013	751
145°	1123	1124	1124	1132	1138	702
155°	1230	1231	1228	1232	1229	567
165°	1297	1292	1292	1300	1291	367
175°	1327	1321	1322	1331	1319	126
180°	1327	1327	1327	1327	1327	

TEST NUMBER: P1001713

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	959.1	959.1	959.1	959.1	959.1
2.5°	963.4	960.2	951.6	959.1	958.0
5°	960.2	957.0	949.4	958.0	957.0
7.5°	953.7	951.6	945.1	954.8	953.7
10°	945.1	944.1	938.7	948.4	947.3
12.5°	933.3	933.3	930.1	938.7	938.7
15°	920.4	921.5	918.3	928.0	926.9
17.5°	903.3	906.5	905.4	915.1	914.0
20°	885.0	888.2	889.3	900.0	900.0
22.5°	864.6	868.9	871.0	881.8	883.9
25°	842.0	848.5	851.7	863.5	864.6
27.5°	817.3	827.0	831.3	842.0	843.1
30°	792.6	801.2	808.7	820.6	822.7
32.5°	765.8	776.5	785.1	799.1	801.2
35°	736.8	749.7	760.4	775.5	778.7
37.5°	707.8	722.8	735.7	750.7	754.0
40°	679.9	693.8	708.9	725.0	729.3
42.5°	647.6	663.8	682.0	700.3	703.5
45°	614.3	634.8	655.2	673.4	678.8
47.5°	583.2	603.6	627.2	645.5	651.9
50°	548.8	572.5	596.1	617.6	624.0
52.5°	514.5	538.1	566.0	587.5	593.9
55°	481.2	503.7	535.9	557.4	563.9
57.5°	443.6	471.5	502.6	528.4	533.8
60°	407.1	435.0	470.4	495.1	503.7
62.5°	371.6	402.8	438.2	462.9	471.5
65°	332.9	367.3	403.8	430.7	439.3
67.5°	296.4	332.9	371.6	398.5	407.1
70°	258.8	295.4	336.2	365.2	372.7
72.5°	222.3	259.9	304.0	331.9	340.5
75°	184.7	224.5	269.6	299.7	309.3
77.5°	149.3	191.2	238.4	268.5	279.2
80°	117.1	160.0	207.3	239.5	248.1
82.5°	84.8	130.0	177.2	210.5	220.2
85°	56.9	102.0	150.4	182.6	193.3
87.5°	35.4	79.5	126.7	157.9	167.5
90°	20.2	74.0	128.1	165.3	175.9
92.5°	31.0	66.6	120.7	156.8	165.4
95°	68.6	70.2	115.2	150.2	160.9
97.5°	117.1	170.1	109.9	142.8	153.5
100°	174.6	220.3	125.3	137.4	145.9
102.5°	240.1	275.6	328.4	133.0	141.6
105°	308.5	335.8	380.6	416.3	389.2
107.5°	373.0	394.1	438.7	470.6	482.0
110°	437.4	455.4	498.9	525.6	537.2

TEST NUMBER: P1001713

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	499.8	518.7	556.0	578.7	591.3
115°	564.2	576.9	610.3	635.9	643.4
117.5°	622.8	633.2	668.4	690.0	698.6
120°	681.3	688.5	718.6	742.1	748.7
122.5°	736.9	738.9	769.9	792.3	797.9
125°	788.4	791.3	816.2	839.6	847.0
127.5°	839.0	838.9	865.4	883.7	890.3
130°	886.6	886.4	906.6	927.0	933.4
132.5°	931.2	932.1	949.0	968.3	973.7
135°	974.8	973.8	985.4	1004.5	1012.9
137.5°	1014.5	1013.5	1022.7	1040.8	1045.2
140°	1053.2	1054.2	1057.2	1074.1	1080.5
142.5°	1086.9	1090.9	1090.8	1104.6	1108.9
145°	1122.7	1124.5	1124.5	1131.9	1138.2
147.5°	1150.5	1155.3	1154.3	1156.4	1161.7
150°	1181.2	1184.1	1183.1	1183.1	1184.1
152.5°	1205.9	1208.9	1206.9	1208.9	1207.9
155°	1229.7	1230.7	1227.8	1231.7	1228.8
157.5°	1250.6	1250.6	1246.6	1251.6	1246.6
160°	1268.5	1265.5	1264.5	1270.4	1264.5
162.5°	1284.3	1280.4	1279.4	1285.3	1278.4
165°	1297.2	1292.3	1292.3	1300.2	1291.3
167.5°	1308.2	1303.2	1302.2	1311.1	1301.2
170°	1317.1	1311.1	1312.1	1320.1	1310.1
172.5°	1323.0	1317.1	1318.1	1326.0	1315.1
175°	1327.0	1321.1	1322.1	1331.0	1319.1
177.5°	1330.0	1323.0	1325.0	1333.0	1321.1
180°	1327.0	1327.0	1327.0	1327.0	1327.0

(END OF REPORT)