

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001405

Luminaire Tested: SA4XXDIP-B575D1035UB27-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001405
REPORT IS A COMBINATION OF REPORTS P996024 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1035UB27-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5980.3 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001405

CATALOG NUMBER: SA4XXDIP-B575D1035UB27-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001405

CATALOG NUMBER: SA4XXDIP-B575D1035UB27-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	94	89	85	82	85	81	77	74	65	63	60	51	49	47	37	36	35
2	85	78	71	66	77	70	65	60	57	53	49	44	41	39	32	31	29
3	78	68	60	55	70	62	55	50	50	45	41	39	35	33	28	26	24
4	71	60	52	46	64	54	47	42	44	39	35	34	31	28	25	23	21
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18
6	60	47	39	34	54	43	36	31	35	30	26	27	24	21	20	18	16
7	55	43	35	29	49	39	32	27	32	26	22	25	21	18	19	16	14
8	51	39	31	26	46	35	28	24	29	24	20	23	19	16	17	14	12
9	47	35	28	23	43	32	25	21	26	21	18	21	17	14	16	13	11
10	44	32	25	20	40	29	23	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5594	5594	5594
5°	5610	5448	5458
10°	5574	5341	5326
15°	5521	5220	5177
20°	5444	5090	5032
25°	5357	4946	4875
30°	5263	4804	4716
35°	5156	4658	4574
40°	5070	4518	4427
45°	4944	4387	4297
50°	4836	4238	4161
55°	4725	4094	4002
60°	4552	3915	3854
65°	4362	3723	3675
70°	4130	3502	3469
75°	3807	3256	3272
80°	3442	3008	3066
85°	2962	2757	2899

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4944 cd/sqm

TEST NUMBER: P1001405

CATALOG NUMBER: SA4XXDIP-B575D1035UB27-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	1.1
10°-20°	186.2	3.1
20°-30°	281.6	4.7
30°-40°	340.7	5.7
40°-50°	360.2	6.0
50°-60°	339.0	5.7
60°-70°	281.3	4.7
70°-80°	197.4	3.3
80°-90°	113.2	1.9
90°-100°	436.7	7.3
100°-110°	802.5	13.4
110°-120°	704.5	11.8
120°-130°	582.6	9.7
130°-140°	478.7	8.0
140°-150°	361.1	6.0
150°-160°	252.7	4.2
160°-170°	148.6	2.5
170°-180°	48.3	0.8
0°-30°	532.8	8.9
0°-40°	873.5	14.6
0°-60°	1572.7	26.3
0°-90°	2164.5	36.2
90°-120°	1943.6	32.5
90°-150°	3366.1	56.3
90°-180°	3816.0	63.8
0°-180°	5980.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	686	686	686	686	686	
5°	687	684	679	685	684	65
15°	658	659	657	664	663	186
25°	602	607	609	618	618	277
35°	527	536	544	555	557	330
45°	439	454	469	482	486	340
55°	344	360	383	399	403	307
65°	238	263	289	308	314	236
75°	132	161	193	214	221	140
85°	41	73	108	131	138	42
90°	13	51	94	118	125	11
95°	42	137	865	483	334	43
105°	122	188	693	1454	1455	130
115°	206	265	609	1154	1382	205
125°	284	336	592	973	1097	254
135°	336	399	572	851	968	260
145°	386	441	562	706	779	242
155°	438	473	547	619	646	202
165°	477	492	524	555	563	135
175°	498	499	503	510	508	47
180°	499	499	499	499	499	

TEST NUMBER: P1001405

CATALOG NUMBER: SA4XXDIP-B575D1035UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	686.0	686.0	686.0	686.0	686.0
2.5°	689.1	686.8	680.7	686.0	685.3
5°	686.8	684.5	679.1	685.3	684.5
7.5°	682.2	680.7	676.1	683.0	682.2
10°	676.1	675.3	671.4	678.4	677.6
12.5°	667.6	667.6	665.3	671.4	671.4
15°	658.4	659.2	656.8	663.8	663.0
17.5°	646.1	648.4	647.6	654.5	653.8
20°	633.0	635.3	636.1	643.8	643.8
22.5°	618.4	621.5	623.0	630.7	632.3
25°	602.3	606.9	609.2	617.7	618.4
27.5°	584.6	591.5	594.6	602.3	603.1
30°	567.0	573.1	578.5	586.9	588.5
32.5°	547.8	555.4	561.6	571.6	573.1
35°	527.0	536.2	543.9	554.7	557.0
37.5°	506.3	517.0	526.2	537.0	539.3
40°	486.3	496.3	507.0	518.6	521.6
42.5°	463.3	474.8	487.8	500.9	503.2
45°	439.4	454.0	468.6	481.7	485.5
47.5°	417.2	431.8	448.7	461.7	466.3
50°	392.6	409.5	426.4	441.7	446.4
52.5°	368.0	384.9	404.9	420.2	424.8
55°	344.2	360.3	383.4	398.7	403.3
57.5°	317.3	337.3	359.5	378.0	381.8
60°	291.2	311.1	336.5	354.2	360.3
62.5°	265.8	288.1	313.4	331.1	337.3
65°	238.2	262.7	288.9	308.1	314.2
67.5°	212.0	238.2	265.8	285.0	291.2
70°	185.1	211.3	240.5	261.2	266.6
72.5°	159.0	185.9	217.4	237.4	243.5
75°	132.1	160.6	192.8	214.3	221.3
77.5°	106.8	136.7	170.6	192.1	199.7
80°	83.7	114.5	148.3	171.3	177.5
82.5°	60.7	93.0	126.8	150.6	157.5
85°	40.7	73.0	107.6	130.6	138.3
87.5°	25.4	56.9	90.7	112.9	119.8
90°	13.3	50.8	93.7	117.9	125.1
92.5°	25.2	113.8	455.5	219.8	188.3
95°	42.3	137.2	865.3	482.9	333.6
97.5°	63.1	144.2	917.3	890.3	664.0
100°	83.0	155.8	846.1	1195.9	982.9
102.5°	102.6	170.4	758.9	1385.4	1261.3
105°	121.5	188.4	693.4	1453.8	1454.6
107.5°	144.1	207.6	649.4	1427.9	1543.9
110°	165.8	226.0	627.7	1344.9	1542.1

TEST NUMBER: P1001405

CATALOG NUMBER: SA4XXDIP-B575D1035UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	186.7	245.4	615.0	1244.3	1479.7
115°	206.4	264.8	609.2	1154.2	1382.0
117.5°	228.0	283.5	604.5	1082.1	1287.0
120°	248.7	301.0	600.6	1031.8	1207.9
122.5°	268.3	318.8	595.8	998.1	1144.6
125°	284.3	336.4	591.7	973.3	1096.9
127.5°	300.0	354.0	585.9	948.6	1065.6
130°	311.9	370.4	581.1	920.8	1037.5
132.5°	324.6	385.0	577.1	888.4	1007.2
135°	335.6	399.2	572.2	851.0	968.3
137.5°	347.3	410.8	569.1	811.9	923.5
140°	360.1	422.0	565.8	773.8	875.6
142.5°	373.1	432.4	564.3	738.8	824.7
145°	385.8	440.9	562.4	706.1	778.7
147.5°	400.5	449.7	559.4	678.3	735.7
150°	414.2	458.0	556.5	655.4	699.5
152.5°	426.2	465.8	551.6	636.8	670.1
155°	437.9	472.8	546.7	619.2	645.6
157.5°	449.7	479.1	541.8	602.5	623.1
160°	460.5	484.5	535.9	585.9	602.5
162.5°	470.3	488.9	530.0	569.7	582.9
165°	477.1	491.8	524.2	555.0	563.3
167.5°	485.0	494.2	518.3	542.3	547.7
170°	489.9	496.2	512.4	529.6	533.0
172.5°	494.8	497.7	506.5	518.3	518.3
175°	497.7	498.7	502.6	509.5	507.5
177.5°	499.7	498.7	499.7	503.1	499.7
180°	498.7	498.7	498.7	498.7	498.7

(END OF REPORT)