

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001833

Luminaire Tested: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001833
REPORT IS A COMBINATION OF REPORTS P996456 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4701.0 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001833

CATALOG NUMBER: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001833

CATALOG NUMBER: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	100	95	90	86	93	89	85	81	78	75	72	68	66	64	59	57	55
2	90	82	75	69	84	77	71	66	68	63	59	59	55	52	51	48	46
3	82	72	64	57	76	67	60	54	59	53	49	52	47	43	45	41	38
4	75	63	55	48	70	59	52	46	52	46	41	46	41	37	40	36	33
5	69	56	47	41	64	53	45	39	47	40	35	41	36	32	36	31	28
6	63	50	42	35	59	47	40	34	42	36	31	37	32	28	32	28	25
7	58	45	37	31	54	43	35	30	38	32	27	34	28	24	29	25	22
8	54	41	33	27	51	39	31	26	35	28	24	31	25	22	27	23	19
9	50	38	30	24	47	36	28	23	32	26	21	28	23	19	25	21	18
10	47	34	27	22	44	33	26	21	29	23	19	26	21	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7742	7742	7742
5°	7763	7541	7554
10°	7713	7392	7371
15°	7641	7225	7164
20°	7534	7044	6964
25°	7413	6845	6747
30°	7283	6648	6527
35°	7136	6446	6330
40°	7017	6253	6127
45°	6842	6071	5947
50°	6693	5865	5757
55°	6538	5665	5539
60°	6300	5418	5333
65°	6036	5152	5085
70°	5716	4846	4799
75°	5271	4507	4527
80°	4767	4162	4242
85°	4097	3813	4012

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6842 cd/sqm

TEST NUMBER: P1001833

CATALOG NUMBER: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	1.9
10°-20°	257.7	5.5
20°-30°	389.7	8.3
30°-40°	471.5	10.0
40°-50°	498.4	10.6
50°-60°	469.1	10.0
60°-70°	389.3	8.3
70°-80°	273.2	5.8
80°-90°	155.0	3.3
90°-100°	107.4	2.3
100°-110°	171.3	3.6
110°-120°	242.9	5.2
120°-130°	276.2	5.9
130°-140°	279.1	5.9
140°-150°	252.8	5.4
150°-160°	202.1	4.3
160°-170°	130.3	2.8
170°-180°	44.9	1.0
0°-30°	737.4	15.7
0°-40°	1208.9	25.7
0°-60°	2176.5	46.3
0°-90°	2993.9	63.7
90°-120°	521.6	11.1
90°-150°	1329.7	28.3
90°-180°	1707.0	36.3
0°-180°	4701.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	949	949	949	949	949	
5°	950	947	940	948	947	90
15°	911	912	909	919	918	257
25°	834	840	843	855	856	384
35°	729	742	753	768	771	457
45°	608	628	648	667	672	470
55°	476	499	530	552	558	424
65°	330	364	400	426	435	327
75°	183	222	267	297	306	194
85°	56	101	149	181	191	59
90°	18	64	113	146	155	13
95°	33	56	100	131	141	35
105°	116	139	180	210	206	122
115°	205	216	249	274	281	202
125°	284	284	310	331	338	254
135°	349	348	357	375	382	269
145°	401	401	401	407	412	250
155°	438	438	437	439	438	202
165°	462	460	460	463	460	131
175°	473	471	471	474	470	45
180°	473	473	473	473	473	

TEST NUMBER: P1001833

CATALOG NUMBER: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	949.4	949.4	949.4	949.4	949.4
2.5°	953.7	950.5	942.0	949.4	948.4
5°	950.5	947.3	939.9	948.4	947.3
7.5°	944.1	942.0	935.6	945.2	944.1
10°	935.6	934.5	929.2	938.8	937.7
12.5°	923.9	923.9	920.7	929.2	929.2
15°	911.2	912.2	909.0	918.6	917.5
17.5°	894.1	897.3	896.3	905.8	904.8
20°	876.1	879.3	880.3	891.0	891.0
22.5°	855.9	860.1	862.2	872.9	875.0
25°	833.5	839.9	843.1	854.8	855.9
27.5°	809.1	818.7	822.9	833.5	834.6
30°	784.6	793.1	800.6	812.3	814.4
32.5°	758.1	768.7	777.2	791.0	793.1
35°	729.4	742.1	752.7	767.6	770.8
37.5°	700.6	715.5	728.3	743.2	746.4
40°	673.0	686.8	701.7	717.7	721.9
42.5°	641.1	657.1	675.1	693.2	696.4
45°	608.1	628.3	648.5	666.6	671.9
47.5°	577.3	597.5	620.9	639.0	645.4
50°	543.3	566.7	590.1	611.3	617.7
52.5°	509.3	532.7	560.3	581.6	587.9
55°	476.3	498.6	530.5	551.8	558.2
57.5°	439.1	466.7	497.6	523.1	528.4
60°	403.0	430.6	465.7	490.1	498.6
62.5°	367.9	398.7	433.8	458.2	466.7
65°	329.6	363.6	399.8	426.3	434.8
67.5°	293.4	329.6	367.9	394.4	403.0
70°	256.2	292.4	332.8	361.5	368.9
72.5°	220.1	257.3	300.9	328.5	337.0
75°	182.9	222.2	266.9	296.6	306.2
77.5°	147.8	189.2	236.0	265.8	276.4
80°	115.9	158.4	205.2	237.1	245.6
82.5°	84.0	128.6	175.4	208.4	218.0
85°	56.3	101.0	148.8	180.7	191.4
87.5°	35.1	78.7	125.5	156.3	165.9
90°	18.1	64.5	113.1	146.0	155.2
92.5°	21.2	57.8	106.3	138.1	146.7
95°	33.2	56.3	100.3	131.1	141.1
97.5°	49.9	88.5	95.0	124.3	134.3
100°	69.7	103.7	96.4	119.0	126.9
102.5°	93.0	120.7	165.3	113.4	121.9
105°	116.0	139.4	180.5	210.3	206.1
107.5°	139.0	158.1	197.9	226.1	235.0
110°	161.3	177.2	216.6	241.8	251.3

TEST NUMBER: P1001833

CATALOG NUMBER: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.8	197.7	233.5	256.6	266.5
115°	205.1	215.7	249.4	273.6	281.0
117.5°	226.0	233.8	266.8	288.7	297.2
120°	246.1	250.7	281.2	303.2	311.0
122.5°	265.9	266.6	296.0	317.7	324.4
125°	283.7	284.0	309.9	331.1	337.8
127.5°	301.7	301.0	324.0	342.8	349.8
130°	317.9	317.2	335.2	354.8	361.2
132.5°	333.8	333.5	347.7	366.1	372.1
135°	348.7	348.3	357.2	374.9	382.0
137.5°	362.8	361.8	367.8	384.5	389.4
140°	376.6	376.3	378.0	392.9	398.6
142.5°	388.0	389.4	388.6	401.0	405.2
145°	400.7	400.7	400.7	407.4	412.3
147.5°	410.6	411.6	411.3	412.7	417.3
150°	421.6	421.9	421.5	421.5	421.9
152.5°	429.7	430.7	430.0	430.7	430.4
155°	438.1	438.5	437.4	438.9	437.8
157.5°	445.6	445.6	444.2	445.9	444.2
160°	451.9	450.9	450.5	452.6	450.5
162.5°	457.6	456.2	455.8	458.0	455.5
165°	462.2	460.4	460.4	463.3	460.1
167.5°	466.1	464.3	464.0	467.1	463.6
170°	469.3	467.1	467.5	470.3	466.8
172.5°	471.4	469.3	469.6	472.5	468.6
175°	472.8	470.7	471.0	474.2	470.0
177.5°	473.9	471.4	472.1	474.9	470.7
180°	472.8	472.8	472.8	472.8	472.8

(END OF REPORT)