

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001440

Luminaire Tested: SA4XXDIP-B575D1035UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001440
REPORT IS A COMBINATION OF REPORTS P996059 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1035UB35-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6056.0 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001440

CATALOG NUMBER: SA4XXDIP-B575D1035UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001440

CATALOG NUMBER: SA4XXDIP-B575D1035UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	105	105	105	105	96	96	96	96		78	78	78		63	63	63		48	48	48
1	96	91	88	84	87	84	80	77		69	66	64		55	53	52		42	41	40
2	87	80	74	69	79	73	68	63		60	56	53		48	46	43		37	36	34
3	80	70	63	57	72	64	58	53		53	48	45		43	39	37		33	31	29
4	73	62	54	48	66	57	50	45		47	42	38		38	34	31		30	27	25
5	67	55	47	41	61	51	44	38		42	37	33		34	30	27		27	24	22
6	61	49	41	36	56	45	38	33		38	32	28		31	27	24		24	21	19
7	57	45	37	31	52	41	34	29		34	29	25		28	24	21		22	19	17
8	53	40	33	28	48	37	30	26		31	26	22		26	22	19		20	17	15
9	49	37	29	24	45	34	27	23		29	23	20		23	20	17		19	16	14
10	46	34	27	22	42	31	25	21		26	21	18		22	18	15		17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7920	7920	7920
5°	7927	7692	7702
10°	7860	7479	7426
15°	7747	7225	7116
20°	7603	6951	6794
25°	7441	6660	6449
30°	7246	6347	6069
35°	7043	6026	5701
40°	6832	5680	5310
45°	6611	5333	4946
50°	6367	4997	4541
55°	6100	4605	4140
60°	5828	4175	3721
65°	5516	3730	3249
70°	5156	3196	2744
75°	4619	2575	2199
80°	3936	1862	1546
85°	3056	1038	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6611 cd/sqm

TEST NUMBER: P1001440

CATALOG NUMBER: SA4XXDIP-B575D1035UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.5
10°-20°	257.9	4.3
20°-30°	379.6	6.3
30°-40°	441.2	7.3
40°-50°	441.2	7.3
50°-60°	385.9	6.4
60°-70°	286.5	4.7
70°-80°	162.5	2.7
80°-90°	49.3	0.8
90°-100°	83.6	1.4
100°-110°	250.5	4.1
110°-120°	425.6	7.0
120°-130°	561.3	9.3
130°-140°	630.4	10.4
140°-150°	619.6	10.2
150°-160°	521.1	8.6
160°-170°	346.7	5.7
170°-180°	121.4	2.0
0°-30°	729.1	12.0
0°-40°	1170.3	19.3
0°-60°	1997.4	33.0
0°-90°	2495.7	41.2
90°-120°	759.7	12.5
90°-150°	2571.0	42.5
90°-180°	3560.0	58.8
0°-180°	6056.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	921	909	914	911	260
25°	837	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	149	149	170
85°	42	42	40	40	40	45
90°	3	14	22	28	30	7
95°	60	68	75	78	78	64
105°	231	232	236	239	242	245
115°	433	433	431	430	429	427
125°	630	630	629	627	625	562
135°	813	819	819	817	814	629
145°	987	991	992	991	988	618
155°	1131	1131	1130	1134	1130	521
165°	1232	1229	1227	1232	1229	347
175°	1281	1276	1275	1282	1275	122
180°	1283	1283	1283	1283	1283	

TEST NUMBER: P1001440

CATALOG NUMBER: SA4XXDIP-B575D1035UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	971.3	971.3	971.3	971.3	971.3
2.5°	974.4	972.1	963.5	971.3	970.5
5°	970.5	967.4	958.8	967.4	965.8
7.5°	963.5	960.4	951.1	958.1	957.3
10°	953.4	950.3	940.2	946.4	944.8
12.5°	940.2	937.0	926.1	933.2	930.8
15°	923.8	920.7	909.0	913.7	911.4
17.5°	905.1	901.2	890.3	893.5	891.9
20°	884.1	880.2	868.6	870.9	869.3
22.5°	861.6	856.1	844.4	849.1	846.0
25°	836.6	831.2	820.3	821.1	818.0
27.5°	808.6	803.2	793.1	791.5	787.6
30°	780.6	774.4	764.3	761.2	757.3
32.5°	751.0	745.6	734.7	730.8	726.9
35°	719.9	714.5	703.6	698.1	694.2
37.5°	687.2	682.5	670.9	665.4	660.0
40°	655.3	649.1	637.4	629.6	625.7
42.5°	621.1	618.0	604.7	595.4	593.0
45°	587.6	582.2	569.7	561.1	558.8
47.5°	552.6	548.7	537.0	527.7	521.4
50°	516.8	513.7	502.8	491.9	487.2
52.5°	481.8	477.9	466.2	456.8	450.6
55°	444.4	442.1	431.2	421.8	417.2
57.5°	409.4	407.0	396.1	386.8	382.1
60°	372.8	368.9	358.8	351.8	347.9
62.5°	337.0	333.9	323.0	316.8	312.9
65°	301.2	297.3	289.5	281.7	277.8
67.5°	264.6	261.5	253.7	245.9	245.2
70°	231.1	225.7	219.5	213.2	210.9
72.5°	195.3	189.9	185.2	180.6	178.2
75°	160.3	156.4	152.5	149.4	148.7
77.5°	126.1	124.5	120.6	119.9	117.5
80°	95.7	93.4	91.8	90.3	89.5
82.5°	66.2	65.4	65.4	64.6	63.8
85°	42.0	42.0	40.5	40.5	39.7
87.5°	20.2	19.5	18.7	18.7	18.7
90°	3.0	13.9	21.8	27.8	29.8
92.5°	25.8	38.7	43.7	46.6	47.6
95°	59.5	68.5	75.4	78.4	78.4
97.5°	95.3	103.2	111.1	115.1	115.1
100°	138.9	142.9	151.8	153.8	153.8
102.5°	184.6	185.6	193.5	196.5	197.5
105°	231.2	232.2	236.2	239.2	242.1
107.5°	279.9	280.8	281.8	285.8	284.8
110°	329.5	331.5	330.5	328.5	331.5

TEST NUMBER: P1001440

CATALOG NUMBER: SA4XXDIP-B575D1035UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	381.1	381.1	379.1	379.1	379.1
115°	432.7	432.7	430.7	429.7	428.7
117.5°	481.3	481.3	480.3	477.3	474.4
120°	529.9	533.9	530.9	526.0	527.9
122.5°	580.5	581.5	580.5	577.6	572.6
125°	630.2	630.2	629.2	627.2	625.2
127.5°	674.8	677.8	675.8	673.8	672.8
130°	722.5	725.4	725.4	723.4	719.5
132.5°	771.1	773.1	772.1	770.1	769.1
135°	812.8	818.7	818.7	816.7	813.8
137.5°	859.4	862.4	864.4	861.4	862.4
140°	906.0	908.0	908.0	907.0	906.0
142.5°	948.7	950.7	949.7	949.7	949.7
145°	987.4	991.4	992.4	991.4	988.4
147.5°	1027.1	1032.1	1031.1	1030.1	1029.1
150°	1062.8	1066.8	1066.8	1066.8	1065.8
152.5°	1096.6	1098.6	1099.6	1102.5	1099.6
155°	1131.3	1131.3	1130.3	1134.3	1130.3
157.5°	1161.1	1159.1	1159.1	1162.1	1159.1
160°	1186.9	1185.9	1184.9	1187.9	1182.9
162.5°	1210.7	1207.7	1206.7	1212.7	1207.7
165°	1231.5	1228.6	1226.6	1232.5	1228.6
167.5°	1248.4	1244.4	1244.4	1250.4	1244.4
170°	1262.3	1257.3	1258.3	1264.3	1257.3
172.5°	1272.2	1268.3	1268.3	1275.2	1268.3
175°	1281.2	1276.2	1275.2	1282.2	1275.2
177.5°	1285.1	1280.2	1280.2	1287.1	1279.2
180°	1283.1	1283.1	1283.1	1283.1	1283.1

(END OF REPORT)