

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001895

Luminaire Tested: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001895
REPORT IS A COMBINATION OF REPORTS P996520 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5817.0 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001895

CATALOG NUMBER: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1001895

CATALOG NUMBER: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	42	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10929	10929	10929
5°	10938	10615	10627
10°	10845	10320	10247
15°	10690	9969	9820
20°	10491	9591	9376
25°	10268	9190	8898
30°	9998	8757	8374
35°	9719	8314	7867
40°	9427	7837	7328
45°	9122	7359	6824
50°	8785	6895	6266
55°	8417	6353	5711
60°	8041	5760	5134
65°	7611	5148	4484
70°	7117	4409	3786
75°	6374	3555	3032
80°	5433	2570	2133
85°	4221	1430	1149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9122 cd/sqm

TEST NUMBER: P1001895

CATALOG NUMBER: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.2
10°-20°	355.9	6.1
20°-30°	523.8	9.0
30°-40°	608.9	10.5
40°-50°	608.8	10.5
50°-60°	532.5	9.2
60°-70°	395.3	6.8
70°-80°	224.3	3.9
80°-90°	65.8	1.1
90°-100°	25.5	0.4
100°-110°	167.8	2.9
110°-120°	320.5	5.5
120°-130°	406.8	7.0
130°-140°	435.2	7.5
140°-150°	406.9	7.0
150°-160°	328.2	5.6
160°-170°	211.6	3.6
170°-180°	72.9	1.3
0°-30°	1006.0	17.3
0°-40°	1614.9	27.8
0°-60°	2756.1	47.4
0°-90°	3441.6	59.2
90°-120°	513.8	8.8
90°-150°	1762.7	30.3
90°-180°	2375.0	40.8
0°-180°	5817.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1339	1335	1323	1335	1333	127
15°	1275	1270	1254	1261	1258	359
25°	1154	1147	1132	1133	1129	531
35°	993	986	971	963	958	621
45°	811	803	786	774	771	625
55°	613	610	595	582	576	549
65°	416	410	400	389	383	411
75°	221	216	210	206	205	235
85°	58	58	56	56	55	62
90°	2	8	13	16	17	5
95°	32	12	13	16	17	39
105°	173	176	179	184	164	181
115°	323	324	324	325	325	318
125°	454	456	455	456	457	405
135°	563	562	564	566	567	434
145°	649	650	650	651	652	405
155°	711	712	710	712	711	328
165°	750	748	748	752	747	212
175°	768	764	765	770	763	73
180°	768	768	768	768	768	

TEST NUMBER: P1001895

CATALOG NUMBER: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.2	1340.2	1340.2	1340.2	1340.2
2.5°	1344.5	1341.3	1329.5	1340.2	1339.2
5°	1339.2	1334.9	1323.1	1334.9	1332.7
7.5°	1329.5	1325.2	1312.3	1322.0	1320.9
10°	1315.5	1311.2	1297.3	1305.9	1303.7
12.5°	1297.3	1293.0	1278.0	1287.6	1284.4
15°	1274.7	1270.4	1254.3	1260.8	1257.6
17.5°	1249.0	1243.6	1228.6	1232.9	1230.7
20°	1220.0	1214.6	1198.5	1201.7	1199.6
22.5°	1188.8	1181.3	1165.2	1171.6	1167.3
25°	1154.5	1146.9	1131.9	1133.0	1128.7
27.5°	1115.8	1108.3	1094.3	1092.2	1086.8
30°	1077.1	1068.5	1054.6	1050.3	1044.9
32.5°	1036.3	1028.8	1013.8	1008.4	1003.0
35°	993.4	985.9	970.8	963.3	957.9
37.5°	948.3	941.8	925.7	918.2	910.7
40°	904.2	895.6	879.5	868.8	863.4
42.5°	857.0	852.7	834.4	821.5	818.3
45°	810.8	803.3	786.1	774.3	771.1
47.5°	762.5	757.1	741.0	728.1	719.5
50°	713.1	708.8	693.7	678.7	672.3
52.5°	664.8	659.4	643.3	630.4	621.8
55°	613.2	610.0	594.9	582.1	575.6
57.5°	564.9	561.7	546.6	533.7	527.3
60°	514.4	509.0	495.1	485.4	480.0
62.5°	465.0	460.7	445.7	437.1	431.7
65°	415.6	410.2	399.5	388.8	383.4
67.5°	365.1	360.8	350.1	339.4	338.3
70°	319.0	311.4	302.8	294.3	291.0
72.5°	269.6	262.0	255.6	249.1	245.9
75°	221.2	215.9	210.5	206.2	205.1
77.5°	174.0	171.8	166.5	165.4	162.2
80°	132.1	128.9	126.7	124.6	123.5
82.5°	91.3	90.2	90.2	89.1	88.1
85°	58.0	58.0	55.8	55.8	54.8
87.5°	27.9	26.8	25.8	25.8	25.8
90°	1.7	8.0	12.6	16.1	17.2
92.5°	8.6	7.5	12.1	15.5	15.5
95°	31.6	12.1	12.6	16.1	16.7
97.5°	60.3	72.9	12.6	15.5	16.1
100°	94.2	104.5	25.3	15.5	16.1
102.5°	132.1	138.9	145.8	16.7	16.7
105°	172.8	176.3	179.1	184.3	163.6
107.5°	210.1	211.9	215.9	218.8	221.1
110°	248.0	249.8	253.2	254.4	256.1



TEST NUMBER: P1001895

CATALOG NUMBER: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.8	288.2	289.4	288.8	291.1
115°	322.7	324.4	323.8	325.0	325.0
117.5°	356.6	358.9	360.6	360.0	360.0
120°	391.0	393.3	392.7	393.9	392.7
122.5°	423.2	424.3	425.5	426.0	424.9
125°	453.6	455.9	454.7	456.5	457.0
127.5°	482.9	483.4	486.3	485.7	485.2
130°	511.0	511.6	513.3	513.9	513.9
132.5°	536.8	538.0	540.3	540.9	540.3
135°	562.7	562.1	564.4	565.6	566.7
137.5°	585.7	585.7	588.5	589.7	589.1
140°	608.0	609.2	610.3	612.1	612.6
142.5°	628.1	630.4	631.0	632.2	632.2
145°	648.8	650.5	650.5	651.1	652.3
147.5°	664.9	668.3	667.8	668.3	668.9
150°	682.7	685.0	684.4	684.4	685.0
152.5°	697.6	699.3	698.2	699.3	698.8
155°	711.4	712.0	710.2	712.5	710.8
157.5°	723.5	723.5	721.2	724.0	721.2
160°	733.8	732.1	731.5	734.9	731.5
162.5°	743.0	740.7	740.1	743.5	739.5
165°	750.4	747.6	747.6	752.2	747.0
167.5°	756.8	753.9	753.3	758.5	752.7
170°	761.9	758.5	759.0	763.6	757.9
172.5°	765.4	761.9	762.5	767.1	760.8
175°	767.7	764.2	764.8	770.0	763.1
177.5°	769.4	765.4	766.5	771.1	764.2
180°	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)