

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001896

Luminaire Tested: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001896
REPORT IS A COMBINATION OF REPORTS P996521 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5759.0 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001896

CATALOG NUMBER: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001896

CATALOG NUMBER: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	42	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10821	10821	10821
5°	10830	10510	10523
10°	10738	10218	10146
15°	10584	9871	9722
20°	10387	9495	9283
25°	10166	9099	8810
30°	9899	8671	8291
35°	9623	8232	7789
40°	9335	7759	7255
45°	9032	7286	6756
50°	8697	6827	6204
55°	8334	6291	5655
60°	7961	5703	5084
65°	7536	5096	4439
70°	7045	4367	3750
75°	6311	3519	3003
80°	5380	2545	2113
85°	4177	1417	1136

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9032 cd/sqm

TEST NUMBER: P1001896

CATALOG NUMBER: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.2
10°-20°	352.4	6.1
20°-30°	518.6	9.0
30°-40°	602.8	10.5
40°-50°	602.8	10.5
50°-60°	527.2	9.2
60°-70°	391.4	6.8
70°-80°	222.1	3.9
80°-90°	65.2	1.1
90°-100°	25.2	0.4
100°-110°	166.1	2.9
110°-120°	317.2	5.5
120°-130°	402.7	7.0
130°-140°	430.8	7.5
140°-150°	402.8	7.0
150°-160°	324.8	5.6
160°-170°	209.5	3.6
170°-180°	72.2	1.3
0°-30°	996.1	17.3
0°-40°	1598.9	27.8
0°-60°	2728.9	47.4
0°-90°	3407.6	59.2
90°-120°	508.5	8.8
90°-150°	1744.9	30.3
90°-180°	2351.0	40.8
0°-180°	5759.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1327	1327	1327	1327	1327	
5°	1326	1322	1310	1322	1320	126
15°	1262	1258	1242	1248	1245	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	961	954	948	615
45°	803	795	778	767	763	619
55°	607	604	589	576	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	232
85°	57	57	55	55	54	62
90°	2	8	12	16	17	5
95°	31	12	12	16	16	39
105°	171	174	177	182	162	179
115°	319	321	321	322	322	314
125°	449	451	450	452	452	401
135°	557	556	559	560	561	429
145°	642	644	644	644	646	401
155°	704	705	703	705	704	325
165°	743	740	740	745	739	210
175°	760	756	757	762	755	72
180°	760	760	760	760	760	

TEST NUMBER: P1001896

CATALOG NUMBER: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1327.0	1327.0	1327.0	1327.0	1327.0
2.5°	1331.3	1328.1	1316.4	1327.0	1325.9
5°	1325.9	1321.7	1310.0	1321.7	1319.6
7.5°	1316.4	1312.1	1299.4	1308.9	1307.9
10°	1302.5	1298.3	1284.5	1293.0	1290.8
12.5°	1284.5	1280.2	1265.3	1274.9	1271.7
15°	1262.1	1257.9	1241.9	1248.3	1245.1
17.5°	1236.6	1231.3	1216.4	1220.7	1218.5
20°	1207.9	1202.6	1186.6	1189.8	1187.7
22.5°	1177.1	1169.6	1153.7	1160.1	1155.8
25°	1143.0	1135.6	1120.7	1121.8	1117.5
27.5°	1104.8	1097.3	1083.5	1081.4	1076.1
30°	1066.5	1058.0	1044.2	1039.9	1034.6
32.5°	1026.1	1018.6	1003.8	998.4	993.1
35°	983.6	976.1	961.2	953.8	948.5
37.5°	938.9	932.5	916.6	909.1	901.7
40°	895.3	886.8	870.8	860.2	854.9
42.5°	848.5	844.3	826.2	813.4	810.2
45°	802.8	795.3	778.3	766.6	763.4
47.5°	754.9	749.6	733.7	720.9	712.4
50°	706.0	701.8	686.9	672.0	665.6
52.5°	658.2	652.9	636.9	624.2	615.7
55°	607.1	604.0	589.1	576.3	569.9
57.5°	559.3	556.1	541.2	528.5	522.1
60°	509.3	504.0	490.2	480.6	475.3
62.5°	460.4	456.2	441.3	432.8	427.4
65°	411.5	406.2	395.5	384.9	379.6
67.5°	361.5	357.3	346.6	336.0	334.9
70°	315.8	308.4	299.9	291.3	288.2
72.5°	266.9	259.4	253.1	246.7	243.5
75°	219.0	213.7	208.4	204.2	203.1
77.5°	172.3	170.1	164.8	163.7	160.6
80°	130.8	127.6	125.5	123.3	122.3
82.5°	90.4	89.3	89.3	88.3	87.2
85°	57.4	57.4	55.3	55.3	54.2
87.5°	27.6	26.6	25.5	25.5	25.5
90°	1.7	8.0	12.5	15.9	17.1
92.5°	8.5	7.4	11.9	15.3	15.3
95°	31.3	11.9	12.5	15.9	16.5
97.5°	59.7	72.2	12.5	15.3	15.9
100°	93.2	103.4	25.0	15.3	15.9
102.5°	130.7	137.5	144.4	16.5	16.5
105°	171.1	174.5	177.3	182.4	162.0
107.5°	208.0	209.7	213.7	216.5	218.8
110°	245.5	247.2	250.7	251.8	253.5



TEST NUMBER: P1001896

CATALOG NUMBER: SA4XXDIP-B795D590UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.9	285.3	286.5	285.9	288.2
115°	319.4	321.1	320.6	321.7	321.7
117.5°	353.0	355.2	356.9	356.4	356.4
120°	387.1	389.3	388.8	389.9	388.8
122.5°	418.9	420.0	421.2	421.7	420.6
125°	449.0	451.3	450.1	451.9	452.4
127.5°	478.0	478.6	481.4	480.8	480.3
130°	505.8	506.4	508.1	508.7	508.7
132.5°	531.4	532.6	534.8	535.4	534.8
135°	557.0	556.4	558.7	559.8	561.0
137.5°	579.7	579.7	582.6	583.7	583.1
140°	601.9	603.0	604.2	605.9	606.5
142.5°	621.8	624.1	624.6	625.8	625.8
145°	642.3	644.0	644.0	644.5	645.7
147.5°	658.2	661.6	661.0	661.6	662.2
150°	675.8	678.1	677.5	677.5	678.1
152.5°	690.6	692.3	691.1	692.3	691.7
155°	704.2	704.8	703.1	705.3	703.6
157.5°	716.1	716.1	713.9	716.7	713.9
160°	726.4	724.7	724.1	727.5	724.1
162.5°	735.5	733.2	732.6	736.0	732.1
165°	742.9	740.0	740.0	744.6	739.4
167.5°	749.1	746.3	745.7	750.8	745.1
170°	754.2	750.8	751.4	755.9	750.2
172.5°	757.6	754.2	754.8	759.3	753.1
175°	759.9	756.5	757.1	762.2	755.4
177.5°	761.6	757.6	758.8	763.3	756.5
180°	759.9	759.9	759.9	759.9	759.9

(END OF REPORT)