

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001456

Luminaire Tested: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001456
REPORT IS A COMBINATION OF REPORTS P996075 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5801.1 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001456

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001456

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	94	89	85	82	85	81	77	74	65	63	60	51	49	47	37	36	35
2	85	78	71	66	77	70	65	60	57	53	49	44	41	39	32	31	29
3	78	68	60	55	70	62	55	50	50	45	41	39	35	33	28	26	24
4	71	60	52	46	64	54	47	42	44	39	35	34	31	28	25	23	21
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18
6	60	47	39	34	54	43	36	31	35	30	26	27	24	21	20	18	16
7	55	43	35	29	49	39	32	27	32	26	22	25	21	18	19	16	14
8	51	39	31	26	46	35	28	24	29	24	20	23	19	16	17	14	12
9	47	35	28	23	43	32	25	21	26	21	18	21	17	14	16	13	11
10	44	32	25	20	40	29	23	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5427	5427	5427
5°	5442	5285	5295
10°	5406	5182	5167
15°	5356	5065	5022
20°	5281	4938	4881
25°	5197	4798	4729
30°	5105	4660	4575
35°	5001	4518	4437
40°	4918	4383	4294
45°	4796	4255	4168
50°	4691	4111	4036
55°	4583	3972	3883
60°	4416	3798	3738
65°	4230	3611	3565
70°	4007	3397	3364
75°	3694	3160	3173
80°	3340	2916	2975
85°	2874	2673	2811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4796 cd/sqm

TEST NUMBER: P1001456

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.1
10°-20°	180.7	3.1
20°-30°	273.2	4.7
30°-40°	330.5	5.7
40°-50°	349.4	6.0
50°-60°	328.8	5.7
60°-70°	272.9	4.7
70°-80°	191.5	3.3
80°-90°	109.8	1.9
90°-100°	423.6	7.3
100°-110°	778.4	13.4
110°-120°	683.3	11.8
120°-130°	565.2	9.7
130°-140°	464.4	8.0
140°-150°	350.3	6.0
150°-160°	245.1	4.2
160°-170°	144.2	2.5
170°-180°	46.9	0.8
0°-30°	516.9	8.9
0°-40°	847.4	14.6
0°-60°	1525.6	26.3
0°-90°	2099.8	36.2
90°-120°	1885.3	32.5
90°-150°	3265.1	56.3
90°-180°	3701.0	63.8
0°-180°	5801.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	666	666	666	666	666	
5°	666	664	659	665	664	63
15°	639	639	637	644	643	180
25°	584	589	591	599	600	269
35°	511	520	528	538	540	320
45°	426	440	455	467	471	329
55°	334	350	372	387	391	298
65°	231	255	280	299	305	229
75°	128	156	187	208	215	136
85°	40	71	104	127	134	41
90°	13	49	91	114	121	10
95°	41	133	839	468	324	42
105°	118	183	673	1410	1411	126
115°	200	257	591	1120	1340	199
125°	276	326	574	944	1064	246
135°	326	387	555	825	939	252
145°	374	428	546	685	755	235
155°	425	459	530	601	626	196
165°	463	477	508	538	546	131
175°	483	484	488	494	492	46
180°	484	484	484	484	484	

TEST NUMBER: P1001456

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	665.5	665.5	665.5	665.5	665.5
2.5°	668.5	666.3	660.3	665.5	664.8
5°	666.3	664.0	658.8	664.8	664.0
7.5°	661.8	660.3	655.8	662.5	661.8
10°	655.8	655.1	651.4	658.1	657.3
12.5°	647.6	647.6	645.4	651.4	651.4
15°	638.7	639.4	637.2	643.9	643.2
17.5°	626.8	629.0	628.2	635.0	634.2
20°	614.1	616.3	617.1	624.5	624.5
22.5°	599.9	602.9	604.4	611.9	613.3
25°	584.3	588.7	591.0	599.2	599.9
27.5°	567.1	573.8	576.8	584.3	585.0
30°	550.0	556.0	561.2	569.4	570.9
32.5°	531.4	538.8	544.8	554.5	556.0
35°	511.2	520.2	527.6	538.1	540.3
37.5°	491.1	501.6	510.5	520.9	523.2
40°	471.7	481.4	491.9	503.0	506.0
42.5°	449.4	460.6	473.2	485.9	488.1
45°	426.3	440.4	454.6	467.3	471.0
47.5°	404.7	418.8	435.2	447.9	452.4
50°	380.8	397.2	413.6	428.5	433.0
52.5°	357.0	373.4	392.7	407.7	412.1
55°	333.9	349.5	371.9	386.8	391.3
57.5°	307.8	327.2	348.8	366.7	370.4
60°	282.5	301.8	326.4	343.6	349.5
62.5°	257.9	279.5	304.1	321.2	327.2
65°	231.0	254.9	280.2	298.8	304.8
67.5°	205.7	231.0	257.9	276.5	282.5
70°	179.6	204.9	233.3	253.4	258.6
72.5°	154.3	180.4	210.9	230.3	236.2
75°	128.2	155.8	187.1	207.9	214.6
77.5°	103.6	132.7	165.4	186.3	193.8
80°	81.2	111.0	143.8	166.2	172.2
82.5°	58.9	90.2	123.0	146.1	152.8
85°	39.5	70.8	104.3	126.7	134.1
87.5°	24.6	55.1	87.9	109.6	116.3
90°	12.9	49.3	90.9	114.4	121.4
92.5°	24.5	110.4	441.8	213.2	182.6
95°	41.1	133.1	839.3	468.5	323.6
97.5°	61.2	139.9	889.8	863.6	644.1
100°	80.4	151.2	820.7	1160.2	953.5
102.5°	99.4	165.2	736.2	1343.9	1223.5
105°	117.9	182.7	672.6	1410.1	1410.9
107.5°	139.7	201.4	630.0	1385.1	1497.7
110°	160.9	219.3	608.9	1304.6	1495.9

TEST NUMBER: P1001456

CATALOG NUMBER: SA4XXDIP-B575D1035UB50-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.0	238.0	596.7	1206.9	1435.3
115°	200.3	256.8	591.0	1119.6	1340.5
117.5°	221.2	275.0	586.3	1049.6	1248.4
120°	241.3	292.0	582.6	1001.0	1171.7
122.5°	260.3	309.2	577.9	968.2	1110.3
125°	275.7	326.3	574.0	944.0	1064.0
127.5°	291.0	343.4	568.3	920.1	1033.7
130°	302.5	359.3	563.6	893.0	1006.4
132.5°	314.9	373.5	559.7	861.8	977.0
135°	325.6	387.4	555.0	825.4	939.2
137.5°	337.0	398.4	552.0	787.6	895.8
140°	349.3	409.3	548.9	750.6	849.3
142.5°	361.8	419.4	547.4	716.7	800.0
145°	374.2	427.6	545.5	685.0	755.4
147.5°	388.4	436.2	542.6	657.9	713.6
150°	401.7	444.3	539.8	635.8	678.5
152.5°	413.4	451.9	535.0	617.8	650.0
155°	424.8	458.6	530.3	600.6	626.3
157.5°	436.2	464.7	525.5	584.4	604.4
160°	446.7	470.0	519.8	568.3	584.5
162.5°	456.2	474.2	514.1	552.6	565.5
165°	462.8	477.0	508.4	538.4	546.4
167.5°	470.4	479.4	502.7	526.0	531.2
170°	475.2	481.4	497.0	513.7	517.0
172.5°	479.9	482.8	491.3	502.8	502.7
175°	482.8	483.7	487.5	494.2	492.3
177.5°	484.7	483.7	484.7	488.0	484.7
180°	483.7	483.7	483.7	483.7	483.7

(END OF REPORT)