

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001950

Luminaire Tested: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001950
REPORT IS A COMBINATION OF REPORTS P996575 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6445.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001950

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1001950

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53			47
1	96	91	87	83	88	84	80	77	70	67	65	57	55	54	46	44	43			38
2	87	79	73	67	80	73	67	62	61	57	53	50	47	44	40	37	36			31
3	79	69	62	56	72	64	57	52	53	48	44	44	40	37	35	32	30			26
4	72	61	53	47	66	56	49	43	47	42	37	39	35	31	31	28	25			22
5	66	54	46	40	60	50	43	37	42	36	32	35	30	27	28	24	22			19
6	61	49	40	34	56	45	37	32	38	32	28	31	27	23	25	22	19			16
7	56	44	36	30	51	40	33	28	34	28	24	28	24	21	23	19	17			14
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	18	15			13
9	49	36	28	23	44	33	27	22	28	23	19	24	19	16	19	16	14			11
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	15	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7821	7821	7821
5°	7843	7617	7631
10°	7791	7467	7446
15°	7718	7299	7237
20°	7611	7116	7034
25°	7489	6915	6816
30°	7357	6715	6593
35°	7208	6512	6395
40°	7089	6317	6190
45°	6911	6133	6008
50°	6761	5924	5816
55°	6605	5723	5595
60°	6364	5473	5387
65°	6097	5203	5138
70°	5774	4896	4849
75°	5323	4553	4573
80°	4816	4204	4286
85°	4141	3854	4052

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6911 cd/sqm

TEST NUMBER: P1001950

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	1.4
10°-20°	260.4	4.0
20°-30°	393.7	6.1
30°-40°	476.3	7.4
40°-50°	503.5	7.8
50°-60°	473.9	7.4
60°-70°	393.2	6.1
70°-80°	276.0	4.3
80°-90°	157.7	2.4
90°-100°	126.7	2.0
100°-110°	292.7	4.5
110°-120°	474.0	7.4
120°-130°	569.3	8.8
130°-140°	592.5	9.2
140°-150°	545.8	8.5
150°-160°	438.3	6.8
160°-170°	282.7	4.4
170°-180°	97.4	1.5
0°-30°	744.9	11.6
0°-40°	1221.2	18.9
0°-60°	2198.6	34.1
0°-90°	3025.5	46.9
90°-120°	893.4	13.9
90°-150°	2601.0	40.4
90°-180°	3419.0	53.0
0°-180°	6445.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	960	957	949	958	957	91
15°	920	922	918	928	927	259
25°	842	848	852	864	865	388
35°	737	750	760	776	779	461
45°	614	635	655	673	679	475
55°	481	504	536	557	564	429
65°	333	367	404	431	439	330
75°	185	224	270	300	309	196
85°	57	102	150	183	193	59
90°	20	71	123	159	169	14
95°	56	66	110	144	154	63
105°	240	266	310	344	325	253
115°	437	449	483	508	516	431
125°	610	612	638	660	667	545
135°	754	753	764	782	790	581
145°	868	869	869	876	882	542
155°	950	951	949	952	950	438
165°	1002	998	998	1005	998	283
175°	1025	1021	1022	1028	1019	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1001950

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	959.1	959.1	959.1	959.1	959.1
2.5°	963.4	960.2	951.6	959.1	958.0
5°	960.2	957.0	949.4	958.0	957.0
7.5°	953.7	951.6	945.1	954.8	953.7
10°	945.1	944.1	938.7	948.4	947.3
12.5°	933.3	933.3	930.1	938.7	938.7
15°	920.4	921.5	918.3	928.0	926.9
17.5°	903.3	906.5	905.4	915.1	914.0
20°	885.0	888.2	889.3	900.0	900.0
22.5°	864.6	868.9	871.0	881.8	883.9
25°	842.0	848.5	851.7	863.5	864.6
27.5°	817.3	827.0	831.3	842.0	843.1
30°	792.6	801.2	808.7	820.6	822.7
32.5°	765.8	776.5	785.1	799.1	801.2
35°	736.8	749.7	760.4	775.5	778.7
37.5°	707.8	722.8	735.7	750.7	754.0
40°	679.9	693.8	708.9	725.0	729.3
42.5°	647.6	663.8	682.0	700.3	703.5
45°	614.3	634.8	655.2	673.4	678.8
47.5°	583.2	603.6	627.2	645.5	651.9
50°	548.8	572.5	596.1	617.6	624.0
52.5°	514.5	538.1	566.0	587.5	593.9
55°	481.2	503.7	535.9	557.4	563.9
57.5°	443.6	471.5	502.6	528.4	533.8
60°	407.1	435.0	470.4	495.1	503.7
62.5°	371.6	402.8	438.2	462.9	471.5
65°	332.9	367.3	403.8	430.7	439.3
67.5°	296.4	332.9	371.6	398.5	407.1
70°	258.8	295.4	336.2	365.2	372.7
72.5°	222.3	259.9	304.0	331.9	340.5
75°	184.7	224.5	269.6	299.7	309.3
77.5°	149.3	191.2	238.4	268.5	279.2
80°	117.1	160.0	207.3	239.5	248.1
82.5°	84.8	130.0	177.2	210.5	220.2
85°	56.9	102.0	150.4	182.6	193.3
87.5°	35.4	79.5	126.7	157.9	167.5
90°	19.5	70.8	123.2	159.0	169.1
92.5°	27.6	63.7	116.0	150.7	159.3
95°	56.2	65.5	110.3	143.9	154.3
97.5°	93.4	141.4	105.0	136.7	147.2
100°	137.6	179.3	115.3	131.3	139.6
102.5°	188.2	221.0	271.1	126.4	135.0
105°	240.5	266.5	310.2	343.9	324.9
107.5°	290.4	310.9	353.9	384.6	395.2
110°	339.9	357.2	399.4	425.6	436.5

TEST NUMBER: P1001950

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	387.9	405.4	442.3	465.3	476.9
115°	437.4	449.4	483.0	508.2	515.7
117.5°	482.7	492.2	526.7	548.6	557.2
120°	527.7	533.9	564.3	587.3	594.4
122.5°	570.6	572.2	602.7	624.9	630.9
125°	610.2	612.1	637.5	660.2	667.4
127.5°	649.3	649.0	674.3	692.8	699.7
130°	685.8	685.4	704.9	725.1	731.5
132.5°	720.3	720.7	736.7	755.7	761.4
135°	753.7	752.9	763.6	782.3	790.3
137.5°	784.4	783.4	791.5	809.1	813.8
140°	814.3	814.8	817.3	833.6	839.8
142.5°	840.1	843.2	842.9	856.2	860.5
145°	867.7	868.9	868.9	876.1	881.9
147.5°	889.2	892.7	891.9	893.8	898.9
150°	913.0	914.9	914.2	914.2	914.9
152.5°	931.8	934.1	932.6	934.1	933.3
155°	950.2	951.0	948.7	951.8	949.5
157.5°	966.3	966.3	963.3	967.1	963.3
160°	980.1	977.8	977.1	981.7	977.1
162.5°	992.4	989.3	988.6	993.2	987.8
165°	1002.4	998.5	998.5	1004.7	997.8
167.5°	1010.8	1007.0	1006.2	1013.1	1005.4
170°	1017.7	1013.1	1013.9	1020.0	1012.3
172.5°	1022.3	1017.7	1018.5	1024.6	1016.2
175°	1025.4	1020.8	1021.5	1028.4	1019.2
177.5°	1027.7	1022.3	1023.8	1030.0	1020.8
180°	1025.4	1025.4	1025.4	1025.4	1025.4

(END OF REPORT)