

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001467

Luminaire Tested: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001467
REPORT IS A COMBINATION OF REPORTS P996086 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6594.0 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001467

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001467

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	91	87	83	86	82	79	76	67	65	62	52	51	50	39	38	37
2	86	79	73	68	78	72	67	62	58	55	52	46	44	41	35	33	32
3	79	70	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16
8	52	40	32	27	47	37	30	25	30	25	21	24	21	18	19	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13
10	45	33	26	22	41	31	24	20	25	21	17	21	17	14	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7826	7594	7603
10°	7759	7383	7331
15°	7648	7133	7025
20°	7506	6861	6708
25°	7345	6575	6366
30°	7153	6265	5990
35°	6953	5948	5628
40°	6745	5607	5242
45°	6527	5265	4882
50°	6284	4933	4482
55°	6022	4545	4086
60°	5753	4121	3673
65°	5445	3683	3208
70°	5091	3156	2709
75°	4562	2543	2169
80°	3887	1839	1527
85°	3020	1025	822

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6527 cd/sqm

TEST NUMBER: P1001467

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.4	1.4
10°-20°	254.6	3.9
20°-30°	374.7	5.7
30°-40°	435.6	6.6
40°-50°	435.5	6.6
50°-60°	380.9	5.8
60°-70°	282.8	4.3
70°-80°	160.5	2.4
80°-90°	49.1	0.7
90°-100°	97.0	1.5
100°-110°	290.6	4.4
110°-120°	493.7	7.5
120°-130°	651.1	9.9
130°-140°	731.2	11.1
140°-150°	718.7	10.9
150°-160°	604.5	9.2
160°-170°	402.2	6.1
170°-180°	140.8	2.1
0°-30°	719.7	10.9
0°-40°	1155.3	17.5
0°-60°	1971.8	29.9
0°-90°	2464.2	37.4
90°-120°	881.3	13.4
90°-150°	2982.3	45.2
90°-180°	4130.0	62.6
0°-180°	6594.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	958	955	946	955	953	91
15°	912	909	897	902	900	257
25°	826	820	810	810	808	380
35°	711	705	694	689	685	444
45°	580	575	562	554	552	447
55°	439	436	426	416	412	393
65°	297	294	286	278	274	294
75°	158	154	151	148	147	168
85°	42	42	40	40	39	45
90°	4	16	25	32	34	8
95°	69	79	88	91	91	75
105°	268	269	274	277	281	284
115°	502	502	500	498	497	495
125°	731	731	730	728	725	652
135°	943	950	950	947	944	729
145°	1145	1150	1151	1150	1146	717
155°	1312	1312	1311	1316	1311	604
165°	1429	1425	1423	1430	1425	403
175°	1486	1480	1479	1487	1479	141
180°	1488	1488	1488	1488	1488	

TEST NUMBER: P1001467

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	958.8	958.8	958.8	958.8	958.8
2.5°	961.9	959.6	951.1	958.8	958.1
5°	958.1	955.0	946.5	955.0	953.4
7.5°	951.1	948.1	938.8	945.8	945.0
10°	941.2	938.1	928.1	934.2	932.7
12.5°	928.1	925.0	914.3	921.2	918.9
15°	912.0	908.9	897.4	902.0	899.7
17.5°	893.5	889.7	878.9	882.0	880.5
20°	872.8	868.9	857.4	859.7	858.2
22.5°	850.5	845.1	833.6	838.2	835.1
25°	825.9	820.5	809.8	810.5	807.5
27.5°	798.2	792.9	782.9	781.3	777.5
30°	770.6	764.4	754.5	751.4	747.5
32.5°	741.4	736.0	725.3	721.4	717.6
35°	710.7	705.3	694.5	689.2	685.3
37.5°	678.4	673.8	662.3	656.9	651.5
40°	646.9	640.8	629.2	621.5	617.7
42.5°	613.1	610.0	597.0	587.7	585.4
45°	580.1	574.7	562.4	553.9	551.6
47.5°	545.5	541.6	530.1	520.9	514.8
50°	510.1	507.1	496.3	485.6	480.9
52.5°	475.6	471.7	460.2	451.0	444.8
55°	438.7	436.4	425.6	416.4	411.8
57.5°	404.1	401.8	391.1	381.8	377.2
60°	368.0	364.2	354.2	347.3	343.4
62.5°	332.7	329.6	318.8	312.7	308.9
65°	297.3	293.5	285.8	278.1	274.3
67.5°	261.2	258.1	250.5	242.8	242.0
70°	228.2	222.8	216.7	210.5	208.2
72.5°	192.8	187.5	182.9	178.2	175.9
75°	158.3	154.4	150.6	147.5	146.7
77.5°	124.5	122.9	119.1	118.3	116.0
80°	94.5	92.2	90.7	89.1	88.4
82.5°	65.3	64.5	64.5	63.8	63.0
85°	41.5	41.5	40.0	40.0	39.2
87.5°	20.0	19.2	18.4	18.4	18.4
90°	3.5	16.1	25.3	32.2	34.5
92.5°	29.9	44.9	50.7	54.1	55.3
95°	69.1	79.4	87.5	90.9	90.9
97.5°	110.5	119.7	128.9	133.5	133.5
100°	161.2	165.8	176.1	178.4	178.4
102.5°	214.1	215.3	224.5	227.9	229.1
105°	268.2	269.4	274.0	277.4	280.9
107.5°	324.6	325.8	326.9	331.5	330.4
110°	382.2	384.5	383.3	381.0	384.5

TEST NUMBER: P1001467

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	442.0	442.0	439.7	439.7	439.7
115°	501.9	501.9	499.6	498.4	497.3
117.5°	558.3	558.3	557.2	553.7	550.2
120°	614.7	619.3	615.9	610.1	612.4
122.5°	673.4	674.6	673.4	670.0	664.2
125°	731.0	731.0	729.8	727.5	725.2
127.5°	782.8	786.2	783.9	781.6	780.5
130°	838.0	841.5	841.5	839.2	834.6
132.5°	894.4	896.7	895.6	893.3	892.1
135°	942.8	949.7	949.7	947.4	943.9
137.5°	996.9	1000.3	1002.6	999.2	1000.3
140°	1051.0	1053.3	1053.3	1052.1	1051.0
142.5°	1100.5	1102.8	1101.6	1101.6	1101.6
145°	1145.4	1150.0	1151.1	1150.0	1146.5
147.5°	1191.4	1197.2	1196.0	1194.9	1193.7
150°	1232.9	1237.5	1237.5	1237.5	1236.3
152.5°	1272.0	1274.3	1275.5	1278.9	1275.5
155°	1312.3	1312.3	1311.1	1315.7	1311.1
157.5°	1346.8	1344.5	1344.5	1348.0	1344.5
160°	1376.8	1375.6	1374.5	1377.9	1372.2
162.5°	1404.4	1400.9	1399.8	1406.7	1400.9
165°	1428.6	1425.1	1422.8	1429.7	1425.1
167.5°	1448.1	1443.5	1443.5	1450.4	1443.5
170°	1464.2	1458.5	1459.6	1466.5	1458.5
172.5°	1475.8	1471.2	1471.2	1479.2	1471.2
175°	1486.1	1480.4	1479.2	1487.3	1479.2
177.5°	1490.7	1485.0	1485.0	1493.0	1483.8
180°	1488.4	1488.4	1488.4	1488.4	1488.4

(END OF REPORT)