

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001468

Luminaire Tested: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001468
REPORT IS A COMBINATION OF REPORTS P996087 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6739.6 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001468

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001468

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37
2	86	79	73	68	78	72	67	62	58	54	51	46	43	41	34	32	31
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7826	7594	7603
10°	7759	7383	7331
15°	7648	7133	7025
20°	7506	6861	6708
25°	7345	6575	6366
30°	7153	6265	5990
35°	6953	5948	5628
40°	6745	5607	5242
45°	6527	5265	4882
50°	6284	4933	4482
55°	6022	4545	4086
60°	5753	4121	3673
65°	5445	3683	3208
70°	5091	3156	2709
75°	4562	2543	2169
80°	3887	1839	1527
85°	3020	1025	822

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6527 cd/sqm

TEST NUMBER: P1001468

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.4	1.3
10°-20°	254.6	3.8
20°-30°	374.7	5.6
30°-40°	435.6	6.5
40°-50°	435.5	6.5
50°-60°	380.9	5.7
60°-70°	282.8	4.2
70°-80°	160.5	2.4
80°-90°	48.2	0.7
90°-100°	435.3	6.5
100°-110°	885.3	13.1
110°-120°	789.1	11.7
120°-130°	662.8	9.8
130°-140°	553.1	8.2
140°-150°	422.4	6.3
150°-160°	296.9	4.4
160°-170°	174.6	2.6
170°-180°	56.8	0.8
0°-30°	719.7	10.7
0°-40°	1155.3	17.1
0°-60°	1971.8	29.3
0°-90°	2463.3	36.5
90°-120°	2109.6	31.3
90°-150°	3748.0	55.6
90°-180°	4276.0	63.4
0°-180°	6739.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	958	955	946	955	953	91
15°	912	909	897	902	900	257
25°	826	820	810	810	808	380
35°	711	705	694	689	685	444
45°	580	575	562	554	552	447
55°	439	436	426	416	412	393
65°	297	294	286	278	274	294
75°	158	154	151	148	147	168
85°	42	42	40	40	39	45
90°	1	9	21	23	24	5
95°	38	120	938	464	281	42
105°	135	195	755	1626	1620	143
115°	237	298	674	1294	1555	235
125°	330	392	670	1101	1241	294
135°	393	467	664	977	1110	303
145°	452	518	661	824	906	284
155°	515	555	642	728	759	237
165°	561	578	616	652	662	158
175°	585	586	591	599	596	56
180°	586	586	586	586	586	

TEST NUMBER: P1001468

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	958.8	958.8	958.8	958.8	958.8
2.5°	961.9	959.6	951.1	958.8	958.1
5°	958.1	955.0	946.5	955.0	953.4
7.5°	951.1	948.1	938.8	945.8	945.0
10°	941.2	938.1	928.1	934.2	932.7
12.5°	928.1	925.0	914.3	921.2	918.9
15°	912.0	908.9	897.4	902.0	899.7
17.5°	893.5	889.7	878.9	882.0	880.5
20°	872.8	868.9	857.4	859.7	858.2
22.5°	850.5	845.1	833.6	838.2	835.1
25°	825.9	820.5	809.8	810.5	807.5
27.5°	798.2	792.9	782.9	781.3	777.5
30°	770.6	764.4	754.5	751.4	747.5
32.5°	741.4	736.0	725.3	721.4	717.6
35°	710.7	705.3	694.5	689.2	685.3
37.5°	678.4	673.8	662.3	656.9	651.5
40°	646.9	640.8	629.2	621.5	617.7
42.5°	613.1	610.0	597.0	587.7	585.4
45°	580.1	574.7	562.4	553.9	551.6
47.5°	545.5	541.6	530.1	520.9	514.8
50°	510.1	507.1	496.3	485.6	480.9
52.5°	475.6	471.7	460.2	451.0	444.8
55°	438.7	436.4	425.6	416.4	411.8
57.5°	404.1	401.8	391.1	381.8	377.2
60°	368.0	364.2	354.2	347.3	343.4
62.5°	332.7	329.6	318.8	312.7	308.9
65°	297.3	293.5	285.8	278.1	274.3
67.5°	261.2	258.1	250.5	242.8	242.0
70°	228.2	222.8	216.7	210.5	208.2
72.5°	192.8	187.5	182.9	178.2	175.9
75°	158.3	154.4	150.6	147.5	146.7
77.5°	124.5	122.9	119.1	118.3	116.0
80°	94.5	92.2	90.7	89.1	88.4
82.5°	65.3	64.5	64.5	63.8	63.0
85°	41.5	41.5	40.0	40.0	39.2
87.5°	20.0	19.2	18.4	18.4	18.4
90°	1.2	9.2	20.7	23.0	24.2
92.5°	16.1	88.6	451.3	149.1	104.8
95°	38.0	119.7	938.2	464.5	280.9
97.5°	63.3	132.4	1003.8	948.6	674.6
100°	87.5	149.6	925.6	1312.4	1055.6
102.5°	110.5	170.4	827.7	1540.3	1387.2
105°	134.7	195.1	755.2	1626.1	1619.7
107.5°	161.2	220.4	708.0	1600.2	1730.3
110°	187.6	245.8	686.1	1508.1	1732.6

TEST NUMBER: P1001468

CATALOG NUMBER: SA4XXDIP-B575D1205UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.0	271.1	675.8	1395.2	1664.6
115°	237.1	297.6	673.5	1294.0	1555.3
117.5°	262.5	322.4	672.3	1214.6	1448.2
120°	287.8	346.5	672.3	1161.0	1360.7
122.5°	310.8	370.2	671.1	1125.8	1291.6
125°	330.4	392.5	670.0	1101.2	1241.0
127.5°	348.8	413.3	667.7	1077.6	1208.8
130°	363.8	433.4	666.5	1049.3	1181.1
132.5°	378.7	450.7	665.4	1015.9	1150.0
135°	392.6	467.4	664.2	977.4	1109.8
137.5°	406.4	481.8	664.2	935.9	1062.6
140°	421.3	495.0	663.1	895.6	1010.8
142.5°	437.5	507.1	663.1	858.2	955.5
145°	452.4	518.0	660.8	824.2	906.0
147.5°	469.7	528.4	657.3	796.0	859.9
150°	485.8	538.2	653.9	770.2	822.0
152.5°	500.8	547.4	648.1	748.2	787.4
155°	514.6	555.4	642.4	727.6	758.6
157.5°	528.4	562.9	636.6	708.0	732.2
160°	541.1	569.2	629.7	688.4	708.0
162.5°	552.6	574.4	622.8	669.4	685.0
165°	560.6	577.9	615.9	652.2	661.9
167.5°	569.8	580.8	609.0	637.2	643.5
170°	575.6	583.1	602.1	622.2	626.3
172.5°	581.4	584.8	595.2	609.0	609.0
175°	584.8	586.0	590.6	598.6	596.3
177.5°	587.1	586.0	587.1	591.2	587.1
180°	586.0	586.0	586.0	586.0	586.0

(END OF REPORT)