

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000537

Luminaire Tested: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000537
REPORT IS A COMBINATION OF REPORTS P995147 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7732.0 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000537

CATALOG NUMBER: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1000537

CATALOG NUMBER: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	81	78	72	69	66	59	57	56	48	47	45
2	88	80	73	68	80	74	68	63	62	58	54	51	48	46	42	39	37
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	37	34	31
4	73	61	53	47	67	57	50	44	48	42	38	40	36	32	32	29	27
5	67	55	46	40	61	51	43	37	43	37	33	36	31	28	29	26	23
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	26	23	20
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	20	18
8	53	40	32	26	48	37	30	25	32	26	22	27	22	19	22	19	16
9	49	36	29	24	45	34	27	22	29	23	20	25	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	18	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10007	10007	10007
5°	10035	9746	9764
10°	9969	9555	9527
15°	9876	9339	9260
20°	9738	9106	9001
25°	9582	8848	8722
30°	9414	8593	8436
35°	9223	8333	8182
40°	9070	8082	7919
45°	8844	7847	7686
50°	8650	7580	7441
55°	8452	7323	7159
60°	8141	7003	6893
65°	7801	6658	6574
70°	7389	6263	6205
75°	6813	5825	5852
80°	6161	5378	5483
85°	5298	4930	5186

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8844 cd/sqm

TEST NUMBER: P1000537

CATALOG NUMBER: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	1.5
10°-20°	333.2	4.3
20°-30°	503.7	6.5
30°-40°	609.4	7.9
40°-50°	644.3	8.3
50°-60°	606.3	7.8
60°-70°	503.1	6.5
70°-80°	353.1	4.6
80°-90°	201.8	2.6
90°-100°	201.8	2.6
100°-110°	337.2	4.4
110°-120°	482.7	6.2
120°-130°	592.1	7.7
130°-140°	642.1	8.3
140°-150°	619.8	8.0
150°-160°	518.9	6.7
160°-170°	345.3	4.5
170°-180°	120.9	1.6
0°-30°	953.2	12.3
0°-40°	1562.6	20.2
0°-60°	2813.2	36.4
0°-90°	3871.2	50.1
90°-120°	1021.7	13.2
90°-150°	2875.7	37.2
90°-180°	3861.0	49.9
0°-180°	7732.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1227	1227	1227	1227	1227	
5°	1229	1224	1215	1226	1224	117
15°	1178	1179	1175	1187	1186	332
25°	1077	1086	1090	1105	1106	496
35°	943	959	973	992	996	590
45°	786	812	838	862	868	608
55°	616	644	686	713	722	549
65°	426	470	517	551	562	422
75°	236	287	345	383	396	251
85°	73	131	192	234	247	76
90°	25	91	158	204	216	19
95°	77	131	195	235	247	78
105°	243	271	326	363	377	258
115°	439	452	494	523	531	434
125°	633	632	665	689	695	565
135°	812	818	828	848	853	629
145°	985	987	988	995	998	616
155°	1126	1126	1126	1130	1126	519
165°	1226	1223	1221	1227	1223	346
175°	1276	1271	1270	1277	1270	121
180°	1278	1278	1278	1278	1278	

TEST NUMBER: P1000537

CATALOG NUMBER: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1227.2	1227.2	1227.2	1227.2	1227.2
2.5°	1232.7	1228.6	1217.6	1227.2	1225.8
5°	1228.6	1224.4	1214.8	1225.8	1224.4
7.5°	1220.3	1217.6	1209.3	1221.7	1220.3
10°	1209.3	1208.0	1201.1	1213.4	1212.1
12.5°	1194.2	1194.2	1190.1	1201.1	1201.1
15°	1177.7	1179.1	1175.0	1187.3	1186.0
17.5°	1155.7	1159.9	1158.5	1170.8	1169.5
20°	1132.4	1136.5	1137.9	1151.6	1151.6
22.5°	1106.3	1111.8	1114.5	1128.2	1131.0
25°	1077.4	1085.6	1089.8	1104.9	1106.3
27.5°	1045.8	1058.2	1063.7	1077.4	1078.8
30°	1014.2	1025.2	1034.8	1049.9	1052.7
32.5°	979.8	993.6	1004.6	1022.4	1025.2
35°	942.7	959.2	973.0	992.2	996.3
37.5°	905.6	924.9	941.4	960.6	964.7
40°	869.9	887.8	907.0	927.6	933.1
42.5°	828.7	849.3	872.6	896.0	900.1
45°	786.1	812.2	838.3	861.6	868.5
47.5°	746.2	772.3	802.6	825.9	834.2
50°	702.2	732.5	762.7	790.2	798.4
52.5°	658.3	688.5	724.2	751.7	760.0
55°	615.7	644.5	685.7	713.2	721.5
57.5°	567.6	603.3	643.1	676.1	683.0
60°	520.8	556.6	601.9	633.5	644.5
62.5°	475.5	515.3	560.7	592.3	603.3
65°	426.0	470.0	516.7	551.1	562.1
67.5°	379.3	426.0	475.5	509.8	520.8
70°	331.2	377.9	430.1	467.2	476.9
72.5°	284.5	332.6	388.9	424.6	435.6
75°	236.4	287.2	344.9	383.4	395.8
77.5°	191.0	244.6	305.1	343.6	357.3
80°	149.8	204.8	265.2	306.5	317.4
82.5°	108.6	166.3	226.7	269.4	281.7
85°	72.8	130.6	192.4	233.6	247.4
87.5°	45.3	101.7	162.2	202.0	214.4
90°	25.0	90.8	157.7	203.6	216.5
92.5°	46.3	107.2	171.3	212.7	224.7
95°	77.2	131.4	194.7	234.8	247.1
97.5°	111.4	159.1	223.4	263.0	275.4
100°	153.4	193.1	255.6	294.7	304.4
102.5°	198.9	230.1	290.3	329.0	341.0
105°	242.7	271.1	325.9	363.3	377.1
107.5°	291.1	315.4	364.4	402.8	411.4
110°	339.1	360.3	407.4	437.0	451.0

TEST NUMBER: P1000537

CATALOG NUMBER: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	389.1	405.6	449.0	479.2	490.2
115°	439.1	451.5	493.5	522.7	531.3
117.5°	487.5	495.8	536.0	561.9	570.0
120°	534.6	542.7	579.5	602.0	615.0
122.5°	585.0	586.0	622.1	646.6	651.3
125°	633.0	631.6	665.0	689.1	695.4
127.5°	677.5	679.0	704.6	727.3	736.0
130°	723.5	725.1	747.1	769.9	774.1
132.5°	771.9	772.5	788.0	809.4	816.7
135°	812.0	818.0	827.7	847.7	852.9
137.5°	858.5	860.1	867.6	885.3	893.1
140°	904.9	905.6	906.9	923.8	929.7
142.5°	946.1	948.1	945.7	960.8	966.3
145°	984.7	987.2	988.2	995.4	997.9
147.5°	1024.2	1027.7	1026.7	1027.2	1031.7
150°	1059.8	1062.3	1062.3	1062.3	1061.3
152.5°	1092.0	1093.9	1094.9	1097.9	1094.9
155°	1126.5	1126.5	1125.6	1129.5	1125.6
157.5°	1156.2	1154.2	1154.2	1157.2	1154.2
160°	1181.9	1180.9	1179.9	1182.9	1177.9
162.5°	1205.6	1202.6	1201.7	1207.6	1202.6
165°	1226.4	1223.4	1221.4	1227.3	1223.4
167.5°	1243.2	1239.2	1239.2	1245.1	1239.2
170°	1257.0	1252.1	1253.0	1259.0	1252.1
172.5°	1266.9	1262.9	1262.9	1269.8	1262.9
175°	1275.8	1270.8	1269.8	1276.8	1269.8
177.5°	1279.7	1274.8	1274.8	1281.7	1273.8
180°	1277.7	1277.7	1277.7	1277.7	1277.7

(END OF REPORT)