

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001488

Luminaire Tested: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001488
REPORT IS A COMBINATION OF REPORTS P996107 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6528.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001488

CATALOG NUMBER: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001488

CATALOG NUMBER: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	93	89	85	81	84	80	77	74	64	61	59	49	47	46	35	34	33
2	85	77	71	66	76	70	64	60	56	52	48	42	40	38	30	29	27
3	77	68	60	54	69	61	55	50	49	44	40	37	34	32	27	25	23
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	21	20
5	64	53	45	39	58	48	41	36	38	33	29	29	26	23	21	19	17
6	59	47	39	33	53	43	36	31	34	29	25	27	23	20	19	17	15
7	55	42	35	29	49	38	32	27	31	26	22	24	20	17	17	15	13
8	51	38	31	25	45	35	28	23	28	23	19	22	18	15	16	13	12
9	47	35	27	22	42	32	25	21	26	21	17	20	16	14	15	12	10
10	44	32	25	20	39	29	23	18	24	19	15	18	15	12	14	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5642	5642	5642
5°	5658	5495	5505
10°	5621	5387	5372
15°	5568	5266	5221
20°	5490	5133	5075
25°	5403	4988	4917
30°	5307	4845	4756
35°	5200	4698	4613
40°	5114	4557	4465
45°	4986	4424	4334
50°	4877	4274	4196
55°	4765	4129	4037
60°	4591	3949	3887
65°	4399	3754	3706
70°	4165	3531	3498
75°	3841	3285	3299
80°	3475	3032	3092
85°	2991	2780	2924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 5186 cd/sqm

TEST NUMBER: P1001488

CATALOG NUMBER: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	1.0
10°-20°	187.8	2.9
20°-30°	284.0	4.4
30°-40°	343.6	5.3
40°-50°	363.2	5.6
50°-60°	341.9	5.2
60°-70°	283.7	4.3
70°-80°	199.1	3.0
80°-90°	115.4	1.8
90°-100°	164.7	2.5
100°-110°	342.6	5.2
110°-120°	531.2	8.1
120°-130°	675.4	10.3
130°-140°	745.7	11.4
140°-150°	726.6	11.1
150°-160°	609.8	9.3
160°-170°	405.7	6.2
170°-180°	142.1	2.2
0°-30°	537.4	8.2
0°-40°	881.0	13.5
0°-60°	1586.1	24.3
0°-90°	2184.3	33.5
90°-120°	1038.5	15.9
90°-150°	3186.2	48.8
90°-180°	4344.0	66.5
0°-180°	6528.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	692	692	692	692	692	
5°	693	690	685	691	690	66
15°	664	665	662	669	669	187
25°	608	612	614	623	624	280
35°	532	541	549	559	562	333
45°	443	458	473	486	490	343
55°	347	363	387	402	407	309
65°	240	265	291	311	317	238
75°	133	162	194	216	223	142
85°	41	74	108	132	140	43
90°	16	60	102	132	140	14
95°	80	116	156	180	187	84
105°	278	294	328	350	360	295
115°	511	518	540	556	560	504
125°	740	740	758	770	773	660
135°	952	960	965	975	976	737
145°	1156	1160	1161	1165	1164	724
155°	1324	1324	1323	1327	1323	609
165°	1441	1438	1435	1442	1438	406
175°	1499	1493	1492	1500	1492	142
180°	1501	1501	1501	1501	1501	

TEST NUMBER: P1001488

CATALOG NUMBER: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	691.9	691.9	691.9	691.9	691.9
2.5°	695.0	692.7	686.5	691.9	691.1
5°	692.7	690.4	684.9	691.1	690.4
7.5°	688.0	686.5	681.8	688.8	688.0
10°	681.8	681.1	677.2	684.2	683.4
12.5°	673.3	673.3	671.0	677.2	677.2
15°	664.0	664.8	662.5	669.4	668.7
17.5°	651.6	653.9	653.2	660.1	659.4
20°	638.4	640.8	641.5	649.3	649.3
22.5°	623.7	626.8	628.4	636.1	637.7
25°	607.5	612.1	614.4	623.0	623.7
27.5°	589.6	596.6	599.7	607.5	608.2
30°	571.8	578.0	583.4	592.0	593.5
32.5°	552.4	560.2	566.4	576.5	578.0
35°	531.5	540.8	548.6	559.4	561.7
37.5°	510.6	521.4	530.7	541.6	543.9
40°	490.5	500.5	511.4	523.0	526.1
42.5°	467.2	478.8	492.0	505.2	507.5
45°	443.2	457.9	472.6	485.8	489.7
47.5°	420.7	435.4	452.5	465.7	470.3
50°	395.9	413.0	430.0	445.5	450.2
52.5°	371.1	388.2	408.3	423.8	428.5
55°	347.1	363.4	386.6	402.1	406.8
57.5°	320.0	340.1	362.6	381.2	385.1
60°	293.7	313.8	339.4	357.2	363.4
62.5°	268.1	290.6	316.1	333.9	340.1
65°	240.2	265.0	291.3	310.7	316.9
67.5°	213.8	240.2	268.1	287.5	293.7
70°	186.7	213.1	242.5	263.4	268.9
72.5°	160.4	187.5	219.3	239.4	245.6
75°	133.3	161.9	194.5	216.2	223.1
77.5°	107.7	137.9	172.0	193.7	201.5
80°	84.5	115.4	149.5	172.8	179.0
82.5°	61.2	93.8	127.8	151.9	158.8
85°	41.1	73.6	108.5	131.7	139.5
87.5°	25.6	57.3	91.4	113.9	120.9
90°	15.9	59.7	102.2	131.7	140.2
92.5°	41.8	84.0	123.2	148.4	155.7
95°	79.8	115.7	155.6	180.0	187.0
97.5°	120.8	152.6	193.6	218.4	225.4
100°	171.1	195.9	236.6	259.8	265.2
102.5°	224.5	242.7	281.4	305.1	312.5
105°	277.6	294.2	327.5	350.3	360.0
107.5°	334.4	348.7	377.1	401.0	405.4
110°	391.7	404.8	430.9	446.3	456.0

TEST NUMBER: P1001488

CATALOG NUMBER: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	451.3	460.6	483.9	500.9	507.1
115°	510.9	517.9	540.3	556.3	560.5
117.5°	567.8	572.5	594.5	607.3	610.0
120°	624.0	630.9	649.9	659.6	668.1
122.5°	683.2	684.3	704.1	716.1	715.7
125°	740.4	739.6	757.9	770.3	772.6
127.5°	792.7	795.4	808.6	820.2	824.5
130°	847.6	850.3	862.7	874.4	874.3
132.5°	904.5	906.0	914.2	925.1	928.6
135°	952.5	959.5	965.0	975.0	976.2
137.5°	1007.1	1009.9	1015.3	1023.4	1028.5
140°	1061.6	1063.3	1064.0	1072.9	1075.6
142.5°	1110.9	1113.2	1111.2	1119.7	1122.8
145°	1156.2	1160.0	1161.2	1164.6	1164.2
147.5°	1202.6	1207.6	1206.4	1206.1	1208.0
150°	1244.4	1248.3	1248.3	1248.3	1247.1
152.5°	1283.1	1285.4	1286.6	1290.1	1286.6
155°	1323.7	1323.7	1322.6	1327.2	1322.6
157.5°	1358.6	1356.2	1356.2	1359.7	1356.2
160°	1388.8	1387.6	1386.4	1389.9	1384.1
162.5°	1416.6	1413.1	1412.0	1418.9	1413.1
165°	1441.0	1437.5	1435.2	1442.2	1437.5
167.5°	1460.7	1456.1	1456.1	1463.1	1456.1
170°	1477.0	1471.2	1472.4	1479.3	1471.2
172.5°	1488.6	1484.0	1484.0	1492.1	1484.0
175°	1499.1	1493.3	1492.1	1500.2	1492.1
177.5°	1503.7	1497.9	1497.9	1506.0	1496.7
180°	1501.4	1501.4	1501.4	1501.4	1501.4

(END OF REPORT)