

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001491

Luminaire Tested: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001491
REPORT IS A COMBINATION OF REPORTS P996110 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6651.0 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001491

CATALOG NUMBER: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001491

CATALOG NUMBER: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	91	87	83	86	82	79	76	67	65	62	52	51	50	39	38	37
2	86	79	73	68	78	72	67	62	58	55	52	46	44	41	35	33	32
3	79	70	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16
8	52	40	32	27	47	37	30	25	30	25	21	24	21	18	19	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13
10	45	33	26	22	41	31	24	20	25	21	17	21	17	14	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7885	7885	7885
5°	7892	7659	7668
10°	7825	7446	7394
15°	7713	7193	7084
20°	7569	6920	6765
25°	7409	6631	6420
30°	7214	6318	6042
35°	7012	5999	5676
40°	6802	5655	5287
45°	6582	5309	4923
50°	6338	4974	4521
55°	6073	4585	4121
60°	5801	4156	3705
65°	5492	3714	3235
70°	5133	3182	2732
75°	4599	2565	2188
80°	3920	1854	1539
85°	3042	1033	828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6582 cd/sqm

TEST NUMBER: P1001491

CATALOG NUMBER: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	1.4
10°-20°	256.8	3.9
20°-30°	377.9	5.7
30°-40°	439.3	6.6
40°-50°	439.3	6.6
50°-60°	384.2	5.8
60°-70°	285.2	4.3
70°-80°	161.8	2.4
80°-90°	49.5	0.7
90°-100°	97.9	1.5
100°-110°	293.1	4.4
110°-120°	498.0	7.5
120°-130°	656.7	9.9
130°-140°	737.6	11.1
140°-150°	725.0	10.9
150°-160°	609.8	9.2
160°-170°	405.7	6.1
170°-180°	142.1	2.1
0°-30°	725.8	10.9
0°-40°	1165.1	17.5
0°-60°	1988.6	29.9
0°-90°	2485.2	37.4
90°-120°	889.0	13.4
90°-150°	3008.3	45.2
90°-180°	4166.0	62.6
0°-180°	6651.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	967	967	967	967	967	
5°	966	963	955	963	962	92
15°	920	917	905	910	907	259
25°	833	828	817	818	814	383
35°	717	711	700	695	691	448
45°	585	580	567	559	556	451
55°	442	440	429	420	415	396
65°	300	296	288	280	277	297
75°	160	156	152	149	148	169
85°	42	42	40	40	40	45
90°	4	16	26	32	35	8
95°	70	80	88	92	92	75
105°	271	272	276	280	283	287
115°	506	506	504	503	502	499
125°	737	737	736	734	732	657
135°	951	958	958	956	952	736
145°	1155	1160	1161	1160	1156	723
155°	1324	1324	1323	1327	1323	609
165°	1441	1438	1435	1442	1438	406
175°	1499	1493	1492	1500	1492	142
180°	1501	1501	1501	1501	1501	

TEST NUMBER: P1001491

CATALOG NUMBER: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	967.0	967.0	967.0	967.0	967.0
2.5°	970.1	967.8	959.3	967.0	966.2
5°	966.2	963.1	954.6	963.1	961.6
7.5°	959.3	956.2	946.9	953.8	953.1
10°	949.2	946.1	936.0	942.2	940.7
12.5°	936.0	932.9	922.1	929.0	926.7
15°	919.7	916.6	905.0	909.7	907.3
17.5°	901.1	897.3	886.4	889.5	888.0
20°	880.2	876.3	864.7	867.0	865.5
22.5°	857.7	852.3	840.7	845.4	842.3
25°	833.0	827.5	816.7	817.5	814.4
27.5°	805.1	799.6	789.6	788.0	784.1
30°	777.2	771.0	760.9	757.8	753.9
32.5°	747.7	742.3	731.5	727.6	723.7
35°	716.7	711.3	700.5	695.0	691.2
37.5°	684.2	679.5	667.9	662.5	657.1
40°	652.4	646.2	634.6	626.8	623.0
42.5°	618.3	615.2	602.1	592.8	590.4
45°	585.0	579.6	567.2	558.7	556.3
47.5°	550.1	546.3	534.6	525.3	519.1
50°	514.5	511.4	500.5	489.7	485.1
52.5°	479.6	475.8	464.1	454.8	448.6
55°	442.4	440.1	429.3	420.0	415.3
57.5°	407.6	405.2	394.4	385.1	380.4
60°	371.1	367.3	357.2	350.2	346.4
62.5°	335.5	332.4	321.6	315.4	311.5
65°	299.9	296.0	288.2	280.5	276.6
67.5°	263.4	260.3	252.6	244.8	244.1
70°	230.1	224.7	218.5	212.3	210.0
72.5°	194.5	189.1	184.4	179.8	177.4
75°	159.6	155.7	151.9	148.8	148.0
77.5°	125.5	124.0	120.1	119.3	117.0
80°	95.3	93.0	91.4	89.9	89.1
82.5°	65.9	65.1	65.1	64.3	63.5
85°	41.8	41.8	40.3	40.3	39.5
87.5°	20.1	19.4	18.6	18.6	18.6
90°	3.5	16.3	25.5	32.5	34.8
92.5°	30.2	45.3	51.1	54.6	55.7
95°	69.7	80.1	88.2	91.7	91.7
97.5°	111.5	120.8	130.1	134.7	134.7
100°	162.6	167.2	177.7	180.0	180.0
102.5°	216.0	217.1	226.4	229.9	231.1
105°	270.6	271.7	276.4	279.8	283.3
107.5°	327.4	328.6	329.8	334.4	333.3
110°	385.5	387.8	386.7	384.3	387.8

TEST NUMBER: P1001491

CATALOG NUMBER: SA4XXDIP-B575D1205UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	445.9	445.9	443.6	443.6	443.6
115°	506.3	506.3	503.9	502.8	501.6
117.5°	563.2	563.2	562.0	558.5	555.0
120°	620.1	624.7	621.2	615.4	617.7
122.5°	679.3	680.4	679.3	675.8	670.0
125°	737.3	737.3	736.2	733.9	731.5
127.5°	789.6	793.1	790.8	788.4	787.3
130°	845.3	848.8	848.8	846.5	841.8
132.5°	902.2	904.5	903.4	901.1	899.9
135°	951.0	958.0	958.0	955.6	952.2
137.5°	1005.6	1009.1	1011.4	1007.9	1009.1
140°	1060.1	1062.5	1062.5	1061.3	1060.1
142.5°	1110.1	1112.4	1111.2	1111.2	1111.2
145°	1155.4	1160.0	1161.2	1160.0	1156.5
147.5°	1201.8	1207.6	1206.4	1205.3	1204.1
150°	1243.6	1248.3	1248.3	1248.3	1247.1
152.5°	1283.1	1285.4	1286.6	1290.1	1286.6
155°	1323.7	1323.7	1322.6	1327.2	1322.6
157.5°	1358.6	1356.2	1356.2	1359.7	1356.2
160°	1388.8	1387.6	1386.4	1389.9	1384.1
162.5°	1416.6	1413.1	1412.0	1418.9	1413.1
165°	1441.0	1437.5	1435.2	1442.2	1437.5
167.5°	1460.7	1456.1	1456.1	1463.1	1456.1
170°	1477.0	1471.2	1472.4	1479.3	1471.2
172.5°	1488.6	1484.0	1484.0	1492.1	1484.0
175°	1499.1	1493.3	1492.1	1500.2	1492.1
177.5°	1503.7	1497.9	1497.9	1506.0	1496.7
180°	1501.4	1501.4	1501.4	1501.4	1501.4

(END OF REPORT)