

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000541

Luminaire Tested: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000541
REPORT IS A COMBINATION OF REPORTS P995151 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8075.3 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000541

CATALOG NUMBER: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000541

CATALOG NUMBER: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	67	61	56	58	53	49	50	46	43	42	39	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	33	30	27
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	24	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13985	13985	13985
5°	13997	13583	13599
10°	13878	13206	13113
15°	13679	12758	12565
20°	13425	12272	11997
25°	13139	11760	11386
30°	12794	11206	10715
35°	12437	10639	10067
40°	12064	10029	9377
45°	11673	9416	8733
50°	11241	8824	8018
55°	10771	8130	7309
60°	10291	7371	6570
65°	9739	6587	5738
70°	9105	5643	4845
75°	8158	4550	3881
80°	6951	3290	2729
85°	5399	1832	1469

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11673 cd/sqm

TEST NUMBER: P1000541

CATALOG NUMBER: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	2.0
10°-20°	455.4	5.6
20°-30°	670.3	8.3
30°-40°	779.1	9.6
40°-50°	779.0	9.6
50°-60°	681.4	8.4
60°-70°	505.9	6.3
70°-80°	287.0	3.6
80°-90°	84.1	1.0
90°-100°	373.7	4.6
100°-110°	760.0	9.4
110°-120°	677.5	8.4
120°-130°	569.1	7.0
130°-140°	474.9	5.9
140°-150°	362.7	4.5
150°-160°	254.9	3.2
160°-170°	149.9	1.9
170°-180°	48.8	0.6
0°-30°	1287.3	15.9
0°-40°	2066.5	25.6
0°-60°	3526.9	43.7
0°-90°	4403.9	54.5
90°-120°	1811.2	22.4
90°-150°	3217.8	39.8
90°-180°	3671.0	45.5
0°-180°	8075.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1715	1715	1715	1715	1715	
5°	1714	1708	1693	1708	1705	163
15°	1631	1626	1605	1613	1609	460
25°	1477	1468	1448	1450	1444	680
35°	1271	1262	1242	1233	1226	795
45°	1038	1028	1006	991	987	800
55°	785	781	761	745	737	703
65°	532	525	511	498	491	526
75°	283	276	269	264	262	300
85°	74	74	72	72	70	80
90°	1	8	18	20	21	7
95°	33	103	806	399	241	36
105°	116	168	648	1396	1391	123
115°	204	255	578	1111	1335	202
125°	284	337	575	945	1066	253
135°	337	401	570	839	953	260
145°	388	445	567	708	778	244
155°	442	477	552	625	651	204
165°	481	496	529	560	568	136
175°	502	503	507	514	512	48
180°	503	503	503	503	503	



TEST NUMBER: P1000541

CATALOG NUMBER: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1715.0	1715.0	1715.0	1715.0	1715.0
2.5°	1720.5	1716.4	1701.3	1715.0	1713.7
5°	1713.7	1708.2	1693.1	1708.2	1705.4
7.5°	1701.3	1695.8	1679.3	1691.7	1690.3
10°	1683.4	1677.9	1660.1	1671.1	1668.3
12.5°	1660.1	1654.6	1635.3	1647.7	1643.6
15°	1631.2	1625.7	1605.1	1613.4	1609.2
17.5°	1598.2	1591.4	1572.1	1577.6	1574.9
20°	1561.1	1554.3	1533.6	1537.8	1535.0
22.5°	1521.3	1511.7	1491.0	1499.3	1493.8
25°	1477.3	1467.7	1448.4	1449.8	1444.3
27.5°	1427.8	1418.2	1400.3	1397.6	1390.7
30°	1378.4	1367.4	1349.5	1344.0	1337.1
32.5°	1326.1	1316.5	1297.3	1290.4	1283.5
35°	1271.2	1261.5	1242.3	1232.7	1225.8
37.5°	1213.5	1205.2	1184.6	1175.0	1165.4
40°	1157.1	1146.1	1125.5	1111.8	1104.9
42.5°	1096.6	1091.1	1067.8	1051.3	1047.2
45°	1037.5	1027.9	1005.9	990.8	986.7
47.5°	975.7	968.8	948.2	931.7	920.7
50°	912.5	907.0	887.8	868.5	860.3
52.5°	850.7	843.8	823.2	806.7	795.7
55°	784.7	780.6	761.3	744.8	736.6
57.5°	722.8	718.7	699.5	683.0	674.7
60°	658.3	651.4	633.5	621.2	614.3
62.5°	595.0	589.5	570.3	559.3	552.4
65°	531.8	525.0	511.2	497.5	490.6
67.5°	467.2	461.7	448.0	434.3	432.9
70°	408.1	398.5	387.5	376.5	372.4
72.5°	344.9	335.3	327.1	318.8	314.7
75°	283.1	276.2	269.4	263.9	262.5
77.5°	222.6	219.9	213.0	211.6	207.5
80°	169.0	164.9	162.2	159.4	158.0
82.5°	116.8	115.4	115.4	114.1	112.7
85°	74.2	74.2	71.5	71.5	70.1
87.5°	35.7	34.4	33.0	33.0	33.0
90°	1.0	7.9	17.8	19.8	20.8
92.5°	13.8	76.2	387.4	128.0	89.9
95°	32.6	102.8	805.5	398.8	241.2
97.5°	54.4	113.7	861.8	814.4	579.2
100°	75.1	128.5	794.6	1126.8	906.3
102.5°	94.9	146.3	710.6	1322.4	1191.0
105°	115.6	167.6	648.4	1396.0	1390.6
107.5°	138.4	189.2	607.8	1373.8	1485.5
110°	161.1	211.0	589.1	1294.8	1487.5

TEST NUMBER: P1000541

CATALOG NUMBER: SA4XXDIP-B1020D1035UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.8	232.8	580.2	1197.9	1429.2
115°	203.6	255.4	578.2	1111.0	1335.3
117.5°	225.3	276.8	577.2	1042.7	1243.4
120°	247.1	297.5	577.2	996.8	1168.2
122.5°	266.9	317.8	576.2	966.6	1108.9
125°	283.7	337.0	575.2	945.4	1065.5
127.5°	299.5	354.8	573.2	925.1	1037.8
130°	312.3	372.1	572.3	900.9	1014.1
132.5°	325.2	387.0	571.3	872.2	987.4
135°	337.0	401.2	570.3	839.1	952.8
137.5°	348.9	413.6	570.3	803.6	912.3
140°	361.7	425.0	569.3	769.0	867.8
142.5°	375.6	435.4	569.3	736.8	820.3
145°	388.4	444.8	567.3	707.6	777.8
147.5°	403.3	453.6	564.4	683.4	738.3
150°	417.1	462.0	561.4	661.2	705.7
152.5°	429.9	470.0	556.4	642.4	676.0
155°	441.8	476.9	551.5	624.7	651.3
157.5°	453.7	483.3	546.6	607.8	628.6
160°	464.5	488.8	540.6	591.0	607.8
162.5°	474.4	493.2	534.7	574.8	588.1
165°	481.3	496.2	528.8	559.9	568.3
167.5°	489.2	498.6	522.8	547.0	552.5
170°	494.2	500.6	516.9	534.2	537.7
172.5°	499.1	502.1	511.0	522.8	522.8
175°	502.1	503.1	507.0	513.9	512.0
177.5°	504.1	503.1	504.1	507.5	504.1
180°	503.1	503.1	503.1	503.1	503.1

(END OF REPORT)