

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001497

Luminaire Tested: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001497
REPORT IS A COMBINATION OF REPORTS P996116 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6557.0 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001497

CATALOG NUMBER: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001497

CATALOG NUMBER: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	93	89	85	81	84	80	77	74	64	61	59	49	47	46	35	34	33
2	85	77	71	66	76	70	64	60	56	52	48	42	40	38	30	29	27
3	77	68	60	54	69	61	55	50	49	44	40	37	34	32	27	25	23
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	21	20
5	64	53	45	39	58	48	41	36	38	33	29	29	26	23	21	19	17
6	59	47	39	33	53	43	36	31	34	29	25	27	23	20	19	17	15
7	55	42	35	29	49	38	32	27	31	26	22	24	20	17	17	15	13
8	51	38	31	25	45	35	28	23	28	23	19	22	18	15	16	13	12
9	47	35	27	22	42	32	25	21	26	21	17	20	16	14	15	12	10
10	44	32	25	20	39	29	23	18	24	19	15	18	15	12	14	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5668	5668	5668
5°	5684	5521	5531
10°	5647	5412	5397
15°	5594	5290	5246
20°	5516	5157	5098
25°	5428	5012	4940
30°	5333	4868	4779
35°	5224	4720	4635
40°	5137	4578	4486
45°	5010	4445	4354
50°	4901	4294	4216
55°	4787	4148	4055
60°	4611	3967	3905
65°	4419	3772	3724
70°	4185	3547	3514
75°	3859	3300	3315
80°	3488	3046	3106
85°	3005	2793	2937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 5219 cd/sqm

TEST NUMBER: P1001497

CATALOG NUMBER: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	1.0
10°-20°	188.7	2.9
20°-30°	285.3	4.4
30°-40°	345.2	5.3
40°-50°	364.9	5.6
50°-60°	343.5	5.2
60°-70°	285.0	4.3
70°-80°	200.0	3.1
80°-90°	116.0	1.8
90°-100°	165.4	2.5
100°-110°	344.1	5.2
110°-120°	533.5	8.1
120°-130°	678.3	10.3
130°-140°	748.9	11.4
140°-150°	729.7	11.1
150°-160°	612.4	9.3
160°-170°	407.5	6.2
170°-180°	142.7	2.2
0°-30°	539.9	8.2
0°-40°	885.1	13.5
0°-60°	1593.5	24.3
0°-90°	2194.5	33.5
90°-120°	1043.0	15.9
90°-150°	3200.0	48.8
90°-180°	4363.0	66.5
0°-180°	6557.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	696	694	688	694	694	66
15°	667	668	666	673	672	188
25°	610	615	617	626	627	281
35°	534	543	551	562	564	334
45°	445	460	475	488	492	344
55°	349	365	388	404	409	311
65°	241	266	293	312	318	239
75°	134	163	195	217	224	142
85°	41	74	109	132	140	43
90°	16	60	103	132	141	14
95°	80	116	156	181	188	84
105°	279	296	329	352	362	296
115°	513	520	543	559	563	506
125°	744	743	761	774	776	663
135°	957	964	969	979	980	740
145°	1161	1165	1166	1170	1169	727
155°	1329	1329	1328	1333	1328	612
165°	1447	1444	1441	1448	1444	408
175°	1506	1500	1498	1507	1498	143
180°	1508	1508	1508	1508	1508	

TEST NUMBER: P1001497

CATALOG NUMBER: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.1	695.1	695.1	695.1	695.1
2.5°	698.2	695.9	689.7	695.1	694.4
5°	695.9	693.6	688.1	694.4	693.6
7.5°	691.2	689.7	685.0	692.0	691.2
10°	685.0	684.2	680.3	687.4	686.6
12.5°	676.5	676.5	674.1	680.3	680.3
15°	667.1	667.9	665.6	672.6	671.8
17.5°	654.7	657.0	656.2	663.2	662.4
20°	641.4	643.8	644.5	652.3	652.3
22.5°	626.6	629.7	631.3	639.1	640.6
25°	610.3	615.0	617.3	625.9	626.6
27.5°	592.4	599.4	602.5	610.3	611.1
30°	574.5	580.7	586.2	594.7	596.3
32.5°	555.0	562.8	569.0	579.1	580.7
35°	534.0	543.3	551.1	562.0	564.4
37.5°	513.0	523.9	533.2	544.1	546.5
40°	492.7	502.9	513.8	525.4	528.6
42.5°	469.4	481.1	494.3	507.5	509.9
45°	445.3	460.1	474.8	488.1	492.0
47.5°	422.7	437.5	454.6	467.8	472.5
50°	397.8	414.9	432.0	447.6	452.3
52.5°	372.9	390.0	410.2	425.8	430.5
55°	348.7	365.1	388.4	404.0	408.7
57.5°	321.5	341.7	364.3	383.0	386.9
60°	295.0	315.3	341.0	358.9	365.1
62.5°	269.3	291.9	317.6	335.5	341.7
65°	241.3	266.2	292.7	312.1	318.4
67.5°	214.8	241.3	269.3	288.8	295.0
70°	187.6	214.1	243.6	264.7	270.1
72.5°	161.1	188.4	220.3	240.5	246.8
75°	133.9	162.7	195.4	217.2	224.2
77.5°	108.2	138.6	172.8	194.6	202.4
80°	84.8	116.0	150.2	173.6	179.8
82.5°	61.5	94.2	128.4	152.6	159.6
85°	41.3	74.0	109.0	132.3	140.1
87.5°	25.7	57.6	91.9	114.4	121.4
90°	16.0	59.9	102.8	132.3	140.9
92.5°	42.0	84.4	123.7	149.0	156.4
95°	80.1	116.3	156.3	180.8	187.8
97.5°	121.3	153.2	194.4	219.4	226.4
100°	171.9	196.7	237.6	261.0	266.4
102.5°	225.5	243.8	282.7	306.4	313.8
105°	278.7	295.5	329.0	351.8	361.6
107.5°	335.9	350.2	378.7	402.8	407.1
110°	393.4	406.6	432.7	448.3	458.0

TEST NUMBER: P1001497

CATALOG NUMBER: SA4XXDIP-B575D1205UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	453.2	462.6	486.0	503.1	509.3
115°	513.2	520.2	542.7	558.7	563.0
117.5°	570.3	574.9	597.1	609.9	612.7
120°	626.6	633.6	652.7	662.5	671.0
122.5°	686.1	687.3	707.1	719.2	718.8
125°	743.6	742.8	761.2	773.6	776.0
127.5°	796.1	798.8	812.1	823.7	828.1
130°	851.3	854.1	866.5	878.1	878.2
132.5°	908.4	910.1	918.2	929.1	932.6
135°	956.7	963.7	969.1	979.3	980.4
137.5°	1011.5	1014.2	1019.6	1027.8	1032.9
140°	1066.3	1067.9	1068.7	1077.6	1080.3
142.5°	1115.7	1118.0	1116.0	1124.6	1127.7
145°	1161.1	1165.0	1166.2	1169.7	1169.3
147.5°	1207.8	1212.8	1211.7	1211.3	1213.2
150°	1249.8	1253.6	1253.6	1253.6	1252.5
152.5°	1288.6	1291.0	1292.1	1295.6	1292.1
155°	1329.4	1329.4	1328.3	1332.9	1328.3
157.5°	1364.4	1362.1	1362.1	1365.6	1362.1
160°	1394.7	1393.6	1392.4	1395.9	1390.1
162.5°	1422.7	1419.2	1418.1	1425.1	1419.2
165°	1447.2	1443.7	1441.4	1448.4	1443.7
167.5°	1467.1	1462.4	1462.4	1469.4	1462.4
170°	1483.4	1477.5	1478.7	1485.7	1477.5
172.5°	1495.0	1490.4	1490.4	1498.5	1490.4
175°	1505.5	1499.7	1498.5	1506.7	1498.5
177.5°	1510.2	1504.4	1504.4	1512.5	1503.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)