

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000550

Luminaire Tested: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000550
REPORT IS A COMBINATION OF REPORTS P995160 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8110.3 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000550

CATALOG NUMBER: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000550

CATALOG NUMBER: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	67	61	56	58	53	49	50	46	43	42	39	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	33	30	27
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	24	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14045	14045	14045
5°	14058	13642	13658
10°	13938	13262	13170
15°	13739	12812	12620
20°	13483	12326	12049
25°	13196	11811	11436
30°	12849	11254	10762
35°	12491	10685	10110
40°	12116	10073	9418
45°	11723	9457	8771
50°	11289	8861	8053
55°	10818	8165	7341
60°	10334	7403	6598
65°	9781	6615	5762
70°	9145	5668	4866
75°	8193	4568	3897
80°	6984	3304	2741
85°	5421	1840	1476

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11723 cd/sqm

TEST NUMBER: P1000550

CATALOG NUMBER: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.0
10°-20°	457.4	5.6
20°-30°	673.1	8.3
30°-40°	782.5	9.6
40°-50°	782.4	9.6
50°-60°	684.3	8.4
60°-70°	508.0	6.3
70°-80°	288.3	3.6
80°-90°	84.5	1.0
90°-100°	375.3	4.6
100°-110°	763.4	9.4
110°-120°	680.4	8.4
120°-130°	571.5	7.0
130°-140°	476.9	5.9
140°-150°	364.2	4.5
150°-160°	256.0	3.2
160°-170°	150.6	1.9
170°-180°	49.0	0.6
0°-30°	1292.9	15.9
0°-40°	2075.4	25.6
0°-60°	3542.1	43.7
0°-90°	4422.9	54.5
90°-120°	1819.1	22.4
90°-150°	3231.8	39.8
90°-180°	3687.0	45.5
0°-180°	8110.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1722	1722	1722	1722	1722	
5°	1721	1716	1700	1716	1713	163
15°	1638	1633	1612	1620	1616	462
25°	1484	1474	1455	1456	1451	683
35°	1277	1267	1248	1238	1231	798
45°	1042	1032	1010	995	991	803
55°	788	784	765	748	740	706
65°	534	527	513	500	493	529
75°	284	277	270	265	264	302
85°	74	74	72	72	70	80
90°	1	8	18	20	21	7
95°	33	103	809	400	242	36
105°	116	168	651	1402	1397	124
115°	204	257	581	1116	1341	203
125°	285	338	578	950	1070	254
135°	338	403	573	843	957	262
145°	390	447	570	711	781	245
155°	444	479	554	627	654	205
165°	483	498	531	562	571	137
175°	504	505	509	516	514	48
180°	505	505	505	505	505	

TEST NUMBER: P1000550

CATALOG NUMBER: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1722.4	1722.4	1722.4	1722.4	1722.4
2.5°	1728.0	1723.8	1708.6	1722.4	1721.1
5°	1721.1	1715.5	1700.4	1715.5	1712.8
7.5°	1708.6	1703.1	1686.6	1699.0	1697.6
10°	1690.7	1685.2	1667.2	1678.3	1675.5
12.5°	1667.2	1661.7	1642.4	1654.8	1650.7
15°	1638.3	1632.7	1612.0	1620.3	1616.2
17.5°	1605.1	1598.2	1578.9	1584.4	1581.7
20°	1567.9	1561.0	1540.3	1544.4	1541.6
22.5°	1527.8	1518.2	1497.5	1505.8	1500.2
25°	1483.7	1474.0	1454.7	1456.1	1450.6
27.5°	1434.0	1424.3	1406.4	1403.6	1396.7
30°	1384.3	1373.3	1355.3	1349.8	1342.9
32.5°	1331.9	1322.2	1302.9	1296.0	1289.1
35°	1276.7	1267.0	1247.7	1238.0	1231.1
37.5°	1218.7	1210.4	1189.7	1180.0	1170.4
40°	1162.1	1151.1	1130.4	1116.6	1109.7
42.5°	1101.4	1095.9	1072.4	1055.8	1051.7
45°	1042.0	1032.4	1010.3	995.1	991.0
47.5°	979.9	973.0	952.3	935.8	924.7
50°	916.4	910.9	891.6	872.3	864.0
52.5°	854.3	847.4	826.7	810.2	799.1
55°	788.1	783.9	764.6	748.1	739.8
57.5°	726.0	721.8	702.5	685.9	677.7
60°	661.1	654.2	636.3	623.8	616.9
62.5°	597.6	592.1	572.8	561.7	554.8
65°	534.1	527.2	513.4	499.6	492.7
67.5°	469.3	463.7	449.9	436.1	434.8
70°	409.9	400.2	389.2	378.2	374.0
72.5°	346.4	336.8	328.5	320.2	316.1
75°	284.3	277.4	270.5	265.0	263.6
77.5°	223.6	220.8	213.9	212.5	208.4
80°	169.8	165.6	162.9	160.1	158.7
82.5°	117.3	115.9	115.9	114.6	113.2
85°	74.5	74.5	71.8	71.8	70.4
87.5°	35.9	34.5	33.1	33.1	33.1
90°	1.0	7.9	17.9	19.9	20.8
92.5°	13.9	76.4	389.1	128.6	90.3
95°	32.8	103.2	809.0	400.5	242.2
97.5°	54.6	114.2	865.6	818.0	581.7
100°	75.4	129.0	798.1	1131.6	910.3
102.5°	95.3	146.9	713.7	1328.2	1196.2
105°	116.1	168.3	651.2	1402.2	1396.7
107.5°	139.0	190.1	610.5	1379.8	1492.0
110°	161.8	211.9	591.6	1300.4	1494.0

TEST NUMBER: P1000550

CATALOG NUMBER: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	183.6	233.8	582.7	1203.1	1435.4
115°	204.5	256.6	580.7	1115.8	1341.1
117.5°	226.3	278.0	579.7	1047.3	1248.8
120°	248.2	298.8	579.7	1001.2	1173.3
122.5°	268.0	319.1	578.7	970.8	1113.8
125°	284.9	338.5	577.7	949.5	1070.1
127.5°	300.8	356.4	575.8	929.2	1042.3
130°	313.7	373.7	574.8	904.8	1018.5
132.5°	326.6	388.6	573.8	876.0	991.7
135°	338.5	403.0	572.8	842.8	956.9
137.5°	350.4	415.4	572.8	807.0	916.2
140°	363.3	426.8	571.8	772.3	871.6
142.5°	377.2	437.3	571.8	740.0	823.9
145°	390.1	446.7	569.8	710.8	781.2
147.5°	405.0	455.6	566.8	686.4	741.5
150°	418.9	464.0	563.8	664.1	708.8
152.5°	431.8	472.0	558.9	645.2	679.0
155°	443.7	479.0	553.9	627.3	654.2
157.5°	455.6	485.4	548.9	610.5	631.3
160°	466.6	490.8	543.0	593.6	610.5
162.5°	476.5	495.4	537.0	577.2	590.6
165°	483.4	498.3	531.1	562.3	570.8
167.5°	491.4	500.8	525.1	549.4	554.9
170°	496.3	502.8	519.2	536.6	540.0
172.5°	501.3	504.3	513.2	525.1	525.1
175°	504.3	505.3	509.2	516.2	514.2
177.5°	506.3	505.3	506.3	509.7	506.3
180°	505.3	505.3	505.3	505.3	505.3

(END OF REPORT)