

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001515

Luminaire Tested: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001515
REPORT IS A COMBINATION OF REPORTS P996134 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6277.0 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001515

CATALOG NUMBER: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001515

CATALOG NUMBER: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	93	89	85	81	84	80	77	74	64	61	59	49	47	46	35	34	33
2	85	77	71	66	76	70	64	60	56	52	48	42	40	38	30	29	27
3	77	68	60	54	69	61	55	50	49	44	40	37	34	32	27	25	23
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	21	20
5	64	53	45	39	58	48	41	36	38	33	29	29	26	23	21	19	17
6	59	47	39	33	53	43	36	31	34	29	25	27	23	20	19	17	15
7	55	42	35	29	49	38	32	27	31	26	22	24	20	17	17	15	13
8	51	38	31	25	45	35	28	23	28	23	19	22	18	15	16	13	12
9	47	35	27	22	42	32	25	21	26	21	17	20	16	14	15	12	10
10	44	32	25	20	39	29	23	18	24	19	15	18	15	12	14	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5427	5427	5427
5°	5442	5285	5295
10°	5406	5182	5167
15°	5356	5065	5022
20°	5281	4938	4881
25°	5197	4798	4729
30°	5105	4660	4575
35°	5001	4518	4437
40°	4918	4383	4294
45°	4796	4255	4168
50°	4691	4111	4036
55°	4583	3972	3883
60°	4416	3798	3738
65°	4230	3611	3565
70°	4007	3397	3364
75°	3694	3160	3173
80°	3340	2916	2975
85°	2874	2673	2811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 4958 cd/sqm

TEST NUMBER: P1001515

CATALOG NUMBER: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.0
10°-20°	180.7	2.9
20°-30°	273.2	4.4
30°-40°	330.5	5.3
40°-50°	349.4	5.6
50°-60°	328.8	5.2
60°-70°	272.9	4.3
70°-80°	191.5	3.1
80°-90°	111.0	1.8
90°-100°	158.4	2.5
100°-110°	329.4	5.2
110°-120°	510.7	8.1
120°-130°	649.3	10.3
130°-140°	716.9	11.4
140°-150°	698.5	11.1
150°-160°	586.2	9.3
160°-170°	390.0	6.2
170°-180°	136.6	2.2
0°-30°	516.9	8.2
0°-40°	847.4	13.5
0°-60°	1525.6	24.3
0°-90°	2101.0	33.5
90°-120°	998.4	15.9
90°-150°	3063.2	48.8
90°-180°	4176.0	66.5
0°-180°	6277.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	666	666	666	666	666	
5°	666	664	659	665	664	63
15°	639	639	637	644	643	180
25°	584	589	591	599	600	269
35°	511	520	528	538	540	320
45°	426	440	455	467	471	329
55°	334	350	372	387	391	298
65°	231	255	280	299	305	229
75°	128	156	187	208	215	136
85°	40	71	104	127	134	41
90°	15	57	98	127	135	13
95°	77	111	150	173	180	80
105°	267	283	315	337	346	283
115°	491	498	520	535	539	485
125°	712	711	729	740	743	635
135°	916	922	928	937	938	709
145°	1111	1115	1116	1120	1119	696
155°	1273	1273	1272	1276	1272	586
165°	1385	1382	1380	1386	1382	391
175°	1441	1436	1434	1442	1434	137
180°	1443	1443	1443	1443	1443	

TEST NUMBER: P1001515

CATALOG NUMBER: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	665.5	665.5	665.5	665.5	665.5
2.5°	668.5	666.3	660.3	665.5	664.8
5°	666.3	664.0	658.8	664.8	664.0
7.5°	661.8	660.3	655.8	662.5	661.8
10°	655.8	655.1	651.4	658.1	657.3
12.5°	647.6	647.6	645.4	651.4	651.4
15°	638.7	639.4	637.2	643.9	643.2
17.5°	626.8	629.0	628.2	635.0	634.2
20°	614.1	616.3	617.1	624.5	624.5
22.5°	599.9	602.9	604.4	611.9	613.3
25°	584.3	588.7	591.0	599.2	599.9
27.5°	567.1	573.8	576.8	584.3	585.0
30°	550.0	556.0	561.2	569.4	570.9
32.5°	531.4	538.8	544.8	554.5	556.0
35°	511.2	520.2	527.6	538.1	540.3
37.5°	491.1	501.6	510.5	520.9	523.2
40°	471.7	481.4	491.9	503.0	506.0
42.5°	449.4	460.6	473.2	485.9	488.1
45°	426.3	440.4	454.6	467.3	471.0
47.5°	404.7	418.8	435.2	447.9	452.4
50°	380.8	397.2	413.6	428.5	433.0
52.5°	357.0	373.4	392.7	407.7	412.1
55°	333.9	349.5	371.9	386.8	391.3
57.5°	307.8	327.2	348.8	366.7	370.4
60°	282.5	301.8	326.4	343.6	349.5
62.5°	257.9	279.5	304.1	321.2	327.2
65°	231.0	254.9	280.2	298.8	304.8
67.5°	205.7	231.0	257.9	276.5	282.5
70°	179.6	204.9	233.3	253.4	258.6
72.5°	154.3	180.4	210.9	230.3	236.2
75°	128.2	155.8	187.1	207.9	214.6
77.5°	103.6	132.7	165.4	186.3	193.8
80°	81.2	111.0	143.8	166.2	172.2
82.5°	58.9	90.2	123.0	146.1	152.8
85°	39.5	70.8	104.3	126.7	134.1
87.5°	24.6	55.1	87.9	109.6	116.3
90°	15.2	57.3	98.4	126.7	134.9
92.5°	40.2	80.8	118.4	142.7	149.7
95°	76.7	111.3	149.6	173.2	179.9
97.5°	116.1	146.7	186.1	210.0	216.7
100°	164.5	188.4	227.4	249.8	255.0
102.5°	215.8	233.4	270.6	293.3	300.4
105°	266.8	282.8	314.9	336.8	346.2
107.5°	321.5	335.3	362.5	385.6	389.7
110°	376.6	389.3	414.2	429.1	438.5

TEST NUMBER: P1001515

CATALOG NUMBER: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	433.9	442.9	465.2	481.5	487.5
115°	491.2	497.9	519.5	534.8	538.9
117.5°	545.9	550.3	571.6	584.0	586.5
120°	599.8	606.6	624.8	634.2	642.3
122.5°	656.7	657.9	676.8	688.5	688.1
125°	711.9	711.1	728.6	740.5	742.8
127.5°	762.1	764.6	777.3	788.6	792.7
130°	814.9	817.5	829.4	840.6	840.6
132.5°	869.6	871.1	878.9	889.4	892.7
135°	915.8	922.5	927.7	937.3	938.5
137.5°	968.2	970.8	976.0	983.9	988.7
140°	1020.7	1022.1	1022.9	1031.5	1034.1
142.5°	1067.9	1070.1	1068.3	1076.5	1079.5
145°	1111.4	1115.2	1116.3	1119.7	1119.4
147.5°	1156.1	1161.0	1159.9	1159.4	1161.3
150°	1196.3	1200.0	1200.0	1200.0	1198.9
152.5°	1233.5	1235.8	1236.9	1240.2	1236.9
155°	1272.6	1272.6	1271.5	1276.0	1271.5
157.5°	1306.1	1303.9	1303.9	1307.2	1303.9
160°	1335.1	1334.0	1332.9	1336.2	1330.7
162.5°	1361.9	1358.6	1357.4	1364.1	1358.6
165°	1385.4	1382.0	1379.8	1386.5	1382.0
167.5°	1404.3	1399.9	1399.9	1406.6	1399.9
170°	1420.0	1414.4	1415.5	1422.2	1414.4
172.5°	1431.1	1426.7	1426.7	1434.5	1426.7
175°	1441.2	1435.6	1434.5	1442.3	1434.5
177.5°	1445.6	1440.1	1440.1	1447.9	1438.9
180°	1443.4	1443.4	1443.4	1443.4	1443.4

(END OF REPORT)