

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001516

Luminaire Tested: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001516
REPORT IS A COMBINATION OF REPORTS P996135 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6419.2 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001516

CATALOG NUMBER: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001516

CATALOG NUMBER: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	93	89	85	81	84	80	77	73	64	61	59	48	47	45	34	34	33
2	85	77	71	66	76	69	64	60	55	51	48	42	40	37	30	28	27
3	77	67	60	54	69	61	55	49	48	44	40	37	34	31	26	24	23
4	70	59	52	46	63	54	47	42	43	38	34	33	29	26	23	21	19
5	64	53	45	39	58	48	41	35	38	33	29	29	26	23	21	19	17
6	59	47	39	33	53	43	36	31	34	29	25	26	23	20	19	16	14
7	54	42	34	29	49	38	31	27	31	26	22	24	20	17	17	15	13
8	50	38	31	25	45	35	28	23	28	23	19	22	18	15	16	13	11
9	47	35	27	22	42	32	25	21	26	21	17	20	16	14	14	12	10
10	44	32	25	20	39	29	23	18	23	19	15	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5427	5427	5427
5°	5442	5285	5295
10°	5406	5182	5167
15°	5356	5065	5022
20°	5281	4938	4881
25°	5197	4798	4729
30°	5105	4660	4575
35°	5001	4518	4437
40°	4918	4383	4294
45°	4796	4255	4168
50°	4691	4111	4036
55°	4583	3972	3883
60°	4416	3798	3738
65°	4230	3611	3565
70°	4007	3397	3364
75°	3694	3160	3173
80°	3340	2916	2975
85°	2874	2673	2811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4796 cd/sqm

TEST NUMBER: P1001516

CATALOG NUMBER: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.0
10°-20°	180.7	2.8
20°-30°	273.2	4.3
30°-40°	330.5	5.1
40°-50°	349.4	5.4
50°-60°	328.8	5.1
60°-70°	272.9	4.3
70°-80°	191.5	3.0
80°-90°	110.1	1.7
90°-100°	486.5	7.6
100°-110°	906.3	14.1
110°-120°	797.3	12.4
120°-130°	660.9	10.3
130°-140°	544.3	8.5
140°-150°	411.3	6.4
150°-160°	288.0	4.5
160°-170°	169.4	2.6
170°-180°	55.1	0.9
0°-30°	516.9	8.1
0°-40°	847.4	13.2
0°-60°	1525.6	23.8
0°-90°	2100.1	32.7
90°-120°	2190.1	34.1
90°-150°	3806.6	59.3
90°-180°	4319.0	67.3
0°-180°	6419.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	666	666	666	666	666	
5°	666	664	659	665	664	63
15°	639	639	637	644	643	180
25°	584	589	591	599	600	269
35°	511	520	528	538	540	320
45°	426	440	455	467	471	329
55°	334	350	372	387	391	298
65°	231	255	280	299	305	229
75°	128	156	187	208	215	136
85°	40	71	104	127	134	41
90°	13	51	94	118	125	11
95°	47	150	975	536	364	48
105°	137	211	782	1645	1645	147
115°	234	300	688	1307	1565	233
125°	324	383	671	1103	1243	289
135°	382	455	651	967	1100	296
145°	440	502	641	804	886	276
155°	499	539	623	706	736	230
165°	544	561	597	633	642	154
175°	567	568	573	581	578	54
180°	568	568	568	568	568	

TEST NUMBER: P1001516

CATALOG NUMBER: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	665.5	665.5	665.5	665.5	665.5
2.5°	668.5	666.3	660.3	665.5	664.8
5°	666.3	664.0	658.8	664.8	664.0
7.5°	661.8	660.3	655.8	662.5	661.8
10°	655.8	655.1	651.4	658.1	657.3
12.5°	647.6	647.6	645.4	651.4	651.4
15°	638.7	639.4	637.2	643.9	643.2
17.5°	626.8	629.0	628.2	635.0	634.2
20°	614.1	616.3	617.1	624.5	624.5
22.5°	599.9	602.9	604.4	611.9	613.3
25°	584.3	588.7	591.0	599.2	599.9
27.5°	567.1	573.8	576.8	584.3	585.0
30°	550.0	556.0	561.2	569.4	570.9
32.5°	531.4	538.8	544.8	554.5	556.0
35°	511.2	520.2	527.6	538.1	540.3
37.5°	491.1	501.6	510.5	520.9	523.2
40°	471.7	481.4	491.9	503.0	506.0
42.5°	449.4	460.6	473.2	485.9	488.1
45°	426.3	440.4	454.6	467.3	471.0
47.5°	404.7	418.8	435.2	447.9	452.4
50°	380.8	397.2	413.6	428.5	433.0
52.5°	357.0	373.4	392.7	407.7	412.1
55°	333.9	349.5	371.9	386.8	391.3
57.5°	307.8	327.2	348.8	366.7	370.4
60°	282.5	301.8	326.4	343.6	349.5
62.5°	257.9	279.5	304.1	321.2	327.2
65°	231.0	254.9	280.2	298.8	304.8
67.5°	205.7	231.0	257.9	276.5	282.5
70°	179.6	204.9	233.3	253.4	258.6
72.5°	154.3	180.4	210.9	230.3	236.2
75°	128.2	155.8	187.1	207.9	214.6
77.5°	103.6	132.7	165.4	186.3	193.8
80°	81.2	111.0	143.8	166.2	172.2
82.5°	58.9	90.2	123.0	146.1	152.8
85°	39.5	70.8	104.3	126.7	134.1
87.5°	24.6	55.1	87.9	109.6	116.3
90°	13.0	50.6	93.9	117.7	124.9
92.5°	26.8	123.3	507.0	234.8	197.7
95°	46.6	150.4	974.9	535.6	364.2
97.5°	70.3	159.0	1034.9	1000.6	741.6
100°	93.1	172.8	954.4	1349.8	1106.0
102.5°	115.4	189.8	855.8	1566.4	1423.9
105°	137.4	210.9	781.7	1645.1	1645.0
107.5°	163.0	233.2	732.3	1616.3	1747.7
110°	188.0	254.8	708.0	1522.4	1746.2

TEST NUMBER: P1001516

CATALOG NUMBER: SA4XXDIP-B575D1205UB50-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.8	277.2	694.3	1408.5	1675.8
115°	234.5	299.8	688.3	1306.6	1565.2
117.5°	259.1	321.5	683.4	1225.1	1457.7
120°	282.9	342.2	679.7	1168.6	1368.3
122.5°	305.2	362.7	674.8	1130.9	1296.9
125°	323.5	383.0	670.8	1103.1	1243.3
127.5°	341.4	403.1	664.8	1075.8	1208.3
130°	355.1	421.9	660.0	1044.7	1177.0
132.5°	369.6	438.7	655.8	1008.6	1143.2
135°	382.3	454.9	651.0	966.7	1099.6
137.5°	395.7	468.0	648.0	922.8	1049.3
140°	410.2	480.9	644.7	880.0	995.4
142.5°	425.0	492.6	643.2	840.6	938.1
145°	439.6	502.5	641.0	804.0	886.3
147.5°	456.3	512.6	637.6	772.8	837.9
150°	471.9	522.0	634.3	747.0	797.3
152.5°	485.8	531.0	628.7	725.8	763.8
155°	499.2	538.8	623.1	705.7	735.9
157.5°	512.6	546.1	617.5	686.8	710.2
160°	524.8	552.2	610.8	667.8	686.8
162.5°	536.0	557.2	604.1	649.3	664.4
165°	543.8	560.6	597.4	632.6	642.1
167.5°	552.8	563.4	590.7	618.1	624.2
170°	558.3	565.6	584.0	603.6	607.5
172.5°	563.9	567.3	577.3	590.7	590.7
175°	567.3	568.4	572.9	580.7	578.4
177.5°	569.5	568.4	569.5	573.4	569.5
180°	568.4	568.4	568.4	568.4	568.4

(END OF REPORT)