

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001546

Luminaire Tested: SA4XXDIP-B575D365UB30-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001546
REPORT IS A COMBINATION OF REPORTS P996168 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D365UB30-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3680.6 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001546

CATALOG NUMBER: SA4XXDIP-B575D365UB30-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001546

CATALOG NUMBER: SA4XXDIP-B575D365UB30-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	99	94	89	85	92	88	84	80	76	73	70	65	63	61	55	54	52
2	89	81	74	69	83	76	70	65	66	61	57	56	53	50	48	45	43
3	81	71	63	57	75	66	59	54	58	52	48	50	45	42	42	39	36
4	74	63	54	48	69	59	51	45	51	45	40	44	39	35	37	34	31
5	68	56	47	41	63	52	44	39	45	39	34	39	34	30	33	30	27
6	63	50	41	35	58	47	39	33	41	35	30	35	30	27	30	26	23
7	58	45	37	31	54	42	35	29	37	31	26	32	27	23	28	24	21
8	54	41	33	27	50	38	31	26	34	28	23	29	24	21	25	21	18
9	50	37	29	24	46	35	28	23	31	25	21	27	22	19	23	19	16
10	47	34	27	22	43	32	25	21	28	23	19	25	20	17	22	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5642	5642	5642
5°	5658	5495	5505
10°	5621	5387	5372
15°	5568	5266	5221
20°	5490	5133	5075
25°	5403	4988	4917
30°	5307	4845	4756
35°	5200	4698	4613
40°	5114	4557	4465
45°	4986	4424	4334
50°	4877	4274	4196
55°	4765	4129	4037
60°	4591	3949	3887
65°	4399	3754	3706
70°	4165	3531	3498
75°	3841	3285	3299
80°	3475	3032	3092
85°	2991	2780	2924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4986 cd/sqm

TEST NUMBER: P1001546

CATALOG NUMBER: SA4XXDIP-B575D365UB30-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	1.8
10°-20°	187.8	5.1
20°-30°	284.0	7.7
30°-40°	343.6	9.3
40°-50°	363.2	9.9
50°-60°	341.9	9.3
60°-70°	283.7	7.7
70°-80°	199.1	5.4
80°-90°	112.9	3.1
90°-100°	201.3	5.5
100°-110°	322.9	8.8
110°-120°	276.9	7.5
120°-130°	223.4	6.1
130°-140°	178.9	4.9
140°-150°	132.1	3.6
150°-160°	91.7	2.5
160°-170°	53.9	1.5
170°-180°	17.5	0.5
0°-30°	537.4	14.6
0°-40°	881.0	23.9
0°-60°	1586.1	43.1
0°-90°	2181.8	59.3
90°-120°	801.1	21.8
90°-150°	1335.6	36.3
90°-180°	1499.0	40.7
0°-180°	3680.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	692	692	692	692	692	
5°	693	690	685	691	690	66
15°	664	665	662	669	669	187
25°	608	612	614	623	624	280
35°	532	541	549	559	562	333
45°	443	458	473	486	490	343
55°	347	363	387	402	407	309
65°	240	265	291	311	317	238
75°	133	162	194	216	223	142
85°	41	74	108	132	140	43
90°	13	46	83	106	113	9
95°	22	73	357	232	182	21
105°	49	83	284	573	577	52
115°	78	104	244	453	539	78
125°	105	124	229	376	424	94
135°	123	146	212	321	367	95
145°	141	160	204	259	288	88
155°	159	172	198	225	234	73
165°	173	178	190	201	204	49
175°	181	181	182	185	184	17
180°	181	181	181	181	181	



TEST NUMBER: P1001546

CATALOG NUMBER: SA4XXDIP-B575D365UB30-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	691.9	691.9	691.9	691.9	691.9
2.5°	695.0	692.7	686.5	691.9	691.1
5°	692.7	690.4	684.9	691.1	690.4
7.5°	688.0	686.5	681.8	688.8	688.0
10°	681.8	681.1	677.2	684.2	683.4
12.5°	673.3	673.3	671.0	677.2	677.2
15°	664.0	664.8	662.5	669.4	668.7
17.5°	651.6	653.9	653.2	660.1	659.4
20°	638.4	640.8	641.5	649.3	649.3
22.5°	623.7	626.8	628.4	636.1	637.7
25°	607.5	612.1	614.4	623.0	623.7
27.5°	589.6	596.6	599.7	607.5	608.2
30°	571.8	578.0	583.4	592.0	593.5
32.5°	552.4	560.2	566.4	576.5	578.0
35°	531.5	540.8	548.6	559.4	561.7
37.5°	510.6	521.4	530.7	541.6	543.9
40°	490.5	500.5	511.4	523.0	526.1
42.5°	467.2	478.8	492.0	505.2	507.5
45°	443.2	457.9	472.6	485.8	489.7
47.5°	420.7	435.4	452.5	465.7	470.3
50°	395.9	413.0	430.0	445.5	450.2
52.5°	371.1	388.2	408.3	423.8	428.5
55°	347.1	363.4	386.6	402.1	406.8
57.5°	320.0	340.1	362.6	381.2	385.1
60°	293.7	313.8	339.4	357.2	363.4
62.5°	268.1	290.6	316.1	333.9	340.1
65°	240.2	265.0	291.3	310.7	316.9
67.5°	213.8	240.2	268.1	287.5	293.7
70°	186.7	213.1	242.5	263.4	268.9
72.5°	160.4	187.5	219.3	239.4	245.6
75°	133.3	161.9	194.5	216.2	223.1
77.5°	107.7	137.9	172.0	193.7	201.5
80°	84.5	115.4	149.5	172.8	179.0
82.5°	61.2	93.8	127.8	151.9	158.8
85°	41.1	73.6	108.5	131.7	139.5
87.5°	25.6	57.3	91.4	113.9	120.9
90°	12.8	46.2	83.1	106.3	112.9
92.5°	16.6	66.1	211.5	139.8	132.4
95°	21.8	72.6	357.2	231.8	182.1
97.5°	28.9	72.7	373.6	376.7	299.1
100°	35.5	74.9	344.8	485.2	411.3
102.5°	42.6	78.2	310.7	551.0	509.9
105°	48.6	82.8	284.4	572.8	577.0
107.5°	56.8	88.2	266.0	560.9	606.6
110°	64.2	92.9	256.1	527.8	603.4



TEST NUMBER: P1001546

CATALOG NUMBER: SA4XXDIP-B575D365UB30-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	71.2	98.4	249.0	488.3	577.7
115°	77.9	103.5	244.4	453.2	539.3
117.5°	85.7	108.8	240.2	424.0	502.4
120°	92.8	113.2	236.4	402.8	470.7
122.5°	99.9	118.2	232.1	388.0	444.7
125°	105.2	123.6	228.7	376.5	424.4
127.5°	110.8	130.0	224.1	364.7	410.6
130°	114.7	135.4	219.8	352.0	397.4
132.5°	119.3	140.7	216.3	337.8	383.9
135°	122.8	145.9	212.2	321.3	366.8
137.5°	127.0	149.7	209.1	304.6	347.6
140°	131.7	153.7	206.3	288.2	327.7
142.5°	135.9	157.4	204.8	273.6	306.8
145°	140.6	160.0	204.1	259.2	287.6
147.5°	145.9	163.2	203.1	246.7	269.5
150°	150.9	166.2	202.0	237.9	253.9
152.5°	154.7	169.1	200.2	231.2	243.2
155°	159.0	171.6	198.4	224.8	234.3
157.5°	163.2	173.9	196.6	218.7	226.2
160°	167.1	175.9	194.5	212.6	218.7
162.5°	170.7	177.4	192.4	206.8	211.6
165°	173.2	178.5	190.2	201.4	204.5
167.5°	176.0	179.4	188.1	196.9	198.8
170°	177.8	180.1	186.0	192.2	193.4
172.5°	179.6	180.6	183.8	188.2	188.1
175°	180.6	181.0	182.4	184.9	184.2
177.5°	181.4	181.0	181.4	182.6	181.4
180°	181.0	181.0	181.0	181.0	181.0

(END OF REPORT)