

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001555

Luminaire Tested: SA4XXDIP-B575D365UB35-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001555
REPORT IS A COMBINATION OF REPORTS P996177 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D365UB35-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3697.6 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001555

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001555

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		102	102	102	102		88	88	88		76	76	76		65	65	65
1	99	94	89	85		92	88	84	80		76	73	70		65	63	61		55	54	52
2	89	81	74	69		83	76	70	65		66	61	57		56	53	50		48	45	43
3	81	71	63	57		75	66	59	54		58	52	48		50	45	42		42	39	36
4	74	63	54	48		69	59	51	45		51	45	40		44	39	35		37	34	31
5	68	56	47	41		63	52	44	39		45	39	34		39	34	30		33	30	27
6	63	50	41	35		58	47	39	33		41	35	30		35	30	27		30	26	23
7	58	45	37	31		54	42	35	29		37	31	26		32	27	23		28	24	21
8	54	41	33	27		50	38	31	26		34	28	23		29	24	21		25	21	18
9	50	37	29	24		46	35	28	23		31	25	21		27	22	19		23	19	16
10	47	34	27	22		43	32	25	21		28	23	19		25	20	17		22	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5668	5668	5668
5°	5684	5521	5531
10°	5647	5412	5397
15°	5594	5290	5246
20°	5516	5157	5098
25°	5428	5012	4940
30°	5333	4868	4779
35°	5224	4720	4635
40°	5137	4578	4486
45°	5010	4445	4354
50°	4901	4294	4216
55°	4787	4148	4055
60°	4611	3967	3905
65°	4419	3772	3724
70°	4185	3547	3514
75°	3859	3300	3315
80°	3488	3046	3106
85°	3005	2793	2937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5010 cd/sqm

TEST NUMBER: P1001555

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	1.8
10°-20°	188.7	5.1
20°-30°	285.3	7.7
30°-40°	345.2	9.3
40°-50°	364.9	9.9
50°-60°	343.5	9.3
60°-70°	285.0	7.7
70°-80°	200.0	5.4
80°-90°	113.5	3.1
90°-100°	202.2	5.5
100°-110°	324.4	8.8
110°-120°	278.2	7.5
120°-130°	224.5	6.1
130°-140°	179.8	4.9
140°-150°	132.7	3.6
150°-160°	92.1	2.5
160°-170°	54.2	1.5
170°-180°	17.6	0.5
0°-30°	539.9	14.6
0°-40°	885.1	23.9
0°-60°	1593.5	43.1
0°-90°	2192.0	59.3
90°-120°	804.8	21.8
90°-150°	1341.7	36.3
90°-180°	1506.0	40.7
0°-180°	3697.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	696	694	688	694	694	66
15°	667	668	666	673	672	188
25°	610	615	617	626	627	281
35°	534	543	551	562	564	334
45°	445	460	475	488	492	344
55°	349	365	388	404	409	311
65°	241	266	293	312	318	239
75°	134	163	195	217	224	142
85°	41	74	109	132	140	43
90°	13	46	84	107	113	9
95°	22	73	359	233	183	21
105°	49	83	286	575	580	52
115°	78	104	246	455	542	78
125°	106	124	230	378	426	94
135°	123	147	213	323	368	96
145°	141	161	205	260	289	89
155°	160	172	199	226	235	74
165°	174	179	191	202	205	49
175°	182	182	183	186	185	17
180°	182	182	182	182	182	

TEST NUMBER: P1001555

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.1	695.1	695.1	695.1	695.1
2.5°	698.2	695.9	689.7	695.1	694.4
5°	695.9	693.6	688.1	694.4	693.6
7.5°	691.2	689.7	685.0	692.0	691.2
10°	685.0	684.2	680.3	687.4	686.6
12.5°	676.5	676.5	674.1	680.3	680.3
15°	667.1	667.9	665.6	672.6	671.8
17.5°	654.7	657.0	656.2	663.2	662.4
20°	641.4	643.8	644.5	652.3	652.3
22.5°	626.6	629.7	631.3	639.1	640.6
25°	610.3	615.0	617.3	625.9	626.6
27.5°	592.4	599.4	602.5	610.3	611.1
30°	574.5	580.7	586.2	594.7	596.3
32.5°	555.0	562.8	569.0	579.1	580.7
35°	534.0	543.3	551.1	562.0	564.4
37.5°	513.0	523.9	533.2	544.1	546.5
40°	492.7	502.9	513.8	525.4	528.6
42.5°	469.4	481.1	494.3	507.5	509.9
45°	445.3	460.1	474.8	488.1	492.0
47.5°	422.7	437.5	454.6	467.8	472.5
50°	397.8	414.9	432.0	447.6	452.3
52.5°	372.9	390.0	410.2	425.8	430.5
55°	348.7	365.1	388.4	404.0	408.7
57.5°	321.5	341.7	364.3	383.0	386.9
60°	295.0	315.3	341.0	358.9	365.1
62.5°	269.3	291.9	317.6	335.5	341.7
65°	241.3	266.2	292.7	312.1	318.4
67.5°	214.8	241.3	269.3	288.8	295.0
70°	187.6	214.1	243.6	264.7	270.1
72.5°	161.1	188.4	220.3	240.5	246.8
75°	133.9	162.7	195.4	217.2	224.2
77.5°	108.2	138.6	172.8	194.6	202.4
80°	84.8	116.0	150.2	173.6	179.8
82.5°	61.5	94.2	128.4	152.6	159.6
85°	41.3	74.0	109.0	132.3	140.1
87.5°	25.7	57.6	91.9	114.4	121.4
90°	12.9	46.5	83.5	106.7	113.4
92.5°	16.7	66.4	212.4	140.4	132.9
95°	21.9	73.0	358.8	232.8	182.9
97.5°	28.9	73.0	375.3	378.5	300.4
100°	35.7	75.2	346.4	487.4	413.2
102.5°	42.9	78.6	312.1	553.4	512.2
105°	48.8	83.2	285.7	575.4	579.7
107.5°	57.0	88.6	267.2	563.4	609.3
110°	64.4	93.4	257.3	530.2	606.1

TEST NUMBER: P1001555

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	71.5	98.9	250.2	490.6	580.3
115°	78.3	104.0	245.6	455.2	541.8
117.5°	86.1	109.3	241.3	425.9	504.7
120°	93.2	113.7	237.4	404.6	472.8
122.5°	100.3	118.8	233.2	389.8	446.7
125°	105.6	124.1	229.7	378.3	426.4
127.5°	111.3	130.5	225.1	366.2	412.5
130°	115.2	136.1	220.8	353.6	399.2
132.5°	119.8	141.4	217.4	339.4	385.7
135°	123.4	146.6	213.1	322.8	368.5
137.5°	127.7	150.3	210.0	306.0	349.2
140°	132.3	154.4	207.4	289.6	329.2
142.5°	136.5	158.2	205.8	275.0	308.2
145°	141.2	160.8	205.0	260.5	288.9
147.5°	146.5	164.0	204.0	247.8	270.7
150°	151.5	167.0	202.9	239.0	255.1
152.5°	155.4	169.9	201.1	232.2	244.3
155°	159.7	172.4	199.3	225.8	235.4
157.5°	164.0	174.6	197.5	219.7	227.2
160°	167.9	176.6	195.4	213.6	219.7
162.5°	171.5	178.2	193.3	207.8	212.5
165°	174.0	179.4	191.1	202.4	205.4
167.5°	176.8	180.2	189.0	197.8	199.7
170°	178.6	181.0	186.8	193.0	194.3
172.5°	180.4	181.4	184.7	189.0	189.0
175°	181.5	181.8	183.3	185.8	185.0
177.5°	182.2	181.8	182.2	183.4	182.2
180°	181.8	181.8	181.8	181.8	181.8

(END OF REPORT)