

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001567

Luminaire Tested: SA4XXDIP-B575D365UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001567
REPORT IS A COMBINATION OF REPORTS P996189 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D365UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3781.6 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001567

CATALOG NUMBER: SA4XXDIP-B575D365UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001567

CATALOG NUMBER: SA4XXDIP-B575D365UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	61	59
2	92	84	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	50	45	49	44	41	43	40	37
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25
8	56	43	36	30	53	41	34	29	37	31	27	33	28	25	30	26	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7841	7841	7841
5°	7848	7615	7625
10°	7781	7404	7353
15°	7669	7153	7045
20°	7527	6880	6726
25°	7367	6594	6384
30°	7173	6283	6008
35°	6973	5965	5644
40°	6763	5623	5258
45°	6545	5280	4896
50°	6302	4947	4495
55°	6038	4558	4098
60°	5770	4133	3683
65°	5461	3693	3217
70°	5104	3164	2717
75°	4573	2550	2176
80°	3899	1844	1530
85°	3027	1028	824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6545 cd/sqm

TEST NUMBER: P1001567

CATALOG NUMBER: SA4XXDIP-B575D365UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	2.4
10°-20°	255.3	6.8
20°-30°	375.8	9.9
30°-40°	436.8	11.6
40°-50°	436.8	11.6
50°-60°	382.0	10.1
60°-70°	283.6	7.5
70°-80°	160.9	4.3
80°-90°	46.8	1.2
90°-100°	133.6	3.5
100°-110°	271.8	7.2
110°-120°	242.3	6.4
120°-130°	203.5	5.4
130°-140°	169.8	4.5
140°-150°	129.7	3.4
150°-160°	91.2	2.4
160°-170°	53.6	1.4
170°-180°	17.4	0.5
0°-30°	721.7	19.1
0°-40°	1158.6	30.6
0°-60°	1977.4	52.3
0°-90°	2468.7	65.3
90°-120°	647.7	17.1
90°-150°	1150.7	30.4
90°-180°	1313.0	34.7
0°-180°	3781.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	962	962	962	962	962	
5°	961	958	949	958	956	91
15°	914	912	900	904	902	258
25°	828	823	812	813	810	381
35°	713	707	696	691	687	446
45°	582	576	564	556	553	448
55°	440	438	427	418	413	394
65°	298	294	287	279	275	295
75°	159	155	151	148	147	168
85°	42	42	40	40	39	45
90°	0	3	6	7	7	4
95°	12	37	288	143	86	13
105°	41	60	232	499	497	44
115°	73	91	207	397	478	72
125°	101	121	206	338	381	90
135°	120	144	204	300	341	93
145°	139	159	203	253	278	87
155°	158	171	197	223	233	73
165°	172	177	189	200	203	49
175°	180	180	181	184	183	17
180°	180	180	180	180	180	

TEST NUMBER: P1001567

CATALOG NUMBER: SA4XXDIP-B575D365UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	961.5	961.5	961.5	961.5	961.5
2.5°	964.6	962.3	953.8	961.5	960.8
5°	960.8	957.7	949.2	957.7	956.2
7.5°	953.8	950.8	941.5	948.4	947.7
10°	943.8	940.7	930.7	936.9	935.4
12.5°	930.7	927.6	916.9	923.8	921.5
15°	914.5	911.5	899.9	904.5	902.2
17.5°	896.1	892.2	881.4	884.5	883.0
20°	875.3	871.4	859.8	862.2	860.6
22.5°	852.9	847.5	836.0	840.6	837.5
25°	828.3	822.9	812.1	812.8	809.8
27.5°	800.5	795.1	785.1	783.6	779.7
30°	772.8	766.6	756.6	753.5	749.7
32.5°	743.5	738.1	727.3	723.5	719.6
35°	712.7	707.3	696.5	691.1	687.3
37.5°	680.3	675.7	664.1	658.8	653.4
40°	648.7	642.6	631.0	623.3	619.5
42.5°	614.8	611.8	598.7	589.4	587.1
45°	581.7	576.3	564.0	555.5	553.2
47.5°	547.0	543.2	531.6	522.4	516.2
50°	511.6	508.5	497.7	486.9	482.3
52.5°	476.9	473.1	461.5	452.3	446.1
55°	439.9	437.6	426.8	417.6	413.0
57.5°	405.3	403.0	392.2	382.9	378.3
60°	369.1	365.2	355.2	348.3	344.4
62.5°	333.6	330.5	319.7	313.6	309.7
65°	298.2	294.3	286.6	278.9	275.1
67.5°	262.0	258.9	251.2	243.5	242.7
70°	228.8	223.4	217.3	211.1	208.8
72.5°	193.4	188.0	183.4	178.7	176.4
75°	158.7	154.9	151.0	147.9	147.2
77.5°	124.8	123.3	119.4	118.7	116.3
80°	94.8	92.5	90.9	89.4	88.6
82.5°	65.5	64.7	64.7	63.9	63.2
85°	41.6	41.6	40.1	40.1	39.3
87.5°	20.0	19.3	18.5	18.5	18.5
90°	0.4	2.8	6.4	7.1	7.4
92.5°	4.9	27.2	138.6	45.8	32.2
95°	11.7	36.8	288.1	142.6	86.2
97.5°	19.4	40.6	308.2	291.2	207.1
100°	26.9	46.0	284.2	403.0	324.1
102.5°	33.9	52.3	254.1	472.9	425.9
105°	41.4	59.9	231.9	499.2	497.3
107.5°	49.5	67.7	217.4	491.2	531.2
110°	57.6	75.4	210.7	463.0	531.9



TEST NUMBER: P1001567

CATALOG NUMBER: SA4XXDIP-B575D365UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.4	83.2	207.5	428.4	511.1
115°	72.8	91.4	206.8	397.2	477.5
117.5°	80.6	99.0	206.4	372.8	444.6
120°	88.4	106.4	206.4	356.4	417.8
122.5°	95.4	113.6	206.1	345.7	396.6
125°	101.4	120.6	205.7	338.1	381.0
127.5°	107.1	126.8	205.0	330.8	371.1
130°	111.7	133.0	204.6	322.2	362.6
132.5°	116.3	138.4	204.3	312.0	353.1
135°	120.5	143.5	203.9	300.0	340.7
137.5°	124.8	147.9	203.9	287.4	326.2
140°	129.4	152.0	203.6	275.0	310.3
142.5°	134.3	155.7	203.6	263.5	293.4
145°	138.9	159.0	202.9	253.0	278.2
147.5°	144.2	162.2	201.8	244.4	264.0
150°	149.2	165.2	200.8	236.4	252.4
152.5°	153.7	168.1	199.0	229.8	241.8
155°	158.0	170.6	197.2	223.4	232.9
157.5°	162.2	172.8	195.5	217.4	224.8
160°	166.1	174.8	193.3	211.4	217.4
162.5°	169.7	176.4	191.2	205.6	210.3
165°	172.1	177.4	189.1	200.2	203.2
167.5°	175.0	178.3	187.0	195.6	197.6
170°	176.7	179.0	184.9	191.0	192.3
172.5°	178.5	179.6	182.7	187.0	187.0
175°	179.6	179.9	181.3	183.8	183.1
177.5°	180.3	179.9	180.3	181.5	180.3
180°	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)