

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001582

Luminaire Tested: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001582
REPORT IS A COMBINATION OF REPORTS P996204 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4445.2 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001582

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001582

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	97	92	88	84	89	85	81	78	71	68	66	58	57	55	47	46	44
2	87	80	73	67	80	73	68	63	62	57	54	51	48	45	41	39	37
3	80	70	62	56	73	64	57	52	54	49	45	45	41	38	36	33	31
4	73	61	53	47	66	57	49	44	48	42	38	39	35	32	32	29	26
5	66	54	46	40	61	50	43	37	43	37	32	35	31	27	28	25	23
6	61	49	40	34	56	45	38	32	38	32	28	32	27	24	26	22	20
7	56	44	36	30	52	41	33	28	35	29	25	29	24	21	23	20	17
8	52	40	32	26	48	37	30	25	31	26	22	26	22	19	21	18	16
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	16	14
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5594	5594	5594
5°	5610	5448	5458
10°	5574	5341	5326
15°	5521	5220	5177
20°	5444	5090	5032
25°	5357	4946	4875
30°	5263	4804	4716
35°	5156	4658	4574
40°	5070	4518	4427
45°	4944	4387	4297
50°	4836	4238	4161
55°	4725	4094	4002
60°	4552	3915	3854
65°	4362	3723	3675
70°	4130	3502	3469
75°	3807	3256	3272
80°	3442	3008	3066
85°	2962	2757	2899

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4944 cd/sqm

TEST NUMBER: P1001582

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	1.5
10°-20°	186.2	4.2
20°-30°	281.6	6.3
30°-40°	340.7	7.7
40°-50°	360.2	8.1
50°-60°	339.0	7.6
60°-70°	281.3	6.3
70°-80°	197.4	4.4
80°-90°	112.4	2.5
90°-100°	280.5	6.3
100°-110°	484.9	10.9
110°-120°	421.4	9.5
120°-130°	344.8	7.8
130°-140°	280.3	6.3
140°-150°	209.5	4.7
150°-160°	146.2	3.3
160°-170°	86.0	1.9
170°-180°	28.0	0.6
0°-30°	532.8	12.0
0°-40°	873.5	19.7
0°-60°	1572.7	35.4
0°-90°	2163.7	48.7
90°-120°	1186.7	26.7
90°-150°	2021.4	45.5
90°-180°	2281.0	51.3
0°-180°	4445.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	686	686	686	686	686	
5°	687	684	679	685	684	65
15°	658	659	657	664	663	186
25°	602	607	609	618	618	277
35°	527	536	544	555	557	330
45°	439	454	469	482	486	340
55°	344	360	383	399	403	307
65°	238	263	289	308	314	236
75°	132	161	193	214	221	140
85°	41	73	108	131	138	42
90°	13	48	86	110	116	10
95°	29	94	529	316	233	28
105°	73	118	422	870	874	78
115°	121	158	368	690	824	121
125°	166	196	351	578	652	148
135°	195	232	334	500	570	151
145°	224	255	325	410	454	140
155°	253	273	316	358	374	117
165°	276	284	303	321	326	78
175°	288	288	291	295	294	27
180°	288	288	288	288	288	

TEST NUMBER: P1001582

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	686.0	686.0	686.0	686.0	686.0
2.5°	689.1	686.8	680.7	686.0	685.3
5°	686.8	684.5	679.1	685.3	684.5
7.5°	682.2	680.7	676.1	683.0	682.2
10°	676.1	675.3	671.4	678.4	677.6
12.5°	667.6	667.6	665.3	671.4	671.4
15°	658.4	659.2	656.8	663.8	663.0
17.5°	646.1	648.4	647.6	654.5	653.8
20°	633.0	635.3	636.1	643.8	643.8
22.5°	618.4	621.5	623.0	630.7	632.3
25°	602.3	606.9	609.2	617.7	618.4
27.5°	584.6	591.5	594.6	602.3	603.1
30°	567.0	573.1	578.5	586.9	588.5
32.5°	547.8	555.4	561.6	571.6	573.1
35°	527.0	536.2	543.9	554.7	557.0
37.5°	506.3	517.0	526.2	537.0	539.3
40°	486.3	496.3	507.0	518.6	521.6
42.5°	463.3	474.8	487.8	500.9	503.2
45°	439.4	454.0	468.6	481.7	485.5
47.5°	417.2	431.8	448.7	461.7	466.3
50°	392.6	409.5	426.4	441.7	446.4
52.5°	368.0	384.9	404.9	420.2	424.8
55°	344.2	360.3	383.4	398.7	403.3
57.5°	317.3	337.3	359.5	378.0	381.8
60°	291.2	311.1	336.5	354.2	360.3
62.5°	265.8	288.1	313.4	331.1	337.3
65°	238.2	262.7	288.9	308.1	314.2
67.5°	212.0	238.2	265.8	285.0	291.2
70°	185.1	211.3	240.5	261.2	266.6
72.5°	159.0	185.9	217.4	237.4	243.5
75°	132.1	160.6	192.8	214.3	221.3
77.5°	106.8	136.7	170.6	192.1	199.7
80°	83.7	114.5	148.3	171.3	177.5
82.5°	60.7	93.0	126.8	150.6	157.5
85°	40.7	73.0	107.6	130.6	138.3
87.5°	25.4	56.9	90.7	112.9	119.8
90°	12.9	47.5	86.3	109.6	116.4
92.5°	19.4	82.0	293.5	166.4	150.7
95°	28.7	94.2	528.7	316.2	232.8
97.5°	40.4	96.7	557.2	550.0	422.0
100°	51.6	102.1	514.0	725.2	604.2
102.5°	62.9	109.3	462.0	832.8	763.6
105°	73.2	118.4	422.5	870.4	873.5
107.5°	86.2	128.5	395.4	853.8	923.2
110°	98.5	137.8	381.6	803.8	920.5

TEST NUMBER: P1001582

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	110.2	148.0	372.6	743.8	882.5
115°	121.3	158.0	367.6	690.0	824.0
117.5°	133.8	167.8	363.3	646.3	767.4
120°	145.5	176.6	359.4	615.3	719.7
122.5°	156.8	186.0	355.0	594.1	681.1
125°	165.7	195.6	351.3	578.2	651.6
127.5°	174.8	205.8	346.4	562.0	631.9
130°	181.4	214.8	341.9	544.2	613.7
132.5°	188.7	223.4	338.4	523.9	594.5
135°	194.7	231.6	333.9	500.4	570.1
137.5°	201.5	238.0	330.8	476.2	542.3
140°	208.9	244.5	327.9	452.4	513.0
142.5°	216.1	250.4	326.4	431.0	481.9
145°	223.5	255.0	325.3	410.4	453.7
147.5°	232.0	260.1	323.6	392.7	427.1
150°	239.9	264.9	321.9	379.1	404.6
152.5°	246.5	269.5	319.1	368.4	387.6
155°	253.3	273.4	316.2	358.2	373.5
157.5°	260.1	277.1	313.4	348.5	360.4
160°	266.4	280.2	310.0	338.9	348.5
162.5°	272.0	282.8	306.6	329.6	337.2
165°	276.0	284.5	303.2	321.0	325.9
167.5°	280.5	285.9	299.8	313.6	316.8
170°	283.4	287.0	296.4	306.4	308.3
172.5°	286.2	287.9	293.0	299.8	299.8
175°	287.9	288.5	290.7	294.7	293.6
177.5°	289.0	288.5	289.0	291.0	289.0
180°	288.5	288.5	288.5	288.5	288.5

(END OF REPORT)