

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001608

Luminaire Tested: SA4XXDIP-B575D590UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001608
REPORT IS A COMBINATION OF REPORTS P996230 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB30-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4534.0 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001608

CATALOG NUMBER: SA4XXDIP-B575D590UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001608

CATALOG NUMBER: SA4XXDIP-B575D590UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73		61	61	61
1	99	94	90	87		92	88	84	81		75	73	71		64	62	61		53	52	51
2	90	82	76	71		83	77	71	67		66	62	58		56	53	51		47	45	43
3	82	72	65	59		76	68	61	56		58	53	49		50	46	43		42	39	37
4	75	64	56	50		69	60	53	47		52	46	42		44	40	37		37	34	32
5	69	57	49	43		64	53	46	41		46	41	36		40	35	32		34	30	27
6	64	51	43	37		59	48	41	35		42	36	32		36	31	28		30	27	24
7	59	46	38	33		54	43	36	31		38	32	28		33	28	25		28	24	22
8	55	42	34	29		51	40	32	28		35	29	25		30	25	22		26	22	19
9	51	39	31	26		47	36	29	25		32	26	22		28	23	20		24	20	17
10	48	35	28	23		44	33	27	22		29	24	20		25	21	18		22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7885	7885	7885
5°	7892	7659	7668
10°	7825	7446	7394
15°	7713	7193	7084
20°	7569	6920	6765
25°	7409	6631	6420
30°	7214	6318	6042
35°	7012	5999	5676
40°	6802	5655	5287
45°	6582	5309	4923
50°	6338	4974	4521
55°	6073	4585	4121
60°	5801	4156	3705
65°	5492	3714	3235
70°	5133	3182	2732
75°	4599	2565	2188
80°	3920	1854	1539
85°	3042	1033	828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6582 cd/sqm

TEST NUMBER: P1001608

CATALOG NUMBER: SA4XXDIP-B575D590UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	2.0
10°-20°	256.8	5.7
20°-30°	377.9	8.3
30°-40°	439.3	9.7
40°-50°	439.3	9.7
50°-60°	384.2	8.5
60°-70°	285.2	6.3
70°-80°	161.8	3.6
80°-90°	47.9	1.1
90°-100°	48.2	1.1
100°-110°	144.3	3.2
110°-120°	245.1	5.4
120°-130°	323.2	7.1
130°-140°	363.1	8.0
140°-150°	356.8	7.9
150°-160°	300.1	6.6
160°-170°	199.7	4.4
170°-180°	69.9	1.5
0°-30°	725.8	16.0
0°-40°	1165.1	25.7
0°-60°	1988.6	43.9
0°-90°	2483.6	54.8
90°-120°	437.5	9.7
90°-150°	1480.7	32.7
90°-180°	2050.0	45.2
0°-180°	4534.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	967	967	967	967	967	
5°	966	963	955	963	962	92
15°	920	917	905	910	907	259
25°	833	828	817	818	814	383
35°	717	711	700	695	691	448
45°	585	580	567	559	556	451
55°	442	440	429	420	415	396
65°	300	296	288	280	277	297
75°	160	156	152	149	148	169
85°	42	42	40	40	40	45
90°	2	8	13	16	17	5
95°	34	39	43	45	45	37
105°	133	134	136	138	140	141
115°	249	249	248	248	247	246
125°	363	363	362	361	360	323
135°	468	472	472	470	469	362
145°	569	571	572	571	569	356
155°	652	652	651	653	651	300
165°	709	708	706	710	708	200
175°	738	735	734	738	734	70
180°	739	739	739	739	739	

TEST NUMBER: P1001608

CATALOG NUMBER: SA4XXDIP-B575D590UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	967.0	967.0	967.0	967.0	967.0
2.5°	970.1	967.8	959.3	967.0	966.2
5°	966.2	963.1	954.6	963.1	961.6
7.5°	959.3	956.2	946.9	953.8	953.1
10°	949.2	946.1	936.0	942.2	940.7
12.5°	936.0	932.9	922.1	929.0	926.7
15°	919.7	916.6	905.0	909.7	907.3
17.5°	901.1	897.3	886.4	889.5	888.0
20°	880.2	876.3	864.7	867.0	865.5
22.5°	857.7	852.3	840.7	845.4	842.3
25°	833.0	827.5	816.7	817.5	814.4
27.5°	805.1	799.6	789.6	788.0	784.1
30°	777.2	771.0	760.9	757.8	753.9
32.5°	747.7	742.3	731.5	727.6	723.7
35°	716.7	711.3	700.5	695.0	691.2
37.5°	684.2	679.5	667.9	662.5	657.1
40°	652.4	646.2	634.6	626.8	623.0
42.5°	618.3	615.2	602.1	592.8	590.4
45°	585.0	579.6	567.2	558.7	556.3
47.5°	550.1	546.3	534.6	525.3	519.1
50°	514.5	511.4	500.5	489.7	485.1
52.5°	479.6	475.8	464.1	454.8	448.6
55°	442.4	440.1	429.3	420.0	415.3
57.5°	407.6	405.2	394.4	385.1	380.4
60°	371.1	367.3	357.2	350.2	346.4
62.5°	335.5	332.4	321.6	315.4	311.5
65°	299.9	296.0	288.2	280.5	276.6
67.5°	263.4	260.3	252.6	244.8	244.1
70°	230.1	224.7	218.5	212.3	210.0
72.5°	194.5	189.1	184.4	179.8	177.4
75°	159.6	155.7	151.9	148.8	148.0
77.5°	125.5	124.0	120.1	119.3	117.0
80°	95.3	93.0	91.4	89.9	89.1
82.5°	65.9	65.1	65.1	64.3	63.5
85°	41.8	41.8	40.3	40.3	39.5
87.5°	20.1	19.4	18.6	18.6	18.6
90°	1.7	8.0	12.6	16.0	17.1
92.5°	14.9	22.3	25.1	26.9	27.4
95°	34.3	39.4	43.4	45.2	45.2
97.5°	54.9	59.4	64.0	66.3	66.3
100°	80.0	82.3	87.4	88.6	88.6
102.5°	106.3	106.9	111.4	113.2	113.7
105°	133.2	133.7	136.0	137.7	139.5
107.5°	161.2	161.7	162.3	164.6	164.0
110°	189.7	190.9	190.3	189.2	190.9

TEST NUMBER: P1001608

CATALOG NUMBER: SA4XXDIP-B575D590UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	219.5	219.5	218.3	218.3	218.3
115°	249.2	249.2	248.0	247.5	246.9
117.5°	277.2	277.2	276.6	274.9	273.2
120°	305.2	307.5	305.8	302.9	304.1
122.5°	334.3	334.9	334.3	332.6	329.8
125°	362.9	362.9	362.3	361.2	360.1
127.5°	388.6	390.4	389.2	388.1	387.5
130°	416.1	417.8	417.8	416.6	414.4
132.5°	444.1	445.2	444.7	443.5	442.9
135°	468.1	471.5	471.5	470.4	468.7
137.5°	494.9	496.7	497.8	496.1	496.7
140°	521.8	522.9	522.9	522.4	521.8
142.5°	546.4	547.5	547.0	547.0	547.0
145°	568.7	571.0	571.5	571.0	569.2
147.5°	591.5	594.4	593.8	593.2	592.7
150°	612.1	614.4	614.4	614.4	613.8
152.5°	631.5	632.7	633.3	635.0	633.3
155°	651.5	651.5	651.0	653.3	651.0
157.5°	668.7	667.5	667.5	669.3	667.5
160°	683.5	683.0	682.4	684.1	681.3
162.5°	697.3	695.6	695.0	698.4	695.6
165°	709.3	707.6	706.4	709.8	707.6
167.5°	719.0	716.7	716.7	720.1	716.7
170°	727.0	724.1	724.7	728.1	724.1
172.5°	732.7	730.4	730.4	734.4	730.4
175°	737.8	735.0	734.4	738.4	734.4
177.5°	740.1	737.3	737.3	741.3	736.7
180°	739.0	739.0	739.0	739.0	739.0

(END OF REPORT)