

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000670

Luminaire Tested: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000670
REPORT IS A COMBINATION OF REPORTS P995283 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5862.0 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	82	82	82
1	104	100	96	92	99	96	92	89	87	85	82	80	78	76	73	71	70
2	95	88	81	76	91	84	78	74	77	72	69	70	67	64	64	62	59
3	87	78	70	64	83	74	67	62	68	63	58	63	58	54	57	54	51
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	52	47	44
5	74	62	53	47	70	59	52	46	55	48	43	51	45	41	47	42	39
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	42	38	34
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	39	34	31
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	36	31	27
9	55	42	35	29	52	41	34	29	38	32	27	36	30	26	33	28	25
10	51	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13449	13449	13449	13449
5°	13415	15429	13493	11594
10°	13315	18001	13416	10171
15°	13154	20752	13246	9100
20°	12984	22502	13078	8159
25°	12736	22244	12858	7465
30°	12493	18386	12645	7107
35°	12152	13701	12285	6890
40°	11753	10321	11867	6784
45°	11145	8284	11284	6639
50°	10419	6979	10571	6572
55°	9566	6075	9716	6494
60°	8737	5349	8993	6386
65°	7957	4602	8032	6120
70°	7041	3786	7195	5636
75°	6144	2910	6104	4788
80°	4833	1912	4775	3634
85°	3180	859	2984	2119

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 17390 cd/sqm

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.5	2.7
10°-20°	495.4	8.5
20°-30°	787.1	13.4
30°-40°	874.6	14.9
40°-50°	795.3	13.6
50°-60°	649.9	11.1
60°-70°	463.9	7.9
70°-80°	255.3	4.4
80°-90°	69.7	1.2
90°-100°	130.4	2.2
100°-110°	272.2	4.6
110°-120°	242.0	4.1
120°-130°	203.7	3.5
130°-140°	169.9	2.9
140°-150°	129.8	2.2
150°-160°	91.2	1.6
160°-170°	53.7	0.9
170°-180°	17.4	0.3
0°-30°	1443.0	24.6
0°-40°	2317.6	39.5
0°-60°	3762.8	64.2
0°-90°	4551.7	77.6
90°-120°	644.6	11.0
90°-150°	1148.0	19.6
90°-180°	1310.0	22.3
0°-180°	5862.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1649	1649	1649	1649	1649	
5°	1642	1935	1652	1454	1642	156
15°	1569	2658	1580	1166	1569	443
25°	1432	2822	1446	947	1432	660
35°	1242	1668	1256	839	1242	776
45°	991	936	1003	750	991	764
55°	697	612	708	654	697	627
65°	434	394	439	523	434	429
75°	213	197	212	324	213	224
85°	44	41	41	101	44	51
90°	0	7	0	7	0	3
95°	12	86	12	86	12	13
105°	41	497	41	497	41	44
115°	73	478	73	478	73	72
125°	101	381	101	381	101	90
135°	120	341	120	341	120	93
145°	139	278	139	278	139	87
155°	158	233	158	233	158	73
165°	172	203	172	203	172	49
175°	180	183	180	183	180	17
180°	180	180	180	180	180	

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3
2.5°	1649.3	1665.7	1672.5	1677.9	1695.7	1701.2	1702.5	1710.7	1717.6	1718.9	1718.9
5°	1642.4	1668.4	1688.9	1708.0	1736.7	1749.0	1764.0	1780.4	1802.3	1816.0	1822.8
7.5°	1631.5	1669.8	1701.2	1734.0	1773.6	1798.2	1811.9	1855.6	1885.6	1910.2	1940.3
10°	1615.1	1664.3	1709.4	1757.2	1813.2	1843.3	1873.3	1926.6	1969.0	2016.8	2055.1
12.5°	1590.5	1654.7	1709.4	1776.3	1846.0	1881.5	1917.1	2010.0	2059.2	2101.5	2169.9
15°	1568.6	1632.9	1710.7	1779.1	1865.1	1918.4	1970.4	2030.5	2108.4	2199.9	2265.5
17.5°	1544.0	1624.7	1697.1	1792.7	1888.4	1938.9	1981.3	2074.2	2183.5	2273.7	2333.8
20°	1509.9	1591.9	1687.5	1788.6	1902.0	1941.7	1997.7	2122.0	2220.4	2309.2	2407.6
22.5°	1470.3	1565.9	1667.0	1764.0	1881.5	1964.9	2026.4	2135.7	2254.6	2357.1	2467.7
25°	1432.0	1535.8	1624.7	1757.2	1881.5	1937.6	2007.3	2137.1	2266.9	2391.2	2504.6
27.5°	1391.0	1488.0	1608.3	1713.5	1854.2	1915.7	1990.9	2133.0	2271.0	2395.3	2516.9
30°	1345.9	1449.8	1549.5	1673.9	1810.5	1889.7	1959.4	2113.8	2254.6	2384.4	2497.8
32.5°	1295.4	1393.7	1500.3	1617.8	1761.3	1841.9	1929.4	2087.9	2238.2	2350.2	2437.7
35°	1242.1	1341.8	1434.7	1555.0	1702.5	1783.2	1867.9	2042.8	2191.7	2283.3	2333.8
37.5°	1183.3	1277.6	1369.1	1488.0	1635.6	1721.7	1807.8	1977.2	2117.9	2194.5	2180.8
40°	1127.3	1212.0	1296.7	1408.8	1563.2	1654.7	1729.9	1900.7	2023.7	2056.4	2011.4
42.5°	1063.1	1135.5	1217.5	1332.2	1482.6	1568.6	1662.9	1818.7	1910.2	1896.6	1820.1
45°	990.6	1054.9	1136.9	1244.8	1397.8	1486.7	1565.9	1713.5	1780.4	1746.3	1606.9
47.5°	921.0	983.8	1050.8	1158.7	1307.7	1382.8	1463.4	1596.0	1634.2	1561.8	1422.4
50°	845.8	897.7	967.4	1069.9	1209.3	1288.5	1355.5	1462.1	1475.7	1386.9	1242.1
52.5°	773.4	817.1	884.1	985.2	1115.0	1177.8	1243.4	1337.7	1326.8	1235.2	1095.9
55°	696.9	737.9	799.3	892.3	1007.0	1067.2	1123.2	1206.5	1183.3	1089.0	967.4
57.5°	632.6	661.3	721.5	807.5	901.8	967.4	1015.2	1080.8	1045.3	951.0	837.6
60°	558.9	594.4	644.9	714.6	807.5	851.3	893.6	937.4	912.8	822.6	721.5
62.5°	491.9	519.2	563.0	629.9	702.3	742.0	787.1	814.4	789.8	706.4	621.7
65°	434.5	456.4	490.5	545.2	614.9	647.7	673.6	699.6	679.1	601.2	539.7
67.5°	371.7	390.8	419.5	463.2	522.0	545.2	569.8	587.6	564.3	512.4	452.3
70°	315.6	329.3	356.6	389.4	430.4	452.3	472.8	490.5	470.0	426.3	381.2
72.5°	258.3	269.2	293.8	317.0	353.9	368.9	384.0	397.6	390.8	349.8	312.9
75°	213.2	217.3	233.7	252.8	276.0	292.4	303.3	311.5	306.1	273.3	250.1
77.5°	161.2	166.7	179.0	194.0	214.5	224.1	230.9	239.1	232.3	206.3	189.9
80°	117.5	118.9	125.7	139.4	153.0	154.4	161.2	172.2	168.1	150.3	138.0
82.5°	75.2	79.3	82.0	90.2	99.7	102.5	106.6	109.3	107.9	97.0	92.9
85°	43.7	43.7	46.5	51.9	54.7	58.8	60.1	61.5	64.2	57.4	53.3
87.5°	19.1	20.5	20.5	21.9	24.6	24.6	26.0	27.3	28.7	27.3	23.2
90°	0.4	1.1	2.1	2.5	2.8	2.8	2.8	4.9	4.9	5.7	6.4
92.5°	4.9	7.1	11.0	16.3	22.6	27.2	31.8	53.7	88.0	121.2	138.6
95°	11.7	12.7	16.3	20.9	29.3	36.8	44.2	74.9	132.9	217.4	288.1
97.5°	19.4	19.4	22.6	26.9	34.3	40.6	47.0	71.4	121.2	208.2	308.2
100°	26.9	26.9	29.3	33.6	40.3	46.0	51.6	72.5	112.4	184.5	284.2
102.5°	33.9	34.6	36.8	40.6	47.0	52.3	57.6	76.0	109.9	168.6	254.1
105°	41.4	42.4	44.2	48.4	54.8	59.9	65.0	82.0	111.3	160.8	231.9
107.5°	49.5	50.2	52.0	56.6	62.6	67.7	72.8	88.4	115.6	158.7	217.4
110°	57.6	58.3	60.1	64.3	70.7	75.4	80.2	95.8	120.5	159.4	210.7

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	65.4	66.1	68.2	72.1	78.5	83.2	88.0	102.9	125.8	161.5	207.5
115°	72.8	73.9	76.3	79.9	86.6	91.4	96.1	110.3	131.5	164.4	206.8
117.5°	80.6	81.6	83.8	87.7	94.0	99.0	103.9	117.3	137.1	167.2	206.4
120°	88.4	89.1	91.5	95.4	101.4	106.4	111.3	124.8	143.1	170.4	206.4
122.5°	95.4	96.1	98.6	102.1	108.9	113.6	118.4	131.8	148.8	173.5	206.1
125°	101.4	102.9	105.0	108.9	115.6	120.6	125.5	138.2	154.5	176.7	205.7
127.5°	107.1	108.2	110.6	114.9	121.9	126.8	131.8	144.2	159.4	179.2	205.0
130°	111.7	113.1	115.9	121.2	127.9	133.0	138.2	150.2	164.0	182.0	204.6
132.5°	116.3	117.3	121.2	126.2	133.6	138.4	143.1	155.2	168.6	184.5	204.3
135°	120.5	121.9	125.5	131.5	138.9	143.5	148.1	159.8	172.5	187.0	203.9
137.5°	124.8	126.2	130.1	135.7	143.5	147.9	152.3	163.3	175.3	188.4	203.9
140°	129.4	130.4	134.3	140.3	147.7	152.0	156.2	166.8	178.1	190.2	203.6
142.5°	134.3	135.4	138.9	144.6	151.6	155.7	159.8	170.0	180.3	191.6	203.6
145°	138.9	140.0	143.5	148.4	155.2	159.0	162.9	172.1	181.7	191.9	202.9
147.5°	144.2	144.6	147.7	153.0	158.7	162.2	165.8	174.6	183.1	192.3	201.8
150°	149.2	149.5	152.3	156.6	161.9	165.2	168.6	176.4	184.1	192.3	200.8
152.5°	153.7	153.7	156.6	160.5	165.1	168.1	171.1	177.8	184.9	191.6	199.0
155°	158.0	158.3	160.5	164.0	167.9	170.6	173.2	179.2	185.2	190.9	197.2
157.5°	162.2	162.2	164.4	167.2	170.7	172.8	175.0	180.3	185.2	190.2	195.5
160°	166.1	166.1	167.5	170.0	172.8	174.8	176.7	181.0	185.2	189.1	193.3
162.5°	169.7	169.3	170.4	172.5	175.0	176.4	177.8	181.7	185.2	188.0	191.2
165°	172.1	172.1	172.8	174.6	176.4	177.4	178.5	181.7	184.5	186.6	189.1
167.5°	175.0	174.6	175.0	176.4	177.4	178.3	179.2	181.7	183.8	185.2	187.0
170°	176.7	176.4	176.7	177.8	178.5	179.0	179.6	181.3	183.1	183.8	184.9
172.5°	178.5	178.1	178.1	178.8	179.2	179.6	179.9	181.0	182.4	182.4	182.7
175°	179.6	179.2	179.2	179.6	179.9	179.9	179.9	180.6	181.7	181.3	181.3
177.5°	180.3	179.9	179.6	179.9	179.9	179.9	179.9	180.3	181.0	180.3	180.3
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3
2.5°	1723.0	1747.6	1758.6	1761.3	1776.3	1766.8	1770.9	1769.5	1780.4	1781.8	1781.8
5°	1848.8	1877.4	1887.0	1900.7	1921.2	1926.6	1922.5	1930.7	1945.8	1934.8	1951.2
7.5°	1981.3	2012.7	2034.6	2064.6	2071.5	2089.2	2100.2	2109.7	2112.5	2113.8	2116.6
10°	2104.3	2143.9	2174.0	2224.5	2235.4	2245.0	2292.8	2273.7	2298.3	2290.1	2292.8
12.5°	2204.0	2281.9	2306.5	2391.2	2399.4	2432.2	2429.5	2459.5	2465.0	2475.9	2465.0
15°	2335.2	2425.4	2465.0	2512.8	2540.2	2578.4	2585.2	2626.2	2642.6	2657.7	2642.6
17.5°	2455.4	2503.3	2604.4	2642.6	2660.4	2680.9	2732.8	2747.8	2772.4	2762.9	2790.2
20°	2515.6	2583.9	2690.5	2756.0	2783.4	2802.5	2846.2	2869.5	2879.0	2879.0	2881.8
22.5°	2568.8	2667.2	2746.5	2821.6	2846.2	2859.9	2885.9	2903.6	2907.7	2910.4	2913.2
25°	2616.7	2705.5	2769.7	2812.1	2821.6	2821.6	2836.7	2825.7	2808.0	2821.6	2829.8
27.5°	2616.7	2679.5	2708.2	2723.3	2723.3	2686.4	2664.5	2619.4	2581.1	2570.2	2594.8
30°	2572.9	2601.6	2562.0	2525.1	2496.4	2471.8	2385.7	2317.4	2303.8	2294.2	2331.1
32.5°	2471.8	2434.9	2357.1	2250.5	2208.1	2152.1	2085.1	2033.2	2001.8	1990.9	1982.7
35°	2292.8	2197.2	2096.1	1952.6	1922.5	1851.5	1759.9	1721.7	1669.8	1668.4	1686.1
37.5°	2097.4	1949.9	1840.6	1703.9	1661.6	1586.4	1500.3	1460.7	1425.2	1397.8	1430.6
40°	1869.2	1740.8	1574.1	1462.1	1401.9	1362.3	1289.9	1246.2	1229.8	1216.1	1236.6
42.5°	1656.1	1515.3	1385.5	1270.8	1221.6	1176.5	1128.7	1086.3	1074.0	1072.6	1087.7
45°	1444.3	1306.3	1186.0	1087.7	1056.2	1028.9	982.4	970.1	949.7	936.0	942.8
47.5°	1274.9	1132.8	1033.0	957.9	930.5	907.3	877.2	856.7	839.0	833.5	841.7
50°	1108.2	1012.5	910.0	847.2	826.7	804.8	781.6	762.5	754.3	748.8	754.3
52.5°	974.2	871.8	802.1	751.5	731.0	714.6	698.2	690.0	679.1	681.8	687.3
55°	854.0	763.8	705.1	668.2	655.9	649.0	628.5	619.0	614.9	612.2	614.9
57.5°	740.6	675.0	631.3	599.9	583.5	579.4	563.0	563.0	558.9	554.8	556.1
60°	650.4	594.4	552.0	527.4	524.7	517.9	506.9	505.6	496.0	500.1	501.5
62.5°	558.9	513.8	485.1	470.0	460.5	457.7	450.9	449.5	445.4	446.8	444.1
65°	486.4	449.5	420.9	408.6	404.5	403.1	397.6	393.5	390.8	393.5	390.8
67.5°	414.0	389.4	367.6	355.3	349.8	348.4	344.3	341.6	343.0	338.9	341.6
70°	345.7	321.1	307.4	300.6	297.9	293.8	293.8	293.8	293.8	291.0	289.7
72.5°	291.0	266.4	256.9	252.8	250.1	248.7	244.6	246.0	244.6	243.2	248.7
75°	230.9	215.9	206.3	202.2	205.0	200.9	196.8	199.5	195.4	196.8	202.2
77.5°	174.9	168.1	162.6	159.9	157.1	154.4	154.4	151.7	151.7	151.7	151.7
80°	127.1	125.7	116.1	114.8	114.8	112.0	112.0	112.0	112.0	110.7	112.0
82.5°	84.7	83.4	80.6	79.3	76.5	77.9	77.9	75.2	75.2	73.8	75.2
85°	49.2	49.2	46.5	45.1	43.7	45.1	42.4	41.0	42.4	41.0	42.4
87.5°	23.2	20.5	21.9	20.5	17.8	19.1	16.4	17.8	16.4	15.0	17.8
90°	6.0	6.4	6.7	7.1	7.1	7.1	7.4	7.8	7.4	7.4	7.4
92.5°	115.2	85.2	63.6	50.2	45.8	41.4	36.1	33.6	32.2	32.2	32.2
95°	296.2	261.9	207.1	159.8	142.6	125.5	108.2	97.2	90.8	86.2	90.8
97.5°	371.5	377.1	349.9	311.0	291.2	271.4	247.4	226.2	215.6	207.1	215.6
100°	374.7	426.3	433.3	416.0	403.0	389.9	359.1	337.5	326.9	324.1	326.9
102.5°	348.1	423.8	465.8	476.4	472.9	469.4	453.5	439.3	428.0	425.9	428.0
105°	314.9	395.9	457.0	492.0	499.2	506.5	507.2	504.4	499.4	497.3	499.4
107.5°	287.7	361.6	427.7	476.4	491.2	506.1	521.7	528.1	530.9	531.2	530.9
110°	268.3	331.2	392.3	443.6	463.0	482.5	507.6	522.4	528.8	531.9	528.8

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	257.3	308.9	361.2	408.9	428.4	447.8	477.2	495.9	505.4	511.1	505.4
115°	251.3	295.5	339.0	380.3	397.2	414.2	442.2	463.4	474.7	477.5	474.7
117.5°	248.1	287.7	324.5	358.0	372.8	387.7	412.5	430.9	442.9	444.6	442.9
120°	245.6	282.8	315.6	343.9	356.4	369.0	389.1	404.7	413.9	417.8	413.9
122.5°	242.8	278.5	310.0	335.1	345.7	356.3	372.5	385.3	392.7	396.6	392.7
125°	239.6	273.6	304.0	328.4	338.1	347.8	361.9	372.2	378.9	381.0	378.9
127.5°	235.4	267.9	297.2	321.6	330.8	340.0	354.2	363.3	369.0	371.1	369.0
130°	231.5	260.8	288.8	312.8	322.2	331.5	346.0	354.9	360.5	362.6	360.5
132.5°	228.0	253.4	279.2	302.6	312.0	321.3	335.4	345.7	351.0	353.1	351.0
135°	224.4	246.7	269.7	291.2	300.0	308.9	323.1	332.9	338.6	340.7	338.6
137.5°	221.3	240.3	260.5	279.2	287.4	295.5	308.9	319.2	323.8	326.2	323.8
140°	218.8	235.0	251.7	267.6	275.0	282.4	294.8	302.6	307.5	310.3	307.5
142.5°	216.7	230.1	244.2	257.3	263.5	269.7	280.3	287.4	291.6	293.4	291.6
145°	214.2	225.5	237.5	248.1	253.0	258.0	266.9	272.9	276.4	278.2	276.4
147.5°	212.1	221.6	231.5	240.3	244.4	248.5	255.2	260.5	263.3	264.0	263.3
150°	209.6	218.1	226.2	233.3	236.4	239.6	245.3	249.9	252.0	252.4	252.0
152.5°	206.8	214.2	220.9	227.3	229.8	232.2	236.8	240.3	241.4	241.8	241.4
155°	203.9	210.3	216.0	221.3	223.4	225.5	229.0	231.9	232.9	232.9	232.9
157.5°	201.1	206.1	211.0	215.6	217.4	219.1	222.0	224.1	224.8	224.8	224.8
160°	197.9	202.2	206.1	209.9	211.4	212.8	214.9	217.0	217.4	217.4	217.4
162.5°	195.1	198.3	201.5	204.3	205.6	206.8	208.2	210.3	210.7	210.3	210.7
165°	191.9	194.7	196.9	199.3	200.2	201.1	202.5	203.9	203.6	203.2	203.6
167.5°	189.1	191.2	193.0	195.1	195.6	196.2	196.9	197.9	197.9	197.6	197.9
170°	186.3	188.0	189.1	190.5	191.0	191.6	192.3	192.6	192.3	192.3	192.3
172.5°	183.8	185.2	185.9	186.6	187.0	187.3	187.7	188.0	187.7	187.0	187.7
175°	182.0	182.7	183.1	183.8	183.8	183.8	183.8	184.5	183.8	183.1	183.8
177.5°	180.6	181.0	181.3	181.3	181.5	181.7	181.3	181.7	181.0	180.3	181.0
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3
2.5°	1779.1	1775.0	1769.5	1769.5	1762.7	1762.7	1751.7	1732.6	1716.2	1710.7	1713.5
5°	1930.7	1932.1	1923.9	1917.1	1904.8	1895.2	1877.4	1843.3	1832.4	1810.5	1795.5
7.5°	2104.3	2098.8	2083.8	2072.8	2070.1	2048.2	2010.0	1969.0	1936.2	1914.3	1882.9
10°	2299.7	2277.8	2255.9	2249.1	2232.7	2195.8	2152.1	2107.0	2061.9	2014.1	1960.8
12.5°	2463.6	2421.3	2419.9	2403.5	2372.1	2351.6	2299.7	2235.4	2157.6	2104.3	2044.1
15°	2639.9	2600.3	2567.5	2537.4	2522.4	2462.3	2418.5	2337.9	2245.0	2187.6	2146.6
17.5°	2765.6	2747.8	2691.8	2678.2	2657.7	2588.0	2518.3	2439.0	2358.4	2277.8	2167.1
20°	2866.7	2855.8	2818.9	2799.8	2767.0	2712.3	2627.6	2536.1	2443.1	2328.4	2224.5
22.5°	2910.4	2896.8	2866.7	2850.3	2829.8	2783.4	2711.0	2607.1	2485.5	2383.0	2272.3
25°	2824.4	2849.0	2840.8	2833.9	2825.7	2798.4	2743.7	2652.2	2533.3	2417.2	2279.2
27.5°	2630.3	2672.7	2713.7	2719.2	2732.8	2743.7	2721.9	2656.3	2556.6	2433.6	2281.9
30°	2369.4	2388.5	2471.8	2496.4	2515.6	2585.2	2626.2	2609.8	2533.3	2422.6	2283.3
32.5°	2034.6	2085.1	2169.9	2228.6	2280.5	2358.4	2465.0	2507.4	2480.0	2389.8	2251.8
35°	1717.6	1777.7	1876.1	1951.2	2003.2	2113.8	2239.5	2331.1	2365.3	2320.2	2197.2
37.5°	1458.0	1530.4	1617.8	1646.5	1706.6	1843.3	2016.8	2143.9	2227.2	2231.3	2135.7
40°	1262.6	1299.5	1369.1	1412.9	1471.6	1586.4	1755.8	1923.9	2049.6	2092.0	2041.4
42.5°	1097.2	1125.9	1177.8	1231.1	1284.4	1371.9	1527.6	1684.8	1854.2	1938.9	1937.6
45°	966.1	996.1	1031.6	1075.4	1112.3	1206.5	1329.5	1490.8	1637.0	1768.1	1800.9
47.5°	851.3	877.2	921.0	940.1	964.7	1053.5	1160.1	1310.4	1462.1	1612.4	1650.6
50°	766.6	788.4	818.5	830.8	858.1	923.7	1011.1	1132.8	1300.8	1438.8	1509.9
52.5°	690.0	706.4	729.7	739.2	758.4	807.5	886.8	982.4	1121.8	1263.9	1363.7
55°	624.4	635.4	651.8	662.7	676.4	720.1	778.9	864.9	985.2	1108.2	1205.2
57.5°	563.0	571.2	587.6	593.0	604.0	638.1	679.1	751.5	862.2	971.5	1065.8
60°	505.6	511.0	520.6	532.9	541.1	564.3	602.6	662.7	751.5	851.3	927.8
62.5°	450.9	459.1	461.8	467.3	474.1	496.0	526.1	569.8	647.7	729.7	810.3
65°	394.9	401.7	407.2	408.6	415.4	431.8	459.1	497.4	547.9	619.0	694.1
67.5°	343.0	347.1	349.8	355.3	362.1	370.3	392.2	420.9	467.3	524.7	584.8
70°	295.1	295.1	299.2	300.6	308.8	318.4	327.9	355.3	396.3	442.7	483.7
72.5°	243.2	250.1	248.7	255.5	254.2	261.0	273.3	291.0	321.1	358.0	397.6
75°	198.1	202.2	202.2	202.2	205.0	210.4	217.3	233.7	256.9	286.9	310.2
77.5°	154.4	157.1	157.1	157.1	158.5	164.0	170.8	181.7	198.1	215.9	229.6
80°	110.7	113.4	113.4	116.1	116.1	117.5	124.3	129.8	138.0	151.7	165.3
82.5°	75.2	76.5	79.3	79.3	77.9	80.6	82.0	87.5	95.6	98.4	107.9
85°	41.0	42.4	43.7	43.7	45.1	47.8	46.5	51.9	51.9	57.4	60.1
87.5°	16.4	19.1	19.1	17.8	19.1	19.1	19.1	21.9	23.2	24.6	23.2
90°	7.8	7.4	7.1	7.1	7.1	6.7	6.4	6.0	6.4	5.7	4.9
92.5°	33.6	36.1	41.4	45.8	50.2	63.6	85.2	115.2	138.6	121.2	88.0
95°	97.2	108.2	125.5	142.6	159.8	207.1	261.9	296.2	288.1	217.4	132.9
97.5°	226.2	247.4	271.4	291.2	311.0	349.9	377.1	371.5	308.2	208.2	121.2
100°	337.5	359.1	389.9	403.0	416.0	433.3	426.3	374.7	284.2	184.5	112.4
102.5°	439.3	453.5	469.4	472.9	476.4	465.8	423.8	348.1	254.1	168.6	109.9
105°	504.4	507.2	506.5	499.2	492.0	457.0	395.9	314.9	231.9	160.8	111.3
107.5°	528.1	521.7	506.1	491.2	476.4	427.7	361.6	287.7	217.4	158.7	115.6
110°	522.4	507.6	482.5	463.0	443.6	392.3	331.2	268.3	210.7	159.4	120.5

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	495.9	477.2	447.8	428.4	408.9	361.2	308.9	257.3	207.5	161.5	125.8
115°	463.4	442.2	414.2	397.2	380.3	339.0	295.5	251.3	206.8	164.4	131.5
117.5°	430.9	412.5	387.7	372.8	358.0	324.5	287.7	248.1	206.4	167.2	137.1
120°	404.7	389.1	369.0	356.4	343.9	315.6	282.8	245.6	206.4	170.4	143.1
122.5°	385.3	372.5	356.3	345.7	335.1	310.0	278.5	242.8	206.1	173.5	148.8
125°	372.2	361.9	347.8	338.1	328.4	304.0	273.6	239.6	205.7	176.7	154.5
127.5°	363.3	354.2	340.0	330.8	321.6	297.2	267.9	235.4	205.0	179.2	159.4
130°	354.9	346.0	331.5	322.2	312.8	288.8	260.8	231.5	204.6	182.0	164.0
132.5°	345.7	335.4	321.3	312.0	302.6	279.2	253.4	228.0	204.3	184.5	168.6
135°	332.9	323.1	308.9	300.0	291.2	269.7	246.7	224.4	203.9	187.0	172.5
137.5°	319.2	308.9	295.5	287.4	279.2	260.5	240.3	221.3	203.9	188.4	175.3
140°	302.6	294.8	282.4	275.0	267.6	251.7	235.0	218.8	203.6	190.2	178.1
142.5°	287.4	280.3	269.7	263.5	257.3	244.2	230.1	216.7	203.6	191.6	180.3
145°	272.9	266.9	258.0	253.0	248.1	237.5	225.5	214.2	202.9	191.9	181.7
147.5°	260.5	255.2	248.5	244.4	240.3	231.5	221.6	212.1	201.8	192.3	183.1
150°	249.9	245.3	239.6	236.4	233.3	226.2	218.1	209.6	200.8	192.3	184.1
152.5°	240.3	236.8	232.2	229.8	227.3	220.9	214.2	206.8	199.0	191.6	184.9
155°	231.9	229.0	225.5	223.4	221.3	216.0	210.3	203.9	197.2	190.9	185.2
157.5°	224.1	222.0	219.1	217.4	215.6	211.0	206.1	201.1	195.5	190.2	185.2
160°	217.0	214.9	212.8	211.4	209.9	206.1	202.2	197.9	193.3	189.1	185.2
162.5°	210.3	208.2	206.8	205.6	204.3	201.5	198.3	195.1	191.2	188.0	185.2
165°	203.9	202.5	201.1	200.2	199.3	196.9	194.7	191.9	189.1	186.6	184.5
167.5°	197.9	196.9	196.2	195.6	195.1	193.0	191.2	189.1	187.0	185.2	183.8
170°	192.6	192.3	191.6	191.0	190.5	189.1	188.0	186.3	184.9	183.8	183.1
172.5°	188.0	187.7	187.3	187.0	186.6	185.9	185.2	183.8	182.7	182.4	182.4
175°	184.5	183.8	183.8	183.8	183.8	183.1	182.7	182.0	181.3	181.3	181.7
177.5°	181.7	181.3	181.7	181.5	181.3	181.3	181.0	180.6	180.3	180.3	181.0
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3
2.5°	1701.2	1695.7	1691.6	1691.6	1679.3	1667.0	1660.2	1657.5	1654.7	1643.8	1628.8
5°	1770.9	1753.1	1740.8	1728.5	1708.0	1686.1	1664.3	1652.0	1634.2	1609.6	1591.9
7.5°	1848.8	1806.4	1792.7	1777.7	1736.7	1699.8	1669.8	1643.8	1615.1	1583.7	1552.2
10°	1914.3	1869.2	1839.2	1813.2	1759.9	1710.7	1665.7	1627.4	1590.5	1549.5	1511.2
12.5°	1977.2	1913.0	1881.5	1843.3	1787.3	1716.2	1657.5	1609.6	1555.0	1512.6	1466.2
15°	2064.6	1956.7	1904.8	1880.2	1805.0	1721.7	1650.6	1579.6	1534.5	1470.3	1429.3
17.5°	2078.3	1990.9	1956.7	1893.8	1803.7	1709.4	1627.4	1556.3	1488.0	1430.6	1377.3
20°	2126.1	2011.4	1956.7	1917.1	1798.2	1702.5	1612.4	1520.8	1455.2	1393.7	1333.6
22.5°	2156.2	2026.4	1969.0	1906.1	1792.7	1677.9	1571.4	1492.1	1411.5	1348.6	1300.8
25°	2148.0	2018.2	1954.0	1895.2	1757.2	1642.4	1546.8	1445.7	1370.5	1302.2	1239.3
27.5°	2143.9	1997.7	1929.4	1863.8	1734.0	1613.7	1493.5	1411.5	1328.1	1248.9	1202.4
30°	2133.0	1971.7	1892.5	1821.4	1686.1	1560.4	1458.0	1362.3	1279.0	1206.5	1145.1
32.5°	2096.1	1928.0	1851.5	1775.0	1634.2	1508.5	1404.7	1315.9	1232.5	1157.3	1098.6
35°	2046.9	1876.1	1792.7	1712.1	1571.4	1444.3	1348.6	1255.7	1177.8	1105.4	1049.4
37.5°	1997.7	1816.0	1738.1	1645.2	1515.3	1382.8	1284.4	1201.1	1128.7	1053.5	992.0
40°	1926.6	1744.9	1658.8	1579.6	1427.9	1303.6	1213.4	1138.2	1067.2	996.1	944.2
42.5°	1829.6	1667.0	1578.2	1490.8	1348.6	1225.7	1138.2	1071.3	1004.3	945.6	888.2
45°	1731.2	1572.7	1493.5	1415.6	1261.2	1145.1	1064.4	1002.9	946.9	882.7	836.2
47.5°	1612.4	1478.5	1399.2	1322.7	1176.5	1060.3	986.5	929.2	877.2	823.9	780.2
50°	1490.8	1374.6	1302.2	1222.9	1083.6	978.3	905.9	858.1	815.7	765.2	729.7
52.5°	1359.6	1258.5	1197.0	1120.5	997.5	900.5	826.7	778.9	743.3	706.4	675.0
55°	1220.2	1146.4	1080.8	1019.3	903.2	815.7	750.2	707.8	683.2	649.0	621.7
57.5°	1094.5	1023.4	983.8	914.1	813.0	726.9	675.0	639.5	610.8	590.3	568.4
60°	963.3	905.9	862.2	811.6	722.8	650.4	595.8	575.3	545.2	530.2	520.6
62.5°	837.6	796.6	755.6	717.4	638.1	569.8	528.8	502.8	485.1	470.0	461.8
65°	718.7	680.5	651.8	617.6	552.0	497.4	459.1	438.6	420.9	416.8	407.2
67.5°	602.6	586.2	554.8	527.4	471.4	429.1	400.4	374.4	364.8	360.7	352.5
70°	504.2	485.1	460.5	437.3	394.9	358.0	332.0	322.5	308.8	307.4	297.9
72.5°	415.4	392.2	374.4	356.6	325.2	292.4	278.7	265.1	258.3	252.8	248.7
75°	329.3	312.9	300.6	285.6	258.3	236.4	217.3	211.8	207.7	206.3	203.6
77.5°	246.0	235.0	229.6	214.5	195.4	176.3	168.1	159.9	159.9	157.1	158.5
80°	174.9	168.1	161.2	153.0	136.6	128.4	121.6	116.1	113.4	112.0	113.4
82.5°	110.7	106.6	105.2	99.7	88.8	84.7	79.3	75.2	75.2	75.2	75.2
85°	61.5	61.5	61.5	53.3	49.2	45.1	42.4	41.0	41.0	41.0	42.4
87.5°	26.0	26.0	21.9	21.9	20.5	17.8	16.4	16.4	17.8	17.8	19.1
90°	4.9	2.8	2.8	2.8	2.5	2.1	1.1	0.4	1.1	2.1	2.5
92.5°	53.7	31.8	27.2	22.6	16.3	11.0	7.1	4.9	7.1	11.0	16.3
95°	74.9	44.2	36.8	29.3	20.9	16.3	12.7	11.7	12.7	16.3	20.9
97.5°	71.4	47.0	40.6	34.3	26.9	22.6	19.4	19.4	19.4	22.6	26.9
100°	72.5	51.6	46.0	40.3	33.6	29.3	26.9	26.9	26.9	29.3	33.6
102.5°	76.0	57.6	52.3	47.0	40.6	36.8	34.6	33.9	34.6	36.8	40.6
105°	82.0	65.0	59.9	54.8	48.4	44.2	42.4	41.4	42.4	44.2	48.4
107.5°	88.4	72.8	67.7	62.6	56.6	52.0	50.2	49.5	50.2	52.0	56.6
110°	95.8	80.2	75.4	70.7	64.3	60.1	58.3	57.6	58.3	60.1	64.3

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	102.9	88.0	83.2	78.5	72.1	68.2	66.1	65.4	66.1	68.2	72.1
115°	110.3	96.1	91.4	86.6	79.9	76.3	73.9	72.8	73.9	76.3	79.9
117.5°	117.3	103.9	99.0	94.0	87.7	83.8	81.6	80.6	81.6	83.8	87.7
120°	124.8	111.3	106.4	101.4	95.4	91.5	89.1	88.4	89.1	91.5	95.4
122.5°	131.8	118.4	113.6	108.9	102.1	98.6	96.1	95.4	96.1	98.6	102.1
125°	138.2	125.5	120.6	115.6	108.9	105.0	102.9	101.4	102.9	105.0	108.9
127.5°	144.2	131.8	126.8	121.9	114.9	110.6	108.2	107.1	108.2	110.6	114.9
130°	150.2	138.2	133.0	127.9	121.2	115.9	113.1	111.7	113.1	115.9	121.2
132.5°	155.2	143.1	138.4	133.6	126.2	121.2	117.3	116.3	117.3	121.2	126.2
135°	159.8	148.1	143.5	138.9	131.5	125.5	121.9	120.5	121.9	125.5	131.5
137.5°	163.3	152.3	147.9	143.5	135.7	130.1	126.2	124.8	126.2	130.1	135.7
140°	166.8	156.2	152.0	147.7	140.3	134.3	130.4	129.4	130.4	134.3	140.3
142.5°	170.0	159.8	155.7	151.6	144.6	138.9	135.4	134.3	135.4	138.9	144.6
145°	172.1	162.9	159.0	155.2	148.4	143.5	140.0	138.9	140.0	143.5	148.4
147.5°	174.6	165.8	162.2	158.7	153.0	147.7	144.6	144.2	144.6	147.7	153.0
150°	176.4	168.6	165.2	161.9	156.6	152.3	149.5	149.2	149.5	152.3	156.6
152.5°	177.8	171.1	168.1	165.1	160.5	156.6	153.7	153.7	153.7	156.6	160.5
155°	179.2	173.2	170.6	167.9	164.0	160.5	158.3	158.0	158.3	160.5	164.0
157.5°	180.3	175.0	172.8	170.7	167.2	164.4	162.2	162.2	162.2	164.4	167.2
160°	181.0	176.7	174.8	172.8	170.0	167.5	166.1	166.1	166.1	167.5	170.0
162.5°	181.7	177.8	176.4	175.0	172.5	170.4	169.3	169.7	169.3	170.4	172.5
165°	181.7	178.5	177.4	176.4	174.6	172.8	172.1	172.1	172.1	172.8	174.6
167.5°	181.7	179.2	178.3	177.4	176.4	175.0	174.6	175.0	174.6	175.0	176.4
170°	181.3	179.6	179.0	178.5	177.8	176.7	176.4	176.7	176.4	176.7	177.8
172.5°	181.0	179.9	179.6	179.2	178.8	178.1	178.1	178.5	178.1	178.1	178.8
175°	180.6	179.9	179.9	179.9	179.6	179.2	179.2	179.6	179.2	179.2	179.6
177.5°	180.3	179.9	179.9	179.9	179.9	179.6	179.9	180.3	179.9	179.6	179.9
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3
2.5°	1624.7	1619.2	1621.9	1608.3	1596.0	1578.2	1563.2	1560.4	1557.7	1565.9	1560.4
5°	1578.2	1571.4	1564.5	1548.1	1523.5	1508.5	1486.7	1485.3	1477.1	1464.8	1467.5
7.5°	1527.6	1523.5	1514.0	1488.0	1466.2	1440.2	1422.4	1407.4	1400.6	1389.6	1385.5
10°	1486.7	1471.6	1463.4	1434.7	1408.8	1381.4	1358.2	1347.3	1335.0	1325.4	1318.6
12.5°	1430.6	1426.5	1403.3	1380.1	1358.2	1326.8	1309.0	1277.6	1261.2	1269.4	1266.7
15°	1393.7	1374.6	1369.1	1336.3	1299.5	1279.0	1246.2	1225.7	1218.8	1206.5	1191.5
17.5°	1344.5	1332.2	1313.1	1283.1	1240.7	1212.0	1188.8	1169.6	1161.4	1145.1	1132.8
20°	1298.1	1277.6	1262.6	1235.2	1194.2	1157.3	1128.7	1116.4	1095.9	1082.2	1075.4
22.5°	1255.7	1240.7	1218.8	1177.8	1142.3	1106.8	1072.6	1054.9	1035.7	1027.5	1016.6
25°	1203.8	1179.2	1164.2	1119.1	1080.8	1052.1	1020.7	997.5	986.5	972.9	970.1
27.5°	1153.2	1130.0	1112.3	1072.6	1026.2	989.3	970.1	953.8	934.6	934.6	927.8
30°	1102.7	1086.3	1059.0	1020.7	977.0	941.5	919.6	904.6	897.7	892.3	890.9
32.5°	1052.1	1030.3	1013.9	962.0	929.2	896.4	880.0	867.7	859.5	858.1	859.5
35°	1000.2	975.6	959.2	912.8	880.0	849.9	843.1	832.1	828.0	826.7	833.5
37.5°	945.6	926.4	905.9	867.7	830.8	813.0	799.3	795.2	793.9	802.1	804.8
40°	895.0	878.6	859.5	818.5	791.2	772.0	765.2	761.1	766.6	774.8	778.9
42.5°	847.2	823.9	808.9	772.0	747.4	736.5	728.3	728.3	733.8	743.3	750.2
45°	796.6	778.9	763.8	731.0	709.2	696.9	695.5	696.9	703.7	710.5	718.7
47.5°	747.4	729.7	713.3	685.9	666.8	660.0	658.6	660.0	670.9	680.5	690.0
50°	702.3	683.2	668.2	642.2	627.2	619.0	620.3	627.2	635.4	649.0	661.3
52.5°	649.0	635.4	621.7	598.5	584.8	579.4	583.5	588.9	604.0	613.5	628.5
55°	597.1	584.8	573.9	556.1	545.2	541.1	543.8	552.0	564.3	580.7	598.5
57.5°	549.3	535.6	524.7	512.4	500.1	501.5	502.8	513.8	528.8	543.8	564.3
60°	496.0	487.8	478.2	463.2	457.7	457.7	461.8	474.1	487.8	512.4	530.2
62.5°	448.2	437.3	430.4	420.9	412.7	414.0	423.6	434.5	450.9	471.4	494.6
65°	399.0	386.7	381.2	373.0	370.3	371.7	378.5	394.9	412.7	430.4	452.3
67.5°	344.3	340.2	334.8	326.6	329.3	330.7	337.5	351.2	370.3	388.1	412.7
70°	297.9	289.7	288.3	281.5	281.5	285.6	299.2	308.8	326.6	345.7	371.7
72.5°	248.7	241.9	241.9	236.4	240.5	244.6	251.4	265.1	281.5	300.6	322.5
75°	198.1	195.4	198.1	195.4	195.4	202.2	210.4	221.4	239.1	259.6	277.4
77.5°	153.0	153.0	151.7	155.8	155.8	159.9	170.8	181.7	195.4	211.8	230.9
80°	112.0	112.0	112.0	116.1	120.2	120.2	127.1	140.7	153.0	164.0	181.7
82.5°	76.5	76.5	76.5	79.3	84.7	84.7	92.9	101.1	114.8	124.3	132.5
85°	46.5	46.5	45.1	47.8	49.2	53.3	60.1	65.6	72.4	80.6	88.8
87.5°	20.5	20.5	21.9	23.2	24.6	27.3	30.1	32.8	39.6	42.4	46.5
90°	2.8	2.8	2.8	4.9	4.9	5.7	6.4	6.0	6.4	6.7	7.1
92.5°	22.6	27.2	31.8	53.7	88.0	121.2	138.6	115.2	85.2	63.6	50.2
95°	29.3	36.8	44.2	74.9	132.9	217.4	288.1	296.2	261.9	207.1	159.8
97.5°	34.3	40.6	47.0	71.4	121.2	208.2	308.2	371.5	377.1	349.9	311.0
100°	40.3	46.0	51.6	72.5	112.4	184.5	284.2	374.7	426.3	433.3	416.0
102.5°	47.0	52.3	57.6	76.0	109.9	168.6	254.1	348.1	423.8	465.8	476.4
105°	54.8	59.9	65.0	82.0	111.3	160.8	231.9	314.9	395.9	457.0	492.0
107.5°	62.6	67.7	72.8	88.4	115.6	158.7	217.4	287.7	361.6	427.7	476.4
110°	70.7	75.4	80.2	95.8	120.5	159.4	210.7	268.3	331.2	392.3	443.6

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	78.5	83.2	88.0	102.9	125.8	161.5	207.5	257.3	308.9	361.2	408.9
115°	86.6	91.4	96.1	110.3	131.5	164.4	206.8	251.3	295.5	339.0	380.3
117.5°	94.0	99.0	103.9	117.3	137.1	167.2	206.4	248.1	287.7	324.5	358.0
120°	101.4	106.4	111.3	124.8	143.1	170.4	206.4	245.6	282.8	315.6	343.9
122.5°	108.9	113.6	118.4	131.8	148.8	173.5	206.1	242.8	278.5	310.0	335.1
125°	115.6	120.6	125.5	138.2	154.5	176.7	205.7	239.6	273.6	304.0	328.4
127.5°	121.9	126.8	131.8	144.2	159.4	179.2	205.0	235.4	267.9	297.2	321.6
130°	127.9	133.0	138.2	150.2	164.0	182.0	204.6	231.5	260.8	288.8	312.8
132.5°	133.6	138.4	143.1	155.2	168.6	184.5	204.3	228.0	253.4	279.2	302.6
135°	138.9	143.5	148.1	159.8	172.5	187.0	203.9	224.4	246.7	269.7	291.2
137.5°	143.5	147.9	152.3	163.3	175.3	188.4	203.9	221.3	240.3	260.5	279.2
140°	147.7	152.0	156.2	166.8	178.1	190.2	203.6	218.8	235.0	251.7	267.6
142.5°	151.6	155.7	159.8	170.0	180.3	191.6	203.6	216.7	230.1	244.2	257.3
145°	155.2	159.0	162.9	172.1	181.7	191.9	202.9	214.2	225.5	237.5	248.1
147.5°	158.7	162.2	165.8	174.6	183.1	192.3	201.8	212.1	221.6	231.5	240.3
150°	161.9	165.2	168.6	176.4	184.1	192.3	200.8	209.6	218.1	226.2	233.3
152.5°	165.1	168.1	171.1	177.8	184.9	191.6	199.0	206.8	214.2	220.9	227.3
155°	167.9	170.6	173.2	179.2	185.2	190.9	197.2	203.9	210.3	216.0	221.3
157.5°	170.7	172.8	175.0	180.3	185.2	190.2	195.5	201.1	206.1	211.0	215.6
160°	172.8	174.8	176.7	181.0	185.2	189.1	193.3	197.9	202.2	206.1	209.9
162.5°	175.0	176.4	177.8	181.7	185.2	188.0	191.2	195.1	198.3	201.5	204.3
165°	176.4	177.4	178.5	181.7	184.5	186.6	189.1	191.9	194.7	196.9	199.3
167.5°	177.4	178.3	179.2	181.7	183.8	185.2	187.0	189.1	191.2	193.0	195.1
170°	178.5	179.0	179.6	181.3	183.1	183.8	184.9	186.3	188.0	189.1	190.5
172.5°	179.2	179.6	179.9	181.0	182.4	182.4	182.7	183.8	185.2	185.9	186.6
175°	179.9	179.9	179.9	180.6	181.7	181.3	181.3	182.0	182.7	183.1	183.8
177.5°	179.9	179.9	179.9	180.3	181.0	180.3	180.3	180.6	181.0	181.3	181.3
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3
2.5°	1556.3	1555.0	1548.1	1550.9	1542.7	1545.4	1549.5	1550.9	1556.3	1552.2	1550.9
5°	1460.7	1458.0	1453.9	1449.8	1448.4	1453.9	1444.3	1447.0	1449.8	1453.9	1459.3
7.5°	1382.8	1381.4	1377.3	1370.5	1367.8	1365.0	1366.4	1376.0	1374.6	1373.2	1382.8
10°	1311.8	1313.1	1304.9	1303.6	1295.4	1294.0	1295.4	1298.1	1302.2	1307.7	1309.0
12.5°	1238.0	1255.7	1240.7	1235.2	1222.9	1229.8	1232.5	1220.2	1227.0	1231.1	1251.6
15°	1191.5	1183.3	1173.7	1173.7	1168.3	1165.5	1158.7	1168.3	1173.7	1181.9	1179.2
17.5°	1127.3	1113.6	1108.2	1102.7	1104.1	1109.5	1094.5	1116.4	1116.4	1120.5	1113.6
20°	1071.3	1060.3	1053.5	1050.8	1046.7	1043.9	1042.6	1048.0	1056.2	1059.0	1065.8
22.5°	1012.5	1012.5	1001.6	997.5	994.7	990.6	997.5	993.4	998.8	1004.3	1015.2
25°	963.3	963.3	959.2	953.8	949.7	946.9	951.0	949.7	953.8	960.6	963.3
27.5°	923.7	919.6	918.2	916.9	915.5	916.9	915.5	919.6	923.7	925.1	922.3
30°	889.5	885.4	886.8	886.8	888.2	886.8	885.4	889.5	890.9	888.2	889.5
32.5°	858.1	858.1	860.8	862.2	862.2	863.6	864.9	862.2	863.6	859.5	860.8
35°	832.1	834.9	837.6	839.0	840.3	839.0	841.7	840.3	837.6	834.9	833.5
37.5°	806.2	808.9	814.4	815.7	819.8	821.2	818.5	818.5	817.1	811.6	808.9
40°	778.9	781.6	788.4	792.5	795.2	799.3	796.6	796.6	791.2	785.7	781.6
42.5°	752.9	758.4	765.2	769.3	774.8	774.8	774.8	772.0	765.2	759.7	755.6
45°	726.9	728.3	737.9	744.7	750.2	750.2	750.2	746.1	742.0	731.0	725.6
47.5°	698.2	702.3	713.3	720.1	725.6	726.9	726.9	722.8	714.6	705.1	698.2
50°	666.8	673.6	685.9	695.5	702.3	705.1	701.0	698.2	688.7	677.7	669.5
52.5°	636.7	644.9	660.0	668.2	677.7	679.1	677.7	673.6	662.7	647.7	640.8
55°	606.7	613.5	629.9	643.6	651.8	654.5	651.8	644.9	631.3	616.3	609.4
57.5°	573.9	583.5	601.2	614.9	624.4	625.8	623.1	616.3	605.3	586.2	576.6
60°	539.7	552.0	569.8	583.5	595.8	597.1	594.4	584.8	571.2	552.0	543.8
62.5°	505.6	515.1	535.6	550.7	560.2	567.1	561.6	552.0	538.4	519.2	506.9
65°	465.9	479.6	497.4	511.0	522.0	523.3	520.6	512.4	497.4	476.9	467.3
67.5°	427.7	437.3	455.0	472.8	476.9	481.0	476.9	468.7	456.4	438.6	425.0
70°	381.2	389.4	411.3	423.6	429.1	433.2	430.4	422.2	411.3	394.9	384.0
72.5°	334.8	341.6	362.1	371.7	382.6	381.2	379.9	374.4	359.4	348.4	341.6
75°	285.6	293.8	307.4	319.7	323.8	323.8	323.8	319.7	310.2	292.4	285.6
77.5°	240.5	244.6	255.5	262.4	266.4	267.8	266.4	259.6	254.2	241.9	237.8
80°	184.5	195.4	203.6	205.0	210.4	210.4	210.4	207.7	202.2	189.9	188.6
82.5°	139.4	142.1	150.3	154.4	157.1	155.8	155.8	150.3	148.9	142.1	139.4
85°	94.3	98.4	97.0	102.5	103.8	101.1	101.1	103.8	97.0	98.4	94.3
87.5°	51.9	51.9	54.7	53.3	58.8	58.8	56.0	57.4	54.7	53.3	51.9
90°	7.1	7.1	7.4	7.8	7.4	7.4	7.4	7.8	7.4	7.1	7.1
92.5°	45.8	41.4	36.1	33.6	32.2	32.2	32.2	33.6	36.1	41.4	45.8
95°	142.6	125.5	108.2	97.2	90.8	86.2	90.8	97.2	108.2	125.5	142.6
97.5°	291.2	271.4	247.4	226.2	215.6	207.1	215.6	226.2	247.4	271.4	291.2
100°	403.0	389.9	359.1	337.5	326.9	324.1	326.9	337.5	359.1	389.9	403.0
102.5°	472.9	469.4	453.5	439.3	428.0	425.9	428.0	439.3	453.5	469.4	472.9
105°	499.2	506.5	507.2	504.4	499.4	497.3	499.4	504.4	507.2	506.5	499.2
107.5°	491.2	506.1	521.7	528.1	530.9	531.2	530.9	528.1	521.7	506.1	491.2
110°	463.0	482.5	507.6	522.4	528.8	531.9	528.8	522.4	507.6	482.5	463.0

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	428.4	447.8	477.2	495.9	505.4	511.1	505.4	495.9	477.2	447.8	428.4
115°	397.2	414.2	442.2	463.4	474.7	477.5	474.7	463.4	442.2	414.2	397.2
117.5°	372.8	387.7	412.5	430.9	442.9	444.6	442.9	430.9	412.5	387.7	372.8
120°	356.4	369.0	389.1	404.7	413.9	417.8	413.9	404.7	389.1	369.0	356.4
122.5°	345.7	356.3	372.5	385.3	392.7	396.6	392.7	385.3	372.5	356.3	345.7
125°	338.1	347.8	361.9	372.2	378.9	381.0	378.9	372.2	361.9	347.8	338.1
127.5°	330.8	340.0	354.2	363.3	369.0	371.1	369.0	363.3	354.2	340.0	330.8
130°	322.2	331.5	346.0	354.9	360.5	362.6	360.5	354.9	346.0	331.5	322.2
132.5°	312.0	321.3	335.4	345.7	351.0	353.1	351.0	345.7	335.4	321.3	312.0
135°	300.0	308.9	323.1	332.9	338.6	340.7	338.6	332.9	323.1	308.9	300.0
137.5°	287.4	295.5	308.9	319.2	323.8	326.2	323.8	319.2	308.9	295.5	287.4
140°	275.0	282.4	294.8	302.6	307.5	310.3	307.5	302.6	294.8	282.4	275.0
142.5°	263.5	269.7	280.3	287.4	291.6	293.4	291.6	287.4	280.3	269.7	263.5
145°	253.0	258.0	266.9	272.9	276.4	278.2	276.4	272.9	266.9	258.0	253.0
147.5°	244.4	248.5	255.2	260.5	263.3	264.0	263.3	260.5	255.2	248.5	244.4
150°	236.4	239.6	245.3	249.9	252.0	252.4	252.0	249.9	245.3	239.6	236.4
152.5°	229.8	232.2	236.8	240.3	241.4	241.8	241.4	240.3	236.8	232.2	229.8
155°	223.4	225.5	229.0	231.9	232.9	232.9	232.9	231.9	229.0	225.5	223.4
157.5°	217.4	219.1	222.0	224.1	224.8	224.8	224.8	224.1	222.0	219.1	217.4
160°	211.4	212.8	214.9	217.0	217.4	217.4	217.4	217.0	214.9	212.8	211.4
162.5°	205.6	206.8	208.2	210.3	210.7	210.3	210.7	210.3	208.2	206.8	205.6
165°	200.2	201.1	202.5	203.9	203.6	203.2	203.6	203.9	202.5	201.1	200.2
167.5°	195.6	196.2	196.9	197.9	197.9	197.6	197.9	197.9	196.9	196.2	195.6
170°	191.0	191.6	192.3	192.6	192.3	192.3	192.3	192.6	192.3	191.6	191.0
172.5°	187.0	187.3	187.7	188.0	187.7	187.0	187.7	188.0	187.7	187.3	187.0
175°	183.8	183.8	183.8	184.5	183.8	183.1	183.8	184.5	183.8	183.8	183.8
177.5°	181.5	181.7	181.3	181.7	181.0	180.3	181.0	181.7	181.3	181.7	181.5
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3	1649.3
2.5°	1550.9	1559.1	1550.9	1556.3	1559.1	1565.9	1568.6	1580.9	1585.0	1594.6	1594.6
5°	1458.0	1462.1	1463.4	1468.9	1474.4	1488.0	1497.6	1515.3	1535.8	1538.6	1550.9
7.5°	1382.8	1389.6	1400.6	1396.5	1406.0	1426.5	1438.8	1460.7	1481.2	1492.1	1507.1
10°	1315.9	1324.0	1328.1	1332.2	1350.0	1367.8	1386.9	1401.9	1429.3	1445.7	1458.0
12.5°	1261.2	1254.4	1262.6	1277.6	1298.1	1309.0	1335.0	1358.2	1378.7	1396.5	1407.4
15°	1190.1	1195.6	1203.8	1229.8	1235.2	1262.6	1272.1	1298.1	1336.3	1352.7	1366.4
17.5°	1121.8	1139.6	1156.0	1165.5	1181.9	1203.8	1231.1	1259.8	1284.4	1303.6	1320.0
20°	1067.2	1084.9	1094.5	1101.3	1117.7	1147.8	1173.7	1209.3	1240.7	1255.7	1277.6
22.5°	1023.4	1023.4	1037.1	1057.6	1067.2	1095.9	1117.7	1156.0	1190.1	1209.3	1229.8
25°	968.8	977.0	987.9	1005.7	1019.3	1042.6	1074.0	1106.8	1143.7	1160.1	1186.0
27.5°	923.7	933.3	948.3	952.4	966.1	986.5	1019.3	1054.9	1093.1	1110.9	1132.8
30°	889.5	895.0	900.5	908.7	921.0	938.7	966.1	997.5	1043.9	1057.6	1084.9
32.5°	859.5	862.2	864.9	871.8	878.6	896.4	918.2	952.4	990.6	1011.1	1035.7
35°	832.1	829.4	830.8	834.9	841.7	848.5	871.8	900.5	936.0	960.6	979.7
37.5°	806.2	800.7	799.3	799.3	802.1	810.3	828.0	852.6	890.9	911.4	930.5
40°	777.5	772.0	769.3	767.9	766.6	772.0	785.7	810.3	840.3	859.5	881.3
42.5°	750.2	744.7	737.9	736.5	733.8	736.5	746.1	769.3	795.2	814.4	832.1
45°	722.8	713.3	705.1	699.6	701.0	696.9	703.7	721.5	751.5	763.8	781.6
47.5°	692.8	681.8	670.9	665.4	660.0	662.7	665.4	680.5	706.4	718.7	736.5
50°	664.1	649.0	636.7	629.9	625.8	623.1	625.8	640.8	660.0	670.9	685.9
52.5°	631.3	616.3	604.0	593.0	587.6	583.5	584.8	598.5	616.3	627.2	642.2
55°	601.2	582.1	565.7	552.0	547.9	546.6	545.2	554.8	569.8	580.7	593.0
57.5°	567.1	547.9	530.2	513.8	505.6	504.2	504.2	506.9	526.1	534.3	541.1
60°	532.9	512.4	493.3	478.2	465.9	461.8	460.5	465.9	475.5	483.7	493.3
62.5°	494.6	474.1	450.9	437.3	425.0	414.0	418.1	419.5	433.2	437.3	445.4
65°	457.7	434.5	415.4	393.5	379.9	373.0	370.3	373.0	384.0	385.3	390.8
67.5°	415.4	393.5	370.3	355.3	343.0	330.7	327.9	327.9	333.4	337.5	344.3
70°	374.4	352.5	326.6	310.2	297.9	286.9	282.8	281.5	285.6	288.3	295.1
72.5°	326.6	304.7	285.6	267.8	252.8	244.6	240.5	237.8	241.9	244.6	246.0
75°	276.0	258.3	239.1	221.4	211.8	203.6	198.1	194.0	196.8	196.8	196.8
77.5°	228.2	210.4	195.4	183.1	170.8	161.2	157.1	153.0	154.4	154.4	157.1
80°	177.6	165.3	153.0	142.1	131.2	123.0	120.2	116.1	113.4	112.0	112.0
82.5°	131.2	121.6	110.7	101.1	95.6	87.5	84.7	79.3	79.3	77.9	77.9
85°	87.5	82.0	71.1	64.2	60.1	56.0	53.3	50.6	46.5	46.5	45.1
87.5°	46.5	43.7	41.0	32.8	32.8	28.7	27.3	26.0	21.9	23.2	23.2
90°	7.1	6.7	6.4	6.0	6.4	5.7	4.9	4.9	2.8	2.8	2.8
92.5°	50.2	63.6	85.2	115.2	138.6	121.2	88.0	53.7	31.8	27.2	22.6
95°	159.8	207.1	261.9	296.2	288.1	217.4	132.9	74.9	44.2	36.8	29.3
97.5°	311.0	349.9	377.1	371.5	308.2	208.2	121.2	71.4	47.0	40.6	34.3
100°	416.0	433.3	426.3	374.7	284.2	184.5	112.4	72.5	51.6	46.0	40.3
102.5°	476.4	465.8	423.8	348.1	254.1	168.6	109.9	76.0	57.6	52.3	47.0
105°	492.0	457.0	395.9	314.9	231.9	160.8	111.3	82.0	65.0	59.9	54.8
107.5°	476.4	427.7	361.6	287.7	217.4	158.7	115.6	88.4	72.8	67.7	62.6
110°	443.6	392.3	331.2	268.3	210.7	159.4	120.5	95.8	80.2	75.4	70.7

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	408.9	361.2	308.9	257.3	207.5	161.5	125.8	102.9	88.0	83.2	78.5
115°	380.3	339.0	295.5	251.3	206.8	164.4	131.5	110.3	96.1	91.4	86.6
117.5°	358.0	324.5	287.7	248.1	206.4	167.2	137.1	117.3	103.9	99.0	94.0
120°	343.9	315.6	282.8	245.6	206.4	170.4	143.1	124.8	111.3	106.4	101.4
122.5°	335.1	310.0	278.5	242.8	206.1	173.5	148.8	131.8	118.4	113.6	108.9
125°	328.4	304.0	273.6	239.6	205.7	176.7	154.5	138.2	125.5	120.6	115.6
127.5°	321.6	297.2	267.9	235.4	205.0	179.2	159.4	144.2	131.8	126.8	121.9
130°	312.8	288.8	260.8	231.5	204.6	182.0	164.0	150.2	138.2	133.0	127.9
132.5°	302.6	279.2	253.4	228.0	204.3	184.5	168.6	155.2	143.1	138.4	133.6
135°	291.2	269.7	246.7	224.4	203.9	187.0	172.5	159.8	148.1	143.5	138.9
137.5°	279.2	260.5	240.3	221.3	203.9	188.4	175.3	163.3	152.3	147.9	143.5
140°	267.6	251.7	235.0	218.8	203.6	190.2	178.1	166.8	156.2	152.0	147.7
142.5°	257.3	244.2	230.1	216.7	203.6	191.6	180.3	170.0	159.8	155.7	151.6
145°	248.1	237.5	225.5	214.2	202.9	191.9	181.7	172.1	162.9	159.0	155.2
147.5°	240.3	231.5	221.6	212.1	201.8	192.3	183.1	174.6	165.8	162.2	158.7
150°	233.3	226.2	218.1	209.6	200.8	192.3	184.1	176.4	168.6	165.2	161.9
152.5°	227.3	220.9	214.2	206.8	199.0	191.6	184.9	177.8	171.1	168.1	165.1
155°	221.3	216.0	210.3	203.9	197.2	190.9	185.2	179.2	173.2	170.6	167.9
157.5°	215.6	211.0	206.1	201.1	195.5	190.2	185.2	180.3	175.0	172.8	170.7
160°	209.9	206.1	202.2	197.9	193.3	189.1	185.2	181.0	176.7	174.8	172.8
162.5°	204.3	201.5	198.3	195.1	191.2	188.0	185.2	181.7	177.8	176.4	175.0
165°	199.3	196.9	194.7	191.9	189.1	186.6	184.5	181.7	178.5	177.4	176.4
167.5°	195.1	193.0	191.2	189.1	187.0	185.2	183.8	181.7	179.2	178.3	177.4
170°	190.5	189.1	188.0	186.3	184.9	183.8	183.1	181.3	179.6	179.0	178.5
172.5°	186.6	185.9	185.2	183.8	182.7	182.4	182.4	181.0	179.9	179.6	179.2
175°	183.8	183.1	182.7	182.0	181.3	181.3	181.7	180.6	179.9	179.9	179.9
177.5°	181.3	181.3	181.0	180.6	180.3	180.3	181.0	180.3	179.9	179.9	179.9
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1649.3	1649.3	1649.3	1649.3
2.5°	1604.2	1617.8	1630.1	1649.3
5°	1568.6	1587.8	1613.7	1642.4
7.5°	1527.6	1557.7	1591.9	1631.5
10°	1489.4	1523.5	1567.3	1615.1
12.5°	1449.8	1490.8	1538.6	1590.5
15°	1404.7	1445.7	1498.9	1568.6
17.5°	1363.7	1412.9	1470.3	1544.0
20°	1315.9	1362.3	1425.2	1509.9
22.5°	1273.5	1326.8	1396.5	1470.3
25°	1227.0	1273.5	1343.2	1432.0
27.5°	1180.6	1238.0	1304.9	1391.0
30°	1135.5	1183.3	1255.7	1345.9
32.5°	1086.3	1143.7	1210.6	1295.4
35°	1033.0	1087.7	1150.5	1242.1
37.5°	985.2	1038.5	1102.7	1183.3
40°	931.9	987.9	1046.7	1127.3
42.5°	880.0	930.5	989.3	1063.1
45°	829.4	873.1	926.4	990.6
47.5°	777.5	814.4	863.6	921.0
50°	721.5	761.1	798.0	845.8
52.5°	669.5	703.7	733.8	773.4
55°	619.0	642.2	666.8	696.9
57.5°	565.7	583.5	601.2	632.6
60°	512.4	528.8	538.4	558.9
62.5°	460.5	467.3	479.6	491.9
65°	403.1	412.7	419.5	434.5
67.5°	351.2	355.3	362.1	371.7
70°	296.5	306.1	308.8	315.6
72.5°	250.1	254.2	256.9	258.3
75°	198.1	202.2	205.0	213.2
77.5°	155.8	154.4	159.9	161.2
80°	114.8	110.7	112.0	117.5
82.5°	75.2	76.5	75.2	75.2
85°	46.5	45.1	42.4	43.7
87.5°	20.5	20.5	19.1	19.1
90°	2.5	2.1	1.1	0.4
92.5°	16.3	11.0	7.1	4.9
95°	20.9	16.3	12.7	11.7
97.5°	26.9	22.6	19.4	19.4
100°	33.6	29.3	26.9	26.9
102.5°	40.6	36.8	34.6	33.9
105°	48.4	44.2	42.4	41.4
107.5°	56.6	52.0	50.2	49.5
110°	64.3	60.1	58.3	57.6

TEST NUMBER: P1000670

CATALOG NUMBER: SA4XXDIP-B1020D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	72.1	68.2	66.1	65.4
115°	79.9	76.3	73.9	72.8
117.5°	87.7	83.8	81.6	80.6
120°	95.4	91.5	89.1	88.4
122.5°	102.1	98.6	96.1	95.4
125°	108.9	105.0	102.9	101.4
127.5°	114.9	110.6	108.2	107.1
130°	121.2	115.9	113.1	111.7
132.5°	126.2	121.2	117.3	116.3
135°	131.5	125.5	121.9	120.5
137.5°	135.7	130.1	126.2	124.8
140°	140.3	134.3	130.4	129.4
142.5°	144.6	138.9	135.4	134.3
145°	148.4	143.5	140.0	138.9
147.5°	153.0	147.7	144.6	144.2
150°	156.6	152.3	149.5	149.2
152.5°	160.5	156.6	153.7	153.7
155°	164.0	160.5	158.3	158.0
157.5°	167.2	164.4	162.2	162.2
160°	170.0	167.5	166.1	166.1
162.5°	172.5	170.4	169.3	169.7
165°	174.6	172.8	172.1	172.1
167.5°	176.4	175.0	174.6	175.0
170°	177.8	176.7	176.4	176.7
172.5°	178.8	178.1	178.1	178.5
175°	179.6	179.2	179.2	179.6
177.5°	179.9	179.6	179.9	180.3
180°	179.9	179.9	179.9	179.9

(END OF REPORT)